#### **Product Summary**

### **PWM Generator**

### **1** Description

The iW338 is a generic PWM signal generator IC to convert a 0-0.6V analog voltage to an inverted 0%-100% PWM duty cycle. The PWM frequency range is set by an external capacitor and is programmable from 100Hz to 50kHz. The output of the iW338 is a 5V PWM driver capable of driving an external optocoupler for isolated applications or a MOSFET for non-isolated applications.

### 2 Features

- 8V to 60V DC input voltage •
- 1% PWM duty cycle tolerance
- Programmable PWM frequency range: 100Hz to • 50kHz

### **3** Applications

- Generic PWM duty cycle generator •
- Signal feedback across isolation barrier •

- Shutdown pin to minimize standby power
- SOIC-8 package

8-60V iW338 V<sub>cc</sub> V Ŧ **PWM** Output DRV DIM O 0-0.6V FLT SD GND CF

Figure 3.1 : iW338 Typical Application Circuit

**Rev. 1.1** 






## iW338

### **PWM Generator**



# **4** Pinout Description



#### Figure 4.1 : 8-Lead SOIC Package

Pin Number	Pin Name	Туре	Pin Description
1	V <sub>IN</sub>	Analog Input	Power supply up to 60V.
2	GND	Ground	Ground.
3	V <sub>cc</sub>	Power	Power supply for control logic.
4	DRV	Output	PWM driver. The DRV output changes duty cycle linearly and inversely proportional to the input of the DIM pin. 100% duty cycle output on the DRV pin corresponds to 0V on the DIM pin and 0% duty cycle corresponds to >0.6V on the DIM pin.
5	DIM	Analog Input	Dimming interface connection.
6	FLT	Analog Input	Dimming signal filter capacitor connection.
7	CF	Analog Input	Sets the PWM output frequency: 100Hz to 50kHz.
8	SD	Analog Input	Shuts down the IC if voltage is over 2V.

### **PWM Generator**

### **5 Absolute Maximum Ratings**


Absolute maximum ratings are the parameter values or ranges which can cause permanent damage if exceeded.

Parameter	Symbol	Value	Units
V <sub>IN</sub> to GND	V <sub>cc</sub>	-0.3 to 65	V
DIM to GND		-0.3 to 5	V
DRV, FLT, CF, SD to GND		-0.3 to 5	V
ESD rating per JEDEC JESD22-A114		±2000	V
Storage temperature range		-65 to +150	°C
Maximum junction temperature		150	°C



### **PWM Generator**

#### **6** Physical Dimensions



#### Figure 6.1 : Physical Dimensions of 8-Pin SOIC Package

#### 7 Ordering Information

Part Number	Options	Package	Description
iW338-10		SOIC-8	Tape & Reel <sup>1</sup>

Note 1: Tape and reel packing quantity is 2,500/reel. Minimum packing quantity is 2,500.

Product	Summary	
---------	---------	--

#### **PWM Generator**

#### **IMPORTANT NOTICE AND DISCLAIMER**

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

© 2022 Renesas Electronics Corporation. All rights reserved.

#### **RoHS Compliance**

Dialog Semiconductor's suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on request.

(Rev.1.0 Mar 2020)

#### **Corporate Headquarters**

TOYOSU FORESIA, 3-2-24 Toyosu Koto-ku, Tokyo 135-0061, Japan www.renesas.com

### **Contact Information**

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit: www.renesas.com/contact/

#### **Trademarks**

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Product	Summary
---------	---------