

RENESAS TECHNICAL UPDATE

1753, Shimonumabe, Nakahara-ku, Kawasaki-shi, Kanagawa 211-8668 Japan
Renesas Electronics Corporation

Product Category	MPU/MCU		Document No.	TN-RL*-A013A/E	Rev.	1.00
Title	RL78/I1A Direction of use		Information Category	Technical Notification		
Applicable Product	RL78/I1A Group R5F107xxG, R5F107xxM Please see Appendix1.	Lot No.	Reference Document	RL78/I1A User's Manual: Hardware Rev. 2.10 R01UH0169EJ0210 (Jul. 2013)		
		All lot				

"Operating Precaution for Data Flash read access" directions of use on these products have been added to "RL78/I1A".

1. **Restriction:**

Applicable Usage:

The usage which meets to all of (1), (2), and (3) is applicable to the restriction.

- (1) Using both DMA and Data Flash.
- (2) DMA is operating when Data Flash ^{Note1} read occurs.
- (3) Data Flash is read using flash-related libraries Renesas Electronics is offering, which are listed below. Otherwise instead of using those libraries, the combination of CPU Related instructions ^{Note2} are used for reading related memory ^{Note3} and Data Flash.
 - The EEL(EEPROM emulation library) ^{Note1} Pack01 V1.12 or earlier version.
 - The FDL(Data Flash library) Type01 V1.11 or earlier version.
 - The FDL Type02 V1.00 or earlier version.
 - The FDL Type04 V1.04 or earlier version.

Note1. When EEL is used, commands other than READ command are also related: they also make read access to the Data Flash.

Note2. See Appendix2 about the combination of the related instructions1 and 2.

Note3. Related memory is RAM(Include general purpose register area),SFR,2nd SFR(No wait),ES,CS,PSW,SP

Detail of Restriction:

In the case that DMA transfer is operated and it is immediately followed by read access to the target memory (Related instructions 1) which access is also immediately followed in sequence, by read access to Data Flash (Related instructions 2), because of the conflict on the internal bus between read access to the target memory and to the Data Flash, the read out result from the target memory may be wrongly changed.

Example for an instruction sequence causing this issue:

```

DMA transfer trigger
DMA transfer
MOVW      HL,!addr16      ; read data from RAM (Related instruction 1)
MOV       A,[DE]          ; read data from Data Flash (Related instructions 2)

```

When DMA transfer occurs as mentioned above timing, a wrong data is loaded into HL register.

2. Workaround

If you have any possibility that read access to the Data Flash and the DMA transfer could operate in the same time, please apply the following procedures according to the way to read out the Data Flash.

Case 1:

Data Flash Read access via the 'Data Flash Access Library' (FDL) and/or EEPROM Emulation Library (EEL). Both libraries are developed under the responsibility of Renesas.

Workaround for Case 1:

There are currently one type of EEL supported and three type of FDL supported and all of them will be updated to cover the aforementioned workaround.

Library version (Not installer version)

EEL (Pack01) version V1.13 ^{Note} or later

FDL (Type01) version V1.12 ^{Note} or later

FDL (Type02) version V1.01 ^{Note} or later

FDL (Type04) version V1.05 ^{Note} or later

Case 2:

Data Flash Read access directly executed in the user software without library.

Workaround for Case 2:

Please apply either of the following procedures.

(A) Holding DMA or forcing termination DMA

In case, the user software has to perform a direct Data Flash Read access without using the FDL read command, any possible DMA transfer must be stopped before the Data Flash read access is executed. To stop any DMA transfer, please follow the procedure given in the User Manual.

Furthermore, please make sure to wait at least 3 clocks(f_{CLK}) after setting DWAITn bit to "1" before the Data Flash read instruction is executed. Restart any DMA transfer (by clearing DWAITn bit to "0") after the Data Flash read access have been finished.

(B) Reading Data Flash by using library

When access Data Flash, please use latest Data Flash library of case 1.

(C) Inserting a NOP instruction

Such kind of conflict can be avoided by inserting a NOP instruction immediately prior to any Data Flash Read access.

Example to avoid this issue: operand

```
MOVW    HL, !addr16    ; Read data from RAM
NOP                                           ; Insert a NOP prior to the DF read access
MOV     A,[DE]         ; Read data from Data Flash
```

In case the application software will use the DMA feature, Renesas strongly recommend not to perform a direct Data Flash Read access in the user software, because in case of a high level language (e.g. C-Language) it cannot be avoided that the C-compiler may generate a code sequence as described before. Therefore, Renesas strongly recommend to perform the Data Flash Read access ONLY via the corresponding FDL read command.

Note. The modified version of EEL(EEPROM Emulation library) and FDL(Data Flash library) will be released in sequence after July 2013.

Remark. f_{CLK} : CPU/peripheral hardware clock frequency

3. Modification schedule

This matter is added to “Procedure for accessing data flash memory” of CHAPTER 28 FLASH MEMORY in the user’s manual by the next revision.

4. List of usage restrictions

No.	Description	Products
		RL78/I1A Group R5F107xxD, R5F107xxM (Please see Appendix1.)
1	Operating Precaution for Data Flash read access	X

Remark The meaning of each symbol is as follows:

X: Restriction applicable

-: Restriction not applicable

5. Revision history

Revision history of RL78/I1A directions of use

Document Number	Issued Date	Description
TN-RL*-A013A/E	Aug. 19, 2013	First edition issued List of usage restriction: No.1 (This document)

[Target products' name list]

RL78/I1A with Data Flash (R5F107)

20-pin LSSOP 4.4x6.5mm	R5F1076CGSP R5F1076CMSP
30-pin LSSOP 7.62mm(300)	R5F107ACGSP, R5F107AEGSP R5F107ACMSP, R5F107AEMSP
38-pin SSOP 6.1x12.3mm	R5F107DEGSP R5F107DEMSP

[Related instructions list]

In case that the Data Flash is read out by "Related instructions 2" immediately after the target memory is read out by "Related instructions 1", this is within the restriction; however, particular combinations of related instructions shown in Appendix2-2 are excepted.

Related instructions 1: Read instructions of RAM (Include general purpose register area), SFR,2nd SFR(No wait), ES,CS, PSW,SP

Note: Read instructions of 2nd SFR with wait, mirror area and Data Flash are not related.

	Operand		Operand		Operand		Operand		Operand						
MOV	A, saddr	ADDC	A, saddr	XOR	A, saddr	MOV	ES, saddr	MOV1	CY, saddr.bit						
	A, sfr		A, !addr16		A, !addr16		B, saddr		CY, sfr.bit						
	A, !addr16		A, [HL]		A, [HL]		B, !addr16		CY, PSW.bit						
	A, PSW		A, [HL+byte]		A, [HL+byte]		C, saddr		CY, [HL].bit						
	A, ES		A, [HL+B]		A, [HL+B]		C, !addr16		AND1	CY, saddr.bit					
	A, CS		A, [HL+C]		A, [HL+C]		X, saddr		CY, sfr.bit						
	A, [DE]		SUB		A, saddr		CMP		A, saddr	X, !addr16	CY, PSW.bit				
	A, [DE+byte]				A, !addr16				A, !addr16	A, [HL]	CY, [HL].bit				
	A, [HL]				A, [HL]				A, [HL+byte]	MOVW	BC, saddrp	OR1	CY, saddr.bit		
	A, [HL+byte]				A, [HL+byte]				A, [HL+B]		BC, !addr16		CY, sfr.bit		
	A, [HL+B]	A, [HL+B]		A, [HL+C]	DE, saddrp	CY, PSW.bit									
	A, [HL+C]	A, [HL+C]		A, [HL+C]	DE, !addr16	CY, [HL].bit									
	A, word[B]	SUBC		A, saddr	ADDW	AX, saddrp		XOR1	CY, saddr.bit						
	A, word[C]			A, !addr16		AX, !addr16			BC, SP		CY, sfr.bit				
	A, word[BC]			A, [HL]		AX, [HL+byte]			DE, SP		CY, PSW.bit				
	A, [SP+byte]			A, [HL+byte]		AX, [HL+byte]			HL, SP		CY, [HL].bit				
	MOVW		AX, saddrp	A, [HL+B]		SUBW	AX, saddrp		CMP		saddr, #byte		POP	rp	
			AX, sfrp	A, [HL+C]			AX, !addr16				AX, [HL+byte]		!addr16, #byte		
			AX, !addr16	AND			A, saddr			CMPW	AX, saddrp	CMPO	saddr		
			AX, [DE]				A, !addr16				AX, !addr16		AX, [HL+byte]	!addr16	
AX, [DE+byte]			A, [HL]				MOVW				AX, SP		CMPS	X, [HL+byte]	
AX, [HL]			A, [HL+byte]												
AX, [HL+byte]		A, [HL+B]													
AX, word[B]		A, [HL+C]													
AX, word[C]		OR	A, saddr												
AX, word[BC]			A, !addr16												
AX, [SP+byte]	A, [HL]														
ADD	A, saddr		A, [HL+byte]												
	A, !addr16		A, [HL+B]												
	A, [HL]		A, [HL+C]												
	A, [HL+byte]														
	A, [HL+B]														
	A, [HL+C]														

Related instructions 2: Read instructions of Data Flash

	Operand		Operand		Operand		Operand			
MOV	A, !addr16	ADD	A, !addr16	AND	A, !addr16	MOV	B, !addr16			
	A, [DE]		A, [HL]		A, [HL]		C, !addr16			
	A, [DE+byte]		A, [HL+byte]		A, [HL+byte]		X, !addr16			
	A, [HL]		A, [HL+B]		A, [HL+B]		CMP	!addr16, #byte		
	A, [HL+byte]		A, [HL+C]		A, [HL+C]			CMPO	!addr16	
	A, [HL+B]		ADDC		A, !addr16			OR	A, !addr16	CMPS
	A, [HL+C]	A, [HL]		A, [HL]						
	A, word[B]	A, [HL+byte]		A, [HL+byte]						
	A, word[C]	A, [HL+B]		A, [HL+B]						
	ADD	A, word[BC]		A, [HL+C]	A, [HL+C]	XOR	A, !addr16			
		A, saddr		A, saddr	A, saddr		A, [HL]			
		A, !addr16	A, [HL]	A, [HL]	A, [HL+byte]					
A, [HL]		A, [HL+byte]	A, [HL+byte]	A, [HL+B]						
A, [HL+byte]		A, [HL+B]	A, [HL+B]	A, [HL+C]						
A, [HL+B]		A, [HL+C]	A, [HL+C]	CMP	A, !addr16					
A, [HL+C]	SUB	A, !addr16	XOR		A, [HL]					
A, word[B]		A, [HL]			A, [HL]	A, [HL+byte]				
A, word[C]		A, [HL+byte]			A, [HL+byte]	A, [HL+B]				
SUB		A, word[BC]			A, [HL+B]	A, [HL+B]	A, [HL+C]			
		A, saddr			A, [HL+C]	A, [HL+C]	CMP	A, !addr16		
		A, !addr16		A, saddr	A, saddr	A, [HL]				
	A, [HL]	A, [HL]	A, [HL]	A, [HL+byte]						
	A, [HL+byte]	A, [HL+byte]	A, [HL+byte]	A, [HL+B]						
	A, [HL+B]	A, [HL+B]	A, [HL+B]	A, [HL+C]						
A, [HL+C]	A, [HL+C]	A, [HL+C]								

