

QUICKSWITCH® PRODUCTS HIGH-SPEED CMOS QUICKSWITCH DOUBLE-WIDTH BUS SWITCH

**IDTQS32X2245** 

### **FEATURES:**

- Enhanced N channel FET with no inherent diode to Vcc
- Dual '245 function
- 25 $\Omega$  resistor for low noise
- · Low propagation delay, zero ground bounce
- · Undershoot clamp diodes on all switch and control inputs
- · TTL-compatible control inputs
- · Available in 40-pin QVSOP package

# **DESCRIPTION:**

The QS32X2245 provides a set of 16 high-speed CMOS TTL-compatible bus switches in a flow-through pinout. The QS32X2245 includes internal  $25\Omega$  resistors to reduce reflection noise in high speed applications. The Output Enable ( $\overline{\text{OEn}}$ ) signals turn the switches on similar to the  $\overline{\text{OEn}}$  signal of the 74'245.


QuickSwitch devices provide an order of magnitude faster speed than conventional logic devices.


The QS32X2245 is characterized for operation at -40°C to +85°C.

### **APPLICATIONS:**

- · Hot-swapping, hot-docking
- Voltage translation (5V to 3.3V)
- · Bus switching and isolation
- · Power conservation
- · Clock gating
- · Logic replacement

# **FUNCTIONAL BLOCK DIAGRAM**






INDUSTRIAL TEMPERATURE RANGE

**FEBRUARY 2011** 

# **PIN CONFIGURATION**



### **ABSOLUTE MAXIMUM RATINGS**(1)

Symbol	Description	Max	Unit
VTERM <sup>(2)</sup>	Supply Voltage to Ground	-0.5 to +7	٧
VTERM <sup>(3)</sup>	DC Switch Voltage Vs	-0.5 to +7	V
VTERM <sup>(3)</sup>	DC Input Voltage VIN	-0.5 to +7	V
VAC	AC Input Voltage (pulse width ≤ 20ns)	<b>–</b> 3	V
lout	DC Output Current	120	mA
Рмах	Maximum Power Dissipation (TA = 85°C)	0.92	W
Tstg	Storage Temperature	-65 to +150	°C

#### NOTE:

- 1. Stresses greater than those listed under ABSOLUTE MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.
- 2. Vcc terminals.
- 3. All terminals except Vcc.

### **CAPACITANCE**

 $(TA = +25^{\circ}C, f = 1.0MHz, VIN = 0V, VOUT = 0V)$ 

Pins	Тур.	Max. <sup>(1)</sup>	Unit
Control Pins	3	5	pF
Quickswitch Channels (Switch OFF)	5	7	pF

#### NOTE:

### **PIN DESCRIPTION**

Pin Names	1/0	Description
OE1, OE2	I	Bus Enable
An	I/O	Bus A
Bn	I/O	Bus B

### **FUNCTION TABLE**(1)

ŌĒ1	ŌE2	A0 - A7	<b>A</b> 8 <b>- A</b> 15	Function
Н	Н	Z	Z	Disconnect
L	Н	B0 - B7	Z	Connect
Н	L	Z	B8 - B15	Connect
L	L	B0 - B7	B8 - B15	Connect

#### NOTE

- 1. H = HIGH Voltage Level
  - L = LOW Voltage Level
  - Z = High-Impedance

<sup>1.</sup> This parameter is measured at characterization but not tested.

# DC ELECTRICAL CHARACTERISTICS OVER OPERATING RANGE

Following Conditions Apply Unless Otherwise Specified: Industrial:  $TA = -40^{\circ}C$  to  $+85^{\circ}C$ ,  $VCC = 5.0V \pm 5\%$ 


Symbol	Parameter	Test Conditions	Min.	Typ. <sup>(1)</sup>	Max.	Unit
VIH	Input HIGH Level	Guaranteed Logic HIGH for Control Pins	2	_	_	V
VIL	Input LOW Level	Guaranteed Logic LOW for Control Pins		_	0.8	V
lin	Input LeakageCurrent (Control Inputs) <sup>(2)</sup>	$0V \le VIN \le VCC$	_	±0.01	±1	μA
loz	Off-State Output Current (Hi-Z)	0V ≤ Vouт ≤ Vcc, Switches OFF	_	±0.01	±1	μA
Ron <sup>(3)</sup>	Switch ON Resistance	Vcc = Min., Vin = 0V, Ion = 30mA	18	23	35	Ω
		Vcc = Min., VIN = 2.4V, ION =15mA	18	25	40	
VP	Pass Voltage <sup>(2)</sup>	$V_{IN} = V_{CC} = 5V$ , $I_{OUT} = -5\mu A$	3.7	4	4.2	V

#### NOTES:

- 1. Typical values are at Vcc = 5.0V, TA = 25°C.
- 2. Pass Voltage is guaranteed but not production tested.
- 3. Rout changed on March 8, 2002. See rear page for more information.

# TYPICAL ON RESISTANCE vs Vin AT Vcc = 5V

RON (ohms)



### **POWER SUPPLY CHARACTERISTICS**

Symbol	Parameter	Test Conditions <sup>(1)</sup>	Max.	Unit
Iccq	Quiescent Power Supply Current	Vcc = Max., Vin = GND or Vcc, f = 0	6	μΑ
Δlcc	Power Supply Current per Control Input HIGH (2)	Vcc = Max., Vin = 3.4V, f = 0	1.5	mA
ICCD	Dynamic Power Supply Current per MHz <sup>(3)</sup>	Vcc = Max., A and B pins open	0.25	mA/MHz
		Control Inputs Toggling at 50% Duty Cycle		

#### NOTES:

- 1. For conditions shown as Min. or Max., use the appropriate values specified under DC Electrical Characteristics.
- 2. Per TLL driven input ( $V_{IN} = 3.4V$ , control inputs only). A and B pins do not contribute to  $\Delta lcc$ .
- 3. This current applies to the control inputs only and represents the current required to switch internal capacitance at the specified frequency. The A and B inputs generate no significant AC or DC currents as they transition. This parameter is guaranteed but not production tested.

### SWITCHING CHARACTERISTICS OVER OPERATING RANGE

 $T_A = -40$ °C to +85°C,  $V_{CC} = 5.0V \pm 5\%$ ;


CLOAD = 50pF, RLOAD =  $500\Omega$  unless otherwise noted.

Symbol	Parameter	Min. <sup>(1)</sup>	Тур.	Max.	Unit
tPLH	Data Propagation Delay (2,3)	_	_	1.25	ns
tphL	An to/from Bn				
tpzl	Switch Turn-on Delay	0.5	_	6.6	ns
tpzh	OE to An/Bn				
tPLZ	Switch Turn-off Delay (2)	0.5	_	4.5	ns
tPHZ	OE to An/Bn				

### NOTES:

- 1. Minimums are guaranteed but not production tested.
- 2. This parameter is guaranteed but not production tested.
- 3. The bus switch contributes no propagation delay other than the RC delay of the ON resistance of the switch and the load capacitance. The time constant for the switch alone is of the order of 1.25ns for C<sub>L</sub> = 50pF. Since this time constant is much smaller than the rise and fall times of typical driving signals, it adds very little propagation delay to the system. Propagation delay of the bus switch, when used in a system, is determined by the driving circuit on the driving side of the switch and its interaction with the load on the driven side.

### ORDERING INFORMATION



As per PCN L0201-02, the Output Resistance (Ron) specifications have changed as of March 8, 2002. The original specifications were:

Parameter	Description	Min.	Тур.	Max.	Unit
Ron	Vcc = Min, VIN = 0V, ION = 30mA	20	28	40	Ω
	Vcc = Min, Vin = 2.4V, Ion = 15mA	20	35	48	

# **Datasheet Document History**

02/16/2011 Pg. 5 Updated the ordering inf

Updated the ordering information by removing the "IDT" notation, non RoHS part and by adding Tape and Reel information.

#### **IMPORTANT NOTICE AND DISCLAIMER**

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

### **Corporate Headquarters**

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

#### **Trademarks**

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

#### **Contact Information**

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit <a href="https://www.renesas.com/contact-us/">www.renesas.com/contact-us/</a>.