# Old Company Name in Catalogs and Other Documents

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1<sup>st</sup>, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.

\*

REC19B0001-0200 Rev.2.00								ROM number					
QzROM PROGRAMMING CONFIRMATION FORM SINGLE-CHIP 8-BIT MICROCOMPUTER M37545G4-XXXGP RENESAS TECHNOLOGY							Receipt	Date: Section head signature	Supervisor signature				
					Note	: Plea	se fill i	n all ite	ms ma	rked∗.			
Company name Telephone number Date issued	Date:				(	)					Issuance signature	Supe	rvisor
Specify the name of The submitted flopp and the number of Microcomputer na	by disk mu the mask	ist be	3.5-in	nch 2⊢ be 1 in	ID type	oppy di	sk.	format	if this o	rder is	perfor	med by a flop	ıpy disk.
File code (hexadecimal no					imal notation)	I							
Mask file name .MS						SK (equal or less than eight charact							
ROI Note2: <u>Tř</u>	ita confirm	tta are set R( ted va <b>Cus</b> ation I be p	ea: Add <u>OM dat</u> alue mu stome reque proces	ta (add ust be r) est sed b	s 10 <sub>16</sub> I <u>ress FF</u> set to th ased o	<u>-DA<sub>16</sub>) nose bit</u> nose bit	<u>must be</u> s whos	<u>e set ac</u> <u>e set va</u> le gene	cording alue is fix	to the d ced to 1	<u>ata she</u> or 0.	et.	
mentioned mas	at the rece any prob	ipt of lem, p	the In the In	itial p retur	roduct n imme	deliver diately	y. /. Two	weeks	•	•			
Should you find Renesas will at													
Should you find	otion ("Mas llowing dat	a sho	ould be	e set t	o the R	ROM op	otion d	ata ado	dress (1	,	the m	ask file you h	ave
Should you find Renesas will at Note 2 : ROM op Either of the fol	otion ("Mas lowing dat you don't	a sho prote	ould be	e set t ROM	o the R	ROM op	otion d	ata ado	dress (1		<b>)0</b> <sub>16</sub>	Address	10 <sub>16</sub>
Should you find Renesas will au Note 2 : ROM op Either of the fol ordered. When	ntion ("Mas lowing dat <u>you don't</u> OM data i OM data i	a sho <u>prote</u> s pro s not	ould be ect the tected protec	e set t <u>ROM</u> cted	o the R <u>data, a</u>	OM op a third	otion d party c	ata ado an rea	dress (1 d out it.		00 <sub>16</sub> FF <sub>16</sub>	Address Address	10 <sub>16</sub> 10 <sub>16</sub>

Note 3 : Mark specification

You can appoint the mark by the mark specification form. Without submitting the mark specification form, your mark will be a standard mark. Please fill out the 32P6B/U MARK SPECIFICATION FORM and attach it when you submit the QzROM PROGRAMMING CONFIRMATION FORM. We can't deal with special font marking (customer's trademark etc.) in QZROM microcomputer.

## QzROM PROGRAMMING CONFIRMATION FORM SINGLE-CHIP 8-BIT MICROCOMPUTER M37545G4-XXXGP RENESAS TECHNOLOGY

**ROM-Protection-Area** 

C000 <sub>16</sub> C080 <sub>16</sub>	Reserved ROM area			
$\begin{array}{c} FFD3_{16}\\ FFD4_{16}\\ FFD8_{16}\\ FFDA_{16}\\ FFDA_{16} \end{array}$	Reserved ROM area	All	area	
FFDB <sub>16</sub>	Reserved ROM area (ROM code protect)			
FFDC <sub>16</sub> FFFD <sub>16</sub>			7	NOTE: Do not set any data to address FFDB <sub>16</sub> .
FFFE <sub>16</sub> FFFF <sub>16</sub>	Reserved ROM area		·	Do not set any data to address 11 DD <sub>16</sub> .

#### \*2. Usage conditions

For our reference of new products, please reply to the following questions about the sage of the products you ordered.

(1) Which operation source main clock do you use?

Ceramic resona	tor	External cloc	k input		
Quartz-crystal o	scillation	Other (		)	
	At what frequency	? f(X <sub>IN</sub> )=		MHz	
(2) What is the voltage	of power supply (V	( <sub>DD</sub> ) you use?			
Typ.=	V	Min.=	V	Max.=	V
(3) What is the ambient	t temperature you ι	use?			
Typ.=	C	Min.=	ç	Max.=	c
(4) Please reply to the f	following questions	about timer fur	nction.		
(i) Which timer do yo	u use?				
Timer1	Timer2	Timer	3		
(ii) Which count sour	ce of timer do you	use?			
Timer2	f(X <sub>IN</sub> )/16	f(X <sub>IN</sub> )/8	f(X <sub>IN</sub> )/2	f(X <sub>IN</sub> )/1	
Timer3	f(X <sub>IN</sub> )/16	f(X <sub>IN</sub> )/8	f(X <sub>IN</sub> )/2	carrier-outputtin	g (CARRY)
(iii) Please reply to th	e following questic	ons about carrie	r-generating func	tion.	
<ul> <li>Is 445kHz carrier-</li> </ul>	generating mode e	ffective?	Effective	Ineffective	
<ul> <li>Is software carrier</li> </ul>	-outputting effectiv	e?	Effective	Ineffective	

## QzROM PROGRAMMING CONFIRMATION FORM SINGLE-CHIP 8-BIT MICROCOMPUTER M37545G4-XXXGP RENESAS TECHNOLOGY

(5) Do you use the Watchdog timer?

Not use

(6) Do you use the oscillation stop detection circuit?

Not use

### Thank you cooperation

Use

\*3. Comments