

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

Power supply detection register 1

b7	b6	b5	b4	b3	b2	b1	b0	Symbol	Address	After reset	
0	0	0	0		0	0	0	VCR1	001916	000010002	
								Bit symbol	Bit name	F unction	RW
								—	Reserved bit	Set to "0"	RW
								VC13	VDET4 power supply monitor flag (Note)	0: VCC < VDET4 1: VCC ≥ VDET4	RO
								—	Reserved bit	Set to "0"	RW

Note: The VC13 bit is useful when the VCR2 register's VC27 bit = 1 (VDET4 detection circuit enabled).
The VC13 bit is always 1 ($V_{CC} \geq V_{DET4}$) when the VCR2 register's VC27 bit = 0 (VDET4 detection circuit disabled).

Power supply detection register 2 (Note 1)

b7	b6	b5	b4	b3	b2	b1	b0	Symbol	Address	After reset	
		0	0	0	0	0	0	VCR2	001A ₁₆	00 ₁₆	
								Bit symbol	Bit name	Function	RW
								—	Reserved bit	Set to "0"	RW
								VC26	Power supply V _{DET3} monitor bit	0: Disables detection circuit 1: Enables detection circuit	RW
								VC27	Power supply V _{DET4} monitor bit (Note 2)	0: Disables detection circuit 1: Enables detection circuit	RW

Note 1: Write to this register after the PRCR register's PRC3 bit is set to "1" (write enabled).
Note 2: To use the VCR1 register's VC13 bit or D4INT register's D42 bit, set the VC27 bit to "1" (VDET4 detection circuit enabled).

Power supply VDET4 detection register (Note 1)

b7	b6	b5	b4	b3	b2	b1	b0	Symbol	Address	After reset		
								D4INT	001F16	0016		
								Bit symbol	Bit name	Function	RW	
								D40	VDET4 detection interrupt enable bit.	0 : Disable 1 : Enable	RW	
								D41	STOP mode deactivation control bit (Note 4)	0: Disable (do not use the VDET4 detection interrupt to get out of stop mode) 1: Enable (use the VDET4 detection interrupt to get out of stop mode)	RW	
								D42	VDET4 up/down detection flag (Note 2)	0: Not detected 1: VDET4 up/down detected	RW (Note 3)	
								D43	WDT overflow detected flag	0: Not detected 1: Detected	RW (Note 3)	
								DF0	Sampling clock select bit	b5b4 00 : BCLK divided by 8 01 : BCLK divided by 16 10 : BCLK divided by 32 11 : BCLK divided by 64	RW	
								DF1			RW	
								(b7-b6)	Nothing is assigned. In an attempt to write to these bits, write "0". The value, if read, turns out to be "0".			—

Note 1: Write to this register after the PRCR register's PRC3 bit is set to "1" (write enabled).
Note 2: Useful when the VCR2 register's VC27 bit = 1 (VDET4 detection circuit enabled). If the VC27 bit is cleared to 0 (VDET4 detection circuit disabled), the D42 bit is set to 0 (Not detected).
Note 3: This bit is cleared to "0" by writing a "0" in a program. (Writing a "1" has no effect.)
Note 4: If the VDET4 detection interrupt needs to be used to get out of stop mode again after once used for that purpose, reset the D41 bit by writing a 0 and then a 1.

Figure 2 VCR1, VCR2 and D4INT registers

3.0 Vdet4 voltage detection circuit

A Vdet4 detection interrupt request is generated when the input voltage of the Vcc pin rises over or drops under Vdet4 while the D40 bit of the D4INT register is set (D40 = 1). Setting D41 (D41 = 1) enables the Vdet4 detection interrupt. The Vdet4 detection interrupt shares the interrupt vector with the watchdog timer and oscillation stop detection interrupts.

The D42 bit of D4INT register is set to “1” when an input voltage over or under Vdet4 is detected. A Vdet4 detection interrupt is generated when the D42 bit changes state from “0” to “1”. The D42 bit needs to be cleared to “0” in the program in order to generate an interrupt for the following detection.

The D41 interrupt enable bit needs to be disabled right after entering the interrupt service routine of Vdet4 and enabled once program is out of the service routine. This step prevents unwanted interrupts from being generated once the program is inside the Vdet4 interrupt service routine. Table 1 shows the conditions under which a Vdet4 detection interrupt request is generated. The Vdet4 detection interrupt generation block diagram is shown in Figure 3.

Table 1 Vdet4 detection interrupt request generation conditions

VDET4 up/down detected	D40 bit	Status of D42 bit	Status of D41 bit	VDET4 detection Interrupt request
Detected	1	0 (Change from 0 to 1)	—	Generated
		—	1(Note)	
Detected	1	1(No change)	0	Not generated
	0	—	—	
Not detected	—			

Note : D41 bit = 1 while in stop mode.




Figure 3 Vdet4 detection interrupt generation block

4.0 Vdet4 Limitations in STOP and WAIT modes

The behavior of Vdet4 in STOP and WAIT modes is discussed below:

4.1 Vdet4 in STOP mode

Under the following condition (in STOP mode), if the input voltage goes over Vdet4 when the D41 bit is equal to “1”, a Vdet4 detection interrupt is immediately generated regardless of the value of D42, which causes the MCU to exit STOP mode.

- VC27 bit of the VCR2 register equal to “1” (Vdet4 detection circuit enabled),
- VC13 bit of the VCR1 register equal to “1” ($V_{cc} \geq V_{det4}$),
- D40 bit of the D4INT register equal to “1” (Vdet4 detection interrupt enabled), and
- CM10 bit of the CM1 register is set to “1” (STOP mode)

Thus, in applications where Vdet4 interrupt is used to exit STOP mode, ensure that the CM10 bit is set when the VC13 is equal to 0 ($V_{cc} < V_{det4}$).

4.2 Vdet4 in WAIT mode

The limitation of Vdet4 in WAIT mode is that, if a WAIT instruction is executed under the following condition, a Vdet4 interrupt is immediately generated, causing the MCU to exit from WAIT mode.

- VC27 bit of the VCR2 register is equal to “1” (Vdet4 detection circuit enabled),
- VC13 bit of the VCR1 register equal to “1” ($V_{cc} \geq V_{det4}$), and
- D40 bit of the D4INT register equal to “1” (Vdet4 detection interrupt enabled)

Thus, in applications where Vdet4 is used to exit WAIT mode, ensure that VC13 is equal to 0 ($V_{cc} < V_{det4}$) before entering WAIT mode.

5.0 Implementation Software

5.1 Application code outline

The Vdet4 detection program, written in C and compiled using the KNC30 compiler, will run on the M16C/26 starter kit MSV30262 SKP board. To run the program, follow the steps below.

1. Download the program to the M30262 MCU using the FoUSB Programmer (with USB-ICD).
2. Disconnect USB-ICD from the SKP board. Using a variable voltage power supply, supply 5V to the SKP board using the board's Vcc and GND pins. At this point, the green power LED (D7) should light up.
3. After some time, two more LEDs (D3 and D5) should also light up. If they do not, press the reset switch (S1). The red LED (D3) will be blinking indicating that the MCU is running. The $V_{cc} > V_{det4}$ condition is indicated with the green LED (D5) lit up.

4. Decrease the Vcc supply voltage gradually and at some point the green LED (D5) will turn OFF indicating that $V_{cc} < V_{det4}$. The red LED (D3) will still be blinking at this stage indicating that the program is still running.
5. Increase the Vcc supply voltage gradually and at some point the green LED (D5) will light up again indicating that $V_{cc} > V_{det4}$ once again.
6. To verify Vdet4 behavior in STOP mode, set D41 = "1" (enable Vdet4 in STOP mode) by pressing switch S3. The yellow LED (D4) will light up momentarily indicating that S3 has been pressed.
7. Decrease the Vcc supply voltage gradually and once $V_{cc} < V_{det4}$, the green LED (D5) turns OFF but the red LED (D3) keeps on blinking as in step 4 mentioned above.
8. To enter STOP mode, press switch S4. The red LED (D3) will stop blinking and of indicating that the MCU has entered the STOP mode.
9. Increase the Vcc supply voltage gradually and at a point where $V_{cc} > V_{det4}$, both the red and the green LEDs (D3 and D5) turn ON indicating that the MCU has exited from STOP mode.
10. To verify Vdet4 behavior in STOP mode with a $V_{cc} > V_{det4}$, press switch S4 to enter STOP mode while $V_{cc} > V_{det4}$. The red and the green LEDs (D3 and D5) will only turn OFF momentarily indicating that STOP mode has been exited immediately. This occurs because STOP mode cannot be sustained with a $V_{cc} > V_{det4}$.
11. The Vdet4 behavior in WAIT mode is similar to the Vdet4 behavior in STOP mode and can be verified by repeating steps similar to 6-10 by pressing switch S2 instead of switch 4 to enter WAIT mode.

6.0 Reference

Renesas Technology Corporation Semiconductor Home Page

<http://www.renesas.com>

E-mail Support

support_apl@renesas.com

7.0 Software source code

```

/*****
*
*      File Name: main.c
*
*      Content:   This program demonstrates the usage and bahavior of the Vdet4
*                  voltage detection circuit. The normal execution of a program
*                  loop is simulated by the blinking of the red LED (D3). the
*                  green LED (D5) remains turned ON as long as the supply voltage
*                  Vcc is greater than Vdet4 and turns OFF when  $V_{cc} < V_{det4}$ .
*                  The chip may be made to enter stop mode or wait mode by pressing
*                  switch sw2 or sw4 respectively. Switch sw3 is used to reset the
*                  stop mode deactivation control bit d41 of D4INT register.
*                  If the chip is made to enter stop or wait mode when  $V_{cc} > V_{det4}$ ,

```

```

*           it immediately exits from stop or wait mode and the red and the
*           green LEDs resume flashing. However, sustained stop or wait mode
*           may be entered when Vcc<Vdet4 in which case stop or wait mode
*           is exited when Vcc becomes greater than Vdet4 once again.
*           Note that sw3 must be pressed (resetting bit d41) after exiting
*           stop or wait mode each time in order to make the next exit
*           possible.
*
*           Date: 1-06-2003
*           This program was written to run on the MDECE30262 Board for MSV30262-SKP.
*
*           Copyright 2003 Renesas Technology America, Inc.
*           All rights reserved
*
*=====
*           $Log:$
*=====*/

#include "sfr262.h"    // M16C/26 special function register definitions
#pragma INTERRUPT      Vdet4_ISR /* Interrupt Service Routine for Vdet4 */

/* LEDs */
#define red_led          p7_0
#define yellow_led       p7_1
#define green_led        p7_2

/* SWITCHES */
#define sw2              p10_5
#define sw3              p10_6
#define sw4              p10_7

/*****
void mcu_init(void);    /* routine that initializes the mcu */
void Vdet4_init(void); /* routine that initializes Vdet4 */
void Vdet4_ISR(void);  /* Interrupt service routine for Vdet4 */
void enter_stop(void); /* routine for entering stop mode */
void enter_wait(void); /* routine for entering wait mode with peripheral clocks stopped */
void reset_d41(void);  /* routine that resets d41 bit for successive stop mode exits */
void blink_redLED(void); /* blink red LED to show continuation of program execution */

int delay_count;        /* a delay counter for blinking red LED*/
int delay_counter;      /* a delay counter for blinking yellow LED */
int i;                  /* a delay counter for stop mode switch */
int flag = 0;           /* Vdet4 ISR entry flag */
*****/

Name:    main
Parameters: None
Returns: None
Description:  main program loop and initialization
*****/
main() {
    mcu_init();          /* initialize MCU */

    Vdet4_init();        /* initialize Vdet4 */

```



```

asm( "fset i");          /* enable interrupts */

while(1){                /* program loop */
    /** blink red LED to show continuation of program execution **/
    blink_redLED();

    if( vc13 == 0 ){      /* check is Vcc < Vdet4 */
        green_led    = 1;          /* turn OFF green LED */
    }
    else if( vc13 == 1){  /* check if Vcc > Vdet4 */
        green_led    = 0;          /* turn ON green LED */
    }
    /* invoke stop mode by pressing sw2 */
    if (sw2 == 0 && sw3 != 0 && sw4 != 0){ /* only sw2 is pressed */
        enter_stop();          /* invoke stop mode */

        /** remain in delay loops to avoid sw2 switch bouncing effect **/
        for (delay_count = 0; delay_count<0xffff; delay_count++)
            ;
        for (delay_count = 0; delay_count<0xffff; delay_count++)
            ;
    }

    /* reset stop exit bit of D4INT register by pressing sw3 */
    if (sw3 == 0 && sw2 != 0 && sw4 != 0){ /* only sw3 is pressed */

        reset_d41();          /* reset d41 stop exit bit of D4INT register */
    }

    /* invoke wait mode by pressing sw4*/
    if (sw4 == 0 && sw2 != 0 && sw3 != 0){ /* only sw4 is pressed */
        enter_wait(); /* enter wait mode with peripheral clocks stopped */
    }
    /** remain in delay loops to avoid sw4 switch bouncing effect **/
    for (delay_count = 0; delay_count<0xffff; delay_count++)
        ;
    for (delay_count = 0; delay_count<0xffff; delay_count++)
        ;

    /* re-enable Vdet4 interrupt for next interrupt generation */
    if (flag == 1){ /* Entered Vdet_ISR */
        /* reset flag for detecting next Vdet4 interrupt */
        flag = 0;
        /* enable Vdet4 interrupt for next interrupt generation*/
        prc3 = 1; /* unlock d4int register */
        d40  = 1; /* enable Vdet4 interrupt */
        d42  = 0; /* re-initialize up-down detection bit */
        prc3 = 0; /* lock d4int register */
    }
}
}

```

Name: Vdet4_ISR

Parameters: None

Returns: None

Description: This is the service routine for Vdet4 Interrupt. This routine
will be called whenever Vdet4 interrupt is generated.

*****/

```
void Vdet4_ISR(void) {
    /* disable Vdet4 interrupt */
    prc3 = 1; /* unlock D4INT register */
    d40 = 0; /* disable Vdet4 interrupt to prevent successive unwanted*/
           /* interrupts to be fired due to the comparator circuit */
    prc3 = 0; /* lock D4INT register */
    flag = 1; /* indicate entry to Vdet4 ISR */
}
```

Name: mcu_init

Parameters: None

Returns: None

Description: Initialization routine for the SKP board.

*****/

```
void mcu_init(void) {
    /* LED initialization */
    pd7_0 = 1; /* set LED ports to outputs (connected to LEDs) */
    pd7_1 = 1;
    pd7_2 = 1;
    red_led = 1; /* turn off all LEDs */
    green_led = 1;
    yellow_led = 1;
    return;
}
```

Name: Vdet4_init

Parameters: None

Returns: None

Description: Initialization routine for the Voltage Detection Circuit 4

*****/

```
void Vdet4_init(void) {
    prc3 = 1; /* unlock vcr2 and d4int registers */
    vc27 = 1; /* enable Vdet4 */
    d40 = 1; /* enable Vdet4 interrupt detection */
    d41 = 1; /* enable Vdet4 detection interrupt to get out of stop
mode */
    prc3 = 0; /* lock vcr2 and d4int */
    return;
}
```

```

/*****
Name:          enter_stop
Parameters:    None
Returns:       None
Description:    routine for entering the stop mode. This routine will be called
                when switch sw2 is pressed
*****/
void enter_stop(void){
    /* turn OFF green LED for easy visibility of stop mode being activated*/
    green_led    = 1;

    /* configure clock mode register to enter stop mode */
    prc0 = 1;                /* unlock clock mode register */
    cm10 = 1;                /* stop all clocks */
    prc1 = 0;                /* lock clock mode register */
}
/*****
Name:          enter_wait
Parameters:    None
Returns:       None
Description:    routine for entering the wait mode with peripheral clocks stopped.
                This routine will be called when switch sw4 is pressed
*****/
void enter_wait(void){
    /* stop peripheral clocks */
    prc0 = 1;                /* unlock CM0 register */
    cm02 = 1;                /* stop peripheral clocks */
    prc0 = 0;                /* lock CM0 register */
    /* turn OFF green LED */
    green_led = 1;

    _asm ( "wait" );          /* invoke wait mode */
    return;
}
/*****
Name:          reset_d41
Parameters:    None
Returns:       None
Description:    routine for resetting d41-bit of the D4INT register . This routine
                will be called when switch sw3 is pressed. The yellow LED lights up
                momentarily to indicate that sw3 has been pressed.
*****/
void reset_d41(void){
    /* turn on yellow LED momentarily */
    yellow_led = 0;          /* turn ON yellow LED */
    /* wait for a while to keep yellow LED turned ON */
    for (delay_counter=0; delay_counter<0xffff; delay_counter++)
        ;
    yellow_led = 1;          /* turn off yellow LED */

    /* configure D4INT register */
    prc3 = 1;                /* unlock D4INT register */
    /* reset d41 bit */
    d41  = 0;
    d41  = 1;
}

```

```

    prc3 = 0;                                /* lock D4INT register */
    return;
}
/*****
Name:      blink_redLED
Parameters: None
Returns:   None
Description: routine for blinking red LED. This routine is called from the
            main program loop.
*****/
void blink_redLED(void) {
    /* turn ON red LED */
    red_led = 0;
    /* wait for a while */
    for (delay_count = 0; delay_count<0xffff; delay_count++)
        ;
    /* turn OFF red LED */
    red_led = 1;
    /* wait for a while */
    for (delay_count = 0; delay_count<0xffff; delay_count++)
        ;
    return;
}
/*****
Name:      blink_redLED
Parameters: None
Returns:   None
Description: routine for blinking red LED. This routine is called from the
            main program loop.
*****/
void blink_redLED(void) {
    /* turn ON red LED */
    red_led = 0;
    /* wait for a while */
    for (delay_count = 0; delay_count<0xffff; delay_count++)
        ;
    /* turn OFF red LED */
    red_led = 1;
    /* wait for a while */
    for (delay_count = 0; delay_count<0xffff; delay_count++)
        ;
    return;
}

```

In order for this program to run properly, Vdet4 interrupt vector in the sect30.inc startup file needs to point to the Vdet4 service routine. This is shown below.

```
;      :
;      :
;=====
; fixed vector section
;-----
        .org    0ffffdch
        .glb    _Vdet4_ISR
UDI:
        .lword  dummy_int
OVER_FLOW:
        .lword  dummy_int
BRKI:
        .lword  dummy_int
ADDRESS_MATCH:
        .lword  dummy_int
SINGLE_STEP:
        .lword  dummy_int
WDT:
        .lword  _Vdet4_ISR
DBC:
        .lword  dummy_int
;      :
;      :
```

Keep safety first in your circuit designs!

- Renesas Technology Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

- These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corporation product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corporation or a third party.
- Renesas Technology Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
- All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors.
Renesas Technology Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corporation by various means, including the Renesas Technology Corporation Semiconductor home page (<http://www.renesas.com>).
- When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
- Renesas Technology Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
- The prior written approval of Renesas Technology Corporation is necessary to reprint or reproduce in whole or in part these materials.
- If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- Please contact Renesas Technology Corporation for further details on these materials or the products contained therein.