


RESISTOR READER

PROG1 BOOT VOLTAGE=1V, R3=OPEN; R2=75K OHMS

PROG2 PFM DISABLED, TCOMP=5C AND PMBUS ADDRESS 0X60, R11=OPEN; R10=147K OHMS

PROG3 RETRY,400KHZ,AV49 AND 25KHZ CLAMP DISABLED, R9= 25.5K OHMS; R8= 16.5K OHMS

PROG4 SS= 0.157MV/US, RR=200KOHM AND AVMULTI=2X, R6= 332K OHMS;R5=154K OHMS



DRAWN BY:	TIM KLEMAN	DATE:	12/05/2018	ENGINEER:	PETER LIU	DATE:	
RELEASED BY:		DATE:		TITLE:	ISL8280M EVALUATION BOARD SCHEMATIC		
UPDATED BY:	TIM KLEMAN	DATE:	01/23/2019	TESTER:			
				MASK#	HRDWR ID	REV	A1
FILENAME:	~\ISL8280M\ISL8280MEVAL1ZA			SHEET	1	OF	1