

RD3CYD08

R04DS0040EJ0700 Rev.7.00 Jan 10, 2014

Description


The RD3CYD08 has two-input AND gate in a 5 pin package. This product is suited as IGBT Driver IC for the strobe.

Features

- Supplied on emboss taping for high-speed automatic mounting.
- Supply voltage range : 2.0 to 3.6 V
- Operating temperature range : -40 to +85°C
- High drive current
- I_{OH} short = -130 mA (typ) (@V_{CC} = 3.3 V)
- Low sink current
- I_{OL} short = 45 mA (typ) (@V_{CC} = 3.3 V)
- Ordering Information


Part Name	Package Type	Package Code (Previous Code)	Package Abbreviation	Taping Abbreviation (Quantity)
RD3CYD08CME	CMPAK-5 pin	PTSP0005ZC–A (CMPAK-5V)	СМ	E (3,000 pcs/reel)
RD3CYD08VSE	VSON-5pin	PUSN0005KA–A (TNP-5DV)	VS	E (3,000 pcs/reel)

Outline and Article Indication







Outline and Article Indication



Pin Arrangement



Logic Diagram



Function Table


Inp	uts	Quitaut V
A	В	Output Y
L	L	L
Н	L	L
L	Н	L
Н	Н	Н

H : High level

L : Low level



Block Diagram



Absolute Maximum Ratings

Item	Symbol	Ratings	Unit	Test Conditions
Supply voltage range	V _{CC}	-0.5 to 4.6	V	
Input voltage range *1	VI	-0.5 to V _{CC} + 0.5	V	
Output voltage range *1, 2	Vo	-0.5 to V _{CC} + 0.5	V	
Input clamp current	I _{IK}	±50	mA	$V_{I} < 0 \text{ or } V_{I} > V_{CC}$
Output clamp current	Ι _{ΟΚ}	±50	mA	$V_{\rm O}$ < 0 or $V_{\rm O}$ > $V_{\rm CC}$
		-200		$V_0 = 0$
Continuous output current	lo	100	- mA	$V_{O} = V_{CC}$
Continuous current through V_{CC} or GND	I _{CC} or I _{GND}	±200	mA	
Maximum power dissipation at Ta = 25°C (in still air) $*^3$	PT	200	mW	
Storage temperature	Tstg	-65 to 150	°C	

Notes: The absolute maximum ratings are values, which must not individually be exceeded, and furthermore no two of which may be realized at the same time.

 The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed. When Over shoot / Under shoot pulse width is under 10 ns, input and output voltage permit to -1.5 V or V_{CC}+1.5V.

- 2. This value is limited to 4.6 V maximum.
- 3. The maximum package power dissipation was calculated using a junction temperature of 150°C.

Recommended Operating Conditions

Item	Symbol	Min	Max	Unit	Conditions
Supply voltage range	V _{CC}	2.0	3.6	V	
Input voltage range	VI	0	V _{CC}	V	
Output voltage range	Vo	0	V _{CC}	V	
Operating free-air temperature	Та	-40	85	°C	

Note: Unused or floating inputs must be held high or low.



Electrical Characteristics

ltem	Symbol	V _{cc} (V)	Min	Тур	Max	Unit	Test condition
	V	2.5	1.7	—			
	VIH	3.0 to 3.6	2.0	—			
Input voltage	V	2.5		—	0.7	v	
Input voltage	VIL	3.0 to 3.6		—	0.8	v	
	N/	2.5	_	0.35	_		
	V _H	3.3	_	0.40	_		
	l chort	2.5	-55	-75	-95		$V_{O} = 0 V$
Output ourroat	I _{OH} short	3.3	-100	-130	-160		$v_0 = 0 v$
Output current	l short	2.5	20	30	40	mA	
	I _{OL} short	3.3	30	45	60		$V_{O} = V_{CC}$
Input current	I _{IN}	3.6		—	±5	μΑ	$V_{IN} = 3.6 \text{ V or GND}$
Quiescent supply current	I _{CC}	3.6	_	_	10	μA	$V_{IN} = V_{CC}$ or GND, $I_O = 0$
Input capacitance	C _{IN}	3.3		2.5		pF	$V_{IN} = V_{CC}$ or GND

Switching Characteristics


							١	$V_{\rm CC} = 2.5 \ {\rm V}$
Item	Symbol	Ta = -40		–40 to 85°C		Test	FROM	то
Item	Symbol	Min	Тур	Max	Unit	Conditions	(Input)	(Output)
Propagation dolay time	t _{d(ON)}	—		65			A at D	V
Propagation delay time	t _{d(OFF)}	—	_	200		0 0500 = 5		
Output rise time	tr	—		700	ns	C∟ = 6500 pF	A or B	T
Output fall time	t _f	_		2000				

 $V_{CC}=3.3\pm0.3~V$


Item	Symbol	Ta :	= -40 to 8	5°C	Unit	Test	FROM	ТО
nem	Symbol	Min	Тур	Max	Unit	Conditions	(Input)	(Output)
Dropagation dology time	t _{d(ON)}	_		50			A or B	Y
Propagation delay time	t _{d(OFF)}	—		160	ns	ns $C_{L} = 6500 \text{ pF}$		
Output rise time	tr	—		500				
Output fall time	t _f	—	_	1500				



Test Circuit




Waveforms





Application Note (Strobe circuit)



Combination example

SYSTEM	IGBT	IGBT Driver	Control IC
3.3 V	RJP4002ANS RJP4002ASA	RD3CYD08 RD3CYDT08	3.3 V signal
5.0 V	RJP4003ANS RJP4003ASA	RD5CYD08 RD5CYDT08	5.0 V signal 3.3 V signal

IGBT Driver Lineup

TYPE No.	Specification	Package
RD3CYD08	$ V_{CC} = 2.0 \text{ to } 3.6 \text{V CMOS lever input} \\ I_{OH}(\text{short}) = -130 \text{mA}(\text{typ}) @ V_{CC} = 3.3 \text{V} \\ I_{OL}(\text{short}) = 45 \text{mA}(\text{typ}) @ V_{CC} = 3.3 \text{V} $	CMPAK-5 VSON-5
RD3CYDT08		CMPAK-5
RD5CYD08	$ V_{CC} = 4.0 \text{ to } 6.0 \text{V CMOS lever input} \\ I_{OH}(\text{short}) = -130 \text{mA(typ)} @ V_{CC} = 5.0 \text{V} \\ I_{OL}(\text{short}) = 40 \text{mA(typ)} @ V_{CC} = 5.0 \text{V} $	CMPAK-5
RD5CYDT08	$V_{CC} = 4.0 \text{ to } 6.0 \text{V} \text{ TTL lever input}$ $I_{OH}(\text{short}) = -130 \text{mA}(\text{typ}) @ V_{CC} = 5.0 \text{V}$ $I_{OL}(\text{short}) = 40 \text{mA}(\text{typ}) @ V_{CC} = 5.0 \text{V}$	Givii Art-3


IGBT Lineup


TYPE No.	Specification	Package
RJP4002ANS	V _{CES} = 400V(max), I _{CP} = 150A(max), 2.5V drive	VSON-8
RJP4002ASA	V _{CES} = 400V(max), I _{CP} = 150A(max), 2.5V drive	TSSOP-8
RJP4003ANS	V_{CES} = 400V(max), I _{CP} = 150A(max), 4V drive	VSON-8
RJP4003ASA	V_{CES} = 400V(max), I _{CP} = 150A(max), 4V drive	TSSOP-8




Package Dimensions

JEITA Package Code	RENESAS Code	Previous Code	MASS (Typ) [g]
SC-88A	PTSP0005ZC-A	CMPAK-5 / CMPAK-5V	0.006










A-A Section

Reference	Dimensi	ons in mi	llimeters
Symbol	Min	Nom	Max
Α	0.8		1.1
A ₁	0		0.1
A ₂	0.8	0.9	1.0
A ₃		0.25	
b	0.15	0.22	0.3
С	0.1	0.13	0.15
D	1.8	2.0	2.2
E	1.15	1.25	1.35
е		0.65	
HE	1.8	2.1	2.4
L	0.3		0.7
L ₁	0.1		0.5
LP	0.2		0.6
Х			0.05
У			0.05
Q		0.25	

© 2013 Renesas Electronics Corporation. All rights reserved.



RD3CYD08





Notice

- Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or
- technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.

Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics may way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.

- 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
- 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations.
- 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
- 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



SALES OFFICES

Refer to "http://www.renesas.com/" for the latest and detailed information

Renesas Electronics Corporation

http://www.renesas.com

Renesas Electronics America Inc. 2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A. Tel: +1-40-588-8000, Fax: +1-408-588-6130 Renesas Electronics Canada Limited 1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada Tel: +1-905-989-5041, Fax: +1-905-898-3220 Renesas Electronics Europe Limited Dukes Meadow, Milboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-651-700, Fax: +44-1628-651-804 Renesas Electronics Europe GmbH Arcadiastrasse 10, 40472 Düsseldorf, Germany Tel: +49-211-65030, Fax: +44-1628-651-804 Renesas Electronics (Shanghai) Co., Ltd. 7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China Tel: +86-10-253-1155, Fax: +86-10-253-7679 Renesas Electronics (Shanghai) Co., Ltd. 7th Floor, Quantum Tower, S55 LanGao Rd., Putuo District, Shanghai, China Tel: +86-10-253-1155, Fax: +86-21-2226-0999 Renesas Electronics Hong Kong Limited Unit 1001-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tel: +86-10-280-5175, Fax: +862-21-2226-0999 Renesas Electronics Hong Kong Limited Unit 1001-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tel: +880-24175-9000, Fax: +862-24175-9670 Renesas Electronics Mang Co., Ltd. 13F, No. 363, Fu Shing North Road, Taipei, Taiwan Tel: +882-74175-9600, Fax: +862-24175-9670 Renesas Electronics Mangyais Sdn.Bhd. Unit 906, Block B, Menara Amoorp, Amoorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia Tel: +652-3150, Fax: +65-27300, Fax: +65-27300, Fax: +65-27300, Fax: +60-37955-9510 Renesas Electronics Korea Co., Ltd. 12F, 234 Teheran-ro, Gangham-Gu, Seoul, 135-080, Korea Tel: +65-27300, Fax: +60-57955-9510