

NX7339BB-AA

LASER DIODE

1 310 nm InGaAsP MQW-FP LASER DIODE COAXIAL MODULE FOR OTDR APPLICATION

DESCRIPTION

The NX7339BB-AA is a 1 310 nm Multiple Quantum Well (MQW) structured Fabry-Perot (FP) laser diode coaxial module with single mode fiber. This module is specified to operate under pulsed condition and designed for light source of Optical Time Domain Reflectometer (OTDR).

FEATURES

- High output power $P_f = 50 \text{ mW} @ I_{FP} = 400 \text{ mA}^{1}$
- Long wavelength $\lambda c = 1 310 \text{ nm}$
 - *1 Pulse Conditions: Pulse width (PW) = 10 μ s, Duty = 1%


The mark <R> shows major revised points.

The revised points can be easily searched by copying an "<R>" in the PDF file and specifying it in the "Find what:" field.



R08DS0005EJ0400 Rev.4.00 Jul 12, 2012


PACKAGE DIMENSIONS (UNIT: mm)



OPTICAL FIBER CHARACTERISTICS

Parameter	Specification	Unit
Mode Field Diameter	9.3±0.5	<i>μ</i> m
Cladding Diameter	125±2	<i>µ</i> m
Maximum Cladding Noncircularity	2	%
Maximum Core/Cladding Concentricity	1.6	%
Outer Diameter	0.9±0.1	mm
Cut-off Wavelength	1 100 to 1 280	nm
Minimum Fiber Bending Radius	30	mm
Fiber Length	1 000 MIN.	mm

<R>





ORDERING INFORMATION

Part Number	Flange Type
NX7339BB-AA	flat mount flange



<R> ABSOLUTE MAXIMUM RATINGS (TA = 25°C, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Pulsed Forward Current ^{*1}	IFP	600	mA
Reverse Voltage	VR	2.0	V
Operating Case Temperature	Tc	-20 to +60	°C
Storage Temperature	Tstg	-40 to +85	°C
Lead Soldering Temperature	Tsld	350 (3 sec.)	°C
Relative Humidity (noncondensing)	RH	85	%


*1 Pulse Condition: Pulse Width (PW) = 10 μ s, Duty = 1%

ELECTRO-OPTICAL CHARACTERISTICS (Tc = 25°C, unless otherwise specified)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Forward Voltage	Vfp	I⊧P = 400 mA, PW = 10 μs, Duty = 1%		2.5	4.0	V
Threshold Current	Ith	Tc = 0 to +60°C			50	mA
Optical Output Power from Fiber	Pf	IFP = 400 mA, PW = 10 μs, Duty = 1%	25	50		mW
		IFP = 400 mA, PW = 10 μ s, Duty = 1% Tc = 0 to +60°C	15			
Center Wavelength	λς	RMS (–20 dB), 1εε = 400 mA, PW = 10 μs, Duty = 1%	1 290	1 310	1 330	nm
		RMS (-20 dB), IFP = 400 mA, PW = 10 µs, Duty = 1% Tc = 0 to +60°C	1 280		1 342.5	
Spectral Width	σ	RMS (-20 dB), I⊧P = 400 mA, PW = 10 <i>µ</i> s, Duty = 1% Tc = 0 to +60°C			10.0	nm
Rise Time	tr	10-90%			2.0	ns
Fall Time	tr	90-10%			2.0	ns



TYPICAL CHARACTERISTICS (Tc = 25°C, unless otherwise specified)





REFERENCE

Document Name	Document No.
Opto-Electronics Devices Pamphlet ¹	PX10160E

*1 Published by the former NEC Electronics Corporation.



SAFETY INFORMATION ON THIS PRODUCT



SEMICONDUCTOR LASER

)) $\mathcal{L}($ ≡

AVOID EXPOSURE-Invisible Laser Radiation is emitted from this aperture

Warning Laser Beam	A laser beam is emitted from this diode during operation. The laser beam, visible or invisible, directly or indirectly, may cause injury to the eye or loss of eyesight.
	Do not look directly into the laser beam.
	Avoid exposure to the laser beam, any reflected or collimated beam.
Caution GaAs Products	This product uses gallium arsenide (GaAs). GaAs vapor and powder are hazardous to human health if inhaled or ingested, so please observe the following points.
	• Follow related laws and ordinances when disposing of the product. If there are no applicable laws and/or ordinances, dispose of the product as recommended below.
	 Commission a disposal company able to (with a license to) collect, transport and dispose of materials that contain arsenic and other such industrial waste materials.
	2. Exclude the product from general industrial waste and household garbage, and ensure that the product is controlled (as industrial waste subject to special control) up until final disposal.
	• Do not burn, destroy, cut, crush, or chemically dissolve the product.
	 Do not lick the product or in any way allow it to enter the mouth.
Caution Optical Fiber	 A glass-fiber is attached on the product. Handle with care. When the fiber is broken or damaged, handle carefully to avoid injury from the damaged part or fragments.



Revision History

NX7339BB-AA Data Sheet

		Description		
Rev.	Date	Page	Summary	
_	Jul 2006	-	Previous No. : PL10604EJ02V0DS	
3.00	Sep 19, 2010	p.1	Modification of photograph	
		p.2	Modification of PACKAGE DIMENSIONS	
4.00	Jul 12, 2012	p.2	Modification of OPTICAL FIBER CHARACTERISTICS	
		p.4	Modification of ABSOLUTE MAXIMUM RATINGS	

- Notice 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information, 2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein. 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product. 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. *Standard*: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment: and industrial robots etc. "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc. Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or system implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using j in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics. 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunction ages arisi ng out of the use of Renesas Electronics products beyond such specified ranges. 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the oc of failure at a cert and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of micro computer software alone is very difficult please evaluate the safety of the final products or systems manufactured by you. 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations. r sale is prohibited under any applicable domestic or foreign laws or 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
 - 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
 - 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Elevation
 - 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries. (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
 - (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



SALES OFFICES

Refer to "http://www.renesas.com/" for the latest and detailed information

Renesas Electronics Corporation

http://www.renesas.com

 Renesas Electronics America Inc.

 2880 Scott Boulevard Santa Clara, CA 95060-2554, U.S.A.

 Tel: +1-406-5886:000_Rex: +1-408-588-6130

 Renesas Electronics Canada Limited

 1101 Nicholson Road, Rowmarket, Ontario LSY 963, Canada

 Tel: +1-305-699-5441, Fax: +1-305-699-3220

 Renesas Electronics Europe Limited

 Dukes Meadow, Milloband Road, Bourne End, BuckInghamshire, SL8 5FH, U.K

 Tel: +44-1628-585-100, Fax: +44-1628-585-900

 Renesas Electronics Europe GmbH

 Arcadiastrasse 10, 40472 Düsseldorf, Germany

 Tel: +49-211 +6500, Fax: +44-1023-57679

 Renesas Electronics (China) Co., Ltd.

 7th Floor, Quantum Plaza, No.27 Zh/Chunt.U Haidian District, Beijing 100083, P.R.China

 Tel: +66(0-8235-1155, Fax: +861-0-887-7588 - 77898

 Renesas Electronics (Shanghai) Co., Ltd.

 Unit 204, 205, AZIA Center, No. 1233 Lujiazzi Ring Rd., Pudong District, Shanghai 200120, China

 Tel: +682-587-71816, Fax: +862-0887-7888 - 78988

 Renesas Electronics (Shanghai) Co., Ltd.

 Unit 1601-1613, 16/F, Tower 2, Grand Century Plaze, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong

 Tel: +852-2886-9918, Fax: +852-2886-9022/9044

 Renesas Electronics Taiwan Co., Ltd.

 135 No. 363 Fu Shing North Road, Taipei, Taiwan

 Tel: +880-264175-9600, Fax: +882-28175-9670
 </t