FEATURES:

- Enhanced N channel FET with no inherent diode to Vcc
- 5Ω bidirectional switches connect inputs to outputs
- · Zero propagation delay, zero ground bounce
- · Undershoot Clamp Diodes on all switch and control Inputs
- · Four enables control five bits each
- TTL-compatible input and output levels
- · Available in 48-pin QVSOP package

APPLICATIONS:


- · Hot-swapping, hot-docking
- Voltage translation (5V to 3.3V)
- · Logic replacement (data processing)
- Power conservation
- · Capacitance reduction and isolation
- · Low power for hand held and mobile applications
- · Bus isolation
- Clock gating

DESCRIPTION:

The QS32XL384 provides a set of twenty high-speed CMOS TTL-compatible bus switches. The low ON resistance of the QS32XL384 allows inputs to be connected to outputs without adding propagation delay and without generating additional ground bounce noise. The Bus Enable (\overline{BE}) signals turn the switches on. Four Bus Enable signals are provided, one for each of five bits of the 20-bit bus. The '384 family of QuickSwitch products is ideal for switching wide digital buses, as well as hot-docking, 5V to 3V conversion and capacitance isolation for power conservation.

The QS32XL384 is characterized for operation at -40°C to +85°C.


FUNCTIONAL BLOCK DIAGRAM



 $IDT and the \, IDT logo \, is \, a \, registered \, trademarks \, of \, Integrated \, Device \, Technology, \, Inc. \, and \, the \, IDT logo \, is \, a \, registered \, trademarks \, of \, Integrated \, Device \, Technology, \, Inc. \, and \, the \, IDT logo \, is \, a \, registered \, trademarks \, of \, Integrated \, Device \, Technology, \, Inc. \, and \, the \, IDT logo \, is \, a \, registered \, trademarks \, of \, Integrated \, Device \, Technology, \, Inc. \, and \, the \, IDT logo \, is \, a \, registered \, trademarks \, of \, Integrated \, Device \, Technology, \, Inc. \, and \, the \, IDT logo \, is \, a \, registered \, trademarks \, of \, Integrated \, Device \, Technology, \, Inc. \, and \, the \, IDT logo \, is \, a \, registered \, trademarks \, of \, Integrated \, Device \, Technology, \, Inc. \, and \, the \, IDT logo \, is \, a \, registered \, trademarks \, of \, Integrated \, Device \, Technology, \, Inc. \, and \, the \, IDT logo \, is \, a \, registered \, trademarks \, of \, Integrated \, Device \, Technology, \, Inc. \, and \, the \, IDT logo \, is \, a \, registered \, trademarks \, and \, and$

JUNE 2011

PIN CONFIGURATION



QVSOP TOP VIEW

PIN DESCRIPTION

Pin Names	I/O	Description	
A0 - A19	I/O	Bus A	
B0 - B19	I/O	Bus B	
BEA	1	Enable, 0 - 4	
BEB	I	Enable, 15 - 19	
BEC	I	Enable, 5 - 9	
BED	I	Enable, 10 - 14	

ABSOLUTE MAXIMUM RATINGS(1)

Symbol	Description	Max	Unit
VTERM ⁽²⁾	SupplyVoltage to Ground	-0.5 to +7	٧
VTERM ⁽³⁾	DC Switch Voltage Vs	-0.5 to +7	V
VTERM ⁽³⁾	DC Input Voltage VIN	-0.5 to +7	V
VAC	AC Input Voltage (pulse width ≤20ns)	-3	V
lout	DC Output Current	120	mA
Рмах	Maximum Power Dissipation (TA = 85°C)	0.5	W
Tstg	Storage Temperature	-65 to +150	°C

NOTES:

- 1. Stresses greater than those listed under ABSOLUTE MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.
- 2. Vcc terminals.
- 3. All terminals except Vcc .

CAPACITANCE (TA = +25°C, F = 1MHz, Vin = 0V, Vout = 0V)

Pins	Тур.	Max. ⁽¹⁾	Unit
Control Inputs	3	5	pF
Quickswitch Channels (Switch OFF)	5	7	pF

NOTE:

1. This parameter is guaranteed but not production tested.

FUNCTION TABLE(1)

BEA	BEB	B0 - B4	B15 - B19	Function	
Н	Н	Z	Z	Disconnect	
L	Н	A0 - A4	Z	Connect	
Н	L	Z	A15 - A19	Connect	
L	L	A0 - A4	A15 - A19	Connect	
BEC	BED	B5 - B9	B10 - B14	Function	
Н	Н	Z	Z	Disconnect	
L	Н	A5 - A9	Z	Connect	
Н	L	Z	A10 - A14	Connect	
				Connect	

NOTE:

1. H = HIGH Voltage Level

L = LOW Voltage Level

Z = High-Impedence

DC ELECTRICAL CHARACTERISTICS OVER OPERATING RANGE

 $Following \ Conditions \ Apply \ Unless \ Otherwise \ Specified:$


Industrial: TA = -40°C to +85°C, Vcc = 5.0V ± 5 %

Symbol	Parameter	Test Conditions	Min.	Typ. ⁽¹⁾	Max.	Unit
VIH	Input HIGH Voltage	Guaranteed Logic HIGH for Control Pins	2	_	_	V
VIL	Input LOW Voltage	Guaranteed Logic LOW for Control Pins	_	_	0.8	V
lin	Input Leakage Current (Control Inputs)	$0V \le VIN \le VCC$	_	±0.01	±1	μΑ
loz	Off-State Current (Hi-Z)	0V ≤ Vouт ≤ Vcc, Switches OFF	_	±0.01	±1	μΑ
Ron	Switch ON Resistance	Vcc = Min., VIN = 0V, ION = 30mA	_	5	7	Ω
		Vcc = Min., VIN = 2.4V, ION = 15mA	_	10	15	
VP	Pass Voltage ⁽²⁾	VIN = VCC = 5V, IOUT = -5µA	3.7	4	4.2	V

NOTES:

- 1. Typical values are at Vcc = 5.0V and TA = 25°C.
- 2. Pass voltage is guaranteed but not production tested.

TYPICAL ON RESISTANCE vs Vin AT Vcc = 5V



VIN (Volts)

POWER SUPPLY CHARACTERISTICS

Symbol	Parameter	Test Conditions ⁽¹⁾	Max.	Unit
Iccq	Quiescent Power Supply Current	Vcc = Max., Vin = GND or Vcc, f = 0	6	μА
Δlcc	Power Supply Current per Input HIGH(2)	Vcc = Max., Vin = 3.4V, f = 0	2.5	mA
ICCD	Dynamic Power Supply Current per MHz ⁽³⁾	Vcc = Max., A and B Pins Open	0.25	mA/MHz
		Control Input Toggling @ 50% Duty Cycle		

NOTES:

- 1. For conditions shown as Min. or Max., use the appropriate values specified under DC Electrical Characteristics.
- 2. Per TTL driven input (V_{IN} = 3.4V, control inputs only). A and B pins do not contribute to Δlcc .
- 3. This current applies to the control inputs only and represents the current required to switch internal capacitance at the specified frequency. The A and B inputs generate no significant AC or DC currents as they transition. This parameter is guaranteed but not production tested.

SWITCHING CHARACTERISTICS OVER OPERATING RANGE


 $T_A = -40$ °C to +85°C

Symbol	Parameter	Min. ⁽¹⁾	Тур.	Max.	Unit
t PLH	Data Propagation Delay ^(2,4)	_	_	0.25 ⁽³⁾	ns
tPHL	Ax to Bx, Bx to Ax				
tpzl	Switch Turn-On Delay	1.5	_	6.5	ns
t PZH	BE to Ax, Bx				
t PLZ	Switch Turn-Off Delay ⁽²⁾	1.5	_	5.5	ns
t PHZ	BE to Ax, Bx				

NOTES:

- 1. Minimums are guaranteed but not production tested.
- 2. This parameter is guaranteed but not production tested.
- 3. The time constant for the switch alone is of the order of 0.25ns at C_L = 50pF.
- 4. The bus switch contributes no propagation delay other than the RC delay of the ON resistance of the switch and the load capacitance. Since this time constant is much smaller than the rise and fall times of typical driving signals, it adds very little propagation delay to the system. Propagation delay of the bus switch, when used in a system, is determined by the driving circuit on the driving side of the switch and its interaction with the load on the driven side.

ORDERING INFORMATION



IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.