

R-IN32M3-CL

CC-Link IE

EtherNet/IP

PROFINET


**Highly Precise & Stable CPU Operation,
High speed real time response, low power consumption**

Introduction

R-IN32M3-CL is one of the Industrial Ethernet Communication LSI, which has R-IN32 Engine, CC-Link IE Field (Intelligent Device), Internal RAM and peripherals. R-IN32 Engine consists of 32bit RISC CPU "Cortex-M3 of ARM", Real-Time OS Accelerator (Hardware Real-Time OS[HW-RTOS]), Ethernet Accelerator and 1Gbit EtherMAC 802.3 with 2port switch. R-IN32M3-CL achieves the high-speed real time response and low power consumption for Industrial Ethernet Communication with R-IN32 Engine. Especially Real-Time OS Accelerator makes high speed task changing and high speed interrupt response. As a result, R-IN32M3-CL can realize highly precise and stable CPU operation.

Specification


- Cortex-M3 32bit RISC CPU (operating frequency : 100MHz)
- 10M/100M/1G EtherMAC (MII/GMII I/F)
- SRAM-I/F : 32bit (max) (Master / Slave)
- Non-Ethernet I/F (CAN, CSI, UART, etc...)
- 1.3MBytes Large size memory (RAM)
- Multiprotocol support
- GPIO : 96port(max)
- Power supply voltage : 1.0V±0.1V (Internal) 3.3V±0.3V (I/O)
- Operating temperature : -40~85°C



Application Image

R-IN32M3-CL can be adapted to the communication unit of all FA slave devices at the field network and the motion network. (● : Relevant parts)

- Recommend : PLC, Remote IO, CNC, AC Drive(Inverter), Robot, Servo drive, Servo Motor



Feature


R-IN32M3 achieves high-performance communication rather than conventional "CPU+ Software RTOS" (SW-RTOS) by using the both of "R-IN32 engine" and high-speed real time communication by the effect of Ethernet Accelerator.

On the other hand, R-IN32M3 achieves highly precise, low latency communication and low power consumption by effect of Real-Time OS Accelerator.

Effect of Ethernet Accelerator

(*) A result of measurement by our evaluation environment

TCP/IP Communication




Effects of Real-Time OS Accelerator

(*) A result of measurement by our evaluation environment


Quick Interrupt Response

Measurement operation time (Interrupt insert ~ Task Start)




Real-time multi task operation

Measurement of task change operation time.



Synchronous real time operation

Measurement the OS operation time operating various system calls



Low jitter Real-time OS operation

Protocols

R-IN32M3-CL corresponds the multi protocols as following not only Industrial Ethernet Protocols but also the conventional Open Network Protocols.


Industrial Ethernet Protocols :

CC-Link IE Field, EtherNet/IP, PROFINET RT, Modbus TCP(TBD), POWERLINK(TBD), FL-net(TBD)

Conventional Open Network Protocols :

CANopen, CC-Link, DeviceNet

Image of Protocol stack (Ethernet Protocol)



- ARM and Cortex are a trademark or a registered trademark of ARM Limited in EU and other countries.
- Ethernet is a registered trademark of Fuji Xerox Limited.
- IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers, Inc.
- CC-Link and CC-Link IE Field are a registered trademark of CC-Link Partner Association (CLPA).
- Additionally all product names and service names in this document are a trademark or a registered trademark which belongs to the respective owners.
- ™ mark and ® mark for companies trademark or registered trademark is omitted in this document.
- Real-Time OS Accelerator and Hardware Real-Time OS is based on Hardware Real-Time OS of "ARTESSO" made in KERNELON SILICON Inc.
- The product which is being handled by this document changes contents without notice and abolishes.
- Reprint reproduction on this document is forbidden without our consent by a document.