

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

## M37450T-ADF

Temporary Target Board for M37451RFS\*1

---

### Function

The M37450T-ADF is a temporary target board for PC4701 or PC4600 emulator systems designed for use with the M37451RFS\*1 emulator MCU. The M37450T-ADF provides the power supply, clock signal, RESET signal, CNVss signal and other minimum essential signals for the emulator MCU. One pin number of the standard pitch hole (80-pin) corresponds to one pin number of MCU.

\*1:Discontinued product


### Application

Use the M37450T-ADF only to debug programs using an emulator but no target.

### Dimensions

120.0(D)×100.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".



## M37450T-ADS

Temporary Target Board for M37451RSS\*<sup>1</sup>

### Function

The M37450T-ADS is a temporary target board for PC4701 or PC4600 emulator systems designed for use with the M37451RSS\*<sup>1</sup> emulator MCU. The M37450T-ADS provides the power supply, clock signal, RESET signal, CNVss signal, and other minimum essential signals for the emulator MCU. One pin number of the standard pitch hole (64-pin) corresponds to one pin number of MCU.

\*1:Discontinued product


### Application

Use the M37450T-ADS only to debug programs using an emulator but no target.

### Dimensions

120.0(D)×100.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".



## M37531T-ADS

Temporary Target Board for M37531RSS<sup>\*1</sup>, M37532RSS<sup>\*1</sup>, M37534RSS,  
M37536RSS<sup>\*1</sup>, M37540RSS, M37542RSS and M37544RSS

### Function

The M37531T-ADS is a temporary target board for PC4701 emulator systems designed for use with the M37531RSS<sup>\*1</sup>, M37532RSS<sup>\*1</sup>, MM37534RSS, M37536RSS<sup>\*1</sup>, M37540RSS, M37542RSS and M37544RSS emulator MCU. The M37531T-ADS provides the power supply, clock signal, RESET signal, CNVss signal, and other minimum essential signals for the emulator MCU. One pin number of the standard pitch hole (80-pin) corresponds to one pin number of MCU.

\*1:Discontinued product


### Application

Use the M37531T-ADS only to debug programs using an emulator but no target.

### Dimensions

115.0(D)×90.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".




## M38007T-ADS

Temporary Target Board for M38007RSS\*<sup>1</sup>, M38027RSS\*<sup>1</sup>, M38049RLSS, M38117RSS\*<sup>1</sup>, M38127RSS, M38807RSS\*<sup>1</sup>, M38817RSS\*<sup>1</sup> and M38887RSS\*<sup>1</sup>

### Function

The M38007T-ADS is a temporary target board for PC4701 or PC4600 emulator systems designed for use with the M38007RSS\*<sup>1</sup>, M38027RSS\*<sup>1</sup>, M38049RLSS, M38117RSS\*<sup>1</sup>, M38127RSS, M38807RSS\*<sup>1</sup>, M38817RSS\*<sup>1</sup> and M38887RSS\*<sup>1</sup> emulator MCU. The M38007T-ADS provides the power supply, clock signal, RESET signal, CNVss signal and other minimum essential signals for the emulator MCU. One pin number of the standard pitch hole (64-pin) corresponds to one pin number of MCU.

\*1:Discontinued product



### Application

Use the M38007T-ADS only to debug programs using an emulator but no target.

### Dimensions

120.0(D)×100.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".

## M38067T-ADF

Temporary Target Board for M38067RFS<sup>\*1</sup>, M38078RFS<sup>\*1</sup>,  
M38177RFS<sup>\*1</sup>, M38207RFS<sup>\*1</sup>, M38227RFS and M38867RFS

### Function

The M38067T-ADF is a temporary target board for PC4701 or PC4600 emulator systems designed for use with the M38067RFS<sup>\*1</sup>, M38078RFS<sup>\*1</sup>, M38177RFS<sup>\*1</sup>, M38207RFS<sup>\*1</sup>, M38227RFS and M38867RFS emulator MCU. The M38067T-ADF provides the power supply, clock signal, RESET signal, CNVss signal, and other minimum essential signals for the emulator MCU. One pin number of the standard pitch hole (80-pin) corresponds to one pin number of MCU.

\*1:Discontinued product


### Application

Use the M38067T-ADF only to debug programs using an emulator but no target.

### Dimensions

120.0(D)×100.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".



## M38187T-ADF

Temporary Target Board for M38187RFS\*<sup>1</sup>, M38197RFS\*<sup>1</sup>,  
M38257RFS\*<sup>1</sup>, M38267RLFS and M38277RFS\*<sup>1</sup>

### Function

The M38187T-ADF is a temporary target board for PC4701 or PC4600 emulator systems designed for use with the M38187RFS\*<sup>1</sup>, M38197RFS\*<sup>1</sup>, M38257RFS\*<sup>1</sup>, M38267RLFS and M38277RFS\*<sup>1</sup> emulator MCU. The M38187T-ADF provides the power supply, clock signal, RESET signal, CNVss signal, and other minimum essential signals for the emulator MCU. One pin number of the standard pitch hole (100-pin) corresponds to one pin number of MCU.

\*1:Discontinued product


### Application

Use the M38187T-ADF only to debug programs using an emulator but no target.

### Dimensions

120.0(D)×100.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".



## M38517T-ADS

Temporary Target Board for M38517RSS and M38507ARLSS

### Function

The M38517T-ADS is a temporary target board for PC4701 emulator systems designed for use with the M38517RSS and M38507ARLSS emulator MCUs. The M38517T-ADS provides the power supply, clock signal, RESET signal, CNVss signal, and other minimum essential signals for the emulator MCU. One pin number of the standard 2.54mm-pitch hole (42-pin) corresponds to one pin number of MCU.


### Application

Use the M38517T-ADS only to debug programs using an emulator but no target.

### Dimensions

115.0(D)×90.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".



## M38C29T-ADF

### Temporary Target Board for M38C29RLFS

#### Function

The M38C29T-ADF is a temporary target board for PC4701 emulator systems designed for use with the M38C29RLFS emulator MCU. The M38C29T-ADF provides the power supply, clock signal, RESET signal, CNVss signal, and other minimum essential signals for the emulator MCU. One pin number of the standard pitch hole (100-pin) corresponds to one pin number of MCU.


#### Application

Use the M38C29T-ADF only to debug programs using an emulator but no target.

#### Dimensions

115.0(D)×90.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".



## M38C89T-ADF

### Temporary Target Board for M38C89RLFS

#### Function

The M38C89T-ADF is a temporary target board for PC4701 emulator systems designed for use with the M38C89RLFS emulator MCU. The M38C89T-ADF provides the power supply, clock signal, RESET signal, and other minimum essential signals for the emulator MCU. Peripheral circuit pins of the MCU are output to the standard pitch hole.


This board has not only a socket for mounting an emulator MCU but also the 2 foot patterns below.

- Foot pattern for M38C89MF-xxxFP/M38C89EFP (IC socket and parts for peripheral circuits are not mounted.)
- Foot pattern for LCD bias (Parts such as a capacitor for an LCD bias circuit are not mounted.)

#### Application

The M38C89T-ADF is a temporary target board for 38C8 group. You connect for target system to 2.54mm-pitch connector on M38C89T-ADF when you debug M38C8 group MCUs. Use the M38C89T-ADF only to develop programs using an emulator but no target system because the M38C89T-ADF provides the power supply, clock signal, RESET signal, and other minimum essential signals for the emulator MCU.

By mounting a socket (IC51-1444-1354-18 made by Yamaichi Electronics Co., Ltd.) for M38C89MF-xxxFP/M38C89EFP and a part for oscillation circuit, the M38C89T-ADF can be used to evaluate the program of the M38C89MF-xxxFP/M38C89EFP.



#### Dimensions

160.0(D)×220.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".

## M38K29T-ADF

Temporary Target Board for M38K09RFS, M38K29RFS

### Function

The M38K29T-ADF is a temporary target board for PC4701 emulator systems designed for use with the M38K09RFS or M38K29RFS emulator MCU. The M38K29T-ADF provides the power supply, clock signal, RESET signal, CNVss signal, and other minimum essential signals for the emulator MCU. One pin number of the standard pitch hole (100-pin) corresponds to one pin number of MCU. This board has the pattern of a simplified USB peripheral circuit for evaluation the USB function of MCU.

### Application

Use the M38K29T-ADF only to debug programs using an emulator but no target.

### Dimensions

115.0(D)×90.0(W)mm

[Ordering Information] See Appendix H "Ordering Information".

