









μ PD78F0361,78F0362,78F0363
IOL vs VOL - VDD(P27)
(Ta = -40°C)




μ PD78F0361,78F0362,78F0363
IOL vs VOL - VDD(P124)
(Ta = -40°C)












μ PD78F0361,78F0362,78F0363
IOL vs VOL - VDD(P24)
(Ta = 25°C)




μ PD78F0361,78F0362,78F0363
IOL vs VOL - VDD(P124)
(Ta = 25°C)





μ PD78F0361,78F0362,78F0363
IOL vs VOL - VDD(P27)
(Ta = 85°C)



μ PD78F0361,78F0362,78F0363
IOL vs VOL - VDD(P124)
(Ta = 85°C)

