

General Description

The D7PRO ASIC is an MPEG-2/H.264 contribution encoder/decoder solution with integrated high-speed DDR3 for professional broadcast applications. The D7PRO addresses all contribution market needs from legacy MPEG-2 4:2:0/4:2:2 8-bit to H.264 4:2:0/4:2:2 10-bit to 1080p60 encoding and decoding applications. With over a decade of video quality leadership and technology innovation, the D7PRO is the most advanced encoding and decoding solution for video backhauling, events, and DSNG. The D7PRO offers a complete video-audio-ancillary data-mux integrated solution enabling high video quality and low latency at low bit rates for video encoding and decoding.

Applications

- Events and content origination
- Digital signal news gathering
- Video backhaul
- Ingest and mezzanine

Features

- Enables low latency contribution encoder and decoder applications with production video quality
- MPEG-2 Main and High Profiles
- H.264 CBP to High 4:2:2 Profiles
- Support for AVC-I 50/100, SD/HD, 4:2:0/4:2:2, 8/10-bit
- Dolby®, MPEG-1 Layer II, AAC Audio
- Ancillary data processing
- Advanced video processing
- Market-proven solution across wide range of networks and interoperability with legacy encoders or decoders

Ordering Information

Part	Usage	TDP	Pin-Package
DX8773	Encoder	10 W	FCBGA 896pin 31x31mm
DX9773	Decoder	11 W	FCBGA 896pin 31x31mm

For price, delivery schedules, and to place orders, please contact IDT: www.IDT.com/go/sales

Device Diagram




Figure 1: Device diagram

**Corporate Headquarters**

6024 Silver Creek Valley Road
San Jose, CA 95138

www.IDT.com

Sales

1-800-345-7015 or 408-284-8200

Fax: 408-284-2775

www.IDT.com/go/sales

Tech Support

www.IDT.com/go/support

DISCLAIMER Integrated Device Technology, Inc. (IDT) and its affiliated companies (herein referred to as "IDT") reserve the right to modify the products and/or specifications described herein at any time, without notice, at IDT's sole discretion. Performance specifications and operating parameters of the described products are determined in an independent state and are not guaranteed to perform the same way when installed in customer products. The information contained herein is provided without representation or warranty of any kind, whether express or implied, including, but not limited to, the suitability of IDT's products for any particular purpose, an implied warranty of merchantability, or non-infringement of the intellectual property rights of others. This document is presented only as a guide and does not convey any license under intellectual property rights of IDT or any third parties.

IDT's products are not intended for use in applications involving extreme environmental conditions or in life support systems or similar devices where the failure or malfunction of an IDT product can be reasonably expected to significantly affect the health or safety of users. Anyone using an IDT product in such a manner does so at their own risk, absent an express, written agreement by IDT.

Integrated Device Technology, IDT and the IDT logo are trademarks or registered trademarks of IDT and its subsidiaries in the United States and other countries. Other trademarks used herein are the property of IDT or their respective third party owners. For datasheet type definitions and a glossary of common terms, visit www.idt.com/go/glossary. All contents of this document are copyright of Integrated Device Technology, Inc. All rights reserved.