

Customer Notification

78K0R/Fx3

16-Bit Single-Chip Microcontroller

Injected Current Specification

78K0R/FB3 Series

78K0R/FC3 Series

78K0R/FE3 Series

78K0R/FF3 Series

78K0R/FG3 Series

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.

"Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.

10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority- owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

Table of Contents

A) Related Products.....	5
B) Electrical Specification for Injected Current	7
C) The influence on an adjacent pin caused by the Injected Current.....	9
D) Valid Specification.....	10
E) Revision History	11

A) Related Products

List of related products:

78K0R/FB3

Non A-Version Products

μPD78F1804MCA, μPD78F1805MCA, μPD78F1806MCA, μPD78F1807MCA,
μPD78F1804MCA2, μPD78F1805MCA2, μPD78F1806MCA2, μPD78F1807MCA2

A-Version Products

μPD78F1804AMCA, μPD78F1805AMCA, μPD78F1806AMCA, μPD78F1807AMCA,
μPD78F1804AMCA2, μPD78F1805AMCA2, μPD78F1806AMCA2, μPD78F1807AMCA2

78K0R/FC3

Non A-Version Products

μPD78F1808K8A, μPD78F1809K8A, μPD78F1810K8A, μPD78F1811K8A,
μPD78F1808K8A2, μPD78F1809K8A2, μPD78F1810K8A2, μPD78F1811K8A2

A-Version Products

μPD78F1808AK8A, μPD78F1809AK8A, μPD78F1810AK8A, μPD78F1811AK8A,
μPD78F1808AK8A2, μPD78F1809AK8A2, μPD78F1810AK8A2, μPD78F1811AK8A2

Non A-version Products

μPD78F1812GAA, μPD78F1813GAA, μPD78F1814GAA, μPD78F1815GAA, μPD78F1816GAA,
μPD78F1817GAA, μPD78F1826GAA, μPD78F1827GAA, μPD78F1828GAA, μPD78F1829GAA,
μPD78F1830GAA,
μPD78F1812GAA2, μPD78F1813GAA2, μPD78F1814GAA2, μPD78F1815GAA2, μPD78F1816GAA2,
μPD78F1817GAA2, μPD78F1826GAA2, μPD78F1827GAA2, μPD78F1828GAA2, μPD78F1829GAA2,
μPD78F1830GAA2

A-Version Products

μPD78F1812AGAA, μPD78F1813AGAA, μPD78F1814AGAA, μPD78F1815AGAA,
μPD78F1816AGAA, μPD78F1817AGAA, μPD78F1826AGAA, μPD78F1827AGAA,
μPD78F1828AGAA, μPD78F1829AGAA, μPD78F1830AGAA, μPD78F1812AGAA2,
μPD78F1813AGAA2, μPD78F1814AGAA2, μPD78F1815AGAA2, μPD78F1816AGAA2,
μPD78F1817AGAA2, μPD78F1826AGAA2, μPD78F1827AGAA2, μPD78F1828AGAA2,
μPD78F1829AGAA2, μPD78F1830AGAA2

Non A-version Products

μPD78F1812K8A, μPD78F1813K8A, μPD78F1814K8A, μPD78F1815K8A, μPD78F1816K8A,
μPD78F1817K8A, μPD78F1826K8A, μPD78F1827K8A, μPD78F1828K8A, μPD78F1829K8A,
μPD78F1830K8A
μPD78F1812K8A2, μPD78F1813K8A2, μPD78F1814K8A2, μPD78F1815K8A2, μPD78F1816K8A2,
μPD78F1817K8A2, μPD78F1826K8A2, μPD78F1827K8A2, μPD78F1828K8A2, μPD78F1829K8A2,
μPD78F1830K8A2

A-Version Products

μPD78F1812AK8A, μPD78F1813AK8A, μPD78F1814AK8A, μPD78F1815AK8A, μPD78F1816AK8A,
μPD78F1817AK8A, μPD78F1826AK8A, μPD78F1827AK8A, μPD78F1828AK8A, μPD78F1829AK8A,
μPD78F1830AK8A
μPD78F1812AK8A2, μPD78F1813AK8A2, μPD78F1814AK8A2, μPD78F1815AK8A2,
μPD78F1816AK8A2, μPD78F1817AK8A2, μPD78F1826AK8A2, μPD78F1827AK8A2,
μPD78F1828AK8A2, μPD78F1829AK8A2, μPD78F1830AK8A2

78K0R/FE3

Non A-Version Products

μPD78F1818GBA, μPD78F1819GBA, μPD78F1820GBA, μPD78F1821GBA, μPD78F1822GBA,
μPD78F1831GBA, μPD78F1832GBA, μPD78F1833GBA, μPD78F1834GBA, μPD78F1835GBA,
μPD78F1818GBA2, μPD78F1819GBA2, μPD78F1820GBA2, μPD78F1821GBA2, μPD78F1822GBA2,
μPD78F1831GBA2, μPD78F1832GBA2, μPD78F1833GBA2, μPD78F1834GBA2, μPD78F1835GBA2

A-Version Products

μPD78F1818AGBA, μPD78F1819AGBA, μPD78F1820AGBA, μPD78F1821AGBA,
μPD78F1822AGBA, μPD78F1831AGBA, μPD78F1832AGBA, μPD78F1833AGBA,
μPD78F1834AGBA, μPD78F1835AGBA,
μPD78F1818AGBA2, μPD78F1819AGBA2, μPD78F1820AGBA2, μPD78F1821AGBA2,
μPD78F1822AGBA2, μPD78F1831AGBA2, μPD78F1832AGBA2, μPD78F1833AGBA2,
μPD78F1834AGBA2, μPD78F1835AGBA2

78K0R/FF3

Non A-Version Products

μPD78F1823GKA, μPD78F1824GKA, μPD78F1825GKA, μPD78F1836GKA, μPD78F1837GKA,
μPD78F1838GKA, μPD78F1839GKA, μPD78F1840GKA, μPD78F1823GKA2, μPD78F1824GKA2,
μPD78F1825GKA2, μPD78F1836GKA2, μPD78F1837GKA2, μPD78F1838GKA2, μPD78F1839GKA2,
μPD78F1840GKA2

A-Version Products

μPD78F1823AGKA, μPD78F1824AGKA, μPD78F1825AGKA, μPD78F1836AGKA,
μPD78F1837AGKA, μPD78F1838AGKA, μPD78F1839AGKA, μPD78F1840AGKA
μPD78F1823AGKA2, μPD78F1824AGKA2, μPD78F1825AGKA2, μPD78F1836AGKA2,
μPD78F1837AGKA2, μPD78F1838AGKA2, μPD78F1839AGKA2, μPD78F1840AGKA2

78K0R/FG3

Non A-Version Products

μPD78F1841GCA, μPD78F1842GCA, μPD78F1843GCA, μPD78F1844GCA, μPD78F1845GCA,
μPD78F1841GCA2, μPD78F1842GCA2, μPD78F1843GCA2, μPD78F1844GCA2,
μPD78F1845GCA2

A-Version Products

μPD78F1841AGCA, μPD78F1842AGCA, μPD78F1843AGCA, μPD78F1844AGCA,
μPD78F1845AGCA, μPD78F1841AGCA2, μPD78F1842AGCA2, μPD78F1843AGCA2,
μPD78F1844AGCA2, μPD78F1845AGCA2

B) Electrical Specification for Injected Current

(Ta = -40 to +125 °C, V_{DD}=EV_{DD0}=EV_{DD1}=AV_{REF}= 2.7V to 5.5V, V_{SS}=EV_{SS0}= EV_{SS1}=AV_{SS}=0V) (Notes 1)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Pos. Injected Current V _{IN} > V _{DD} (Peak) (Note 3, 5)	I _{INJP}	Per Digital input pin			5	mA
		Per Analog input pin (Note 2)			2	mA
Neg. Injected Current V _{IN} < V _{SS} (Peak) (Note 5)	I _{INJN}	Per Digital input pin			-5	mA
		Per Analog input pin (Note 2)			-0.15	mA
Sum of all Positive Injected Currents (Peak) (Note 3, 4)	Σ I _{INJP D}	Sum for all Digital input pins			20	mA
	Σ I _{INJP A}	Sum for all Analog input pins (Note 2)			4	mA
Sum of all Negative Injected Currents (Peak) (Note 4)	Σ I _{INJN D}	Sum for all Digital input pins			-20	mA
	Σ I _{INJN A}	Sum for all Analog input pins (Note 2)			-0.6	mA
Total Sum of all Injected Currents (Positive and Negative) (Peak) (Note 3, 4)	Σ I _{INJP D} + Σ I _{INJN D}	Total Sum for all Digital input pins			20	mA
	Σ I _{INJP A} + Σ I _{INJN A}	Total Sum for all Analog input pins (Note 2)			4	mA
Pos. Injected Current (Digital Input) V _{IN} > V _{DD} (Average) (Note 3, 6, 7)	I _{INJPD AVG}	Per Digital input pin			0.4	mA
	Σ I _{INJPD AVG}	Total Sum for all Digital input pins			4	mA
Pos. Injected Current (Analog Input) V _{IN} > V _{DD} (Average) (Note 6, 7)	I _{INJPA AVG}	Per Analog input pin (Note 2)			0.15	mA
	Σ I _{INJPA AVG}	Total Sum for all Analog input pins (Note 2)			1	mA

Note 1: Only 78K0R/FG3(100pin) has EV_{DD1}, EV_{SS1}. For all other products EV_{DD0} is EV_{DD} and EV_{SS0} is EV_{SS}

Note 2: Analog pins for the product are as follows

Series	Analog input port			
78K0R/Fx3	78K0R/FB3	30 pin	MC	P80/ANI00-P87/ANI07
		32 pin	K8	P80/ANI00-P85/ANI05
	78K0R/FC3	40 pin	K8	P80/ANI00-P87/ANI07
		48 pin	GA	P80/ANI00-P87/ANI07
	K8		P90/ANI08-P92/ANI10	
	78K0R/FE3	64 pin	GB	P80/ANI00-P87/ANI07 P90/ANI08-P96/ANI14
	78K0R/FF3	80 pin	GK	P80/ANI00-P87/ANI07 P90/ANI08-P97/ANI15
	78K0R/FG3	100 pin	GC	P80/ANI00-P87/ANI07 P90/ANI08-P97/ANI15 P100/ANI16-P107/ANI23

Note 3: The injection current specification ($V_{IN} > V_{DD} = I_{INJP}$) is not valid for the N-ch Open Drain ports (P60 – P63) and not for P121 to P124, because these port pins don't have the protection Diode to V_{DD} .

Note 4: If the Sum of the Injected Currents specifications (Peak values) are exceed even momentarily, there is a possibility to destroy the device.


Note 5: If any of the above Injected Current specifications (Peak values) are exceeded even momentarily, there is a possibility to destroy the device.

Note 6: When the Injected Current value exceeds the allowed Injected Current value (Average value), the electrical characteristics can't be specified.

Note 7: If the allowed Injected Current value (Average value) is exceeded permanently, the product life time could be influenced.

However, when the injected current exceed the Average value but is **still below** the Peak value the product life time will not be influenced if the injected current will follow the example as given here:

Example for an Analog Input:



Requirement :

$$I_{INJP A AVG} \leq (I_{INJP A (PEAK)} \times t1) + (I_{INJP A} \times t2) / (t1 + t2) \leq 150uA$$

$$I_{INJP A AVG} \leq (2mA \times t1) + (100uA \times t2) / (t1 + t2) \leq 150uA$$

Remark :

The above mentioned example could also be used for the digital input pins with $I_{INJPD AVG} \leq 400uA$

Cautions:

1. An Injected Current conditions occur, if the standard operating conditions are exceeded.
 Example: The input voltage on any pin exceeds the specified range:
 $V_{IN} > EV_{DD} / V_{DD} / AV_{REF} + 0.3 V \rightarrow (I_{INJP} > 0)$ or
 $V_{IN} < EV_{SS} / V_{SS} / AV_{SS} - 0.3 V \rightarrow (I_{INJN} < 0)$.
 I_{INJP}, I_{INJN} = Injected current value that doesn't influence to the operation of the device.
2. The supply voltages must always remain within the specified limits.
3. A proper operation is not specified if an Injected Current occurs on the functional pins such as P121/X1, P122/X2/EXCLK, P123, P124/EXCLKS, P120/EXLVI/INTP0/TI11/TO11, RESET and FLMD0.
4. The above specifications are not tested in the outgoing inspection, but they are specified based on the design rules and the device characterization.

C) The influence on an adjacent pin caused by the Injected Current

($T_a = -40$ to $+125$ °C, $V_{DD}=EV_{DD0}=EV_{DD1}=AV_{REF}= 2.7V$ to $5.5V$, $V_{SS}=EV_{SS0}= EV_{SS1}=AV_{SS}=0V$) (Notes 1)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Leakage current coupling factor for a Positive Injected Current	K_{INJP}	Digital input pins			5×10^{-3}	-
		Analog input pins (Note 2)			1×10^{-4}	-
Leakage current coupling factor for a Negative Injected Current	K_{INJN}	Digital input pins (Except P121 to P124)			1×10^{-2}	-
		Digital input pins (P121 to P124)			3.8×10^{-2}	-
		Analog input pins (Note 2)			3.2×10^{-3}	-

Note 1: Only 78K0R/FG3(100pin) has EV_{DD1} , EV_{SS1} . For all other products EV_{DD0} is EV_{DD} and EV_{SS0} is EV_{SS}

Note 2: Analog pins for the product are as follows

Series				Analog input port
78K0R/Fx3	78K0R/FB3	30 pin	MC	P80/ANI00-P87/ANI07
		32 pin	K8	P80/ANI00-P85/ANI05
	78K0R/FC3	40 pin	K8	P80/ANI00-P87/ANI07
		48 pin	GA	P80/ANI00-P87/ANI07
	K8		P90/ANI08-P92/ANI10	
	78K0R/FE3	64 pin	GB	P80/ANI00-P87/ANI07 P90/ANI08-P96/ANI14
	78K0R/FF3	80 pin	GK	P80/ANI00-P87/ANI07 P90/ANI08-P97/ANI15
	78K0R/FG3	100 pin	GC	P80/ANI00-P87/ANI07 P90/ANI08-P97/ANI15 P100/ANI16-P107/ANI23

Cautions:

1. An Injected Current through a pin will cause a certain error current in the adjacent pins. This error current must be added to the respective leakage current (I_{LH} / I_{LL}) of the adjacent pins.
2. The amount of error leakage current depends on the Injected Current and it is defined by the coupling factor K_{INJ} .
3. The total leakage current through a pin is $|I_{Ltotal}| = |I_{LH} / I_{LL}| + (|I_{INJn}| \times K_{INJn})$
4. The additional error current may affect the input voltage on the analog inputs.
5. These specifications are not tested in the outgoing inspection, but it is specified based on the design rules and the device characterization.

D) Valid Specification

Item	Date published	Document No.	Document Title
1	July 2011 or later	R01UH0007EJ0500 or later	User's Manual: Hardware

E) Revision History

Item	Date published	Document No.	Comment
1	January 30 , 2012	R01TU0031ED0100	1 st Release

