Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.



ROM number	

QZROM PROGRAMMING CONFIRMATION FORM 8BIT SINGLE-CHIP MICROCOMPUTER M38D29GF-XXXFP/HP RENESAS TECHNOLOGY

	Date:			
	Section head signature	Supervisor signature		
<u>e</u>	Signature	Signature		
Receipt				
₾				

Note: Please fill in all items marked*.

*	Customer -	Company		TEL	uance nature	Supervisor
		name		()		
		Date issued	Date:		Iss sigis	

×1. Confirmation

Specify the name of the product being ordered.

The submitted floppy disk must be 3.5-inch 2HD type and DOS/V format if this order is performed by a floppy disk. And the number of the mask files must be 1 in one floppy disk.

Microcomputer name:	□M38D29GF-XXXFP	□M38D29GF-XXXHP	
File code		(hexadecimal notation)	
Mask file name		.MSK (equal or less than eight characters)	

Note: Write data to only ROM data area (addresses 108016 to FFDA16, FFDC16 to FFFD16).

ROM option data area: Addresses 1016

Notes (RENESAS → Customer)

1 : ROM data confirmation request

QzROM programming will be processed based on the mask file generated by the mask file generating utility. Only in case when ROM data programmed in the actual mass produced product differs from that of above mentioned mask file, RENESAS takes the responsibility. There is no Engineering Sample, thus please confirm the ROM data at the receipt of the Initial product delivery.

Should you find any problem, please return immediately. Two weeks without technical error feedback towards RENESAS will automatically be regarded as acceptance of products.

2: ROM option("MASK option" written in the mask file converter MM)

Either of the following data should be set to the ROM option data address (10₁₆) of the mask file you have ordered. When you don't protect the ROM data, a third party can read out it.

When the ROM data of protect area1(108016~EFFF16) is protected

When the ROM data of all area (108016~FFFD16) is protected

When ROM data is not protected

FE₁₆ Address 10₁₆

00₁₆ Address 10₁₆

FF₁₆ Address 10₁₆

If you set except the above data or nothing at the ROM option data address (10₁₆), We can't generate the ROM data. Then we request to submit the data again.

When Renesas ships QzROM write products, we write the data in ROM option address (1016) to the actual ROM code protect address (FFDB16).

Therefore, set FF16 to address FFDB16 in ROM data regardless of the presence or absence of a protect.


When data other than FF16 is set, we may ask that the ROM data be submitted again.

3: Mark specification

You can appoint the mark by the mark specification form. Without submitting the mark specification form, your mark will be a standard mark. Please fill out the 64P6U MARK SPECIFICATION FORM for the M38D29GF-XXXFP, the 64P6Q MARK SPECIFICATION FORM for the M38D29GF-XXXHP, and attach it when you submit the QzROM PROGRAMMING CONFIRMATION FORM. We can't deal with special font marking(customer's trademark etc.) in QzROM microcomputer.

QZROM PROGRAMMING CONFIRMATION FORM 8BIT SINGLE-CHIP MICROCOMPUTER M38D29GF-XXXFP/HP **RENESAS TECHNOLOGY**

ROM-Protection-Area



ucts you

*2. Usage conditions
For our reference of new products, please reply to the following questions about the usage of the prod ordered.
(1) Which operation source main clock do you use? Ceramic resonator External clock input Quartz-crystal oscillation Other(On-chip oscillator
(2) Which operation source sub clock do you use?
Quartz-crystal oscillation ———— At what frequency?
☐ Other() kHz
(3) What is the voltage of power supply (Vcc) you use? Typ.= V Min.= V Max.= V
(4) What is the ambient temperature you use? Typ.= C Min.= C Max.= C
(5) On which condition will you use OSCSEL? ☐ OSCSEL=H ☐ OSCSEL=L
(6) Which main clock (XIN-XOUT) division ratio mode will you use?
\square In frequency/2 mode $(f(\Phi)=f(X_{IN})/2)$ \square In frequency/4 mode $(f(\Phi)=f(X_{IN})/4)$
\square In frequency/8 mode $(f(\Phi)=f(X_{IN})/8)$
(7) Which function will you use the pins P61/Xcin and P62/Xcou⊤ as P61 and P62, or Xcin and Xcou⊤? ☐ P61,P62 ☐ Xcin,Xcou⊤
(2/3)

QZROM PROGRAMMING CONFIRMATION FORM 8BIT SINGLE-CHIP MICROCOMPUTER M38D29GF-XXXFP/HP RENESAS TECHNOLOGY

(8) On which cond	dition will you use LCD dri	ive control circuit?			
LCD drive cor	ntrol circuit	☐ Use ☐ No	ot use		
Duty ratio		□4 □3 □	2		
Range of pow	ver source voltage(VL3)	Min.=	V Max.=	V	
Number of se	gment pins used				
Dividing resis	tor for LCD power	Internal resistor	☐ External r	esistor	
			Resistor v	/alue/piece=	kΩ/piece
LCD drive tim	ning	TypeA	□ТуреВ		
(9) Which timer mo	ode will vou use?				
Timer X [e output mode	GBT output mode	PWM mode	
[Event counter mode	☐ Pulse width me	•	_	
Timer Y [_	od Measurement Mo	_		
	☐ Pulse width HL continu				
Timer 3	☐ Timer mode ☐ PWN	· <u> </u>			
Timer 4	☐ Timer mode ☐ PWN	M mode ☐ Not us	e		
(10) Which serial I/	'O will you use?				
Serial I/O1	☐ Clock synchronous	□UART □Not	use		
Serial I/O2 [☐ Clock synchronous	□UART □Not	use		
(11) On which cond	dition will you use A/D cor	verter?			
10bit or 8bit c	onversion switch 8	bitA/D □10bitA	/D Not use		
A/D conversion	on clock	SOURCE/2	SOURCE/8	ON-chip oscillator	
ADKEY [☐Use ☐Not use				
(12) On which cond	dition will you use Watchd	log timer?			
Count source		ip oscillator ☐Not	use		
	e ROM correction function		(1 1 5011)		
ROM correction	on function Use(Ju	ımp to RAM) ☐Us	e(Jump to ROM)	☐ Not use	
Thank you for c	cooperation.				
*3. Comments					