

MOSFET, IGBT, FRD

Power Discrete Bare Die Products Reliability

Introduction

This document explains the reliability of Renesas power discrete products shipped as bare die.

Contents

1. Bare Die Product Reliability.....	2
1.1 Approach to Quality.....	2
1.2 Bare Die Product Quality Assurance.....	2
1.2.1 Level: KGD (Known Good Die).....	2
1.2.2 Level 2: KTD (Known Tested Die).....	3
1.2.3 Level 3: PD (Probed Die).....	3
1.3 Power Discrete Bare Die Product Reliability.....	4
1.4 Reliability Testing.....	5
Revision History.....	6

1. Bare Die Product Reliability

1.1 Approach to Quality

In accordance with the quality policy stated in Figure 1-1, Renesas Electronics has established a quality assurance system based on the ISO 9001 and ISO/TS 16949 standards. Renesas is developing consistent quality assurance and quality control across all stages from product planning to after-sales services, based on “built-in quality” that is backed up with reliability technologies. Renesas has always placed great emphasis on maintaining and improving levels of quality and reliability. From the development to the delivery of a products, Renesas implements quality control and reliability verification from the three standpoints of “quality control and reliability verification in design”, “quality control in production”, and “quality assurance of product”. All Renesas parties uphold the basic principle that quality comes first. To this end, they are concerned with the achievement of quality levels that satisfy customer expectations.



Figure 1-1 Renesas Electronics Quality Policy

1.2 Bare Die Product Quality Assurance

Guaranteeing the quality of bare die presumes equivalency with packaged products; such equivalency across all semiconductor devices is difficult given current technological and cost considerations.

Therefore, the quality level of bare die is classified into three levels in accordance with JEITA EDR-4703A and is based on four criteria: visual, electrical characteristics, early failures, and long-term reliability. The three levels, Level 1: Known Good Die (KGD), Level 2: Known Tested Die (KTD), and Level 3: Probed Die (PD). Are described in detail below. Table 1-1 shows an overview of the quality assurance scope at each level, including customers and end users.

Renesas power discrete products are classified as Level 3/Probed Die, unless special delivery specifications have been agreed upon.

1.2.1 Level: KGD (Known Good Die)

(1) Visual

A full visual inspection is conducted. Definitions of defects and defective products, inspection items, inspection methods, etc. are stipulated in an individual specification, with user agreement as stipulated in the delivery specifications.

(2) Electrical characteristics

Probing tests are conducted with the aim of meeting the characteristics equivalent to those of packaged products that have passed the final special characteristics inspection. Specific measurement items and standards must be stipulated in an individual specification, with user agreement as stipulated in the delivery specifications.

(3) Characteristics results after semiconductor user implementation

Early defects (including defects resulting from the wafer process that become apparent after user mounting, such as aging on boards and equipment) equivalent to the quality rate of packaged products are guaranteed.

Electrical characteristic defects cannot be guaranteed after mounting because AC characteristics are affected by the mounting configuration itself.

(4) Early failures

The early failure rate of the bare die resulting from the wafer process should be equivalent to that of the packaged products. This excludes any failure modes caused by package assembly or mounting carried out by the user. If the specified level is not met, additional screening processes, including burn-in, will be applied in the same way they are for normal packaged products to ensure the required quality level is achieved.

(5) Long-term reliability

The failure rate of the bare die resulting from the wafer process should be equivalent to that of packaged products. (Failure modes caused by package assembly or mounting carried out by the user are excluded.)

1.2.2 Level 2: KTD (Known Tested Die)**(1) Visual**

The same inspection as for Level 1/KGD is conducted.

(2) Electrical characteristics

The same tests as for Level 1/KGD are conducted.

(3) Characteristics results after semiconductor user implementation

- Early defects:
Early defects resulting from the wafer process are guaranteed to be equivalent to those of packaged products. However, defects that become apparent after user mounting, such as aging on boards and equipment, are not covered by the guarantee.
- Electrical characteristic defects:
Electrical characteristics cannot be guaranteed after mounting because AC characteristics are affected by the mounting configuration itself.

(4) Early failures

Not covered by the guarantee.

(5) Long-term reliability

Not covered by the guarantee.

1.2.3 Level 3: PD (Probed Die)**(1) Visual**

Sampling inspection is conducted.

(2) Electrical characteristics

Probing tests are conducted with the aim of meeting the characteristics equivalent to packaged products that have passed the final special characteristics inspection. The specific measurement items and standards are stipulated in an individual specification, with user agreement as stipulated in the delivery specifications.

(3) Characteristics results after semiconductor user implementation

Not covered by the guarantee.

(4) Early failures

Not covered by the guarantee.

(5) Long-term reliability

Not covered by the guarantee.

Table 1-1 Quality Assurance Application Overview

	Process	Level 1/KGD	Level 2/KTD	Level 3/PD
Semiconductor Manufacturers	Wafer	Products that have completed the wafer process before characteristics inspection.	Same as Level 1	Same as Level 1
	Probing characteristics inspection	Non-defective products selected based on the same criteria as final inspection of packaged products. Details are stipulated in individual specifications.	Same as Level 1	Non-defective products selected based on some of the final inspection criteria for packaged products. Details are stipulated in individual specifications.
	Visual inspection	A full visual inspection is conducted. Details are stipulated in individual specifications.	Same as Level 1	Sampling inspection is conducted. Details are stipulated in individual specifications.
	Shipment	Shipping format is stipulated in individual specifications.	Same as Level 1	Same as Level 1
Semiconductor Users	Acceptance inspection process	Defined in individual specifications. Visual and electrical characteristics are covered by guarantee.	Same as Level 1	Same as Level 1
	Mounting process	Defects caused by mounting are not covered by guarantee.	Same as Level 1	Same as Level 1
	Characteristics inspection process	<ul style="list-style-type: none"> Early defects resulting from the wafer process (including defects that become apparent, such as in-process aging) should be equivalent to those of packaged products. However, failures due to mounting are excluded. Electrical characteristics are not covered by guarantee. 	<ul style="list-style-type: none"> Early defects resulting from the wafer process should be equivalent to those of packaged products. However, defects that become apparent due to in-process aging or mounting are excluded. Electrical characteristics are not covered by guarantee. 	Not covered by guarantee.
Market	Early failures	Failures resulting from the wafer process should be equivalent to those of packaged products.	Not covered by guarantee.	Same as Level 2
	Long-term reliability	Failures resulting from the wafer process should be equivalent to those of packaged products.	Not covered by guarantee.	Same as Level 2

1.3 Power Discrete Bare Die Product Reliability

The reliability of Renesas power discrete bare die products is tested under the conditions stipulated in the reliability documentation. However, the reliability of a bare die product in its fully assembled state depends not only on chip-specific factors, but also on storage conditions, assembly conditions, sealing conditions, etc., so it is difficult to guarantee the reliability of the chip alone. We highly recommend that customers conduct sufficient verification in conditions reflecting the actual application.

1.4 Reliability Testing

Reliability testing is a series of laboratory tests carried out under known stress conditions to evaluate the lifetime of a device or system. Reliability tests are performed to ensure that semiconductor devices maintain the performance and functions throughout their life.

These reliability tests aim to simulate or accelerate by the stresses that the semiconductor device may encounter during all phases of its life, including mounting, aging, field installation and operation.

Reliability tests are defined individually in the specifications for each product. Table 1-2 shows an example of a reliability test for automotive quality bare die product.

Table 1-2 Automotive Quality Bare Die Product Reliability Testing Example

Reliability Testing Example (IGBT)				
No.	Test Item	Symbol	Test Conditions	Test Qty.
1	High Temperature Reverse Bias	HTRB	T _j = 175 °C, VCES = Maximum rating, 1000 h	3 lots 231 pcs
2	High Temperature Gate Bias	HTGB	T _j = 175 °C, VGES = 30 V, 1000 h	3 lots 231 pcs
3	ESD Characterization	HBM	C = 100 pF, R = 1.5 kΩ, ±2000 V	1 lot 30 pcs
4	Estimated Failure Rate	Estimated failure rate: 5 Fit or less T _j = 55 °C, Ea = 0.8 eV, C.L. = 60 %		

Reliability Testing Example (FRD)				
No.	Test Item	Symbol	Test Conditions	Test Qty.
1	High Temperature Reverse Bias	HTRB	T _j = 175 °C, VCES = Maximum rating, 1000 h	3 lots 231 pcs
2	ESD Characterization	HBM	C = 100 pF, R = 1.5 kΩ, ±2000 V	1 lot 30 pcs

Revision History

Rev.	Date	Description	
		Page	Summary
1.00	Nov.11.2024	-	First edition

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 October 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan

www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:

www.renesas.com/contact/.