

BCR16CS-16LB

800V-16A-Triac Medium Power Use R07DS0226EJ0200 Rev.2.00 Oct 19, 2015

Features

I_{T (RMS)}: 16 A
 V_{DRM}: 800 V

• I_{FGTI}, I_{RGTI}, I_{RGT III}: 30 mA

- The product guaranteed maximum junction temperature of 150°C
- Non-Insulated Type
- Planar Passivation Type

Outline

RENESAS Package code: PRSS0004AE-B (Package name: LDPAK(S)-(1))





- 1. T₁ Terminal
- 2. T₂ Terminal
- 3. Gate Terminal
- 4. T₂ Terminal

RENESAS Package code: PRSS0004AS-A (Package name: TO-263)



RENESAS Package code: PRSS0004AR-A (Package name: TO-262)



Applications

Contactless AC switch, light dimmer, electronic flasher unit, hair drier, control of household equipment such as TV sets, stereo systems, refrigerator, washing machine, infrared kotatsu, carpet, electric fan, solenoid driver, small motor control, solid state relay, copying machine, electric tool, electric heater control, and other general purpose control applications

Maximum Ratings

Parameter	Symbol	Voltage class	Unit	
Farameter	Syllibol	16		
Repetitive peak off-state voltageNote1	V_{DRM}	800	V	
Non-repetitive peak off-state voltage ^{Note1}	V _{DSM}	960	V	

Parameter	Symbol	Ratings	Unit	Conditions
RMS on-state current	I _T (RMS)	16	А	Commercial frequency, sine full wave 360° conduction, Tc = 125°C ^{Note3}
Surge on-state current	Ітѕм	160	А	60Hzsinewave 1 full cycle, peak value, non-repetitive
I ² t for fusing	l ² t	106.5	A ² s	Value corresponding to 1 cycle of half wave 60Hz, surge on-state current
Peak gate power dissipation	P _{GM}	5	W	
Average gate power dissipation	P _{G (AV)}	0.5	W	
Peak gate voltage	V_{GM}	10	V	
Peak gate current	I _{GM}	2	Α	
Junction temperature	Tj	- 40 to +150	°C	
Storage temperature	Tstg	- 40 to +150	°C	
Mass	_	1.3	g	Typical value

Notes: 1. Gate open.

Electrical Characteristics


Parameter		Symbol	Min.	Тур.	Max.	Unit	Test conditions
Repetitive peak off-state cur	rent	I _{DRM}	_	_	2.0	mA	Tj = 150°C, V _{DRM} applied
On-state voltage		V_{TM}	_		1.5	V	Tc = 25°C, I _{TM} = 25 A, Instantaneous measurement
Gate trigger voltage ^{Note2}	I	V_{FGTI}			1.5	V	$Tj = 25$ °C, $V_D = 6$ V, $R_L = 6$ Ω,
	II	V_{RGTI}	_	_	1.5	V	$R_G = 330 \Omega$
	III	V_{RGTIII}	_	_	1.5	V	
Gate trigger current ^{Note2}	I	I _{FGTI}	_	_	30	mA	$Tj = 25$ °C, $V_D = 6$ V, $R_L = 6$ Ω,
	II	I _{RGTI}	_	_	30	mA	$R_G = 330 \Omega$
	III	I _{RGTIII}	_	_	30	mA	
Gate non-trigger voltage		V_{GD}	0.2/0.1	_	_	V	Tj = 125°C/150°C, V _D = 1/2 V _{DRM}
Thermal resistance		R _{th (j-c)}	_	_	1.4	°C/W	Junction to caseNote3 Note4
Critical-rate of rise of off-stat commutating voltage ^{Note5}	е	(dv/dt)c	10/1	_	_	V/μs	Tj = 125°C/150°C


Notes: 2. Measurement using the gate trigger characteristics measurement circuit.


- 3. Case temperature is measured on the T_2 tab.
- 4. The contact thermal resistance $R_{th\ (c\text{-}f)}$ in case of greasing is 1.0°C/W.
- 5. Test conditions of the critical-rate of rise of off-state commutating voltage is shown in the table below.


Test conditions	Commutating voltage and current waveforms (inductive load)
1. Junction temperature Tj = 125°C/150°C	Supply Voltage →Time
2. Rate of decay of on-state commutating current (di/dt)c = - 8.0 A/ms	Main Current (di/dt)c → Time
3. Peak off-state voltage VD = 400 V	Main Voltage → Time (dv/dt)c

Performance Curves












Package Dimensions







Ordering Information

Orderable Part Number	Package	Packing	Quantity	Remark
BCR16CS-16LB#BH0	TO-263	Tube	50 pcs.	
BCR16CS-16LBT1#BH0	TO-263	Embossed Tape	800 pcs.	Taping direction "T1"
BCR16CS-16LBA1#BH0	TO-262	Tube	50 pcs.	
BCR16CS-16LB#B00	LDPAK(S)-(1)	Tube	50 pcs.	Not Recommend for New Design
BCR16CS16LBT11#B00	LDPAK(S)-(1)	Embossed Tape	1000 pcs.	Not Recommend for New Design

Note: Please confirm the specification about the shipping in detail.

Notice

- 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information
- 2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc
 - Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.
- 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
- 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics
- 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics



SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

Refer to "http://www.renesas.com/" for the latest and detailed information

Renesas Electronics America Inc. 2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A. Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited 9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3 Tel: +1-905-237-2004

Renesas Electronics Europe Limited Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China Tel: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333
Tel: 486-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2865-6688, Fax: +852 2886-9022

Renesas Electronics Taiwan Co., Ltd. 13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd. 80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949 TEI: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia Tei: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HALII Stage, Indiranagar, Bangalore, India Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd. 12F., 234 Teheran-ro, Gangnam-Gu, Seoul, 135-080, Korea Tel: +82-2-558-3737, Fax: +82-2-558-5141