

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

38C5 Group

Timer X Operation (IGBT Output Mode:Output of IGBT Control Signal)

1. Abstract

The following document describes examples how to set the timer X and application examples in the 38C5 Group.

2. Introduction

The application examples described in this document are applied to the following MCU and conditions:

- Applicable MCU: 38C5 Group
- Oscillation frequency: 8 MHz

In this sample program, the bit of the function which is not used may be operated according to the bit assignment of SFR. Please set these values according to the use status of a user system.

3. Description of IGBT Control Signal Output

3.1 Outline of IGBT Output Mode

The 38C5 Group has the IGBT output mode as a function of timer X (16-bit timer).

In IGBT output mode, IGBT control signal is output from the TXOUT1 pin by the count value of timer X. Period and duty ratio of IGBT control signal are fixed by timer X and the compare register 1 when a trigger is not input from the INT0 pin. Period is determinate.

Period and duty ratio of IGBT control signal are fixed by timer X, the compare register 1, and trigger input from the INT0 pin when the trigger is input from the INT0 pin. Period is variable.

Operation when setting the timer X output 1 polarity switch bit (bit 5 in the timer X control register 1 (002E16)) to “0” and “Start from “L” output” is selected is described. When a trigger is input from the INT0 pin or timer X underflows after the timer X count starts, the TXOUT1 pin outputs “H”⁽¹⁾ (“L”⁽¹⁾ is output for the first period until trigger is input from the INT0 pin, or timer X underflows). When the count value of timer X matches with the value of the compare register 1, the TXOUT1 pin outputs “L”⁽¹⁾. Trigger input from the INT0 pin is valid while the TXOUT1 pin outputs “L”⁽¹⁾. The following selections are available regarding the trigger input:

- Falling edge active or rising edge active
- Sampling clock of noise filter (determined as valid signal if signal levels are the same four times continuously with the sampling clock.)
- Four types of delay time

To set the timer X output 1 control bit or timer X output 2 control bit (bit 3 or 4 in the timer X control register 1) to “1”, the timer X count stop bit (bit 6 in the timer X mode register (002D16)) is set to “1” by input of the INT1 or INT2. Then the timer X count stops and output from the TXOUT1 pin can be held “L”⁽¹⁾. The falling edge active or rising edge active can be selected for input of the INT1 or INT2 pin.

The previous setting value is valid for the value of the compare register until trigger input from the INT0 pin or underflow of timer X after the timer X count starts. However, “L”⁽¹⁾ is output for the first period regardless of the setting value of the compare register after the timer X count starts.

To use the IGBT output mode, note the following:
 (Refer to 4. Notes on Timer X (IGBT Output Mode).)

- Set the port direction register shared with the INT0 pin to input mode and the port direction register shared with the TXOUT1 pin to output mode.
- To use the TXOUT1 pin by switching it with the port output, the port latch value may be changed by the read-modify-write instruction.
- Since the port (P65) shared with the TXOUT1 pin functions as input at reset, stabilize the level by the external pull-down resistor or pull-up resistor.
- Set the timer X register (extension) to “0016”

NOTE:

1. When the timer X output 1 polarity switch bit is set to “1”, the level is inverted.

3.2 Output IGBT Control Signal

Outline:

- IGBT control signal of 20µs period with 5µs for “H” duration is output (IGBT active level is “H”) and starts from “L” output.
- When trigger signal (“H” to “L”) is input to the INT0 pin during “L” output, the output level is “H” and timer X restarts from the setting value of the timer X latch.

Specifications:

- Select $f(XIN) = 8 \text{ MHz}$ (1 count 125 ns) for the timer X count source.
- The timer X initial value is set to 159 and the timer X underflow period is set to 20 µs.
- The setting value of the compare register is set to 120. When trigger signal from the INT0 pin is not input, “L” duration is set to 15 µs. Therefore, “H” duration is set to 5 µs.
- Select $f(XIN)/2$ for the noise filter sampling clock. Select “not delayed” for external trigger delay time.
- Select falling edge active for INT0 input signal.

Figure 3.1 shows the Timer Connection and Setting of Division Ratio; Figure 3.2 shows the TXOUT1 Output Waveform; Figure 3.3 shows the Setting of Related Registers (1); Figure 3.4 shows the Setting of Related Registers (2) and Figure 3.5 shows the Control Procedure.




Figure 3.1 Timer Connection and Setting of Division Ratio




Figure 3.2 TXOUT1 Output Waveform




Figure 3.3 Setting of Related Registers (1)




Figure 3.4 Setting of Related Registers (2)




Figure 3.5 Control Procedure

4. Notes on Timer X (IGBT Output Mode)

(1) Write order to timer X

- In IGBT output mode, do not write “1” to the timer X register (extension). When “1” is already written to the timer X register (extension), ensure to write “0” to the register before using. Write in order of the compare register 1, 2, 3 (high-order, low-order), timer X register (extension), timer X register (low-order), and timer X register (high order). Whichever, high-order or low-order of the compare register 1, 2, 3 can be set first. Write data to both the high order and low order for the compare register 1, 2, 3 and timer X register.

(2) Read order to timer X

- In all modes, read in order of the timer X register (extension), timer X register (high-order), and timer X register (low-order). When reading the timer X register (extension) is not required, read in order of the timer X register (high-order) first and the timer X register (low-order). Read order to the compare register 1, 2, 3 are not specified.
- Write and read operations of the timer X register should be performed in 16-bit units. If write or reade operation is stopped, normal operation will not be performed.

(3) Write to timer X

- Which write control can be selected by the timer X write control bit (b3) of the timer X mode register (address 002D16), writing data to both the latch and the timer at the same time or writng data only to the latch. When writing a value to the timer X address to write to the latch only, the value is set into the timer latch and the timer is updated at the next underflow. Because of the simultaneous write setting after reset, a value is set to the timer and timer latch at the same time when the value is written to the timer X address. When writing to the latch only, if the write timing to the high-order timer latch and the underflow timing are almost the same, the value is set into the timer and the timer latch at the same time. In this time, counting may be stopped during write operation to the high-order timer latch (refer to 5.Notes on Timer Count Stop of Writing Data to Timer Latch Only).
- Do not switch the timer count source during timer count operation. Stop the timer count before switching it.

(4) Set of timer X mode register

- Set the write control bit of the timer X mode register to “1” (write to the latch only) in IGBT output mode.

(5) Timer X output control function

- When using the timer X output control function (INT1 or INT2) in IGBT output mode, set the INT1 or INT2 level to “H” in the falling edge active or to “L” in the rising edge active before switching to IGBT output mode.

(6) Port P65 latch

- When the waveform from the TXOUT1 pin is output and the port P6 is read in IGBT output mode, the pin state (level) is read. At this time, when the read-modify-write instructions are executed, the pin state (level) is reflected to the port latch and the value of bit 5 may be changed. Then when the P65/TXOUT1 pin is switched to the I/O port (output mode) from the timer X output, the unexpected level may be output by the changed value. Switch the I/O port after setting a given value to the port latch.

Read-modify-write instruction: Read one-byte of data from memory (read), modify the data (modify), write the data back to original memory (write).

CLB, SEB, ASL, LSR, ROL, ROR, RRF, DEC, INC, COM

(7) When 000016 is set to the compare register 1 (previous value: other than 000016)

“H” signal is output for one period at the next period after writing to timer X or the compare register 1. And “L” signal is output while timer X counts 3FFFF16. After that, this operation will be repeated. (The timer X output 1 polarity switch bit is set to “0”: start from “L” output and INT0 trigger is not input.)

Figure 4.1 shows an Example of IGBT Control Signal when 0000₁₆ is Set to Compare Register (Previous Value: Other than 0000₁₆).




Figure 4.1 Example of IGBT Control Signal Output when 0000₁₆ is set to Compare Register 1 (previous value: other than 0000₁₆)

(8) When same value is set to timer X and compare register 1

TXOUT1 output is held “H” at the timing of underflow immediately after writing to timer X and the compare register 1. Then TXOUT1 output is held “L” when the timer X value is reloaded and matches with the compare register 1 value. The width of “H” output is assumed as 1 count of the timer X count source (the timer X output 1 polarity switch bit is set to “0”: start from “L” output and INT0 trigger is not input).

Figure 4.2 shows an Example of IGBT Control Signal Output when Same Value is Set to Timer X and Compare Register 1.




Figure 4.2 Example of IGBT Control Signal Output when Same Value is Set to Timer X and Compare Register 1

(9) Time between trigger input to INT0 (INT00/INT01) pin and invert of TXOUT1 output waveform polarity

In IGBT output mode, a trigger input from the INT0 pin is valid only while the opposite polarity level from the active level is output (if the IGBT active level is “H”, the trigger input is valid only while the TXOUT1 output level is held “L”). The TXOUT1 output level is switched to the active level by the valid trigger input of the INT0 pin (if the IGBT active level is “H”, the TXOUT output level is switched to “H”). Time difference is generated by level determined time with a noise filter (determined as four times matches continuously) and delay time with the delay circuit between the input valid edge of the INT0 signal and the polarity invert to the active level. The noise filter sampling clock can be selected by the noise filter sampling clock selection bit (bit 0 of the timer X control register 1). Delay time with the delay circuit can be set by the external trigger delay time selection bits (bit 2, 1 of the timer X control register 1).

Figure 4.3 shows an example of IGBT control signal output when INT0 input is falling edge active and IGBT active level is “H”.




Figure 4.3 Example of IGBT Control Signal Output of TXOUT1 Pin by Trigger Input to INT0 Pin

5. Notes on Timer Count Stop of Writing Data to Timer Latch Only

When writing to the latch only, if the write timing to the timer latch and the underflow timing are the same time, the timer count operates as follows:

- Timer count source \leq internal system clock ϕ
Timer count operation does not stop and starts counting with new timer value.
- Timer count source $>$ internal system clock ϕ
Timer count operation stops for up to one cycle of the system clock. When writing operation (internal system clock ϕ) is completed, count starts with the new timer value.

NOTE:

Timer latch for timer 2, 3, or 4. High-order timer latch for timer X or Y.

6. Reference Program

Please visit the Renesas Technology Web site for a reference program.
Click Application Note in the left menu of the 38C5 Group.

7. Reference Document

Datasheet

38C5 Group Datasheet

38C5 Group (one-time PROM version) Datasheet

(Use the most recent version of the document on the Renesas Technology Web site.)

Technical News/Technical Update

(Use the most recent version of the document on the Renesas Technology Web site.)

Web site and Support

Renesas Technology Web site
<http://www.renesas.com/>

Inquiries
<http://www.renesas.com/inquiry>
csc@renesas.com

REVISION HISTORY	38C5 Group Timer X Operation (IGBT Output Mode:Output of IGBT Control Signal)
------------------	-------------------------------------------------------------------------------

Rev.	Date	Description	
		Page	Summary
1.00	Mar 24, 2006	-	First Edition issued

Keep safety first in your circuit designs!

1. Renesas Technology Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of non-flammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corporation product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corporation or a third party.
2. Renesas Technology Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corporation by various means, including the Renesas Technology Corporation Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corporation is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corporation for further details on these materials or the products contained therein.