

Application Note

DA9083-28UUx Variant Overview

AN-PM-182

Abstract

This application note describes all the register default settings of the DA9083-28UUx variant (the x denotes the package option).

Contents

Abstract	1
Contents	2
Tables	2
1 Terms and Definitions.....	3
2 References	3
3 Variant Table and Ordering Information	4
4 DA9083-28UUx Detailed Description - Production Release	5
5 DA9083-28UUx Variant Overview	7
Revision History	8

Tables

Table 1: Variant Table	4
Table 2: Register Settings DA9083-28UUx Variant	5
Table 3: OTP Variant Overview.....	7

DA9083-28UUx Variant Overview**1 Terms and Definitions**

CH	Channel
DVC	Dynamic voltage control
LDO	Low Drop Out
OTP	One Time Programmable
WLCSP	Wafer Level Chip Scale Package

2 References

[1] DA9083_Datasheet, Renesas Electronics.

Note 1 References are for the latest published version, unless otherwise indicated.

DA9083-28UUx Variant Overview**3 Variant Table and Ordering Information****Table 1: Variant Table**

Part Number	Package	Size (mm)	Shipment Form	Pack Quantity
DA9083-28UUC	36 WLCSP	2.5 x 2.5	Tape & Reel	3000
DA9083-28UU6	36 WLCSP	2.5 x 2.5	Waffle Tray	500

DA9083-28UUx Variant Overview
4 DA9083-28UUx Detailed Description - Production Release
Key settings:

- VCH1 = 0.55 V, VCH2 = 1.5 V, VCH3 = 0.55 V, VCH4 = 1.5 V
- VLDO = 1.8 V
- LSW, CH1, CH2, CH3, CH4 and LDO are OFF by default
- CH1, CH2, CH3 and CH4 operate in PWM mode, 2 MHz
- I²C standard speed. I²C slave address = 0x1B (7-bit)

Table 2: Register Settings DA9083-28UUx Variant

Register Address	Function	Default Value	Description
0x03	PMC_CH1_CFG_REG	0x6A	ILmax = 4 A DVC slew rate up/down= 10/5 mV/μs fSW = 2 MHz
0x05	PMC_CH2_CFG_REG	0x6A	ILmax = 4 A DVC slew rate up/down= 10/5 mV/μs fSW = 2 MHz
0x07	PMC_CH3_CFG_REG	0x6A	ILmax = 4 A DVC slew rate up/down= 10/5 mV/μs fSW = 2 MHz
0x09	PMC_CH4_CFG_REG	0xAA	ILmax = 8.5 A DVC slew rate up/down= 10/5 mV/μs fSW = 2 MHz
0x0B	PMC_LDO_SEL_REG	0xA0	VLDO = 1.80 V
0x0F	PMC_DCDCCTRL0_REG0	0x00	LSW enable, CH<x> enables and LDO enable controlled by the Sequencer
0x10	PMC_SLEEP_REG0	0x00	SLEEP settings not configured
0x11	PMC_DCDCCTRL1_REG	0xF0	CH<x> operating in PWM mode
0x12	PMC_DISCHARGE_REG0	0xFC	LSW, CH<x> and LDO discharge enabled
0x13	PMC_DCDCCTRL2_REG	0x00	CH<x> and LDO operating in Higher Power mode
0x14	PMC_CH1CH2_WAKEUP_TIME	0x00	CH1, CH2 are OFF by default
0x15	PMC_CH3CH4_WAKEUP_TIME	0x00	CH3, CH3 are OFF by default
0x16	PMC_LDO_WAKEUP_TIME	0x00	LDO is OFF by default
0x1B	PMC_IRQ_MASK0	0x00	No IRQ events masked
0x1C	PMC_IRQ_MASK1	0x00	No IRQ events masked
0x1D	PMC_IRQ_MASK2	0x00	No IRQ events masked
0x1E	PMC_VOUT_CH1	0x37	VCH1 = 0.55 V
0x1F	PMC_VOUT_CH2	0x4B	VCH2 = 1.5 V
0x20	PMC_VOUT_CH3	0x37	VCH3 = 0.55 V
0x21	PMC_VOUT_CH4	0x4B	VCH4 = 1.5 V
0x4C	BUCK_BUCK_OPT_04	0x00	Divider mode disabled VCH1 range = 0.5 V to 1.9 V
0x4D	BUCK_BUCK_OPT_05	0x40	Divider mode enabled

DA9083-28UUx Variant Overview

Register Address	Function	Default Value	Description
			VCH2 range = 1.5 V to 2.7 V
0x4E	BUCK_BUCK_OPT_06	0x00	Divider mode disabled VCH3 range = 0.5 V to 1.9 V
0x4F	BUCK_BUCK_OPT_07	0x40	Divider mode enabled VCH4 range = 1.5 V to 2.7 V
0x62	OTP_CONFIG_ID	0x28	OTP variant number: DA9083-28UUx

5 DA9083-28UUx Variant Overview

Table 3: OTP Variant Overview

Reg Add	Function	Standard Variant DA9083-28UUx
0x03	PMC_CH1_CFG_REG	0x6A
0x05	PMC_CH2_CFG_REG	0x6A
0x07	PMC_CH3_CFG_REG	0x6A
0x09	PMC_CH4_CFG_REG	0xAA
0x0B	PMC_LDO_SEL_REG	0xA0
0x0F	PMC_DCDCCTRL0_REG0	0x00
0x10	PMC_SLEEP_REG0	0x00
0x11	PMC_DCDCCTRL1_REG	0xF0
0x12	PMC_DISCHARGE_REG0	0xFC
0x13	PMC_DCDCCTRL2_REG	0x00
0x14	PMC_CH1CH2_WAKEUP_TIME	0x00
0x15	PMC_CH3CH4_WAKEUP_TIME	0x00
0x16	PMC_LDO_WAKEUP_TIME	0x00
0x1B	PMC_IRQ_MASK0	0x00
0x1C	PMC_IRQ_MASK1	0x00
0x1D	PMC_IRQ_MASK2	0x00
0x1E	PMC_VOUT_CH1	0x37
0x1F	PMC_VOUT_CH2	0x4B
0x20	PMC_VOUT_CH3	0x37
0x21	PMC_VOUT_CH4	0x4B
0x4C	BUCK_BUCK_OPT_04	0x00
0x4D	BUCK_BUCK_OPT_05	0x40
0x4E	BUCK_BUCK_OPT_06	0x00
0x4F	BUCK_BUCK_OPT_07	0x40

DA9083-28Ux Variant Overview

Revision History

Revision	Date	Description
1	30-Jan-2024	Initial version.

DA9083-28Ux Variant Overview**Status Definitions**

Status	Definition
DRAFT	The content of this document is under review and subject to formal approval, which may result in modifications or additions.
APPROVED or unmarked	The content of this document has been approved for publication.

RoHS Compliance

Renesas Electronics' suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on request.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.