

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

M16C/62P, M16C/62M Group

Differences between M16C/62P and M16C/62M

1. Abstract

This issue is the reference materials of function differences between M16C/62P and M16C/62M.

2. Introduction

The explanation of this issue is applied to the following condition:

Applicable MCU: M16C/62P, M16C/62M

3. Contents

3.1 Function differences

Table 3.1.1 and table 3.1.2 show the function differences (mask ROM version and flash memory version). Table 3.1.3 shows the function differences (flash memory version).

Table 3.1.1 Function differences (mask ROM version and flash memory version)-1(Note1)

Item	M16C/62P	M16C/62M
Shortest instruction execution time	41.7ns(f(BCLK)=24MHz, VCC1=3.0 to 5.5V) 100ns(f(BCLK)=10MHz, VCC1=2.7 to 5.5V)	100ns(f(XIN)=10MHz, VCC=2.7 to 3.6V) 142.9ns(f(XIN)=7MHz, VCC=2.2 to 3.6V, with software one-wait)
Supply voltage	VCC1=3.0 to 5.5V, VCC2=3.0V to VCC1 (f(BCLK)=24MHz) VCC1=VCC2=2.7 to 5.5V (f(BCLK)=10MHz)	2.7 to 3.6V(f(XIN)=10MHz) 2.4 to 3.6V(f(XIN)=7MHz) 2.2 to 3.6V(f(XIN)=7MHz, with software one-wait)
I/O power supply	Double (VCC1, VCC2)	Single (VCC)
Package	80-pin, 100-pin, 128-pin plastic mold QFP	80-pin, 100-pin plastic mold QFP
Clock generating circuit	PLL, XIN, XCIN, on-chip oscillator When placed in low power mode a divided-8 value is used for these clocks. The XIN drive capability is set to HIGH.	XIN, XCIN When placed in low power mode, the divided-n value for the main clock does not change. Nor does the XIN drive capability change.
System clock protective function	Built-in	None (protected by protect register)
Oscillation stop, re-oscillation detecton function	Built-in	None
Low power consumption	18mA(VCC1=VCC2=5V, f(BCLK)=24MHz) 8mA(VCC1=VCC2=3V, f(BCLK)=10MHz) 1.8uA(VCC1=VCC2=3V, f(XCIN)=32kHz, wait mode)	9.5mA(VCC=3V, f(XIN)=10MHz) 0.9uA(VCC=3V, f(XCIN)=32kHz, wait mode)
Memory area	Memory area expandable (4M bytes)	1 M bytes fixed
External device connect area	04000h to 07FFFh (PM13=0) 08000h to 0FFFFh (PM10=0) 10000h to 26FFFh 28000h to 7FFFFh 80000h to CFFFFh (PM13=0) D0000h to FFFFFh (Microprocessor mode)	04000h to 05FFFh (PM13=0) 06000h to CFFFFh D0000h to FFFFFh (Microprocessor mode)

Note 1: About the details and the characteristics, refer to hardware manual.

Table 3.1.2 Function differences (mask ROM version and flash memory version)-2(Note1)

Item	M16C/62P	M16C/62M
Upper address memory expansion mode and microprocessor mode	P4_0 to P4_3(A16 to A19), P3_4 to P3_7(A12 to A15) : Switchable between address bus and I/O port	P4_0 to P4_3(A16 to A19) : Switchable between address bus and I/O port A12 to A15: No Switchable
Access to SFR	Variable (1 to 2 waits)	1 wait fixed
Software wait to external area	Variable (0 to 3 waits)	Variable (0 to 1 wait)
Protect	Can be set for PM0, PM1, PM2, CM0, CM1, CM2, PLC0, INVC0, INVC1, PD9, S3C, S4C, TB2SC, PCLKR, VCR2, D4INT registers	Can be set for PM0, PM1, CM0, CM1, PD9, S3C, S4C registers
Watchdog timer	Watchdog timer interrupt or watchdog timer reset is selected Count source protective mode is available	Watchdog timer interrupt No count source protective mode
Address match interrupt	4	2
Timers A, timer B Count source	Selectable: f1, f2, f8, f32, fC32	Selectable: f1, f8, f32, fC32
Timer A two-phase pulse signal processing	Function Z-phase (counter reset) input	No function Z-phase (counter reset) input
Timer functions for three-phase motor control	Function protect by protect register Count source is selected f1, f2, f8, f32, fC32 Dead time timer count source is selected: f1, f1 divided by 2, f2, f2 divided by 2 Three-phase output forcible shutoff function based on $\overline{\text{NMI}}$ input is available, output polarity change, carrier wave phase detection	No function protected by protect register Count source is selected :f1, f8, f32, fC32 Dead time timer count source is fixed at f1 divided by 2
Serial I/O (UART0 to UART2)	(UART, Clock synchronous, I ² C-bus™ (Note 2), IEBus™ (Note 3)) x 3	(UART, Clock synchronous) x 2 (UART, Clock synchronous, I ² C-bus™ (Note 2), IEBus™ (Note 3)) x 1
UART0 to UART2, SI/O3, SI/O4 Count source	Select from f1SIO, f2SIO, f8SIO, f32SIO	Select from f1, f8, f32
Serial I/O RTS timing	Assert low when receive buffer is read	Assert low when reception is completed
UART0 to UART2 Overrun error occur timing	This error occurs if the serial I/O started receiving the next data before reading the UiRB register (i=0 to 2) and received the 7th bit of the next data (Clock synchronous). This error occurs if the serial I/O started receiving the next data before reading the UiRB register and received the bit one before the last stop bit of the next data (UART).	This error occurs when the next data is ready before contents of UiRB register (i=0 to 2) are read out
Serial I/O CTS/RTS separate function	Have	None
UART2 data transmit timing	After data was written, transfer starts at the 2nd BRG overflow timing (same as UART0 and UART1)	After data was written, transfer starts at the 1st BRG overflow timing (Output starts one cycle of BRG overflow earlier than UART0 and UART1)
Serial I/O Sleep function	None	Have
Serial I/O I ² C mode	Start condition, stop condition: Auto-generation	Start condition, stop condition: Not auto-generation
Serial I/O I ² C mode SDA delay	Only digital delay is selected as SDA delay SDA digital delay count source: BRG	Analog or digital delay is selected as SDA delay. SDA digital delay count source: 1/f(XIN)
SI/O3, SI/O4 Clock polarity	Selectable	Fixed
A/D converter	10 bits x 8 channels Expandable up to 26 channels	10 bits x 8 channels Expandable up to 10 channels
A/D converter operation clock	Selectable: fAD, fAD divided by 2, 3, 4, 6, 12	Selectable: fAD, fAD/2, fAD/4
A/D converter input pin	Select from ports P0, P2, P10	Fixed at port P10

Note 1: About the details and the characteristics, refer to hardware manual.

Note 2: I²C is a trademark of Philips Semiconductors Corporation.

Note 3: IEBus is a trademark of NEC Electronics Corporation.

Table 3.1.2 Function differences (flash memory version)(Note1)

Item	M16C/62P	M16C/62M
User ROM blocks	14 blocks: 4 Kbytes X 3, 8 Kbytes X 3, 32 Kbytes X 1, 64 Kbytes X 7 (Flash memory: max. 512 Kbytes)	7 blocks: 8Kbytes X 2, 16 Kbytes X 1, 32 Kbytes X 1, 64 Kbytes X 3 (Flash memory: max. 256 Kbytes)
Program manner	Word	Page
Program command (Software command)	Page program command: none Program command: have (Program method: in units of word, in units of byte)	Page program command: have Program command: none (Program method: in units of page)
Block status after program function	None	Have
CPU rewrite mode	EW1 mode is available	No EW1 mode

Note 1: About the details and the characteristics, refer to hardware manual.

3.2 Pin function differences

Table 3.2.1 shows the pin function differences.

Table 3.2.1 Pin function differences

M16C/62P	M16C/62M	Remarks
VCC1	VCC	
P8_4/INT2/ZP	P8_4/INT2	Add ZP
P6_7/TxD1/SDA1	P6_7/TxD1	Add SDA1
P6_6/RxD1/SCL1	P6_6/RxD1	Add SCL1
P6_4/CTS1/RTS1/CTS0/CLKS1	P6_4/CTS1/RTS1/CLKS1	Add CTS0
P6_3/TxD0/SDA0	P6_3/TxD0	Add SDA0
P6_2/RxD0/SCL0	P6_2/RxD0	Add SCL0
VCC2	VCC	
P2_7/AN2_7/A7(/D7/D6)	P2_7/A7(/D7/D6)	Add AN2_7
P2_6/AN2_6/A6(/D6/D5)	P2_6/A6(/D6/D5)	Add AN2_6
P2_5/AN2_5/A5(/D5/D4)	P2_5/A5(/D5/D4)	Add AN2_5
P2_4/AN2_4/A4(/D4/D3)	P2_4/A4(/D4/D3)	Add AN2_4
P2_3/AN2_3/A3(/D3/D2)	P2_3/A3(/D3/D2)	Add AN2_3
P2_2/AN2_2/A2 (/D2/D1)	P2_2/A2 (/D2/D1)	Add AN2_2
P2_1/AN2_1/A1(/D1/D0)	P2_1/A1(/D1/D0)	Add AN2_1
P2_0/AN2_0/A0(/D0/-)	P2_0/A0(/D0/-)	Add AN2_0
P0_7/AN0_7/D7	P0_7/D7	Add AN0_7
P0_6/AN0_6/D6	P0_6/D6	Add AN0_6
P0_5/AN0_5/D5	P0_5/D5	Add AN0_5
P0_4/AN0_4/D4	P0_4/D4	Add AN0_4
P0_3/AN0_3/D3	P0_3/D3	Add AN0_3
P0_2/AN0_2/D2	P0_2/D2	Add AN0_2
P0_1/AN0_1/D1	P0_1/D1	Add AN0_1
P0_0/AN0_0/D0	P0_0/D0	Add AN0_0

3.3 SFR differences

Table 3.3.1 show the SFR differences.

Table 3.3.1 SFR differences-1

M16C/62P	M16C/62M	Remarks
PM1	PM1	Change function
CM0	CM0	Change function
CM1	CM1	Add bit1
PRCR	PRCR	Change function
DBR	-	
CM2	-	
WDC	WDC	Add bit5
VCR1	-	
VCR2	-	
CSE	-	
PLC0	-	
PM2	-	
D4INT	-	
TB4IC,U1BCNIC	TB4IC	Shard with U1BCNIC register
TB3IC,U0BCNIC	TB3IC	Shard with U0BCNIC register
FIDR	-	
RMAD2	-	
AIER2	-	
RMAD3	-	
PCLKR	-	
INVC1	INVC1	Change function
IFSR2A	-	
S3C	S3C	Add bit4
S4C	S4C	Add bit4
U0SMR4	-	
U0SMR3	-	
U0SMR2	-	
U0SMR	-	
U1SMR4	-	
U1SMR3	-	
U1SMR2	-	
U1SMR	-	
U2SMR4	-	
U2SMR3	U2SMR3	Change function
U2SMR2	U2SMR2	Change function
U2SMR	U2SMR	Change function
ONSF	ONSF	Add bit5
TB2SC	-	
U0MR	U0MR	Change function
U0C0	U0C0	Change function
U0C1	U0C1	Add Bits6, 7
U1MR	U1MR	Change function
U1C0	U1C0	Change function

Table 3.3.2 SFR differences-2

M16C/62P	M16C/62M	Remarks
U1C1	U1C1	Add bits6, 7
UCON	UCON	Add bit6
FMR1	FMR1	Address change from 03B6h to 01B5h. Change function.
FMR0	FMR0	Address change from 03B7h to 01B7h. Change function.
ADCON2	ADCON2	Change function

3.4 Interrupt vector differences

Table 3.4.1 shows the fixed vector table differences. Table 3.4.2 shows the relocatable vector table differences.

Table 3.4.1 Fixed vector table differences

M16C/62P interrupt source	M16C/62M interrupt source
Watchdog timer Oscillation stop and re-oscillation detection Voltage down detection	Watchdog timer

Table 3.4.2 Relocatable vector table differences

M16C/62P interrupt source	M16C/62M interrupt source	Software interrupt number
Timer B4, UART1 bus collision detect	Timer B4	6
Timer B3, UART0 bus collision detect	Timer B3	7
UART0 transmit, NACK0	UART0 transmit	17
UART0 receive, ACK0	UART0 receive	18
UART1 transmit, NACK1	UART1 transmit	19
UART1 receive, ACK1	UART1 receive	20

3.5 Support tool differences

Table 3.5.1 shows the support tool differences.

Table 3.5.1 support tool differences

Tool information	M16C/62P tool product (Max.24MHz)	M16C/62P tool product (Max.16MHz)	M16C/62M tool product	Change
C Compiler	M3T-NC30WA	M3T-NC30WA	M3T-NC30WA	
Real-time OS	M3T-MR30	M3T-MR30	M3T-MR30	
Simulator Debugger	M3T-PD30SIM	M3T-PD30SIM	M3T-PD30SIM	
Emulator Debugger	M3T-PD30F	M3T-PD30	M3T-PD30	√
Emulator	PC7501	PC4701U	PC4701U	√
Emulation Pod, Emulation Probe	M3062PT-EPB	M3062PT3-RPD-E	M3062TL-RPD-E	√

4. Reference

DATA SHEET

M16C/62M Group data sheet Rev.B1

(Acquire the most current version from Renesas web-site)

HARDWARE MANUAL

M16C/62P Group Hardware manual Rev.2.30

(Acquire the most current version from Renesas web-site)

5. Web-site and contact for support

Renesas Web-site

<http://www.renesas.com>

Contact for Renesas technical support

Mail to : support_apl@renesas.com

REVISION HISTORY

Rev.	Date	Description	
		Page	Summary
1.00	Jan 16, 2004	-	First edition issued
1.01	Feb 02, 2004	6	Address is revised (FMR0 register, FMR1 register)
1.02	Aug 02, 2004	-	Words standardized: On-chip oscillator, and A/D converter

Keep safety first in your circuit designs!

1. Renesas Technology Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corporation product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corporation or a third party.
2. Renesas Technology Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corporation by various means, including the Renesas Technology Corporation Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corporation is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corporation for further details on these materials or the products contained therein.