

XK13L156L312L625I

XK Crystal Oscillator (ProXO II)

1. Pin Information

1.1 Pin Assignments




Figure 1. 2.0 × 1.6 mm Package Option– Top View

1.2 Pin Descriptions

Pin Number	Pin Name	Description
1	OE	Output Enable (OE) (0 = disabled; pulled High internally) <i>Note:</i> The OE function stops the outputs in a differential state, it does not tri-state the outputs or power down the internal circuitry.
2	FS	Frequency Select (FS). The pin is a 3-state (High, Mid (Float), Low) pin that selects one of the three factory programmed frequencies and output types via ordering option.
3	GND	Connect to ground
4	OUT0	True clock output.
5	OUT0b	Complementary clock output.
6	VDD	Power supply voltage.

1.3 FSEL Configuration

Configuration	FSEL	OE Pin	OE Logic	Frequency	Output Type	Voltage
1	Low	Pin 1	Active High	156.25MHz	LVDS	3.3V
2	Mid (Float)	Pin 1	Active High	312.5MHz	LVDS	3.3V
3	High	Pin 1	Active High	625MHz	LVDS	3.3V

2. Ordering Information

The Minimum Order Quantity (MOQ) for tape and reel packing is 2500 pieces. Orders less than 2500 pieces, or the portion of orders that are not multiples of 2500 pieces will be packed on cut tape. For example, a 3500 pieces order will be packed as 2500 pieces on tape and reel and 1000 pieces on cut tape.

	Family	Package	Voltage	Config. 1 ^[1] (FS = Low)	Config. 2 ^[1] (FS = Floating)	Config. 3 ^[1] (FS = High)	Temperature Range
Ordering Code ^[2]	XK	0: 1.8 × 1.4 mm 1: 2.0 × 1.6 mm 2: 2.5 × 2.0 mm 3: 3.2 × 2.5 mm	1: 1.8V ±5% 2: 2.5V ±5% 3: 3.3V ±5%	Xff	Xff	Xff	I: -40 to +85°C
Part Number ^[3]	XK	1	3	L156	L312	L625	I

1. Refer to [FSEL Configuration](#) table for frequencies and output types.
2. See the Ordering Information section in the [XK datasheet](#) for a full set of codes and details on output types and configurations, frequency performance groups, and frequencies.
3. The ordering code from this table denotes part number XK13L156L312L625I.

3. Revision History

Revision	Date	Description
1.00	Nov 7, 2023	Initial release.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.