

## Supplemental Information

This Document Errata reflects changes required for the device datasheet of 874003AG-02, 874003AG-02T, 874003AG-02LF and 874003AG-02LFT.

## Revision History

**September 17, 2010:** First version of documentation errata for this device.

## Errata Item

**Page 3, Table 4C** - Changed the Input High Current ( $I_{IH}$ ) for nCLK  
 Changed the Input Low Current ( $I_{IL}$ ) for CLK  
 Refer below for details.  
 Only datasheet was corrected. There are no changes to the device.

**FROM:**

| Symbol   | Parameter          | Test Conditions                    | Minimum | Typical | Maximum | Units   |
|----------|--------------------|------------------------------------|---------|---------|---------|---------|
| $I_{IH}$ | Input High Current | CLK<br>$V_{DD} = V_{IN} = 3.465V$  |         |         | 150     | $\mu A$ |
|          |                    | nCLK<br>$V_{DD} = V_{IN} = 3.465V$ | -5      |         |         |         |
| $I_{IL}$ | Input Low Current  | CLK<br>$V_{DD} = V_{IN} = 3.465V$  |         |         | 150     | $\mu A$ |
|          |                    | nCLK<br>$V_{DD} = V_{IN} = 3.465V$ | 150     |         |         |         |

**TO:**

| Symbol   | Parameter          | Test Conditions                    | Minimum | Typical | Maximum | Units   |
|----------|--------------------|------------------------------------|---------|---------|---------|---------|
| $I_{IH}$ | Input High Current | CLK<br>$V_{DD} = V_{IN} = 3.465V$  |         |         | 150     | $\mu A$ |
|          |                    | nCLK<br>$V_{DD} = V_{IN} = 3.465V$ |         |         | 5       |         |
| $I_{IL}$ | Input Low Current  | CLK<br>$V_{DD} = V_{IN} = 3.465V$  | -5      |         |         | $\mu A$ |
|          |                    | nCLK<br>$V_{DD} = V_{IN} = 3.465V$ | 150     |         |         |         |

**Page 13, Table 8** - Changed "Ordering Information" Marking  
 Only datasheet was corrected. Physical marking on parts is not changing.

**FROM:**

| Part/Order Number | Marking   | Package                   |
|-------------------|-----------|---------------------------|
| ICS874003AG-02    | 874003A02 | 20 Lead TSSOP             |
| ICS874003AG-02T   | 874003A02 | 20 Lead TSSOP             |
| ICS874003AG-02LF  | 74003A02L | 20 Lead "Lead-Free" TSSOP |
| ICS874003AG-02LFT | 74003A02L | 20 Lead "Lead-Free" TSSOP |

**TO:**

| Part/Order Number | Marking      | Package                   |
|-------------------|--------------|---------------------------|
| ICS874003AG-02    | ICS874003A02 | 20 Lead TSSOP             |
| ICS874003AG-02T   | ICS874003A02 | 20 Lead TSSOP             |
| ICS874003AG-02LF  | ICS74003A02L | 20 Lead "Lead-Free" TSSOP |
| ICS874003AG-02LFT | ICS74003A02L | 20 Lead "Lead-Free" TSSOP |