


## Device Overview

The IDT Tsi352 is a PCI-to-PCI Bridge that provides a high performance connection path between two peripheral components interconnect (PCI) buses.

Transactions occur between masters on one PCI bus and targets on another PCI bus, and the Tsi352 allows bridged transactions to occur concurrently on both buses. The bridge supports burst-mode transfers to maximize data throughput, and the two bus traffic paths through the bridge act independently.

## Block Diagram



## Features

- Two 32-bit, 33-MHz PCI buses
- Fully compliant with *PCI-to-PCI Bridge Architecture Specification Revision 1.1*
- Configurable for *PCI Power Management Interface Specification Revision 1.0 or 1.1* support
- CompactPCI friendly silicon as defined in the *CompactPCI Hot Swap Specification*
- Provides internal two-tier arbitration for up to four secondary bus masters and supports an external secondary bus arbiter
- Secondary bus is driven low during reset
- Provides five secondary PCI clock outputs
- Burst data transfers with pipeline architecture to maximize data throughput in both directions
- Provides programmable extension windows and port decode options
- Independent read and write buffers for each direction
- Provides VGA palette memory and I/O, and subtractive decoding

## Other

- Advanced submicron, low-power CMOS technology

## Physical

- 160-QFP package
- 3.3 V core logic with universal PCI interface compatible with 3.3 V and 5 V PCI signaling environments

## Benefits


- Bus expansion and electrical load splitting
- Small foot print package making it ideal for applications with tight board real estate requirements
- Expanding the PCI bus and support more slots
- Increases system performance by supporting simultaneous upstream and downstream transactions

## Typical Applications

The Tsi352 can be used in the following applications:

- Multifunction I/O cards
- Motherboards
- Consumer Networking Systems
- Industrial applications
- Back planes

### Typical Application — Digital Video Recorder



## IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

### Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,  
Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

### Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

### Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit [www.renesas.com/contact-us/](http://www.renesas.com/contact-us/).