

Supplemental Information

This notice describes the differences between the updated version (Version 3, dated February 6, 2009) and its previous version (Version 2, dated January 11, 2007) of the IDT82P2828 data sheet. It helps readers to identify the changes when the data sheet is upgraded.

Revision History

Revision Date	PCN Number (if applicable)	Date Code	Changed Items
February 6, 2009	-	-	9
January 11, 2007	-	-	8
December 7, 2005	-	-	1-7

Changed Items

February 6, 2009

Item 9: Changed 'MCLK should be a jitter-free clock with ± 32 ppm (in T1/J1 mode) or ± 50 ppm (in E1 mode) accuracy' to 'MCLK should be a clock with ± 32 ppm (in T1/J1 mode) or ± 50 ppm (in E1 mode) accuracy'. (Page 22, 61, 67)

January 11, 2007

Item 8: Changed the Min and Max values of 'Output Pulse Amplitude' in 'T1/J1 TRANSMITTER ELECTRICAL CHARACTERISTICS' (Page 132)

December 7, 2005

Item 7: Changed the Pd value in '8.1 Absolute Maximum Ratings' (Page 124)

Item 6: Changed the thermal data table and the corresponding data in 3 equations (Page 123)

Item 5: Changed the Figure-10, Figure-59 and Figure-60 (Page 31, 149)

Item 4: Changed test conditions for Analog LOS Level (Line Monitor Mode) (Page 129, 130)

Item 3: Added diodes to Figure-47, Figure-48 and Figure-49 (Page 72, 73, 74)

Item 2: Changed the description for the REF pin (Page 23)

Item 1: Changed data sheet status from 'Advance Information' to final. (Page 10)

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.