

Highlights

- System implements ITU-T telecom profiles
- Composed of Renesas' IEEE 1588 software and Synchronization Management Unit (SMU) hardware
- Operates as IEEE 1588 / PTP slave
- Recovers accurate and stable synchronization signals from packet based IEEE 1588 / PTP master
- Provides integrated physical layer frequency support
- Operates as an IEEE 1588 / PTP master

SOFTWARE

- C99 source code distribution, supporting POSIX-based Operating Systems (OSs) such as Linux
- IEEE 1588 compliant Precision Time Protocol (PTP) stack
- Abstraction interface supports user-supplied IEEE 1588 compliant Precision Time Protocol (PTP) stack
- Reference trackers filter packet synchronization noise from IEEE 1588 unaware networks

HARDWARE

- Synchronization Management Unit (SMU) provides tools to manage physical layer and packet based synchronous clocks for IEEE 1588 Telecom Profile applications
- Supports independent IEEE 1588 and Synchronous Ethernet (SyncE) timing paths
- Combo mode provides SyncE physical layer frequency support for IEEE 1588 Telecom Boundary Clocks (T-BC) and Telecom Time Slave Clocks (T-TSC) per G.8273.2
- Digital PLLs can be configured as Digitally Controlled Oscillators (DCOs) for IEEE 1588 clock synthesis
- Generates G.8262 compliant SyncE clocks
- Fractional-N input dividers support a wide range of reference frequencies
- Locks to 1 pulse per second (PPS) references from GPS based sources
- Loads configuration from an external EPROM after reset

Applications

- Access routers, edge routers, core routers
- Carrier Ethernet switches
- Multiservice access platforms
- PON OLT
- LTE eNodeB
- ITU-T G.8265.1 and G.8275.1 Telecom Profile clock synthesizer
- ITU-T G.8273.2 Telecom Boundary Clock (T-BC) and Telecom Time Slave Clock (T-TSC)
- ITU-T G.8264 Synchronous Equipment Timing Source (SETS)
- ITU-T G.8263 Packet-based Equipment Clock (PEC)
- ITU-T G.8262 Synchronous Ethernet Equipment Clock (EEC)
- ITU-T G.813 Synchronous Equipment Clock (SEC)
- Telcordia GR-253-CORE Stratum 3 Clock (S3) and SONET Minimum Clock (SMC)

Description

IEEE 1588-2008 Precision Time Protocol (PTP) is a packet-based synchronization mechanism used in packet-switched networks. PTP synchronizes the clocks of different devices with the most accurate clock on the network – usually a precise, grandmaster clock, such as one using a Primary Reference Time Clock (PRTC) time signal. The 82P33931-1 is a software and hardware system that can operate as a PTP slave or PTP master. As a PTP slave the 82P33931-1 recovers accurate and stable electrical synchronization signals from a packet based reference generated by a PTP master. As a PTP master the 82P33931-1 can lock to a stable electrical clock source and generate packet based PTP references for downstream PTP slaves

The 82P33931-1 is available with several software and hardware options. The software options are outlined in [Table 1](#) by root part number. The hardware options depend on the choice of Synchronization Management Unit (SMU) hardware; the SMU hardware documentation is listed in [Table 3](#) by root part number.

Table 1: Software Options by Root Part Number

| Root Part Number | Included Software |
|------------------|---|
| 82P33931 | Renesas clock recovery servo software |
| 82P33931-1 | Renesas clock recovery servo software IEEE 1588 Protocol Stack |

System Component Documentation

The detailed characteristics of the 82P33931-1 software and hardware components are described in other documents as shown in [Table 2](#) and [Table 3](#).

Table 2: Software Documentation

| Software System Component | Software Documentation |
|-------------------------------|------------------------|
| 82P33931-1 IEEE 1588 software | Please contact Renesas |

Table 3: SMU Hardware Documentation

| Root Part Number | Documentation |
|------------------------|--|
| 82P33931 82P33931-1 | 82P33831 Datasheet (For specifications information about the 82P33931 and 82P33931-1, see the 82P33831 Datasheet .) |

Package Outline Drawings

The package outline drawings are located at the end of this document and are accessible from the Renesas website. The package information is the most current data available and is subject to change without revision of this document.

Ordering Information

Table 4: Ordering Information


| Part/Order Number ^a | Package | Shipping Packaging | Temperature |
|--------------------------------|-----------------------------|--------------------|---------------|
| 82P33931BAG | 144-pin CABGA green package | Tray | -40° to +85°C |
| 82P33931BAG8 | 144-pin CABGA green package | Tape and Reel | -40° to +85°C |
| 82P33931-1BAG | 144-pin CABGA green package | Tray | -40° to +85°C |
| 82P33931-1BAG8 | 144-pin CABGA green package | Tape and Reel | -40° to +85°C |

a. "G" after the two-letter package code denotes Pb-Free configuration, RoHS compliant.

Revision History

| Date | Description of Change |
|--------------|--|
| Jun 3, 2025 | Added a Package Outline Drawings section. Completed other minor changes. |
| Apr 5, 2017 | Separated parts into individual datasheets. |
| Mar 16, 2016 | Table 4, Ordering Information Table - corrected "Shipping & Packaging" for 82P33913/ -1. |
| Mar 14, 2016 | Added part number 82P33913/82P33913-1 throughout the datasheet. Ordering Information table - added 82P33913/82P33913-1 part number information. |
| May 14, 2015 | Initial release |

A1 BALL PAD CORNER




RECOMMENDED LAND PATTERN

NOTE:

- 1) ALL dimensions are in mm, Angles in degrees.
- 2) Top down view, as view on PCB.
- 3) NSMD Land Pattern Assumed
- 4) Land Pattern Recommendation as per IPC-7351B generic requirement for surface mount design and Land Pattern.

| REVISIONS | | | |
|-----------|--|----------|----------|
| REV | DESCRIPTION | DATE | APPROVED |
| 00 | INITIAL RELEASE | 08/29/13 | CM |
| 01 | CHANGE TOTAL PACKAGE THICKNESS, SOLDER BALL DIMENSIONING | 10/04/13 | CK LEE |
| 02 | ADD MISSING DIMENSION ON MOLD CAP | 2/3/14 | CK LEE |
| 03 | CHANGE MOLD CAP THICKNESS FROM 0.53MM TO 0.55MM | 4/1/14 | CK LEE |

| | | | |
|--------------------------------|----------|---|-----|
| TOLERANCES UNLESS SPECIFIED | |  IDT™ 6024 Silver Creek Valley Road San Jose, CA 95138 PHONE: (408) 248-8333 FAX: (408) 248-8591 www.IDT.com | |
| DECIMAL | ANGULAR | | |
| X±0.01 | | | |
| XX±0.05 | | | |
| XXX±0.03 | | | |
| APPROVALS | DATE | TITLE BA/BAG144 PACKAGE OUTLINE 13.0 X 13.0 mm BODY 1.0 mm PITCH CABGA | |
| DRAWN <i>CM</i> | 08/29/13 | | |
| CHECKED | | | |
| | | SIZE | REV |
| | | C | 03 |
| | | DRAWING No. PSC-4471 | |
| | | DO NOT SCALE DRAWING | |
| | | SHEET 2 OF 2 | |

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.