

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

# RQA0005QXDQS

## Silicon N-Channel MOS FET

REJ03G1325-0100

Rev.1.00


Oct 16, 2006

### Features

- High Output Power, High Gain, High Efficiency  
Pout = +33 dBm, Linear Gain = 21 dB, PAE = 68% (f = 520 MHz)
- Compact package capable of surface mounting

### Outline

RENESAS Package code: PLZZ0004CA-A  
(Package Name : UPAK®)



1. Gate
2. Source
3. Drain
4. Source

Note: Marking is "QX".

\*UPAK is a trademark of Renesas Technology Corp.

### Absolute Maximum Ratings

(Ta = 25°C)

Item	Symbol	Ratings	Unit
Drain to source voltage	$V_{DSS}$	16	V
Gate to source voltage	$V_{GSS}$	±5	V
Drain current	$I_D$	0.8	A
Channel dissipation	$P_{ch}^{note1}$	9	W
Channel temperature	$T_{ch}$	150	°C
Storage temperature	$T_{stg}$	-55 to +150	°C

Note1: Value at  $T_c = 25^\circ\text{C}$


This Device is sensitive to Electro Static Discharge. An Adequate careful handling procedure is requested.

### Electrical Characteristics


(Ta = 25°C)

Item	Symbol	Min.	Typ	Max.	Unit	Test Conditions
Zero gate voltage drain current	$I_{DSS}$	—	—	10	$\mu A$	$V_{DS} = 16 V, V_{GS} = 0$
Gate to source leak current	$I_{GSS}$	—	—	$\pm 2$	$\mu A$	$V_{GS} = \pm 5 V, V_{DS} = 0$
Gate to source cutoff voltage	$V_{GS(off)}$	0.15	0.45	0.75	V	$V_{DS} = 6 V, I_D = 1 mA$
Forward Transfer Admittance	$ y_{fs} $	0.6	1.1	1.6	S	$V_{DS} = 6 V, I_D = 600 mA$
Input capacitance	$C_{iss}$	—	22	—	pF	$V_{GS} = 5 V, V_{DS} = 0, f = 1 MHz$
Output capacitance	$C_{oss}$	—	12	—	pF	$V_{DS} = 6 V, V_{GS} = 0, f = 1 MHz$
Reverse transfer capacitance	$C_{rss}$	—	2.6	—	pF	$V_{DG} = 6 V, V_{GS} = 0, f = 1 MHz$
Output Power	$P_{out}$	32	33	—	dBm	$V_{DS} = 6 V, I_{DQ} = 200 mA$
		1.58	2	—	W	$f = 520 MHz$
Power Added Efficiency	PAE	55	68	—	%	$P_{in} = +20 dBm(100mW)$


### Main Characteristics




Input Capacitance vs. Gate to Source Voltage




Output Capacitance vs. Drain to Source Voltage




Reverse Transfer Capacitance vs. Drain to Gate Voltage




Maximum Stable Gain,  $|S_{21}|^2$  vs. Frequency



Maximum Stable Gain,  $|S_{21}|^2$  vs. Drain Current




## Evaluation Circuit (f = 520 MHz)




C1, C8	68 pF Chip Capacitor
C2	18 pF Chip Capacitor
C3, C9	100 pF Chip Capacitor
C4, C10	1000 pF Chip Capacitor
C5, C11	2.2 $\mu$ F Electrolysis Capacitor
C6	4 pF Chip Capacitor
C7	11 pF Chip Capacitor
L1	8 Turns D: 0.5 mm, $\phi$ 2.4 mm Enamel Wire
L2	2.2 nH Chip Inductor
L3	3.3 nH Chip Inductor
R1	33 $\Omega$ Chip Resistor
R2	2.7 k $\Omega$ Chip Resistor


Output Power, Drain Current vs. Input Power




Power Gain, Power Added Efficiency vs. Input Power




Power Gain, Power Added Efficiency vs. Frequency




Input Return Loss vs. Frequency




Power Gain, Power Added Efficiency, vs. Drain to Source Voltage



Power Gain, Power Added Efficiency vs. Idling Current




S<sub>11</sub> Parameter vs. Frequency




Condition:  $V_{DS} = 6V$ ,  $I_{DQ} = 200\text{ mA}$ ,  $Z_o = 50\ \Omega$   
 100 to 1000 MHz (50 MHz Step)  
 1000 to 2500 MHz (200 MHz Step)

S<sub>21</sub> Parameter vs. Frequency




Condition:  $V_{DS} = 6V$ ,  $I_{DQ} = 200\text{ mA}$ ,  $Z_o = 50\ \Omega$   
 100 to 1000 MHz (50 MHz Step)  
 1000 to 2500 MHz (200 MHz Step)

S<sub>12</sub> Parameter vs. Frequency



Condition:  $V_{DS} = 6V$ ,  $I_{DQ} = 200\text{ mA}$ ,  $Z_o = 50\ \Omega$   
 100 to 1000 MHz (50 MHz Step)  
 1000 to 2500 MHz (200 MHz Step)

S<sub>22</sub> Parameter vs. Frequency



Condition:  $V_{DS} = 6V$ ,  $I_{DQ} = 200\text{ mA}$ ,  $Z_o = 50\ \Omega$   
 100 to 1000 MHz (50 MHz Step)  
 1000 to 2500 MHz (200 MHz Step)



## S Parameter

 $(V_{DS} = 6\text{ V}, I_{DQ} = 50\text{ mA}, Z_o = 50\ \Omega)$ 

f (MHz)	S11		S21		S12		S22	
	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)
100	0.830	-120.1	14.22	111.4	0.055	21.1	0.656	-130.6
150	0.817	-141.3	10.45	99.2	0.057	9.9	0.657	-145.7
200	0.786	-152.5	8.13	91.6	0.058	3.3	0.643	-154.5
250	0.780	-159.3	6.44	86.1	0.057	-1.0	0.645	-159.6
300	0.791	-163.6	5.37	81.6	0.057	-5.0	0.662	-162.8
350	0.785	-167.4	4.58	77.5	0.057	-8.5	0.666	-165.5
400	0.786	-170.2	3.98	74.0	0.056	-11.6	0.672	-167.8
450	0.787	-172.2	3.51	70.5	0.055	-14.4	0.677	-169.3
500	0.792	-174.1	3.14	67.4	0.055	-17.1	0.678	-170.9
550	0.791	-175.8	2.83	64.2	0.054	-19.4	0.685	-172.1
600	0.796	-177.2	2.57	61.2	0.053	-21.8	0.691	-173.4
650	0.796	-178.6	2.36	58.3	0.052	-24.1	0.697	-174.3
700	0.798	180.0	2.17	55.4	0.051	-26.3	0.703	-175.5
750	0.802	178.5	2.01	52.6	0.051	-28.5	0.713	-176.2
800	0.803	177.2	1.86	50.1	0.049	-30.4	0.718	-177.2
850	0.810	175.9	1.73	47.3	0.049	-32.6	0.724	-178.0
900	0.813	174.8	1.62	44.9	0.048	-34.4	0.727	-179.2
950	0.820	173.7	1.51	42.2	0.047	-36.2	0.736	179.9
1000	0.822	172.9	1.42	40.0	0.046	-38.1	0.744	179.0
1050	0.824	172.1	1.34	37.7	0.044	-39.9	0.750	178.1
1100	0.828	171.0	1.26	35.2	0.043	-41.6	0.758	177.0
1150	0.826	169.7	1.19	32.9	0.042	-43.1	0.762	175.9
1200	0.832	168.7	1.13	30.7	0.041	-44.8	0.770	175.1
1250	0.837	167.6	1.07	28.3	0.040	-46.2	0.774	174.0
1300	0.840	166.5	1.01	26.1	0.039	-47.7	0.781	173.2
1350	0.843	165.6	0.96	24.0	0.038	-49.2	0.785	172.2
1400	0.845	164.6	0.91	21.9	0.037	-50.7	0.792	171.3
1450	0.842	163.3	0.87	19.7	0.036	-52.1	0.797	170.1
1500	0.846	161.8	0.83	17.4	0.035	-53.3	0.800	169.1
1550	0.853	160.7	0.79	15.3	0.034	-54.6	0.803	167.9
1600	0.866	159.3	0.76	13.4	0.033	-55.6	0.809	167.0
1650	0.877	158.3	0.73	11.3	0.032	-56.7	0.814	165.8
1700	0.882	157.7	0.70	9.4	0.031	-58.2	0.815	164.9
1750	0.882	156.6	0.68	7.5	0.030	-59.4	0.819	163.7
1800	0.880	155.4	0.65	5.6	0.029	-60.5	0.826	162.2
1850	0.878	154.1	0.62	3.8	0.028	-61.3	0.829	161.1
1900	0.878	152.8	0.60	2.2	0.027	-62.4	0.832	160.0
1950	0.882	151.3	0.58	0.8	0.027	-63.3	0.837	158.9
2000	0.889	150.0	0.56	-1.0	0.026	-64.1	0.842	157.7
2050	0.899	148.8	0.53	-2.7	0.025	-65.0	0.846	156.6
2100	0.900	148.0	0.51	-4.4	0.024	-65.9	0.851	155.3
2150	0.903	146.7	0.49	-6.5	0.023	-66.3	0.853	154.5
2200	0.905	145.4	0.48	-8.5	0.022	-66.8	0.857	153.3
2250	0.904	144.5	0.46	-10.4	0.022	-66.9	0.861	152.2
2300	0.903	143.2	0.44	-12.2	0.021	-68.1	0.863	151.1
2350	0.904	142.0	0.43	-13.8	0.020	-68.6	0.871	149.9
2400	0.905	140.9	0.41	-15.7	0.019	-68.7	0.868	148.9
2450	0.908	139.6	0.40	-17.2	0.019	-69.2	0.871	147.7
2500	0.911	138.5	0.39	-18.8	0.018	-69.8	0.874	146.5

## S Parameter

(V<sub>DS</sub> = 6 V, I<sub>DQ</sub> = 100 mA, Z<sub>o</sub> = 50 Ω)

f (MHz)	S11		S21		S12		S22	
	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)
100	0.853	-132.0	16.16	107.8	0.043	18.5	0.692	-144.3
150	0.838	-150.1	11.60	97.0	0.044	8.7	0.698	-156.6
200	0.824	-159.2	8.86	90.8	0.044	3.3	0.687	-163.0
250	0.810	-164.6	7.01	86.3	0.044	0.3	0.689	-166.9
300	0.822	-168.5	5.86	82.4	0.044	-3.1	0.709	-169.7
350	0.816	-171.6	5.00	79.0	0.044	-6.1	0.709	-172.1
400	0.814	-174.1	4.35	75.9	0.043	-8.6	0.714	-174.1
450	0.818	-176.1	3.85	72.9	0.043	-11.0	0.713	-175.5
500	0.819	-177.8	3.46	70.2	0.042	-13.0	0.715	-176.8
550	0.818	-179.3	3.12	67.6	0.042	-14.8	0.718	-177.8
600	0.820	179.5	2.84	64.8	0.041	-16.7	0.723	-178.8
650	0.819	178.0	2.61	62.1	0.041	-18.4	0.728	-179.7
700	0.817	176.6	2.41	59.7	0.040	-20.5	0.726	179.3
750	0.819	175.2	2.23	57.2	0.040	-22.2	0.735	178.3
800	0.819	174.1	2.08	54.8	0.039	-23.6	0.737	177.6
850	0.821	172.8	1.94	52.5	0.039	-25.3	0.742	176.7
900	0.828	171.8	1.82	50.2	0.038	-26.8	0.745	175.8
950	0.831	170.7	1.71	47.9	0.038	-28.2	0.749	175.0
1000	0.835	170.1	1.61	45.8	0.037	-29.8	0.754	174.3
1050	0.836	169.4	1.52	43.6	0.036	-31.3	0.755	173.4
1100	0.835	168.3	1.44	41.2	0.036	-32.5	0.762	172.6
1150	0.834	167.2	1.37	39.3	0.035	-33.8	0.764	171.8
1200	0.839	166.1	1.30	37.3	0.034	-35.1	0.769	170.9
1250	0.842	165.1	1.24	35.0	0.033	-36.2	0.774	170.0
1300	0.845	164.1	1.17	33.0	0.033	-37.6	0.777	169.2
1350	0.847	163.3	1.12	30.9	0.032	-38.8	0.781	168.3
1400	0.846	162.4	1.06	28.8	0.031	-40.0	0.786	167.5
1450	0.846	161.0	1.02	26.7	0.030	-40.9	0.787	166.6
1500	0.848	159.8	0.97	24.7	0.030	-41.9	0.791	165.6
1550	0.854	158.5	0.94	22.8	0.029	-42.8	0.794	164.6
1600	0.866	157.3	0.90	20.6	0.029	-43.9	0.799	163.9
1650	0.876	156.1	0.87	18.7	0.028	-44.9	0.801	162.8
1700	0.883	155.7	0.84	16.7	0.027	-45.9	0.802	161.8
1750	0.881	154.7	0.81	14.6	0.026	-47.1	0.806	160.9
1800	0.881	153.6	0.78	12.9	0.026	-47.7	0.810	159.5
1850	0.875	152.5	0.75	11.3	0.025	-48.3	0.815	158.6
1900	0.873	151.1	0.73	9.7	0.024	-49.2	0.817	157.4
1950	0.876	149.7	0.70	8.1	0.024	-49.8	0.822	156.5
2000	0.887	148.2	0.68	6.5	0.023	-50.4	0.825	155.4
2050	0.893	147.1	0.65	4.8	0.022	-50.9	0.829	154.2
2100	0.896	146.1	0.63	2.9	0.022	-51.7	0.831	153.2
2150	0.899	145.0	0.60	1.0	0.021	-51.9	0.840	152.3
2200	0.901	144.0	0.59	-1.0	0.021	-52.2	0.843	151.4
2250	0.899	143.0	0.56	-2.8	0.020	-52.3	0.844	150.3
2300	0.897	141.9	0.55	-4.7	0.020	-53.0	0.848	149.2
2350	0.898	140.6	0.53	-6.6	0.019	-53.4	0.851	148.1
2400	0.901	139.5	0.51	-8.3	0.018	-53.6	0.854	147.2
2450	0.902	138.3	0.50	-10.0	0.018	-53.8	0.853	146.1
2500	0.904	137.3	0.48	-11.7	0.017	-53.5	0.855	144.9

## S Parameter

 $(V_{DS} = 6\text{ V}, I_{DQ} = 200\text{ mA}, Z_o = 50\ \Omega)$ 

f (MHz)	S11		S21		S12		S22	
	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)
100	0.873	-138.5	17.05	105.8	0.035	16.9	0.714	-152.4
150	0.861	-154.0	12.18	96.4	0.036	8.2	0.730	-162.4
200	0.854	-162.2	9.29	90.9	0.036	3.7	0.719	-167.9
250	0.850	-167.3	7.37	86.6	0.035	0.7	0.723	-171.4
300	0.845	-171.0	6.14	83.2	0.035	-1.7	0.742	-173.7
350	0.839	-173.8	5.26	80.2	0.035	-4.2	0.747	-175.3
400	0.837	-176.2	4.58	77.5	0.035	-6.2	0.745	-177.1
450	0.840	-178.0	4.05	74.6	0.035	-8.0	0.744	-178.4
500	0.841	-179.7	3.64	72.0	0.034	-9.9	0.748	-180.0
550	0.840	178.8	3.29	69.6	0.034	-11.5	0.748	178.9
600	0.840	177.4	3.00	67.3	0.034	-12.7	0.750	178.1
650	0.838	176.1	2.76	64.8	0.033	-14.0	0.751	177.3
700	0.838	174.8	2.57	62.5	0.033	-15.4	0.754	176.3
750	0.836	173.5	2.37	60.2	0.033	-17.2	0.759	175.5
800	0.838	172.2	2.22	57.9	0.032	-18.1	0.760	174.6
850	0.841	171.1	2.07	55.7	0.032	-19.5	0.760	173.8
900	0.844	170.0	1.95	53.8	0.031	-20.7	0.764	172.8
950	0.848	169.1	1.84	51.7	0.031	-21.9	0.766	172.1
1000	0.849	168.4	1.73	49.7	0.031	-23.0	0.772	171.2
1050	0.849	167.6	1.64	47.6	0.030	-24.3	0.770	170.7
1100	0.849	166.7	1.56	45.5	0.030	-25.3	0.773	169.6
1150	0.847	165.6	1.48	43.5	0.029	-26.2	0.777	169.0
1200	0.851	164.5	1.41	41.7	0.029	-27.3	0.779	168.0
1250	0.854	163.4	1.35	39.6	0.028	-28.1	0.782	167.2
1300	0.854	162.4	1.28	37.7	0.028	-29.1	0.785	166.6
1350	0.855	161.6	1.22	35.7	0.027	-30.0	0.788	165.6
1400	0.855	160.7	1.17	33.6	0.027	-31.0	0.790	164.9
1450	0.855	159.4	1.12	31.7	0.026	-31.5	0.792	163.9
1500	0.856	158.2	1.07	29.6	0.026	-32.4	0.793	163.2
1550	0.863	156.7	1.03	27.6	0.025	-33.2	0.795	162.2
1600	0.875	155.8	1.00	25.6	0.025	-33.7	0.799	161.4
1650	0.883	154.8	0.96	23.9	0.024	-34.5	0.802	160.5
1700	0.890	154.1	0.93	22.0	0.024	-35.4	0.804	159.5
1750	0.887	153.4	0.90	19.9	0.023	-36.0	0.806	158.4
1800	0.884	152.2	0.87	18.2	0.023	-36.8	0.812	157.4
1850	0.879	151.0	0.84	16.5	0.022	-37.0	0.811	156.7
1900	0.877	149.7	0.81	15.1	0.022	-37.4	0.811	155.4
1950	0.880	148.4	0.79	13.6	0.021	-38.3	0.818	154.4
2000	0.888	147.0	0.76	12.0	0.021	-38.6	0.821	153.5
2050	0.893	145.7	0.74	10.4	0.020	-38.8	0.821	152.5
2100	0.899	144.9	0.71	8.5	0.020	-39.1	0.828	151.2
2150	0.902	143.7	0.69	6.4	0.020	-39.5	0.831	150.4
2200	0.904	142.7	0.67	4.5	0.019	-39.4	0.837	149.6
2250	0.900	141.7	0.64	2.7	0.019	-39.2	0.834	148.7
2300	0.902	140.5	0.62	0.9	0.019	-39.9	0.843	147.4
2350	0.899	139.4	0.61	-1.1	0.018	-40.1	0.843	146.4
2400	0.899	138.2	0.59	-2.9	0.018	-40.1	0.844	145.7
2450	0.904	137.1	0.58	-4.3	0.017	-40.1	0.845	144.7
2500	0.904	136.0	0.56	-6.2	0.017	-40.1	0.847	143.3

## S Parameter

 $(V_{DS} = 6 \text{ V}, I_{DQ} = 300 \text{ mA}, Z_o = 50 \Omega)$ 


f (MHz)	S11		S21		S12		S22	
	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)
100	0.893	-138.4	17.02	105.9	0.032	17.9	0.721	-155.6
150	0.871	-154.6	12.28	96.5	0.032	8.2	0.742	-164.6
200	0.862	-162.9	9.39	91.1	0.033	4.2	0.733	-169.8
250	0.857	-167.9	7.47	86.9	0.032	1.5	0.735	-172.9
300	0.854	-171.5	6.23	83.5	0.032	-1.2	0.752	-175.1
350	0.848	-174.5	5.33	80.5	0.032	-3.5	0.758	-176.8
400	0.850	-176.8	4.66	77.7	0.032	-5.2	0.756	-178.7
450	0.850	-178.7	4.12	75.2	0.031	-7.2	0.757	-179.7
500	0.850	179.9	3.72	72.8	0.031	-8.5	0.758	179.0
550	0.846	178.3	3.35	70.3	0.031	-9.6	0.759	177.9
600	0.847	177.0	3.06	68.1	0.031	-11.2	0.762	177.1
650	0.847	175.6	2.82	65.7	0.030	-12.3	0.764	176.0
700	0.846	174.4	2.61	63.5	0.030	-13.8	0.760	175.2
750	0.843	173.0	2.43	61.3	0.030	-14.8	0.768	174.5
800	0.845	171.6	2.26	59.1	0.029	-15.8	0.766	173.7
850	0.848	170.6	2.12	56.9	0.029	-17.1	0.769	172.7
900	0.850	169.4	2.00	54.8	0.029	-18.0	0.772	172.0
950	0.853	168.4	1.88	52.8	0.028	-19.0	0.775	171.2
1000	0.857	167.8	1.77	51.0	0.028	-20.3	0.778	170.3
1050	0.855	167.1	1.68	49.0	0.028	-21.4	0.777	169.3
1100	0.856	166.2	1.60	47.0	0.027	-22.1	0.780	168.7
1150	0.854	164.9	1.53	45.0	0.027	-22.9	0.783	168.0
1200	0.855	163.9	1.45	43.1	0.026	-23.9	0.785	167.0
1250	0.858	163.1	1.38	41.2	0.026	-24.5	0.787	166.3
1300	0.860	161.9	1.32	39.4	0.026	-25.4	0.790	165.7
1350	0.859	160.8	1.26	37.2	0.025	-26.2	0.792	164.9
1400	0.859	160.1	1.20	35.3	0.025	-27.1	0.794	163.9
1450	0.860	158.9	1.15	33.4	0.024	-27.6	0.796	162.9
1500	0.861	157.6	1.11	31.3	0.024	-28.3	0.795	162.4
1550	0.866	156.3	1.07	29.5	0.024	-28.8	0.797	161.3
1600	0.880	155.2	1.04	27.6	0.023	-29.6	0.800	160.5
1650	0.889	154.3	1.00	25.7	0.023	-30.1	0.803	159.7
1700	0.895	153.6	0.97	23.9	0.022	-30.7	0.805	158.5
1750	0.892	152.9	0.93	21.9	0.022	-31.3	0.808	157.6
1800	0.886	151.5	0.91	20.1	0.022	-31.8	0.811	156.5
1850	0.883	150.4	0.88	18.6	0.021	-32.3	0.811	155.6
1900	0.880	149.3	0.85	16.9	0.021	-32.5	0.813	154.5
1950	0.882	147.9	0.82	15.5	0.020	-33.0	0.818	153.6
2000	0.889	146.3	0.79	13.9	0.020	-33.1	0.821	152.7
2050	0.899	145.1	0.77	12.1	0.020	-33.3	0.824	151.6
2100	0.902	144.1	0.74	10.5	0.019	-33.7	0.827	150.6
2150	0.907	143.1	0.72	8.6	0.019	-33.8	0.832	149.7
2200	0.907	142.3	0.69	6.4	0.019	-34.1	0.832	148.9
2250	0.904	141.3	0.67	4.7	0.018	-33.7	0.835	147.7
2300	0.901	140.0	0.65	2.9	0.018	-34.3	0.838	146.7
2350	0.902	138.9	0.63	1.0	0.018	-34.3	0.844	145.8
2400	0.904	137.7	0.62	-0.7	0.017	-34.2	0.843	145.0
2450	0.905	136.6	0.60	-2.3	0.017	-34.2	0.845	143.8
2500	0.905	135.6	0.59	-4.1	0.017	-34.5	0.847	142.5

## S Parameter

 $(V_{DS} = 6 \text{ V}, I_{DQ} = 400 \text{ mA}, Z_o = 50 \Omega)$ 

f (MHz)	S11		S21		S12		S22	
	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)	MAG	ANG (deg.)
100	0.898	-137.8	16.87	106.6	0.030	18.0	0.724	-157.3
150	0.875	-154.8	12.27	96.8	0.031	8.5	0.747	-165.4
200	0.867	-163.1	9.43	91.2	0.031	4.4	0.737	-170.5
250	0.860	-168.0	7.48	87.1	0.030	2.0	0.741	-173.6
300	0.857	-171.7	6.26	83.6	0.030	-0.7	0.760	-175.8
350	0.855	-174.5	5.35	80.9	0.030	-3.1	0.760	-177.5
400	0.851	-176.8	4.67	78.1	0.030	-4.6	0.762	-179.0
450	0.856	-178.8	4.15	75.5	0.030	-6.5	0.760	179.7
500	0.854	179.5	3.72	73.1	0.030	-7.7	0.761	178.7
550	0.851	178.1	3.37	70.7	0.030	-9.0	0.763	177.6
600	0.853	176.7	3.08	68.3	0.029	-10.3	0.766	176.5
650	0.850	175.4	2.84	65.9	0.029	-11.5	0.770	175.7
700	0.848	174.2	2.63	63.7	0.029	-12.8	0.766	174.6
750	0.848	172.8	2.44	61.6	0.028	-13.8	0.769	173.9
800	0.850	171.5	2.28	59.6	0.028	-14.8	0.771	173.3
850	0.851	170.2	2.13	57.3	0.028	-15.8	0.770	172.5
900	0.853	169.1	2.01	55.4	0.027	-16.9	0.776	171.4
950	0.857	168.3	1.89	53.7	0.027	-17.7	0.778	170.6
1000	0.861	167.6	1.79	51.6	0.027	-18.7	0.778	169.9
1050	0.858	166.8	1.70	49.6	0.027	-19.5	0.780	169.2
1100	0.860	165.9	1.61	47.6	0.026	-20.5	0.784	168.3
1150	0.856	164.8	1.53	45.5	0.026	-21.3	0.784	167.5
1200	0.859	163.7	1.46	43.7	0.025	-22.1	0.787	166.6
1250	0.862	162.5	1.40	41.7	0.025	-22.8	0.788	165.9
1300	0.861	161.7	1.33	40.0	0.025	-23.4	0.792	165.1
1350	0.862	160.8	1.27	37.9	0.024	-24.4	0.793	164.5
1400	0.862	159.9	1.21	35.8	0.024	-25.1	0.795	163.6
1450	0.861	158.6	1.17	34.1	0.023	-25.6	0.795	162.8
1500	0.864	157.4	1.12	32.2	0.023	-26.4	0.796	161.7
1550	0.870	156.0	1.08	30.3	0.023	-27.0	0.798	160.9
1600	0.882	155.0	1.05	28.1	0.022	-26.9	0.802	160.1
1650	0.891	154.0	1.01	26.4	0.022	-27.7	0.802	159.2
1700	0.895	153.4	0.98	24.5	0.022	-28.3	0.805	158.2
1750	0.892	152.5	0.95	22.8	0.021	-29.1	0.808	157.3
1800	0.888	151.3	0.92	20.9	0.021	-29.2	0.809	156.3
1850	0.884	150.3	0.89	19.3	0.021	-29.5	0.811	155.3
1900	0.881	148.9	0.86	17.9	0.020	-29.9	0.813	154.3
1950	0.883	147.5	0.83	16.3	0.020	-30.4	0.818	153.3
2000	0.892	146.1	0.81	14.6	0.019	-30.3	0.820	152.2
2050	0.899	144.8	0.78	13.1	0.019	-30.4	0.821	151.4
2100	0.903	143.8	0.75	11.2	0.019	-31.0	0.826	150.4
2150	0.907	142.9	0.73	9.4	0.019	-30.9	0.830	149.4
2200	0.910	141.8	0.70	7.1	0.018	-31.1	0.831	148.3
2250	0.906	140.8	0.68	5.4	0.018	-30.6	0.833	147.3
2300	0.903	139.8	0.66	3.6	0.018	-31.3	0.837	146.6
2350	0.906	138.6	0.65	1.8	0.017	-31.2	0.840	145.5
2400	0.905	137.4	0.63	0.0	0.017	-31.2	0.841	144.7
2450	0.906	136.4	0.61	-1.6	0.017	-31.1	0.843	143.5
2500	0.905	135.3	0.59	-3.4	0.017	-30.9	0.843	142.3

### Package Dimensions



### Ordering Information

Part Name	Quantity	Shipping Container
RQA0005QXTL-E	1000 pcs.	$\phi$ 178 mm Reel, 12 mm Emboss Taping

Notes:

1. This document is provided for reference purposes only so that Renesas customers may select the appropriate Renesas products for their use. Renesas neither makes warranties or representations with respect to the accuracy or completeness of the information contained in this document nor grants any license to any intellectual property rights or any other rights of Renesas or any third party with respect to the information in this document.
2. Renesas shall have no liability for damages or infringement of any intellectual property or other rights arising out of the use of any information in this document, including, but not limited to, product data, diagrams, charts, programs, algorithms, and application circuit examples.
3. You should not use the products or the technology described in this document for the purpose of military applications such as the development of weapons of mass destruction or for the purpose of any other military use. When exporting the products or technology described herein, you should follow the applicable export control laws and regulations, and procedures required by such laws and regulations.
4. All information included in this document such as product data, diagrams, charts, programs, algorithms, and application circuit examples, is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas products listed in this document, please confirm the latest product information with a Renesas sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas such as that disclosed through our website. (<http://www.renesas.com>)
5. Renesas has used reasonable care in compiling the information included in this document, but Renesas assumes no liability whatsoever for any damages incurred as a result of errors or omissions in the information included in this document.
6. When using or otherwise relying on the information in this document, you should evaluate the information in light of the total system before deciding about the applicability of such information to the intended application. Renesas makes no representations, warranties or guarantees regarding the suitability of its products for any particular application and specifically disclaims any liability arising out of the application and use of the information in this document or Renesas products.
7. With the exception of products specified by Renesas as suitable for automobile applications, Renesas products are not designed, manufactured or tested for applications or otherwise in systems the failure or malfunction of which may cause a direct threat to human life or create a risk of human injury or which require especially high quality and reliability such as safety systems, or equipment or systems for transportation and traffic, healthcare, combustion control, aerospace and aeronautics, nuclear power, or undersea communication transmission. If you are considering the use of our products for such purposes, please contact a Renesas sales office beforehand. Renesas shall have no liability for damages arising out of the uses set forth above.
8. Notwithstanding the preceding paragraph, you should not use Renesas products for the purposes listed below:
  - (1) artificial life support devices or systems
  - (2) surgical implantations
  - (3) healthcare intervention (e.g., excision, administration of medication, etc.)
  - (4) any other purposes that pose a direct threat to human lifeRenesas shall have no liability for damages arising out of the uses set forth in the above and purchasers who elect to use Renesas products in any of the foregoing applications shall indemnify and hold harmless Renesas Technology Corp., its affiliated companies and their officers, directors, and employees against any and all damages arising out of such applications.
9. You should use the products described herein within the range specified by Renesas, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas shall have no liability for malfunctions or damages arising out of the use of Renesas products beyond such specified ranges.
10. Although Renesas endeavors to improve the quality and reliability of its products, IC products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Please be sure to implement safety measures to guard against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other applicable measures. Among others, since the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
11. In case Renesas products listed in this document are detached from the products to which the Renesas products are attached or affixed, the risk of accident such as swallowing by infants and small children is very high. You should implement safety measures so that Renesas products may not be easily detached from your products. Renesas shall have no liability for damages arising out of such detachment.
12. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written approval from Renesas.
13. Please contact a Renesas sales office if you have any questions regarding the information contained in this document, Renesas semiconductor products, or if you have any other inquiries.



**RENESAS SALES OFFICES**

<http://www.renesas.com>

Refer to "<http://www.renesas.com/en/network>" for the latest and detailed information.

**Renesas Technology America, Inc.**  
450 Holger Way, San Jose, CA 95134-1368, U.S.A  
Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

**Renesas Technology Europe Limited**  
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.  
Tel: <44> (1628) 585-100, Fax: <44> (1628) 585-900

**Renesas Technology (Shanghai) Co., Ltd.**  
Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd, Pudong District, Shanghai, China 200120  
Tel: <86> (21) 5877-1818, Fax: <86> (21) 6887-7898

**Renesas Technology Hong Kong Ltd.**  
7th Floor, North Tower, World Finance Centre, Harbour City, 1 Canton Road, Tsimshatsui, Kowloon, Hong Kong  
Tel: <852> 2265-6688, Fax: <852> 2730-6071

**Renesas Technology Taiwan Co., Ltd.**  
10th Floor, No.99, Fushing North Road, Taipei, Taiwan  
Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

**Renesas Technology Singapore Pte. Ltd.**  
1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632  
Tel: <65> 6213-0200, Fax: <65> 6278-8001

**Renesas Technology Korea Co., Ltd.**  
Kukje Center Bldg. 18th Fl., 191, 2-ka, Hangang-ro, Yongsan-ku, Seoul 140-702, Korea  
Tel: <82> (2) 796-3115, Fax: <82> (2) 796-2145

**Renesas Technology Malaysia Sdn. Bhd**  
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No.18, Jalan Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia  
Tel: <603> 7955-9390, Fax: <603> 7955-9510