

R2A20133DSP

Critical Conduction Mode PFC Control IC

R03DS0052EJ0401 Rev.4.01 Jan 08, 2016

Description

The R2A20133D controls a boost converter to provide an active power factor correction.

The R2A20133D adopts critical conduction mode for power factor correction and realizes high efficiency and a low switching noise by zero current switching.

Because the zero current is detected by using the GND current, the ZCD Auxiliary winding is unnecessary.

The feedback loop open detection, two mode overvoltage protection, overcurrent protection are built in the R2A20133D, and can constitute a power supply system of high reliability with few external parts.


Features

- Absolute Maximum Ratings
 - Supply voltage Vcc: 24 V
 - Junction temperature Tj: –40 to +150°C
- Electrical characteristics
 - UVLO operation start voltage VH: $9.5 \text{ V} \pm 0.7 \text{ V}$
 - UVLO operation shutdown voltage VL: $8.5 \text{ V} \pm 0.4 \text{ V}$
 - UVLO hysteresis voltage Hysuvl: $1.0 \text{ V} \pm 0.4 \text{ V}$
- Functions
 - Boost converter control with critical conduction mode
 - Two mode overvoltage protection and OVP2
 - Mode 1: Dynamic OVP corresponding to a voltage rise by load change
 - Mode 2: Static OVP corresponding to overvoltage in stable.
 - OVP2: OVP2 senses the PFC output voltage by independence pin.
 - Feedback loop, open detection
 - Overcurrent protection
 - Dynamic UVP corresponding to a voltage fall by load change
 - Frequency limiter, adjustable
 - Zero Current Detect (ZCD) delay time, adjustable
 - CS pin's open detection
 - Package lineup: Pb-free SOP-8 (JEDEC)

Ordering Information

Part No.	Package Name	Package Code	Package Abbreviation	Taping Abbreviation (Quantity)
R2A20133DSP#W5	_	PRSP0008DJ-A	SP	W (2,500 pcs/reel)


Pin Arrangement



Pin Functions

Pin No.	Pin Name	Function
1	FB	Error amplifier input terminal
2	RT	Max-ON time, ZCD-delay and Frequency limiter adjustment terminal
3	COMP	Error amplifier output terminal
4	OVP2	Over voltage detection terminal
5	CS	Zero current detection and overcurrent detection input terminal
6	GND	Ground
7	OUT	Power MOSFET drive terminal
8	VCC	Supply voltage terminal

Block Diagram



Absolute Maximum Ratings

 $(Ta = 25^{\circ}C)$

Item	Symbol	Ratings	Unit	Note	
Supply Voltage	VCC	-0.3 to +24	V		
OUT terminal peak current	lpk-snk-out	+0.9	А	3	
	lpk-src-out	-0.5			
OUT terminal DC current	ldc-snk-out	+100	mA		
	Idc-src-out	-50			
COMP terminal current	Icomp	+1	mA		
		– 1			
RT terminal current	Irt	−50 to −2	μΑ		
Terminal voltage	Vt-group1	-0.3 to VCC	V	4	
	Vt-group2	-0.3 to 5.3]	5	
CS terminal voltage	Vcs	-5 to +0.3	V		
Power dissipation	Pt	0.68	W	6	
Operating ambient temperature	Ta-opr	-40 to +125	°C		
Junction temperature	Tj	-40 to +150	°C	7	
Storage temperature	Tstg	-55 to +150	°C		

Notes: 1. Rated voltages are with reference to the GND terminal.

- 2. For rated currents, inflow to the IC is indicated by (+), and outflow by (-).
- 3. Shows the transient current when driving a capacitive load.
- 4. This is the rated voltage for the following pins:
- 5. This is the rated voltage for the following pins: FB, COMP, OVP2, RT
- 6. θ ja = 120°C/W

This value is a thing mounting on $40 \times 40 \times 1.6$ [mm], a glass epoxy board of wiring density 10%.

- 7. Stresses exceeding the absolute maximum ratings may damage the device.
 - These are stress ratings only. Functional operation above the recommended operating ambient temperature range is not implied.

Extended exposure to stresses above the absolute maximum ratings may affect device reliability.

Electrical Characteristics

 $(Ta = 25^{\circ}C, VCC = 12 \text{ V}, CS = 0.04 \text{ V}, FB = 2 \text{ V}, COMP: Open, OVP2 = 1 \text{ V}, RRT = 200 \text{ k}\Omega)$

Item		Symbol	Min	Тур	Max	Unit	Test Conditions
Supply	UVLO turn-on threshold	Vuvlh	8.8	9.5	10.2	V	
	UVLO turn-off threshold	VuvII	8.1	8.5	8.9	V	
	UVLO hysteresis	Hysuvl	0.6	1.0	1.4	V	
	Standby current	Istby	_	100	200	μΑ	VCC = Vuvlh - 0.2 V
	Operating current	Icc	_	1.8	2.6	mA	
Error	Feedback voltage	Vfb	2.472	2.510	2.548	V	FB-COMP short
amplifier	Temperature stability	dVfb	_	±80	_	ppm/°C	Ta = -40 to $+125$ °C *1
	Input bias current	Ifb	-0.40	-0.15	-0.05	μΑ	Measured pin: FB
	Open loop gain	Av	_	65	_	dB	*1
	Upper clamp voltage	Vclamp-comp	3.75	4.10	4.35	V	FB = 2.45 V COMP: Open
	Low voltage	VI-comp	_	0.1	0.3	V	FB = 3.0 V COMP: Open
	Source current1	Isrc-comp1	-13.5	-10	-6	μА	FB = 1.7 V COMP = 2.5 V
	Source current2	Isrc-comp2	Isrc-comp1 ×3.3	Isrc-comp1 ×3.0	Isrc-comp1 ×2.7	μА	FB = 1.5 V COMP = 2.5 V
	Sink current	Isnk-comp	6	10	13.5	μА	FB = 3.5 V COMP = 2.5 V
	Transconductance	gm	25	46	75	μS	$FB = 2.45V \leftrightarrow 2.55 V$ $COMP = 2.5 V$
RT	RAMP offset voltage	Voff_ramp	_	1.0	_	V	*1
	RAMP amplitude	dVramp	2.90	3.1	3.3	V	*2
	RT voltage	V-rt	2.5	2.6	2.7	V	
	ZCD delay time	Zcd-delay	_	0.87	_	μs	RRT = 200 kΩ *1
	Maximum frequency	fmax	_	500	_	kHz	RRT = 200 kΩ *1
Zero	ZCD threshold voltage	Vzcd	1	3	6	mV	
current detector	Input bias current	Ics	-58	-42	-25	μΑ	Vcs = 0 V
	CS open detect threshold voltage	Vcs-open	45	72.5	130	mV	
Restart	Restart time delay	Tstart	75	150	330	μs	FB = 2.0 V COMP = 2.5 V

Notes: *1 Design spec

*2 dVramp = Vclamp_comp - Voff_ramp

Electrical Characteristics (cont.)


 $(Ta = 25^{\circ}C, VCC = 12 \text{ V}, CS = 0.04 \text{ V}, FB = 2 \text{ V}, COMP: Open, OVP2 = 1 \text{ V}, RRT = 200 \text{ k}\Omega)$

Item		Symbol	Min	Тур	Max	Unit	Test Conditions	
Out	Rise time	tr-out	_	35	100	ns	CL = 1000 pF 90%	
	Fall time	tf-out	_	35	100	ns	CL = 1000 pF 90%	
	Out low voltage	Vol1-out	_	0.08	0.2	V	Isink = 20 mA	
		Vol2-out		0.05	0.7	V	VCC = 5 V, Isink = 10 mA	
	Out high voltage	Voh-out	11.5	11.8	_	V	Isource = -20 mA	
Over current protection	OCP threshold voltage	Vocp	-0.63	-0.6	-0.57	V		
Over & Under	Dynamic OVP threshold voltage	Vdovp	_	Vfb× 1.040	_	V	Measure FB *1	
voltage protection	Dynamic UVP threshold voltage	Vduvp	_	Vfb× 0.920	_	V	*1	
	Static OVP threshold voltage	Vsovp	Vfb× 1.075	Vfb× 1.090	Vfb× 1.105	V		
	Static OVP hysteresis	Hys-sovp	50	100	150	mV		
	FB low detect threshold voltage	Vfblow	0.25	0.3	0.35	V		
	FB low detect hysteresis	Hysfblow	0.16	0.20	0.24	V		
	OVP2 high threshold voltage	Vovp2-high	Vfb× 1.18	Vfb× 1.20	Vfb× 1.22	V	Measure OVP2	
	OVP2 low threshold voltage	Vovp2-low	0.1	0.2	0.3	V		
	OVP2 source current	Isrc-ovp2	-0.40	-0.15	-0.05	μΑ		


Note: *1 Design spec

Waveforms


1. Start-up




2. Shut-down




3. Gate Drive Output




4. Overvoltage Protection (SOVP)




5. FB Low Detection




6. Overcurrent Protection (OCP)




7. Frequency Limiter




8. Overvoltage Protection 2 (OVP2)




9. OVP2 Low Detection



System Diagram



Package Dimensions



Notice

- 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information
- 2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein
- 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or
- 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.

Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.

- 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, lease evaluate the safety of the final products or systems manufactured by you
- 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations
- 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics
- 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics



SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

Refer to "http://www.renesas.com/" for the latest and detailed information.

Renesas Electronics America Inc. 2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A. Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited 9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3 Tel: +1-905-237-2004

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, German Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd. Room 1709, Quantum Plaza. No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China Tel: +88-10-8235-1155, Fax: +88-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited

Treireads Electronics from Konig Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852 2886-9022

Renesas Electronics Taiwan Co., Ltd. 13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd. 80 Bendemeer Road, Unit #06-02 Hyllux Innovation Centre, Singapore 339949 Tel: +65-6213-0200, Fax: +65-6213-0300

1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia +60-3-7955-9390, Fax: +60-3-7955-9510 Renesas Electronics Malaysia Sdn.Bhd. Unit 1207, Block B. Menara Amcorp, Amco

Renesas Electronics India Pvt. Ltd. No.777C, 100 Feet Road, HAL II Stage, Indiranagar, Bangalore, India Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd. 12F., 234 Teheran-ro, Gangnam-Gu, Seoul, 135-080, Korea Tel: +82-2-558-3737, Fax: +82-2-558-5141