RBA300N10EANS-3UA02

REXFET-1 N-Channel Power MOSFET

100 V - 340 A - 1.5 mΩ - TOLL for Automotive

Description

The RBA300N10EANS-3UA02 N-channel power MOSFET features REXFET-1 split-gate technology and is offered in a TOLL package. The TOLL package features compact and optimal thermal performance. Renesas' REXFET-1 split gate technology is suitable for applications requiring low RDS(on) and switching capability for high-power and high-frequency applications.

Features

- Standard level gate drive voltage: $V_{GS(th)}$ = 2.0 to 4.0 V
- Super low on-state resistance: $R_{DS(on)}$ = 1.5 mΩ Max.
- Low input capacitance
- Low thermal resistance
- 100% Avalanche tested
- AEC-Q101 qualified, PPAP capable
- Pb-free lead plating: RoHS compliant
- MSL1 classified according to IPC/JEDEC J-STD-020

Application

Small Traction (2-wheel, 3-wheel vehicle), 48 V load, Onboard charger, Charging station, Low voltage DC/DC

Outline



TOLL



Equivalent Circuit



Marking Specification

Absolute Maximum Ratings

(Tj = 25 °C unless otherwise notice.)

Item	Symbol	Ratings	Unit
Drain to Source Voltage	V_{DSS}	100	V
Gate to Source Voltage	V_{GSS}	±20	V
Drain Current (DC)	$I_{D(DC)}$ Tc=25°C Note 2,6	±340	A
	$I_{D(DC)}$ Tc=100°C Note 2,6	±272	A
Drain Current (Chip limitation)	$I_{D(DC)}$ Tc=25°C Notes2,6	±380	A
Drain Current (pulse)	$I_{D(pulse)}$ Notes1,3,6	±1360	A
Power Dissipation	P_D Note 1,6	468	W
Operating Junction Temperature	T_j	-55 to 175	°C
Storage Temperature	T_{stg}	-55 to 175	°C
Single Avalanche Current	I_{AS} Note 4	64	A
Single Avalanche Energy	E_{AS} Note 4	409	mJ

Thermal Resistance

Item	Symbol	Max.	Unit
Junction to Case Thermal Resistance	$R_{th(j-c)}$ Note 6	0.32	°C/W
Junction to Ambient Thermal Resistance	$R_{th(j-a)}$ Note 5,6	40	°C/W

Electrical Characteristics

(T_j = 25 °C unless otherwise notice.)

Item	Symbol	Min	Typ	Max	Unit	Test Conditions
Zero Gate Voltage Drain Current	I_{DSS}	—	—	10	μA	V_{DS} = 100 V, V_{GS} = 0 V
Gate Leakage Current	I_{GSS}	—	—	±100	nA	V_{GS} = ± 20 V, V_{DS} = 0 V
Gate to Source Threshold Voltage	$V_{GS(th)}$	2.0	—	4.0	V	V_{DS} = V_{GS}, I_D = 250 μA
Drain to Source On-state Resistance	$R_{DS(on)}$	—	1.3	1.5	mΩ	V_{GS} = 10 V, I_D = 100 A
Input Capacitance	C_{iss}	—	13000	—	pF	V_{DS} = 50 V
Output Capacitance	C_{oss}	—	3300	—	pF	V_{GS} = 0 V
Reverse Transfer Capacitance	C_{rss}	—	80	—	pF	f = 100 kHz
Gate resistance	R_g	—	1.8	—	Ω	—
Turn-on Delay Time	$t_{d(on)}$	—	75	—	ns	V_{DD} = 50 V
Rise Time	t_r	—	60	—	ns	I_D = 100 A
Turn-off Delay Time	$t_{d(off)}$	—	130	—	ns	V_{GS} = 10 V
Fall Time	t_f	—	55	—	ns	R_G = 5 Ω
Total Gate Charge	Q_g	—	170	—	nC	V_{DD} = 50 V
Gate to Source Charge	Q_{gs}	—	75	—	nC	V_{GS} = 10 V
Gate to Drain Charge	Q_{gd}	—	30	—	nC	I_D = 100 A
Gate plateau voltage	$V_{plateau}$	—	5.4	—	V	
Output Charge	Q_{oss}	—	280	—	nC	V_{DD} = 50 V, V_{GS} = 0 V
Body Diode Forward Voltage	$V_{F(S-D)}$	—	0.85	1.5	V	I_F = 100 A, V_{GS} = 0 V
Reverse Recovery Time	t_{rr}	—	110	—	ns	I_F = 100 A, V_{GS} = 0 V
Reverse Recovery Charge	Q_{rr}	—	300	—	nC	di/dt = 100 A/μs

Note 1. T_c = 25 °C

2. Value is limited by overall system design including PCB.
3. PW ≤ 10 μs
4. L = 100 μH, V_{DD} = 50 V, R_G = 25 Ω
5. Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4. (2 oz Cu pad.)
6. Defined by design. Not subject to production test.

Typical Characteristics

POWER DISSIPATION vs. CASE TEMPERATURE



DRAIN CURRENT vs. CASE TEMPERATURE



FORWARD BIAS SAFE OPERATING AREA



TRANSIENT THERMAL IMPEDANCE vs. PULSE WIDTH



TYPICAL AVALANCHE CHARACTERISTICS



TYPICAL AVALANCHE ENERGY



DRAIN CURRENT vs. DRAIN TO SOURCE VOLTAGE



DRAIN TO SOURCE ON-STATE RESISTANCE vs. DRAIN CURRENT



DRAIN TO SOURCE ON-STATERESISTANCE vs. GATE TO SOURCE VOLTAGE



DRAIN TO SOURCE ON-STATE RESISTANCE vs JUNCTION TEMPERATURERE



FORWARD TRANSFER CHARACTERISTICS



GATE TO SOURCE THRESHOLD VOLTAGE vs. JUNCTION TEMPERATURE



CAPACITANCE vs. DRAIN TO SOURCE VOLTAGE



DYNAMIC INPUT/OUTPUT CHARACTERISTICS



SOURCE TO DRAIN DIODE FORWARD VOLTAGE



DRAIN TO SOURCE BREAKDOWN VOLTAGE vs. JUNCTION TEMPERATURE



Test Circuit

Avalanche

Test Circuit



Waveform



$$E_{AS} = \frac{1}{2} \cdot L \cdot I_{AS}^{2} \cdot \frac{V_{(BR)DSS}}{V_{(BR)DSS} - V_{DD}}$$

Switching Time

Test Circuit



Waveform



Gate Charge

Test Circuit



Waveform



Reverse Recovery

Test Circuit



Waveform



Package Dimensions



Mass : 0.76 g



	DIMENSION (mm)		
SYMBOL	MIN	NOM	MAX
A	2.20	2.30	2.40
b	0.65	0.80	0.95
b1	9.65	9.80	9.95
b2	8.00	8.20	8.40
c	0.40	0.50	0.60
D	10.18	10.38	10.58
E	9.70	9.90	10.10
e	1.20BSC		
H	11.48	11.68	11.88
H1	6.65	6.95	7.25
L	1.40	1.60	1.80
L1	0.60	0.70	0.80
L2	0.45	0.60	0.75
L4	1.00	1.15	1.30



Wettable flank structure

Mount pad



Unit : mm

Ordering Information

Part No.	Packing	Quantity
RBA300N10EANS-3UA02#GB0	Taping	2000pcs/reel

Packing Specification





Unit : mm

	Symbol	Dimension
Tape Dimension	W	24
	P	12
	P0	4
	P2	2
	A0	10.3
	B0	12.1
	K0	2.7
	F	11.5
	E	1.75
	D0	1.5
	D1	1.5
	T	0.3
Reel Dimension	A	330
	N	100
	W1	25.4
	W2	29.4

Remark : Strong electric field, when exposed to this device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop generation of static electricity as much as possible, and quickly dissipate it once, when it has occurred.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
6. Renesas Electronics products are classified according to the following two quality grades: “Standard” and “High Quality”. The intended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below.
   "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
   "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

   Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user’s manual or other Renesas Electronics document.
7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION (“Vulnerability Issues”). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
8. When using Renesas Electronics products, refer to the latest product information (data sheets, user’s manuals, application notes, “General Notes for Handling and Using Semiconductor Devices” in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 October 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/.

© 2025 Renesas Electronics Corporation. All rights reserved.