

E1 Emulator

Additional Document for User's Manual
(Notes on Connection)

Supported Devices:
RL78 Family

All information contained in these materials, including products and product specifications, represents information on the product at the time of publication and is subject to change by Renesas Electronics Corp. without notice. Please review the latest information published by Renesas Electronics Corp. through various means, including the Renesas Technology Corp. website (<http://www.renesas.com>).

Notice

- All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.

Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.

You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.

Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.

When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.

Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.

Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics.

The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.

"Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.

You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.

Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.

Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.

This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.

Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

Table of Contents

Chapter 1	Outline	4
1.1	Features	4
1.2	Configuration of Manuals	4
Chapter 2	Designing the User System	5
2.1	Connecting the Emulator with the User System	5
2.2	Pin Assignment of the Connector on the User System	6
2.3	Recommend Circuit between the Connector and the CPU	7
2.3.1	Recommend Circuit Connection.....	7
2.3.2	Regarding Connection of RESET.....	7
Chapter 3	Specification	10
Chapter 4	Notes on Usage.....	11
4.1	List	11
4.2	Details	11

Chapter 1 Outline

1.1 Features

E1 Emulator is an on-chip debug emulator with flash programming function, which is used for debugging and programming a program to be embedded in on-chip flash memory microcontrollers. This product can debug with the target microcontroller connected to the user system, and can write programs to the on-chip flash memory of microcontrollers.

1.2 Configuration of Manuals

Documentation for the E1/E20 emulator manual is in two parts: the E1/E20 Emulator User's Manual and the E1/E20 Emulator Supplementary Document for the User's Manual (this manual). Different versions of the latter correspond to different sets of MCU. Be sure to read both of the manuals before using the E1/E20 emulator (hereinafter referred to as "the emulator").

The E1/E20 emulator user's manual has the following contents:

- Components of the emulators
- Emulator hardware specification
- Connection to the emulator and the host computer and user system

The E1/E20 Emulator Supplementary Document for the User's Manual has the following contents:

- For use in hardware design, an example of connection and the interface circuit required to connect the emulator.
- Notes on using the emulator
- Software specifications and so on for using each microcomputers

Chapter 2 Designing the User System

To connect the E1 emulator (hereinafter referred to as the emulator), a connector for the user system interface cable must be mounted on the user system. When designing the user system, read this section of this manual and the hardware manual for the MCUs.

2.1 Connecting the Emulator with the User System


Table 2-1 shows the connector type numbers of the E1 emulators.

Table 2-1 Connector Type Numbers

	Type Number	Manufacturer	Specifications
14-pin Connector	7614-6002	Sumitomo 3M Limited	14-pin straight type (Japan)
	2514-6002	3M Limited	14-pin straight type (other countries)

Figures 2-1 and 2-2 show examples of the connection between a user system interface cable of the 14-pin type. Do not mount other components with a height exceeding 10 mm within 5 mm of the connector on the user system.

Figure 2-1 Connecting the User System Interface Cable to the 14-pin Connector of the E1 Emulator



2.2 Pin Assignment of the Connector on the User System

Table 2-2 shows the pin assignments of the 14-pin connectors.

Table 2-2 Pin assignments of the connector (14-pin)

Pin No.	Signal (—: Low Active)	Input/Output ^{note}
1	R.F.U	-
2	GND	-
3	R.F.U	-
4	R.F.U	-
5	TOOL0	Input/Output
6	$\overline{\text{TRESET}}$	Input
7	R.F.U	-
8	VDD	-
9	EMVDD	-
10	$\overline{\text{RESET}}$	Output
11	R.F.U	-
12	GND	-
13	$\overline{\text{RESET}}$	Output
14	GND	-

Note: Input to or output from the emulator


2.3 Recommend Circuit between the Connector and the CPU

2.3.1 Recommend Circuit Connection

Refer to Figure 2-2 and design an appropriate circuit.

Be sure to take into consideration the specifications of the target device as well as measures to prevent noise when designing your circuit.

Figure 2-2 Recommended Circuit Connection



Note 1 The circuit enclosed by a dashed line is not required when only flash programming is performed.

Note 2 Pull-up resistor is not required if the reset circuit on the user system contains no buffers and the reset signal is only generated via resistors or capacitors.

Note 3 The drive power supply of TOOL0 is different depending on devices. Defer to user's manual of device.

2.3.2 Regarding Connection of RESET

This section describes the connection of the reset pin, for which special attention must be paid, in the circuit connection example shown in the previous section.

During on-chip debugging, a reset signal from the user system is input to the emulator, masked, and then output to the target device. Therefore, the reset signal connection varies depending on whether the emulator is connected.

For flash programming, the circuit must be designed so that the reset signals of the user system and the emulator do not conflict.

Select one of the following methods and connect the reset signal in the circuit. The details of each method are described on the following pages.


- (1) Automatically switching the reset signal via series resistor (recommended; described in recommended circuit connection in the previous section)
- (2) Manually switching the reset signal with jumper
- (3) Resetting the target device by power-on reset (POR) only

- (1) Automatically switching the reset signal via series resistor

Figure 2-3 illustrates the reset pin connection described in 2.3.1 Recommend Circuit Connection.

This connection is designed assuming that the reset circuit on the user system contains an N-ch open-drain buffer (output resistance: 100Ω or less). The VDD or GND level may be unstable when the logic of $\overline{\text{TRESET}}$ / $\overline{\text{RESET}}$ of the emulator is inverted, so observe the conditions described below in **Remark**.

Figure 2-3 Circuit Connection with Reset Circuit That Contains Buffer




Remark Make the resistance of R1 at least ten times that of R2, R1 being 10 kΩ or more.

Pull-up resistor R2 is not required if the buffer of the reset circuit consists of CMOS output.

The circuit enclosed by a dashed line is not required when only flash programming is performed.

Figure 2-4 illustrates the circuit connection for the case where the reset circuit on the user system contains no buffers and the reset signal is only generated via resistors or capacitors. Design the circuit, observing the conditions described below in **Remark**.

Figure 2-4 Circuit Connection with Reset Circuit That Contains No Buffers




Remark Make the resistance of R1 at least ten times that of R2, R1 being 10 kΩ or more.

The circuit enclosed by a dashed line is not required when only flash programming is performed.

- (2) Manually switching the reset signal with jumper

Figure 2-5 illustrates the circuit connection for the case where the reset signal is switched using the jumper, with or without the emulator connected. This connection is simple, but the jumper must be set manually.

Figure 2-5 Circuit in connection for Switching Reset Signal with Jumper




(3) Resetting the target device by power-on reset (POR) only

Figure 2-6 illustrates the circuit connection for the case where the target device is only reset via POR without using the reset pin. RESET is valid only when the debugger is running or during flash programming.

Do not turn off a power supply of the user system during a break.

Figure 2-6 Circuit Connection for the Case Where Target Device Is Only Reset via POR



Chapter 3 Specification

Specifications are shown in Table 3-1 below.

Table 3-1 E1 Specification

Large Item	Middle Item	Small Item	Specification
Hardware Common	Target host machine		Computer equipped with a USB port OS is due to the software tool.
	User system interface		14-pin connector
	Host machine interface		USB2.0 (Full speed/ High speed)
	Connection to the user system		Connection by the provided user-system interface cable
	Power supply function		3.3V or 5.0V, set in software tool, can be supplied to the user system from VDD pin of the emulator (with current up to 200 mA)
	Power supply for the emulator		No need (the host computer supplies power through the USB)
Related debugging	Break	Software break	2000 points
		Hardware break	1points (commonly used by execution and access)
		Forced break	Available
	Event	Number of events	1points (commonly used by execution and access)
		Available function	Only hardware break
	Trace		Unavailable
	Performance measurement	Measurement item	From run to break
		Performance	Resolution 100us, Max. measurement time 100 hour
	Real time RAM monitor		Available (CPU is used when monitoring)
	Direct memory modification		Available (CPU is used when executing)
	Hot plug-in		Unavailable
	Security		10-byte ID code authentication
Related programming	Clock supply		Clock mounted on the user system can be used
	Security flag setting		Available
	Standalone operation		Unavailable (must be connected to host machine)

Chapter 4 Notes on Usage

Make sure to read the notes on usage in this section.

4.1 List

Table 4-1 List of notes on usage

No.	Item
1	Handling of device that was used for debugging
2	Flash self programming
3	Operation after reset
4	Operation when debugger starts
5	Operation at voltage with which flash memory cannot be written
6	On-chip debugging option byte setting (address C3H)
7	Pseudo real-time RAM monitor function

4.2 Details

No. 1 Handling of device that was used for debugging

Do not mount a device that was used for debugging on a mass-produced product, because the flash memory was rewritten during debugging and the number of rewrites of the flash memory cannot be guaranteed.

Moreover, do not embed the debug monitor program into mass-produced products.

No. 2 Flash self programming

If a space where the debug monitor program is allocated is rewritten by flash self programming, the debugger can no longer operate normally. This caution also applies to boot swapping for such an area

No. 3 Operation after reset

After an external pin reset or internal reset, the monitor program performs debug initialization processing. Consequently, the time from reset occurrence until user program execution differs from that in the actual device operation. If “No” is selected in the Permit Flash Programming of the debug tool property, the time until the user program is executed compared with the time when “Yes” is selected is delayed several 100 ms.

No. 4 Operation when debugger starts

When the debugger is started and there is no the debug monitor program in device to debug, the internal flash memory is erased.

No. 5 Operation at voltage with which flash memory cannot be written

If any of the following debugger operations <1> to <7>, which involve flash memory rewriting, is performed while flash memory cannot be rewritten, the debugger automatically changes the register setting so as to enable flash memory rewriting, and restores the register setting after the operation is completed. If any of the

following operations <1> to <7> is performed while flash memory rewriting has been disabled or operation is performed at a voltage with which flash memory cannot be rewritten, however, the debugger outputs an error and the operation is ignored.

<1> Writing to internal flash memory

<2> Setting or canceling of software breakpoint

<3> Starting execution at the set software breakpoint position

<4> Step execution at the set software breakpoint position

<5> Step-over execution, Return Out execution

<6> Come Here

<7> If permit is selected in the Flash Programming area in the Configuration dialog box, the following operations cannot be performed.

- a) Setting, changing, or canceling of hardware breaks
- b) Masking/unmasking of internal reset
- c) Switching of peripheral breaks

No. 6 On-chip debugging option byte setting (address C3H)

The on-chip debugging option byte setting is rewritten arbitrarily by the debugger.

No. 7 Pseudo real-time RAM monitor function

Note the following points when using the pseudo real-time RAM monitor function.

<1> Standby mode (HALT or STOP) may be cancelled during monitoring.

<2> The pseudo real-time RAM monitor function does not operate while the CPU operating clock is stopped.

<3> The pseudo real-time RAM monitor function does not operate while the self programming execution.

E1 Emulator

Additional Document for Preliminary User's Manual (Notes on Connection

Publication Date: Rev.1.00 Jun 06, 2011

Published by: Renesas Electronics Europe GmbH



Renesas Electronics Corporation

SALES OFFICES

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.

2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A.

Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited

1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada

Tel: +1-905-898-5441, Fax: +1-905-898-3220

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K

Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany

Tel: +49-211-65030, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.

7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China

Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.

Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China

Tel: +86-21-5877-1818, Fax: +86-21-6887-7858 / -7898

Renesas Electronics Hong Kong Limited

Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong

Tel: +852-2886-9318, Fax: +852 2886-9022/9044

Renesas Electronics Taiwan Co., Ltd.

7F, No. 363 Fu Shing North Road Taipei, Taiwan

Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.

1 harbourFront Avenue, #06-10, keppel Bay Tower, Singapore 098632

Tel: +65-6213-0200, Fax: +65-6278-8001

Renesas Electronics Malaysia Sdn.Bhd.

Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia

Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics Korea Co., Ltd.

11F., Samik Lavied' or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea

Tel: +82-2-558-3737, Fax: +82-2-558-5141

E1 Emulator

Additional Document for User's Manual (Notes on Connection)



Renesas Electronics Corporation