

## TP65H030G4PRS

650V SuperGaN® GaN FET in TOLT (source tab)

### Description


The TP65H030G4PRS 650V, 30mΩ Gallium Nitride (GaN) FET is a normally-off device using Renesas' Gen IV plus platform. It combines a state-of-the-art high voltage GaN HEMT with a low voltage silicon MOSFET to offer superior performance, standard drive, ease of adoption and reliability.

The Gen IV plus SuperGaN® platform uses advanced epi and patented design technologies to simplify manufacturability while improving efficiency over silicon via lower gate charge, output capacitance, crossover loss, and reverse recovery charge.


### Benefits

- Superior normally off architecture with D-mode GaN HEMT
- Compatible with standard silicon drivers
- Enhanced noise immunity with a 4V threshold voltage with no negative gate drive required
- Enables high-efficiency, high power density, and reliable power conversion
- Facilitates cost-effective GaN adoption reducing system size, weight, and costs


### Product and Schematic Diagrams



TP65H030G4PRS TOLT



Cascode Schematic Symbol



Cascode Device Structure

### Features

- Ultra-fast switching Gen IV plus GaN
- JEDEC-qualified GaN technology
- Dynamic  $R_{DS(on)eff}$  production tested
- Zero reverse recovery charge
- Reduced crossover loss
- RoHS compliant and Halogen-free packaging

### Applications

- AI datacenter and telecom power supplies
- E-mobility charging
- PV inverter
- UPS
- BESS



### Specifications

|                                          |      |
|------------------------------------------|------|
| $V_{DS}$ (V)                             | 650  |
| $V_{DSS(TR)}$ (V) maximum                | 800  |
| $R_{DS(on)}$ (mΩ) maximum <sup>[1]</sup> | 41   |
| $Q_{OSS}$ (nC) typical                   | 135  |
| $Q_G$ (nC) typical                       | 24.5 |

1. Dynamic  $R_{DS(on)}$  (see Figure 20 and Figure 21)

## Contents

|                                                |           |
|------------------------------------------------|-----------|
| <b>1. Pin Information</b>                      | <b>3</b>  |
| 1.1 Pin Assignments                            | 3         |
| 1.2 Pin Descriptions                           | 3         |
| <b>2. Specifications</b>                       | <b>4</b>  |
| 2.1 Absolute Maximum Ratings                   | 4         |
| 2.2 Thermal Specifications                     | 4         |
| 2.3 Circuit Implementation                     | 5         |
| 2.4 Electrical Specifications – Forward Device | 6         |
| 2.5 Electrical Specifications – Reverse Device | 7         |
| <b>3. Typical Performance Graphs</b>           | <b>8</b>  |
| <b>4. Test Circuits and Waveforms</b>          | <b>12</b> |
| <b>5. Package Outline Drawings</b>             | <b>13</b> |
| <b>6. Design Considerations</b>                | <b>13</b> |
| <b>7. Related Information</b>                  | <b>14</b> |
| <b>8. Ordering Information</b>                 | <b>14</b> |
| <b>9. Revision History</b>                     | <b>14</b> |

## Figures

|                                                                       |    |
|-----------------------------------------------------------------------|----|
| Figure 1. Pin Assignments – Bottom View                               | 3  |
| Figure 2. Simplified Half-Bridge Schematic                            | 5  |
| Figure 3. Typical Output Characteristics, $T_J = 25^{\circ}\text{C}$  | 8  |
| Figure 4. Typical Output Characteristics, $T_J = 150^{\circ}\text{C}$ | 8  |
| Figure 5. Typical Transfer Characteristics                            | 8  |
| Figure 6. Normalized On-Resistance                                    | 8  |
| Figure 7. Typical Capacitance                                         | 9  |
| Figure 8. Typical $C_{OSS}$ Stored Energy                             | 9  |
| Figure 9. Typical $Q_{OSS}$                                           | 9  |
| Figure 10. Typical Gate Charge                                        | 9  |
| Figure 11. Power Dissipation                                          | 10 |
| Figure 12. Current Derating                                           | 10 |
| Figure 13. Forward Characteristics of Rev. Diode                      | 10 |
| Figure 14. Transient Thermal Resistance                               | 10 |
| Figure 15. Safe Operating Area $T_C = 25^{\circ}\text{C}$             | 11 |
| Figure 16. Switching Time Test Circuit                                | 12 |
| Figure 17. Switching Time Waveform                                    | 12 |
| Figure 18. Diode Characteristics Test Circuit                         | 12 |
| Figure 19. Diode Recovery Waveform                                    | 12 |
| Figure 20. Dynamic $R_{DS(on)eff}$ Test Circuit                       | 12 |
| Figure 21. Dynamic $R_{DS(on)eff}$ Waveform                           | 12 |

## 1. Pin Information

### 1.1 Pin Assignments




Figure 1. Pin Assignments

### 1.2 Pin Descriptions

| Pin Number             | Pin Name | Description    |
|------------------------|----------|----------------|
| 1, 2, 3, 4, 5, 6, 7, 8 | D        | Drain.         |
| 9                      | G        | Gate.          |
| 10                     | KS       | Kelvin Source. |
| 11, 12, 13, 14, 15, 16 | S        | Source.        |

## 2. Specifications


### 2.1 Absolute Maximum Ratings

$T_c = 25^\circ\text{C}$  unless otherwise stated.

**Caution:** Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions can adversely impact product reliability and result in failures not covered by warranty.

| Symbol                                | Parameter                                                                    | Minimum | Maximum | Unit             |
|---------------------------------------|------------------------------------------------------------------------------|---------|---------|------------------|
| $V_{DSS}$                             | Drain to source voltage ( $T_J = -55^\circ\text{C}$ to $150^\circ\text{C}$ ) | -       | 650     | V                |
| $V_{DSS(TR)}, \text{ non-repetitive}$ | Transient drain to source voltage, non-repetitive <sup>[1]</sup>             | -       | 800     |                  |
| $V_{DSS(TR)}, \text{ repetitive}$     | Transient drain to source voltage, repetitive <sup>[2]</sup>                 | -       | 750     |                  |
| $V_{GSS}$                             | Gate to source voltage                                                       | -20     | +20     |                  |
| $P_D$                                 | Maximum power dissipation at $T_c = 25^\circ\text{C}$                        | -       | 192     | W                |
| $I_D$                                 | Continuous drain current at $T_c = 25^\circ\text{C}$ <sup>[3]</sup>          | -       | 55.7    | A                |
|                                       | Continuous drain current at $T_c = 100^\circ\text{C}$ <sup>[3]</sup>         | -       | 35      | A                |
| $I_{DM}$                              | Pulsed drain current (pulse width: 10 $\mu\text{s}$ )                        | -       | 230     | A                |
| $T_J$                                 | Operating temperature junction                                               | -55     | +150    | $^\circ\text{C}$ |
| $T_S$                                 | Storage temperature                                                          | -55     | +150    | $^\circ\text{C}$ |
| $T_{SOLD}$                            | Reflow soldering temperature <sup>[4]</sup>                                  | -       | 260     | $^\circ\text{C}$ |


1. In off-state, spike duration < 30 $\mu\text{s}$ , non-repetitive.
2. Off-state, spike duration < 5 $\mu\text{s}$ .
3. For increased stability at high current operation, see [Circuit Implementation](#).
4. Reflow MSL3.



### 2.2 Thermal Specifications

| Symbol          | Condition           | Typical Value | Unit               |
|-----------------|---------------------|---------------|--------------------|
| $R_{\theta JC}$ | Junction-to-case    | 0.65          | $^\circ\text{C/W}$ |
| $R_{\theta JA}$ | Junction-to-ambient | 40            |                    |

## 2.3 Circuit Implementation



**Figure 2. Simplified Half-Bridge Schematic**

Recommended gate drive: (0V, 12V) with  $R_{G(tot)} = 30\Omega$  <sup>[1]</sup>

| Gate Ferrite Bead (FB1) | Recommended DC Link RC Snubber ( $RC_{DCL}$ ) <sup>[2]</sup> |
|-------------------------|--------------------------------------------------------------|
| 120 $\Omega$ at 100MHz  | 10nF + 2.3 $\Omega$                                          |

1. For bridge topologies only.
2. Place  $RC_{DCL}$  as close as possible to the drain pin.

For additional driver configurations/options, see application note [Recommended External Circuitry for Renesas GaN FETs](#).

## 2.4 Electrical Specifications – Forward Device

$T_J = 25^\circ\text{C}$  unless otherwise stated.

| Symbol                  | Parameter                                         | Test Conditions                                                                                                                                                | Minimum | Typical | Maximum | Unit                 |
|-------------------------|---------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|---------|---------|----------------------|
| $V_{DSS(BL)}$           | Maximum drain-source voltage                      | $V_{GS} = 0V$                                                                                                                                                  | 650     | -       | -       | V                    |
| $V_{GS(th)}$            | Gate threshold voltage                            | $V_{DS} = V_{GS}, I_D = 1mA$                                                                                                                                   | 3.3     | 4       | 4.8     | V                    |
| $\Delta V_{GS(th)}/T_J$ | Gate threshold voltage temperature coefficient    |                                                                                                                                                                | -       | -6.5    | -       | mV/ $^\circ\text{C}$ |
| $R_{DS(on)eff}$         | Drain-source on-resistance <sup>[1]</sup>         | $V_{GS} = 12V, I_D = 30A, T_J = 25^\circ\text{C}$                                                                                                              | -       | 30      | 41      | m $\Omega$           |
|                         |                                                   | $V_{GS} = 12V, I_D = 30A, T_J = 150^\circ\text{C}$                                                                                                             | -       | 62      | -       |                      |
| $I_{DSS}$               | Drain-to-source leakage current                   | $V_{DS} = 650V, V_{GS} = 0V, T_J = 25^\circ\text{C}$                                                                                                           | -       | 3       | 30      | $\mu\text{A}$        |
|                         |                                                   | $V_{DS} = 650V, V_{GS} = 0V, T_J = 150^\circ\text{C}$                                                                                                          | -       | 20      | -       |                      |
| $I_{GSS}$               | Gate-to-source forward leakage current            | $V_{GS} = 20V$                                                                                                                                                 | -       | -       | 400     | $\mu\text{A}$        |
|                         | Gate-to-source reverse leakage current            | $V_{GS} = -20V$                                                                                                                                                | -       | -       | -400    |                      |
| $C_{iss}$               | Input capacitance                                 | $V_{GS} = 0V, V_{DS} = 400V, f = 1MHz$                                                                                                                         | -       | 1500    | -       | pF                   |
| $C_{oss}$               | Output capacitance                                |                                                                                                                                                                | -       | 127     | -       |                      |
| $C_{rss}$               | Reverse transfer capacitance                      |                                                                                                                                                                | -       | 4.6     | -       |                      |
| $C_{O(er)}$             | Output capacitance, energy related <sup>[2]</sup> | $V_{GS} = 0V, V_{DS} = 0V \text{ to } 400V$                                                                                                                    | -       | 183     | -       | pF                   |
| $C_{O(tr)}$             | Output capacitance, time related <sup>[3]</sup>   |                                                                                                                                                                | -       | 339     | -       |                      |
| $Q_G$                   | Total gate charge                                 | $V_{DS} = 400V, V_{GS} = 0V \text{ to } 12V, I_D = 30A$                                                                                                        | -       | 24.5    | -       | nC                   |
| $Q_{GS}$                | Gate-source charge                                |                                                                                                                                                                | -       | 8.4     | -       |                      |
| $Q_{GD}$                | Gate-drain charge                                 |                                                                                                                                                                | -       | 6.6     | -       |                      |
| $Q_{oss}$               | Output charge                                     | $V_{GS} = 0V, V_{DS} = 0V \text{ to } 400V$                                                                                                                    | -       | 135     | -       | nC                   |
| $t_{D(on)}$             | Turn-on delay                                     | $V_{DS} = 400V, V_{GS} = 0V \text{ to } 12V, R_{G(on)} = 10\Omega, R_{G(off)} = 30\Omega, I_D = 30A, Z_{FB} = 180\Omega \text{ at } 100MHz$<br>(see Figure 16) | -       | 26.4    | -       | ns                   |
| $t_R$                   | Rise time                                         |                                                                                                                                                                | -       | 6.4     | -       |                      |
| $t_{D(off)}$            | Turn-off delay                                    |                                                                                                                                                                | -       | 63.6    | -       |                      |
| $t_F$                   | Fall time                                         |                                                                                                                                                                | -       | 5.2     | -       |                      |

1. Dynamic  $R_{DS(on)}$ , 100% tested; see Figure 20 and Figure 21 for conditions.
2. Equivalent capacitance to give same stored energy from 0V to 400V.
3. Equivalent capacitance to give same charging time from 0V to 400V.

## 2.5 Electrical Specifications – Reverse Device


$T_J = 25^\circ\text{C}$  unless otherwise stated.

| Symbol   | Parameter                              | Test Conditions                                                       | Minimum | Typical | Maximum | Unit |
|----------|----------------------------------------|-----------------------------------------------------------------------|---------|---------|---------|------|
| $I_S$    | Reverse current                        | $V_{GS} = 0V$ , $T_C = 100^\circ\text{C}$ ,<br>$\leq 25\%$ duty cycle | -       | -       | 32      | A    |
| $V_{SD}$ | Reverse voltage <sup>[1]</sup>         | $V_{GS} = 0V$ , $I_S = 32A$                                           | -       | 1.8     | -       | V    |
|          |                                        | $V_{GS} = 0V$ , $I_S = 16A$                                           | -       | 1.3     | -       |      |
| $t_{RR}$ | Reverse recovery time                  | $I_S = 10A$ , $V_{DD} = 400V$ ,<br>$di/dt = 1000A/\mu s$              | -       | 36      | -       | ns   |
| $Q_{RR}$ | Reverse recovery charge <sup>[2]</sup> |                                                                       | -       | 0       | -       | nC   |

1. Includes dynamic  $R_{DS(on)}$  effect.
2. Excludes  $Q_{oss}$ .


### 3. Typical Performance Graphs

$T_c = 25^\circ\text{C}$  unless otherwise stated.




**Figure 3. Typical Output Characteristics,  $T_J = 25^\circ\text{C}$**

Parameter:  $V_{GS}$




**Figure 4. Typical Output Characteristics,  $T_J = 150^\circ\text{C}$**

Parameter:  $V_{GS}$



**Figure 5. Typical Transfer Characteristics**

$V_{DS} = 10\text{V}$ , parameter:  $T_J$



**Figure 6. Normalized On-Resistance**

$I_D = 30\text{A}$ ,  $V_{GS} = 12\text{V}$






Figure 7. Typical Capacitance  
 $V_{GS} = 0V, f = 1MHz$




Figure 8. Typical  $C_{oss}$  Stored Energy




Figure 9. Typical  $Q_{OSS}$






Figure 10. Typical Gate Charge  
 $I_{DS} = 30A, V_{DS} = 400V$




**Figure 11. Power Dissipation**




**Figure 12. Current Derating**

Pulse width  $\leq 10\mu s$ ,  $V_{GS} \geq 12V$



**Figure 13. Forward Characteristics of Rev. Diode**

$I_S = f(V_{SD})$ , parameter:  $T_J$



**Figure 14. Transient Thermal Resistance**






Figure 15. Safe Operating Area  $T_c = 25^\circ\text{C}$

## 4. Test Circuits and Waveforms




**Figure 16. Switching Time Test Circuit**


(For methods to ensure clean switching, see [Circuit Implementation](#))




**Figure 17. Switching Time Waveform**




**Figure 18. Diode Characteristics Test Circuit**



**Figure 19. Diode Recovery Waveform**




**Figure 20. Dynamic  $R_{DS(on)eff}$  Test Circuit**



**Figure 21. Dynamic  $R_{DS(on)eff}$  Waveform**

## 5. Package Outline Drawings



## 6. Design Considerations

The fast switching of GaN devices reduces current-voltage crossover losses and enables high-frequency operation while simultaneously achieving high efficiency. However, taking full advantage of the fast switching characteristics of GaN switches requires adherence to specific PCB layout guidelines and probing techniques.

Before evaluating Renesas GaN devices, see application note [Printed Circuit Board Layout and Probing for GaN Power Switches](#). The following table provides some practical rules to follow during the evaluation.

| When Evaluating Renesas GaN Devices:                                                                         |                                                                     |
|--------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------|
| DO                                                                                                           | DO NOT                                                              |
| Minimize circuit inductance by keeping traces short, both in the drive and power loop.                       | Twist the pins of TO-220 or TO-247 to accommodate GDS board layout. |
| Minimize lead length of TO-220 and TO-247 package when mounting to the PCB.                                  | Use long traces in drive circuit, long lead length of the devices.  |
| Use shortest sense loop for probing; attach the probe and its ground connection directly to the test points. | Use differential mode probe or probe ground clip with long wire.    |

## 7. Related Information

The complete technical library of GaN design tools can be found at [Renesas](#):

- Evaluation kits
- Application notes
- Design guides
- Simulation models
- Technical papers and presentations

Specific resources include:

- [Printed Circuit Board Layout and Probing for Gan Power Switches](#)
- [Recommendations for Vapor Phase Reflow](#)
- [Recommended External Circuitry for GaN FETs](#)

## 8. Ordering Information

| Part Number   | Package Description |
|---------------|---------------------|
| TP65H030G4PRS | TOLT                |

## 9. Revision History

| Revision | Date         | Description      |
|----------|--------------|------------------|
| 1.00     | Jun 25, 2025 | Initial release. |

## IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

### Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,  
Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

### Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit [www.renesas.com/contact-us/](http://www.renesas.com/contact-us/).

### Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.