

### R0E001000PKZ00

REJ10J1896-0200

Rev.2.00

Converter Board for Connecting R0E001000FLX10 to Pitch Converter Board for PC7501

Apr 16, 2010

### 1. Outline

The R0E001000PKZ00 is a converter board for connecting the flexible cable R0E001000FLX10 to a pitch converter board for PC7501.

### 2. Package Components (See Figure 1)

Check to see if the R0E001000PKZ00 package has all the following contents before using this product.

- (1) R0E001000PKZ00 converter board ..... 1 pc.
- (2) R0E001000PKZ00 User's Manual (this manual)

### 3. Specifications

Table 1 Specifications

Insertion/removal iterations of connector	50 times guaranteed
---	---------------------

### 4. Usage (See Figure 2)

The R0E001000PKZ00 can be used for debugging and on-board evaluation in common by mounting the NQPACKxxxxx on the user system.

- (1) For debugging  
Mount the NQPACKxxxxx on the foot pattern of the user system and attach the YQPACKxxxxx on it. In addition, connect the pitch converter board for PC7501 to the YQPACKxxxxx and attach the R0E001000PKZ00 on it. Finally, connect the flexible cable R0E001000FLX10 of the emulator to the upper connector of the R0E001000PKZ00.
- (2) For on-board evaluation  
Mount an MCU with on-chip flash memory or one-time PROM and the HQPACKxxxxx (not included) in order on the NQPACKxxxxx on the user system.

Before using the R0E001000PKZ00, be sure to read the precautions on page 3.

[Connectable PC7501 converter boards]

- For the MCU Unit R0E530640MCU00
  - 100-pin 0.5mm pitch : M3T-F160-100NSD
  - 100-pin 0.65mm pitch : M3T-F160-100NRB
- For the MCU Unit R0E530650MCU00
  - 100-pin 0.5mm pitch : M3T-F160-100NSD
  - 100-pin 0.65mm pitch : M3T-F160-100NRB
  - 80-pin 0.65mm pitch : M3062PT-80FPB
  - 128-pin 0.5mm pitch : M3T-F160-128NRD




Figure 1 Package components of the R0E001000PKZ00




Figure 2 Usage of the R0E001000PKZ00

### 5. Connection Procedure (See Figure 3)

The procedure for connecting the R0E001000PKZ00 is shown below.

- (1) Mount the NQPACKxxxxx on the user system.
- (2) Attach the YQPACKxxxxx on the NQPACKxxxxx.
- (3) Secure the four corners of the YQPACKxxxxx with the YQ-GUIDEs.

- Do NOT use the screws included with the YQPACKxxxxx for fixing the YQPACKxxxxx.
- Do NOT use the screwdriver included with the NQPACKxxxxx for fixing the YQ-GUIDEs. That is used only for the HQPACKxxxxx.

- (4) Mount the pitch converter board for PC7501 on the YQPACKxxxxx.
- (5) Attach the R0E001000PKZ00 on the pitch converter board for PC7501
- (6) Connect the flexible cable R0E001000FLX10 of the emulator to the R0E001000PKZ00.




Figure 3 Connection procedure of the R0E001000PKZ00

### 6. External Dimensions




Figure 4 External dimensions of the R0E001000PKZ00

## 7. Precautions and WEEE Directive

**IMPORTANT**

## Notes on This Product:

- We cannot accept any request for repair.

## Disposal Instruction (This is only valid in the European Union.):



Renesas development tools and products are directly covered by the European Union's Waste Electrical and Electronic Equipment, (WEEE), Directive 2002/96/EC. As a result, this equipment, including all accessories, must not be disposed of as household waste but through your locally recognised recycling or disposal schemes. As part of our commitment to environmental responsibility Renesas also offers to take back the equipment and has implemented a Tools Product Recycling Program for customers in Europe. This allows you to return equipment to Renesas for disposal through our approved Producer Compliance Scheme. To register for the program, click here "<http://www.renesas.com/weee>".

## 8. Correspondence of Connectors CN1 and CN2

Table 2 Correspondence of the connectors

CN1 Pin No.	IC1	CN1 Pin No.	IC1	CN2 Pin No.	IC1	CN2 Pin No.	IC1
1	-	100	-	1	-	100	-
2	-	99	-	2	-	99	-
3	-	98	-	3	-	98	-
4	-	97	-	4	-	97	-
5	CN4-36b	96	CN4-36a	5	CN4-24b	96	-
6	CN4-37a	95	CN4-35b	6	CN4-24a	95	-
7	CN4-37b	94	CN4-35a	7	CN4-23a	94	CN4-27a
8	CN3-40a	93	CN4-34b	8	CN4-22a	93	CN4-27b
9	CN3-39b	92	CN4-34a	9	CN4-18b	92	CN4-28a
10	CN3-39a	91	CN4-33b	10	CN4-18a	91	CN4-38a
11	CN3-38b	90	CN4-32b	11	CN4-17b	90	CN4-38b
12	CN3-38a	89	CN4-31b	12	CN4-17a	89	CN4-39a
13	CN3-37b	88	CN4-30a	13	-	88	CN4-39b
14	CN3-37a	87	CN4-29b	14	-	87	CN4-40a
15	-	86	-	15	-	86	-
16	CN3-36b	85	CN4-29a	16	-	85	CN3-31b
17	CN3-36a	84	CN4-28b	17	-	84	CN3-30a
18	CN3-35b	83	CN4-26b	18	-	83	CN3-29b
19	CN3-35a	82	CN4-26a	19	-	82	CN3-29a
20	CN3-34b	81	CN4-25b	20	-	81	CN3-28b
21	CN3-34a	80	CN4-25a	21	-	80	CN3-28a
22	CN3-33b	79	CN4-21b	22	-	79	CN3-25a
23	CN3-33a	78	CN4-20a	23	-	78	CN3-24b
24	CN3-32b	77	CN4-19b	24	-	77	CN3-24a
25	CN3-32a	76	CN4-19a	25	CN3-25b	76	CN3-23b
26	-	75	-	26	CN3-26a	75	-
27	CN3-12a	74	CN4-16b	27	CN3-26b	74	CN3-17a
28	CN3-11b	73	CN4-16a	28	CN3-27a	73	CN3-16b
29	CN3-10a	72	CN4-15b	29	-	72	CN3-16a
30	CN3-09b	71	CN4-15a	30	CN3-27b	71	CN3-15b
31	CN3-09a	70	CN4-14b	31	CN3-18a	70	CN3-15a
32	CN3-08b	69	CN4-14a	32	CN3-19a	69	CN3-14b
33	CN3-08a	68	CN4-13a	33	CN3-19b	68	CN3-14a
34	CN3-07b	67	CN4-12a	34	CN3-20a	67	CN3-13b
35	CN3-07a	66	CN4-11b	35	CN3-21b	66	CN3-13a
36	CN3-03a	65	CN4-10a	36	CN3-22a	65	CN3-12b
37	-	64	-	37	CN3-22b	64	-
38	CN3-02b	63	CN4-09b	38	CN3-23a	63	CN3-23a
39	CN3-02a	62	CN4-09a	39	-	62	CN3-22b
40	CN3-01b	61	CN4-08b	40	CN3-6b	61	CN3-22a
41	CN4-01b	60	CN4-08a	41	CN3-6a	60	CN3-21b
42	CN4-02a	59	CN4-07b	42	CN3-5b	59	CN3-20a
43	CN4-02b	58	CN4-07a	43	CN3-5a	58	CN3-19b
44	CN4-03a	57	CN4-06b	44	CN3-4b	57	CN3-19a
45	CN4-03b	56	CN4-06a	45	-	56	CN3-18a
46	CN4-04a	55	CN4-05b	46	CN3-03b	55	-
47	CN4-04b	54	CN4-05a	47	CN3-04a	54	-
48	-	53	-	48	-	53	-
49	-	52	-	49	-	52	-
50	-	51	-	50	-	51	-

(-:No connection or signals in the emulator)

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.  
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.  
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.  
"Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



Renesas Electronics Corporation

SALES OFFICES

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.  
2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A.  
Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited  
1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada  
Tel: +1-905-898-5441, Fax: +1-905-898-3220

Renesas Electronics Europe Limited  
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K  
Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH  
Arcadiastrasse 10, 40472 Düsseldorf, Germany  
Tel: +49-211-65030, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.  
7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China  
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.  
Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China  
Tel: +86-21-5877-1818, Fax: +86-21-6887-7858 / -7898

Renesas Electronics Hong Kong Limited  
Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong  
Tel: +852-2886-9318, Fax: +852 2886-9022/9044

Renesas Electronics Taiwan Co., Ltd.  
7F, No. 363 Fu Shing North Road Taipei, Taiwan  
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.  
1 harbourFront Avenue, #06-10, keppel Bay Tower, Singapore 098632  
Tel: +65-6213-0200, Fax: +65-6278-8001

Renesas Electronics Malaysia Sdn.Bhd.  
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia  
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics Korea Co., Ltd.  
11F, Samik Lavied' or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea  
Tel: +82-2-558-3737, Fax: +82-2-558-5141



**CAUTION**

If the requirements shown in the "CAUTION" sentences are ignored, the equipment may cause personal injury or damage to the products.

Renesas Tools Website <http://www.renesas.com/tools>  
All trademarks and registered trademarks are the property of their respective owners.