


# I<sub>cc</sub> vs V<sub>cc</sub> (Low-Speed On-Chip Oscillator mode)

Prepared on Oct. 20, 2006

R5F21248SNFP(Topr=-20 to 85degrees C)  
R5F21248SDFP(Topr=-40 to 85degrees C)  
divide-by-8  
XIN clock off  
High-speed on-chip oscillator off  
Low-speed on-chip oscillator on = 125 kHz  
FMR47 = 1

— 85degreesC      — 25degreesC  
— -40degreesC



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.