


32-BIT MCU FAMILY

RENESAS RA8T2 GROUP

1GHz Arm® Cortex®-M85 ASSP MCU for Real-Time Control Applications

The RA8T2 is an ASSP MCU optimized for applications requiring high real-time performance, such as motor control. Developed with the advanced 22nm process, RA8T2 delivers 1GHz performance based on Arm Cortex-M85; and over 7,000 CoreMark to enable high-speed calculations required for high-end industrial motor equipment. The dual-core variant includes a 250MHz Cortex-M33 that efficiently separates real-time processing from other processing, enabling parallel operation. This capability makes RA8T2 ideal for applications handling complex system control in addition to motor control.



Key Features


- 1GHz Arm® Cortex®-M85 Core
- 250MHz Cortex-M33 Core
- Large Memory: 0.5/1MB MRAM & 4/8MB Flash
- 2MB SRAM (Including TCM 256KB+128KB)
- 224, 289, 303-pin BGA package
- 176-pin HLQFP package

- Renesas Security IP, TrustZone, Tamper protection
- 32-bit PWM timer, High Resolution timer
- 16-bit ADC, 12-bit DAC, High speed comparators
- Gigabit Ethernet, TSN Switch, USB2.0 FS, CAN-FD I/Fs
- EtheCAT slave controller
- SDHI, SPI, I3C/I2C Serial Interfaces

Target Applications

- AC Drive
- AC Servo
- Industrial Motor
- Robotics
- CNC


Block Diagram



RENESAS RA8T2 GROUP

Software Package

The Renesas Flexible Software Package (FSP) is designed to provide easy-to-use, scalable, high-quality software for embedded system designs using RA MCUs.



The FSP is based on an open software ecosystem of production-ready drivers, supporting Azure® RTOS, FreeRTOS™ or bare-metal programming. It also includes a selection of other middleware stacks, providing great flexibility for migrating code from older systems or developing new applications from scratch.

Evaluation Kit

Evaluate key features of the RA8T2 MCU group and develop applications with high real-time performance including motor control. This motor control kit includes a CPU board, inverter board, communication board, BLDC motor, and accessories such as EtherCAT slave I/F. Users can conduct on-board debugging using SEGGER-J-Link®. Get more information about the kit at renesas.com/mck-ra8t2

Ordering References

Ext. Flash/ MRAM/DRAM	EtherCAT	Tj	Max frequency*	* Indicating max frequency as Cortex-M85/Cortex-M33								Coming Soon
Flash 8MB MRAM 1MB SRAM 2MB	Yes	0 to 95 °C	1GHz/250MHz									R7KA8T2LSLSAJ
		-40 to 105 °C	800MHz/200MHz									R7KA8T2LSLSAJ
	No	0 to 95 °C	1GHz/250MHz									R7KA8T2JSLSAJ
		-40 to 105 °C	800MHz/200MHz									R7KA8T2JSLSAJ
Flash 4MB MRAM 1MB SRAM 2MB	Yes	0 to 95 °C	1GHz/250MHz									R7KA8T2LHSAJ
		-40 to 105 °C	800MHz/200MHz									R7KA8T2LRSAJ
	No	0 to 95 °C	1GHz/250MHz									R7KA8T2JHSAJ
		-40 to 105 °C	800MHz/200MHz									R7KA8T2JHSAJ
MRAM 1MB SRAM 2MB	Yes	0 to 95 °C	1GHz/250MHz		R7KA8T2FLCAB	R7KA8T2FLCAC		R7KA8T2FLCAB	R7KA8T2FLCAC			
		-40 to 105 °C	800MHz/200MHz		R7KA8T2CFDCAB	R7KA8T2CFDCAC		R7KA8T2CFDCAB	R7KA8T2CFDCAC			
		-40 to 125 °C	600MHz/200MHz	R7KA8T2CFEHC	R7KA8T2CFECAB	R7KA8T2CFECAC	R7KA8T2LFEHC	R7KA8T2LFEAB	R7KA8T2LFEAC			
		0 to 95 °C	1GHz/250MHz		R7KA8T2AFLCAB	R7KA8T2AFLCAC		R7KA8T2JFLCAB	R7KA8T2JFLCAC			
	No	-40 to 105 °C	800MHz/200MHz		R7KA8T2AFDCAB	R7KA8T2AFDCAC		R7KA8T2JFDCAB	R7KA8T2JFDCAC			
		-40 to 125 °C	600MHz/200MHz	R7KA8T2AFEHC	R7KA8T2AFECAB	R7KA8T2AFECAC	R7KA8T2JFEHC	R7KA8T2JFEAB	R7KA8T2JFEAC			
		0 to 95 °C	1GHz/-									
		-40 to 105 °C	800MHz/-			R7KA8T2CDDCAB						
MRAM 512KB SRAM 2MB	Yes	-40 to 125 °C	600MHz/-		R7KA8T2CDEHC	R7KA8T2CDECAB						
		0 to 95 °C	1GHz/-									
	No	-40 to 105 °C	800MHz/-			R7KA8T2ADDCAB						
		-40 to 125 °C	600MHz/-		R7KA8T2ADEHC	R7KA8T2ADECAB						
	Pin Count			176pin	224-pin	289-pin	176pin	224-pin	289-pin	303-pin		
				HLQFP	BGA	BGA	HLQFP	BGA	BGA	BGA		
	Package size (body)			24 x 24mm	11 x 11 mm	12 x 12 mm	24 x 24mm	11 x 11 mm	12 x 12 mm	15 x 15 mm		
				0.5 mm	0.65 mm	0.65 mm	0.5 mm	0.65 mm	0.65 mm	0.8 mm		
	Core			Single (Cortex-M85)				Dual (Cortex-M85/Cortex-M33)				

For more details, please visit: renesas.com/ra8t2

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Tools and Support

The e²studio IDE provides support with intuitive configurators and intelligent code generation to make programming and debugging easier and faster.

IDE	Renesas e²studio	Keil MDK	IAR EWARM
Compiler	■ GCC ■ LLVM ■ Arm Compiler* ■ IAR Arm Compiler*	■ Arm Compiler*	■ IAR Arm Compiler*
Debug Probe	■ Renesas E2/E2 Lite ■ SEGGER J-Link	■ SEGGER J-Link ■ Keil ULINK / CMSIS-DAP**	■ IAR I-jet ■ SEGGER J-Link ■ Renesas E2/E2 Lite ■ CMSIS-DAP**
Production Programmer	■ Renesas PG-FP6	■ SEGGER J-Flash	■ Partner solutions

* Compiler must be purchased and licensed directly from third party

** limited support

