

I_{CC} VS f(XIN) (High-speed clock mode)

Prepared on Sep. 10, 2007

R8C/28-29 Group

T_{opr} = 25 degrees C

High-speed on-chip oscillator off

Low-speed on-chip oscillator on = 125kHz

— V_{CC}=5.0V, no-division


— V_{CC}=5.0V, divide-by-8

— V_{CC}=3.0V, no-division

— V_{CC}=3.0V, divide-by-8

— V_{CC}=2.2V, no-division

— V_{CC}=2.2V, divide-by-8



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.