



# Analytical Testing Report

Indalloy 228 with NC-SMQ75

**Report Number: R-20220119-124**

Prepared for:

*Cliff Talbot*

**Indium Corporation**

1676 Lincoln Avenue

Utica, NY 13503

P.O. #: NA

February 3, 2022

**NSL Analytical Services, Inc.**  
**NSL Analytical**  
**4450 Cranwood Parkway**  
**Cleveland, Ohio 44128**  
**Phone: 216-438-5200**  
**Fax: 216-438-5050**

**Tests  
Requested:**

- European Directive 2015/863/EU Amending 2011 / 65 / EU Annex II (RoHS; Recasting 2001 / 95 / EC: Cadmium, Lead, Mercury, Hexavalent Chromium, Polybromobiphenyl (PBB), and Polybromodiphenylether (PBDE), (DIBP, DBP, BBP, DEHP) content.
- Antimony, Beryllium and Arsenic Content
- Total Halogen and Sulfur Content
- HBCDD, DnOP, DINP, DIDP, DnHP
- PFOA, PFOS





**Contents**

Project Definition and Scope ..... 3

Sample Identification ..... 3

Method ..... 3

    Table 1: RoHS Results ..... 4

    Table 2: Antimony, Beryllium and Arsenic Content ..... 4

    Table 3: Halogen and Sulfur Content ..... 5

    Table 4: Phthalates Results ..... 5

    Table 5: HBCDD Results ..... 5

    Table 6: PFOA and PFOS Content ..... 6

Process Flow – Analytical Methods for Chemical Analysis ..... 7

    Photo: Sample # S-220120-009 ..... 8

## Project Definition and Scope

**European Directive 2015/863/EU Amending 2011 / 65 / EU Annex II (RoHS; Recasting 2001 / 95 / EC:**

Cadmium, Lead, Mercury, Hexavalent Chromium, Polybromobiphenyl (PBB), and Polybromodiphenylether (PBDE) content.

Antimony, Beryllium, Arsenic Content, Total Halogen and Sulfur content.

HBCDD, DIBP, DBP, BBP, DEHP, DnOP, DINP, DIDP, DnHP content.

PFOA, PFOS content.

## Sample Identification

The sample was received on January 19<sup>th</sup>, 2022 and is labeled as indicated below.

Sample Number	Client Label
S-220120-009	Indalloy 228 with NC-SMQ75

## Method

With reference to IEC 62321-7-2: 2017: Chromium (VI) analysis was conducted by UV-Visible Spectroscopy.

With reference to IEC 62321-6: 2015: PBB, PBDE analysis was conducted by Gas Chromatography – Mass Spectrometry (GC-MS).

With reference to IEC 62321-4: 2013: Mercury analysis was conducted by Inductively Coupled Plasma-Optical Emission Spectroscopy (ICP-OES).

With reference to IEC 62321-5: 2013: Lead, Cadmium and Chromium analysis was conducted by Inductively Coupled Plasma - Mass Spectrometry (ICP-MS).

Antimony, Beryllium and Arsenic analysis was conducted by Inductively Coupled Plasma - Mass Spectrometry (ICP-MS). Following Microwave Assisted Acid Digestion with reference to EPA 3051A/3052

With reference to IEC62321-3-2: 2013, BS EN 14582, ASTM D 7359: Halogen and Sulfur analysis was conducted by Ion Chromatography and SIE.

With reference to IEC62321-8 and CPSC-CH-C1001-09.3: DIBP, DBP, BBP, DEHP, DnOP, DINP, DIDP, DnHP were analyzed by Gas Chromatography – Mass Spectrometry (GC-MS).

HBCDD analysis was conducted by Gas Chromatography-Mass Spectrometry (GC-MS).

PFOA and PFOS attained by calculation from Fluoride and Sulfur analysis.

**Table 1: RoHS Results**

Test Item	Results (mg/kg)	Detection Limit (mg/kg)	Reference Limit (mg/kg)
	Sample # S-220120-009		
Lead (Pb)	743000	5	1000
Cadmium	ND	5	100
Chromium	ND	5	
Hexavalent Chromium (Cr(VI))	ND <sup>2</sup>	1	1000
Mercury (Hg)	ND	5	1000
<b>Sum of PBBs</b>	ND <sup>3</sup>	300	1000
Monobromobiphenyl	ND <sup>3</sup>	100	-
Dibromobiphenyl	ND <sup>3</sup>	100	-
Tribromobiphenyl	ND <sup>3</sup>	10	-
Tetrabromobiphenyl	ND <sup>3</sup>	10	-
Pentabromobiphenyl	ND <sup>3</sup>	10	-
Hexabromobiphenyl	ND <sup>3</sup>	10	-
Heptabromobiphenyl	ND <sup>3</sup>	10	-
Octabromobiphenyl	ND <sup>3</sup>	10	-
Nonabromobiphenyl	ND <sup>3</sup>	10	-
Decabromobiphenyl	ND <sup>3</sup>	10	-
<b>Sum of PBDEs</b>	ND <sup>3</sup>	300	1000
Monobromodiphenyl ether	ND <sup>3</sup>	100	-
Dibromodiphenyl ether	ND <sup>3</sup>	10	-
Tribromodiphenyl ether	ND <sup>3</sup>	10	-
Tetrabromodiphenyl ether	ND <sup>3</sup>	10	-
Pentabromodiphenyl ether	ND <sup>3</sup>	10	-
Hexabromodiphenyl ether	ND <sup>3</sup>	10	-
Heptabromodiphenyl ether	ND <sup>3</sup>	10	-
Octabromodiphenyl ether	ND <sup>3</sup>	10	-
Nonabromodiphenyl ether	ND <sup>3</sup>	50	-
Decabromodiphenyl ether	ND <sup>3</sup>	100	-

**Note:** ND = Not Detected

**Note:** mg/kg = ppm

**Note:** ND<sup>2</sup> = Total Chromium analysis by ICP-MS was not detected in the submitted samples. Therefore, Hexavalent Chromium determination by UV-Visible spectroscopy was not performed.

**Note:** ND<sup>3</sup> = Total Bromine by Ion Chromatography was determined to be < 250 ppm, therefore PBB and PBDE analysis by Gas Chromatography – Mass Spectrometry was not performed.

**Table 2: Antimony, Beryllium and Arsenic Content**

Test Item	Results (mg/kg)	Detection Limit
-----------	-----------------	-----------------

	Sample # S- 220120-009	(mg/kg)
Antimony (Sb)	16	5
Beryllium (Be)	ND	5
Arsenic (As)	ND	5

**Table 3: Halogen and Sulfur Content**

Test Item	Results (mg/kg)	Detection Limit (mg/kg)
	Sample # S- 220120-009	
Chlorine (Cl)	ND	10
Bromine (Br)	ND	10
Fluorine (F)	ND	10
Iodine (I)	ND	10
Sulfur (S)	ND	10

**Table 4: Phthalates Results**

Test Item	Results (mg/kg)	Detection Limit (mg/kg)	Reference Limit (mg/kg)
	Sample # S- 220120-009		
DIBP	ND	100	
DBP	ND	100	1000
BBP	ND	100	1000
DEHP	ND	200	1000
DnOP	ND	100	1000
DINP	ND	500	1000
DIDP	ND	500	1000
DnHP	ND	100	

**Table 5: HBCDD Results**

Test Item	Results (mg/kg)	Detection Limit (mg/kg)	Reference Limit (mg/kg)
	Sample # S- 220120-009		
HBCDD	ND	100	

**Table 6: PFOA and PFOS Content**

Test Item	Results (mg/kg)	Detection Limit (mg/kg)
	Sample # S-220120-009	
PFOA	ND <sup>4</sup>	ND = <20
PFOS	ND <sup>5</sup>	ND = <150

Note: ND = Not Detected      Note: mg/kg = ppm

Note: ND<sup>4</sup> = Total F by Ion Chromatography was determined to be < 10 ppm, therefore PFOA was determined by calculation to be <20 ppm

Note: ND<sup>5</sup> = Total F by Ion Chromatography was determined to be < 10 ppm and total S by Ion Chromatography was determined to be <10ppm, therefore PFOS was determined by calculation to be <150 ppm

If you have any questions regarding these results, please contact us.

Report Prepared By: Jonathan Crandall



Lisa Simko

Technical Specialist

### Process Flow - Analytical Methods for Chemical Analysis




Photo: Sample # S-220120-009

5059473 R-20220119-124

### Indium – SERVICE REQUEST FORM

JAN 19 2022

**Restricted Substance Testing for E&E Products**

Client Requesting NSL Service By: MM

Request Service:  5 days; Rush Service:  2 days;  3 days

Company Name: **INDIUM CORPORATION** CONTRACT REVIEW  
JAN 18 11:15

Invoice:	Address:	1676 Lincoln Ave. P. O. Box 269 Utica, New York 13503	Report:	Address:	<input checked="" type="checkbox"/> Same as billing address
	Contact Name:	Cliff Talbot		Contact Name:	
	Telephone:	315-853-4900 ext. 7415		Telephone:	
	Email:	ctalbot@indium.com		Email:	<input checked="" type="checkbox"/> Ready for testing

---

**Sample Information**

Sample Description: **Indalloy 228 with NC-SMQ75** PO #: **EP21471** Location: **ECD**

Color: **[Redacted]** Contain Phthalates: **No**

Powder Composition: **Pb88/Sn10/Ag2** Contain Bromine: **No**

Special Instructions: **Photo of material not the jar**

Re-test Sample:  If yes, provide previous report number: \_\_\_\_\_

**NSL Service(s) Required: Please check appropriate line(s) below:**  
(Analyze the submitted sample(s) per NSL Quote Number: **NSLQ16763: line 1, 3**)

<input checked="" type="checkbox"/> RoHS: Full Package IEC 62321	<input checked="" type="checkbox"/> Phthalates: DEHP, DBP, DINP, DIDP, DNOP, BBP, DIBP, DnHP
<input type="checkbox"/> Cadmium (Cd)	<input checked="" type="checkbox"/> HBCDD
<input checked="" type="checkbox"/> Lead (Pb) <input checked="" type="checkbox"/> High Concentration	<input type="checkbox"/> XRF Testing (please list substances)
<input type="checkbox"/> Low Concentration	<input checked="" type="checkbox"/> PFOS/PFOA
<input type="checkbox"/> Mercury (Hg)	Packaging Test: <input type="checkbox"/> TPCH (packaging): Pb, Cd, Hg, Cr VI
<input type="checkbox"/> PBBs and PBDEs	<b>Halogens:</b>
<input type="checkbox"/> Chromium VI (Cr VI)	<input checked="" type="checkbox"/> Chlorine (Cl) <input checked="" type="checkbox"/> Bromine (Br)
<input checked="" type="checkbox"/> Antimony <input checked="" type="checkbox"/> Beryllium <input checked="" type="checkbox"/> Arsenic	<input checked="" type="checkbox"/> Iodine (I) <input checked="" type="checkbox"/> Fluorine (F)

Other tests (please specify Analysis/Method): \_\_\_\_\_

Photos Required  Flow Chart  Other Reporting Instruction: **No result conclusion on report cover page**

NSL Customer Service Representative:	NSL Sales Contact:
NSL Analytical Services Inc. 4450 Cranwood Parkway Cleveland, OH 44128 Phone: 1-216-438-5200 Fax: 1-216-438-5050	<input type="checkbox"/> Return Sample Immediately; if returned please provide shipping account number. <input checked="" type="checkbox"/> Destroy/Discard Sample after 90 days

Client Confirmation: We confirm that the above information is complete and understand that the performances of the services described are governed by NSL General Conditions of Service.

Authorized Signature: [Signature]

Sample #: **S-220120-009**

Customer: Indium Corporation of

Request: R-20220119-124

Lab Areas: WCP, AC, ICP, MS, C