



Test Report

Report No. A2230081057101001

Page 1 of 14

Company Name MITSUI HIGH-TEC (SHANGHAI) CO.,LTD
shown on Report
Address NO.2001 XINJIN QIAO ROAD EXPORT PROCESSING ZONE PUDONG
SHANGHAI CHINA

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the applicant

Sample Name C7025+Ag
Sample Received Date Mar. 31, 2023
Testing Period Mar. 31, 2023 to Apr. 7, 2023

Test Requested

1.As specified by client, to test Lead (Pb), Cadmium (Cd), Mercury (Hg), Hexavalent Chromium (Cr(VI)), Polybrominated Biphenyls (PBBs), Polybrominated Diphenyl Ethers (PBDEs), Phthalates, Arsenic(As), Beryllium(Be), Antimony(Sb), Hexabromocyclododecane (HBCDD), Fluorine (F), Chlorine (Cl), Bromine (Br), Iodine (I), Polychlorinated Naphthalenes (PCNs), Polychlorinated terphenyls (PCTs), Polychlorinated Biphenyls(PCBs), Perfluorooctane Sulfonates(PFOS), Perfluorooctanoic Acid(PFOA), Short Chain Chlorinated Paraffins (SCCPs), Organotin compounds, Polyvinyl Chloride (PVC), Phosphorus(P) in the submitted sample(s).
2.As specified by client, to screen Antimony trioxide (Sb₂O₃), Beryllium oxide (BeO) in the submitted sample(s).

Test Method/Test Result(s) Please refer to the following page(s).

Approved by

Chen Kaimin

Date

Apr. 7, 2023

Chen kaimin
Lab Manager

No. R201801345

Centre for Testing International Pinbiao(Shanghai) Co., Ltd.

No.1351, Wanfang Road, Minhang District, Shanghai, China



Test Report

Report No. A2230081057101001

Page 2 of 14

Conclusion

<u>Tested Sample</u>	<u>According to standard/directive</u>	<u>Result</u>
Submitted Sample	RoHS Directive 2011/65/EU with amendment (EU) 2015/863	PASS

PASS means that the results shown on the report comply with the limits set by RoHS Directive 2011/65/EU with amendment (EU) 2015/863.

Test Report

Report No. A2230081057101001

Page 3 of 14

Test Method

Tested Item(s)	Test Method	Measured Equipment(s)
Lead (Pb)	IEC 62321-5:2013	ICP-OES
Cadmium (Cd)	IEC 62321-5:2013	ICP-OES
Mercury (Hg)	IEC 62321-4:2013+AMD1:2017 CSV	ICP-OES
Hexavalent Chromium (Cr(VI))	IEC 62321-7-1:2015	UV-Vis
Polybrominated Biphenyls (PBBs)	IEC 62321-6:2015	GC-MS
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321-6:2015	GC-MS
Phthalates (DBP, BBP, DEHP, DIBP)	IEC 62321-8:2017	GC-MS
Arsenic(As)	Refer to US EPA 3050B:1996 & US EPA 6010D:2018*	ICP-OES
Beryllium(Be)	Refer to US EPA 3050B:1996 & US EPA 6010D:2018*	ICP-OES
Beryllium oxide(BeO)	Refer to US EPA 3052:1996 & US EPA 6010D:2014*	ICP-OES
Antimony(Sb)	Refer to US EPA 3050B:1996 & US EPA 6010D:2018*	ICP-OES
Hexabromocyclododecane (HBCDD)	IEC 62321-9:2021	GC-MS
Fluorine (F)	Refer to EN 14582:2016	IC
Chlorine (Cl)	Refer to EN 14582:2016	IC
Bromine (Br)	Refer to EN 14582:2016	IC
Iodine (I)	Refer to EN 14582:2016	IC
Short Chain Chlorinated Paraffins (SCCPs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS(NCI)
Polychlorinated Naphthalenes (PCNs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS
Polychlorinated terphenyls (PCTs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS
Polychlorinated Biphenyls(PCBs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS
Perfluorooctane Sulfonates(PFOS)	Refer to CEN/TS 15968:2010*	LC-MS-MS/LC-MS
Perfluorooctanoic Acid(PFOA)	Refer to CEN/TS 15968:2010*	LC-MS-MS/LC-MS
Organotin compounds	Refer to ISO 17353:2004(E)*	GC-MS
Phthalates(BBP,DEHP,DBP,DNHP/DHEXP,DPP/DPENP,DIBP, DIDP,DINP,DNOP)	Refer to EN 14372:2004(E)*	GC-MS
Antimony trioxide (Sb ₂ O ₃)	Refer to US EPA 3052:1996 & US EPA 6010D:2018*	ICP-OES

Test Report

Report No. A2230081057101001

Page 4 of 14

Tested Item(s)	Test Method	Measured Equipment(s)
Polyvinyl Chloride (PVC)	Refer to JY/T 001-1996*	FT-IR
Phosphorus(P) [#]	Refer to US EPA 3050B:1996 & US EPA 6010D:2018	ICP-OES

Test Result(s)

Tested Item(s)	Result	MDL	Limit
	001		
Lead (Pb)	29 mg/kg	2 mg/kg	1000 mg/kg
Cadmium (Cd)	N.D.	2 mg/kg	100 mg/kg
Mercury (Hg)	N.D.	2 mg/kg	1000 mg/kg
Hexavalent Chromium (Cr(VI))	N.D. ▼	0.10 µg/cm ² (LOQ)	1000 mg/kg

Tested Item(s)	Result	MDL	Limit
	001		
Polybrominated Biphenyls (PBBs)			
Monobromobiphenyl	N.D.	5 mg/kg	1000 mg/kg
Dibromobiphenyl	N.D.	5 mg/kg	
Tribromobiphenyl	N.D.	5 mg/kg	
Tetrabromobiphenyl	N.D.	5 mg/kg	
Pentabromobiphenyl	N.D.	5 mg/kg	
Hexabromobiphenyl	N.D.	5 mg/kg	
Heptabromobiphenyl	N.D.	5 mg/kg	
Octabromobiphenyl	N.D.	5 mg/kg	
Nonabromobiphenyl	N.D.	5 mg/kg	
Decabromobiphenyl	N.D.	5 mg/kg	

Test Report

Report No. A2230081057101001

Page 5 of 14

Tested Item(s)	Result	MDL	Limit
	001		
Polybrominated Diphenyl Ethers (PBDEs)			
Monobromodiphenyl ether	N.D.	5 mg/kg	1000 mg/kg
Dibromodiphenyl ether	N.D.	5 mg/kg	
Tribromodiphenyl ether	N.D.	5 mg/kg	
Tetrabromodiphenyl ether	N.D.	5 mg/kg	
Pentabromodiphenyl ether	N.D.	5 mg/kg	
Hexabromodiphenyl ether	N.D.	5 mg/kg	
Heptabromodiphenyl ether	N.D.	5 mg/kg	
Octabromodiphenyl ether	N.D.	5 mg/kg	
Nonabromodiphenyl ether	N.D.	5 mg/kg	
Decabromodiphenyl ether	N.D.	5 mg/kg	

Tested Item(s)	Result	MDL	Limit
	001		
Phthalates (DBP, BBP, DEHP, DIBP)			
Dibutyl phthalate (DBP) CAS#:84-74-2	N.D.	50 mg/kg	1000 mg/kg
Butyl benzyl phthalate (BBP) CAS#:85-68-7	N.D.	50 mg/kg	1000 mg/kg
Di-(2-ethylhexyl) phthalate (DEHP) CAS#:117-81-7	N.D.	50 mg/kg	1000 mg/kg
Diisobutyl phthalate (DIBP) CAS#:84-69-5	N.D.	50 mg/kg	1000 mg/kg

Tested Item(s)	Result	MDL
	001	
Arsenic (As)	N.D.	10 mg/kg

Tested Item(s)	Result	MDL
	001	
Beryllium (Be)	N.D.	10 mg/kg

Test Report

Report No. A2230081057101001

Page 6 of 14

Tested Item(s)	Result	MDL
	001	
Antimony (Sb)	N.D.	10 mg/kg

Tested Item(s)	Result	MDL
	001	
Hexabromocyclododecane (HBCDD)	N.D.	20 mg/kg

Tested Item(s)	Result	MDL
	001	
Fluorine (F)	N.D.	10 mg/kg
Chlorine (Cl)	N.D.	10 mg/kg
Bromine (Br)	N.D.	10 mg/kg
Iodine (I)	N.D.	10 mg/kg

Tested Item(s)	Result	MDL
	001	
Short Chain Chlorinated Paraffins (SCCPs)	N.D.	100 mg/kg

Tested Item(s)	Result	MDL
	001	
Polychlorinated Naphthalenes (PCNs)	N.D.	5 mg/kg

Tested Item(s)	Result	MDL
	001	
Polychlorinated Triphenyls (PCTs)	N.D.	5 mg/kg

Test Report

Report No. A2230081057101001

Page 7 of 14

Tested Item(s)	Result	MDL
	001	
Polychlorinated Biphenyls(PCBs)		
Monochlorobiphenyl	N.D.	5 mg/kg
Dichlorobiphenyl	N.D.	5 mg/kg
Trichlorobiphenyl	N.D.	5 mg/kg
Tetrachlorobiphenyl	N.D.	5 mg/kg
Pentachlorobiphenyl	N.D.	5 mg/kg
Hexachlorobiphenyl	N.D.	5 mg/kg
Heptachlorobiphenyl	N.D.	5 mg/kg
Octachlorobiphenyl	N.D.	5 mg/kg
Nonachlorobiphenyl	N.D.	5 mg/kg
Decachlorobiphenyl	N.D.	5 mg/kg

Tested Item(s)	Result	MDL
	001	
Perfluorooctane Sulfonates (PFOS)	N.D.	0.010 mg/kg

Tested Item(s)	Result	MDL
	001	
Perfluorooctanoic Acid (PFOA)	N.D.	0.010 mg/kg

Tested Item(s)	Result	MDL
	001	
Organotin compounds		
Dibutyltin (DBT)	N.D.	5 mg/kg
Diocetyl tin (DOT)	N.D.	5 mg/kg
Triphenyltin (TPHT)	N.D.	5 mg/kg
Tributyltin (TBT)	N.D.	5 mg/kg
Tributyltin oxide (TBTO)* ¹	N.D.	5 mg/kg

Test Report

Report No. A2230081057101001

Page 8 of 14

Tested Item(s)	Result	MDL
	001	
Phthalates		
Dibutyl phthalate (DBP) CAS#:84-74-2	N.D.	50 mg/kg
Butyl benzyl phthalate (BBP) CAS#:85-68-7	N.D.	50 mg/kg
Di-(2-ethylhexyl) phthalate (DEHP) CAS#:117-81-7	N.D.	50 mg/kg
Di-n-octyl phthalate (DNOP) CAS#:117-84-0	N.D.	50 mg/kg
Di-isononyl phthalate (DINP) CAS#:28553-12-0,68515-48-0	N.D.	50 mg/kg
Di-iso-decyl phthalate (DIDP) CAS#:26761-40-0,68515-49-1	N.D.	50 mg/kg
Diisobutyl phthalate (DIBP) CAS#:84-69-5	N.D.	50 mg/kg
Dipentyl phthalate (DPP/DPENP) CAS#:131-18-0	N.D.	50 mg/kg
Di-n-hexyl phthalate (DNHP/DHEXP) CAS#:84-75-3	N.D.	50 mg/kg

Tested Item(s)	Result	MDL
	001	
Antimony trioxide (Sb ₂ O ₃)* ²	N.D.	10 mg/kg

Tested Item(s)	Result	MDL
	001	
Polyvinyl Chloride (PVC)	Negative	/

Tested Item(s)	Result	MDL
	001	
Beryllium oxide (BeO) * ²	N.D.	10 mg/kg

Test Report

Report No. A2230081057101001

Page 9 of 14

Tested Item(s)	Result	MDL
	001	
Phosphorus (P) [#]	N.D.	20 mg/kg

Sample/Part Description

No.	CTI Sample ID	Description
1	001	Silvery/cupreous metal

Remark: The sample(s) had been dissolved totally tested for Lead, Cadmium, Mercury, Arsenic, Beryllium, Antimony, Phosphorus.

-MDL = Method Detection Limit

-N.D. = Not Detected (<MDL or LOQ)

-mg/kg = ppm = parts per million

-1000 mg/kg = 0.1%

-LOQ = Limit of Quantification, The LOQ of Hexavalent chromium is 0.10 $\mu\text{g}/\text{cm}^2$

- ∇ The sample is negative for Cr(VI) – The Cr(VI) concentration is below 0.10 $\mu\text{g}/\text{cm}^2$. The coating is considered a non-Cr(VI) based coating.

-Negative = Not contained Polyvinyl Chloride (PVC)

-*¹=Concentration value of Tributyltin oxide by the conversion from the test results of Tributyl Tins.

-*²=The test result of the item is converted from the test result of certain element.

Note: [#] Indicates the item(s) is (are) fulfilled by Centre Testing International Group Co.,Ltd.

“*” indicates the method(s) is (are) not in CNAS accreditation scope.


Test Report

Report No. A2230081057101001


Page 10 of 14

Test Process


1. Cadmium (Cd), Lead (Pb)




2. Mercury (Hg)



3. Hexavalent Chromium (Cr(VI))



4. Polybrominated Biphenyls (PBBs), Polybrominated Diphenyl Ethers (PBDEs)




Test Report


Report No. A2230081057101001

Page 11 of 14


5. Phthalates




6. Beryllium oxide



7. Antimony(Sb), Arsenic(As), Beryllium(Be)



8. Hexabromocyclododecane (HBCDD)




Test Report


Report No. A2230081057101001

Page 12 of 14


9. Bromine (Br), Chlorine (Cl), Fluorine (F), Iodine (I)




10. Short Chain Chlorinated Paraffins (SCCPs)



11. Polychlorinated Biphenyls(PCBs), Polychlorinated Naphthalenes (PCNs), Polychlorinated terphenyls (PCTs)



12. Perfluorooctane Sulfonates(PFOS), Perfluorooctanoic Acid(PFOA)




Test Report


Report No. A2230081057101001

Page 13 of 14


13. Organotin compounds




14. Antimony trioxide (Sb₂O₃)



15. Polyvinyl Chloride (PVC)



16. Phosphorus(P)




Test Report

Report No. A2230081057101001

Page 14 of 14

Photo(s) of the sample(s)



Statement:

1. This report is considered invalid without approved signature, special seal and the seal on the perforation;
2. The Company Name shown on Report and Address, the sample(s) and sample information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
3. The result(s) shown in this report refer(s) only to the sample(s) tested;
4. Without written approval of CTI, this report can't be reproduced except in full;
5. In case of any discrepancy between the English version and Chinese version of the testing reports (if generated), the Chinese version shall prevail.

*** End of Report ***