

ISL71091SEHXXEV1Z

Evaluation Board

AN1906
Rev.1.00
May 28, 2014

Introduction

The ISL71091SEHXXEV1Z evaluation boards are designed to measure the performance of the radiation hardened ultra low noise, high precision [ISL71091SEH](#) voltage reference family. There are four output voltage options in the reference family, and they have a wide input voltage range up to 30V and an initial accuracy of 0.05%. With ultra low voltage noise of 3.3 μ V_{P-P} in the 0.1Hz to 10Hz range (2.048V option), a maximum output voltage temperature coefficient of 6ppm/°C, and excellent radiation performance, the ISL71091SEH is ideal for space applications.

Specifications

The boards are designed to operate at the following conditions:

- Input voltage range:
 - 2.048V option = 4.2V to 30V
 - 3.3V option = 4.6V to 30V
 - 4.096V option = 6V to 30V
 - 10V option = 12V to 30V
- Output current capability: Source 10mA, Sink 5mA
- Operating temperature range: -55°C to +125°C

Features

- Small, compact design
- Multiple connectors to easily monitor V_{IN} and V_{OUT}
- Four output voltage options

Reference Documents

- [ISL71091SEH20](#) Datasheet
- [ISL71091SEH33](#) Datasheet
- [ISL71091SEH40](#) Datasheet
- [ISL71091SEH10](#) Datasheet

Ordering Information

ORDERING NUMBER	OUTPUT VOLTAGE (V)	TYPE
ISL71091SEH20EV1Z	2.048	Evaluation Board
ISL71091SEH33EV1Z	3.3	Evaluation Board
ISL71091SEH40EV1Z	4.096	Evaluation Board
ISL71091SEH10EV1Z	10.0	Evaluation Board




FIGURE 1. ISL71091SEHXXEV1Z BLOCK DIAGRAM

Functional Description

The schematic of the evaluation board is shown on [page 4](#). The ISL71091SEHXXEV1Z contains the ISL71091SEH voltage reference (U1), input decoupling capacitor (C_1), compensation capacitor (C_2), and load capacitor (C_4). Component values are listed in [Table 1](#).

The power supply leads attach to TP1 and TP2 (VIN, GND). The output is measured at test points TP8 and TP9 (VOUT, GND), and is best measured with a high quality voltmeter in DC conditions. In addition, there is a BNC connector on VOUT to aid in taking measurements such as voltage noise. The SP1 (VIN), SP2 (GND), and SP3 (VOUT) are oscilloscope probe test points for easy connection to an oscilloscope. When testing the output voltage of the device under load, it is recommended to attach the load to the test point turret or BNC connector and monitor the voltage




FIGURE 2. V_{OUT} vs TEMPERATURE

from the oscilloscope test point. If smaller transient overshoot is desired, increase C_4 to $10\mu\text{F}$ and C_2 to 10nF . However, note that the settling time also increases.

TRIM 1-3

The TRIM1, TRIM2, and TRIM3 pins are for factory use only. Do not connect these to the circuit in any way. It will adversely effect the performance of the reference.

Device Performance

The following plots show the performance of the voltage reference that can be expected on the evaluation board. $V_{IN} = 8\text{V}$ unless otherwise specified.




FIGURE 3. LINE REGULATION vs V_{OUT} OVER TEMPERATURE




FIGURE 4. LOAD REGULATION vs V_{OUT} OVER TEMPERATURE




FIGURE 5. LOAD TRANSIENT ($\Delta I_L = 1\text{mA}$)

TABLE 1. COMPONENTS PARTS LIST

REFERENCE	VALUE	DESCRIPTION
BNC1		Coaxial Cable PCB Mount Receptacle
C1	0.1 μ F	Bypass Capacitor 0805, X7R, 50V, 10%
C2	1nF	Compensation Capacitor 0805, X7R, 50V, 10%
C3	DNP	
C4	1 μ F	Load Capacitor 0805, X7R, 50V, 10%
SP1 - SP3		Scope Probe Test Point PCB Mount
TP1, TP2, TP4, TP5, TP8, TP9		1514-2 Test Point Turret
TP3, TP7, TP8	DNP	
U1	ISL71091SEHXX	Radiation Hardened Ultra Low Noise, Precision Voltage Reference




FIGURE 6. VOLTAGE REFERENCE EVALUATION BOARD (FRONT)



FIGURE 7. VOLTAGE REFERENCE EVALUATION BOARD (BACK)

ISL71091SEHXXEV1Z Schematic



Voltage Reference Evaluation Board Layout




FIGURE 8. TOP LAYER




FIGURE 9. BOTTOM LAYER (VIEWED FROM TOP)




FIGURE 10. TOP SILKSCREEN

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
 6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
 11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338