

Henkel Electronic Materials

PRODUCT NUMBER: 2030SC

ISSUE DATE: 26-June-2010



*** MATERIAL SAFETY DATA SHEET ***

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME:	ABLEBOND® 2030SC SILVER-FILLED ADHESIVE
COMPANY ADDRESS	Henkel Electronic Materials 15350 Baranca Parkway Irvine, CA 92618
EMERGENCY CONTACT NUMBERS:	MEDICAL: 1-877-671-4608 (toll free) or 1-303-592-1711 (24 hours - Poison Control Center) TRANSPORT: CHEMTREC: 1-800-424-9300 (24 hours) CHEMTREC International: 1-703-527-3887 (call collect) Contact Information: 1-949-789-2500 Internet: www.henkel.com/electronics

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING.
EYE IRRITANT.
HARMFUL IF SWALLOWED.
SKIN IRRITANT.
SKIN SENSITIZER.
Silver Paste

EYE	Will cause eye irritation. May cause permanent damage if eye is not immediately irrigated.
SKIN CONTACT	Irritating to the skin. Repeated and/or prolonged contact may cause skin sensitization. May be absorbed through the skin.
INHALATION	Irritating and/or toxic vapors may be released at elevated temperatures. Vapor may be irritant to the respiratory tract.
INGESTION	Ingestion may cause irritation of the gastrointestinal tract. May cause nausea, vomiting and diarrhea.

3. COMPOSITION/INFORMATION ON INGREDIENTS

COMPONENT	CAS NUMBER	CONCENTRATION (% by weight)
Silver	7440-22-4	>50
Bismaleimide monomer (Trade Secret - 10049)	TS ref# 10049	1 - 5
Acrylate monomer (Trade Secret - 10089)	TS ref# 10089	1 - 5
Acrylate monomer (Trade Secret - 10050)	TS ref# 10050	1 - 5
Acrylate monomer (Trade Secret - 10250)	TS ref# 10250	<1

Henkel Electronic Materials

PRODUCT NUMBER: 2030SC

ISSUE DATE: 26-June-2010

4. FIRST-AID MEASURES

EYE	Immediately irrigate with eyewash solution or clean water, holding the eyelids apart, for at least 15 minutes. Obtain immediate medical attention.
SKIN CONTACT	Wash skin with water. If symptoms (irritation or blistering) persist obtain medical attention.
INHALATION	Remove to fresh air. If breathing is difficult, give oxygen. If breathing has stopped, give artificial respiration. Get medical attention.
INGESTION	DO NOT attempt to give anything by mouth to an unconscious person. Treat symptomatically and supportively. Get medical attention.

5. FIREFIGHTING MEASURES

AUTOIGNITION	Not available
FLASH POINT	> 200 °F
EXTINGUISHING MEDIA	CO2; Dry Chemical; Foam
SPECIAL FIREFIGHTING PROCEDURES	A self contained breathing apparatus and suitable protective clothing should be worn in fire conditions.; Cool exposed equipment with water spray.
FIRE & EXPLOSION HAZARDS	Combustible at high temperatures. Polymerization may take place at elevated temperatures.
HAZARDOUS COMBUSTION PRODUCTS	Carbon dioxide, carbon monoxide, oxides of nitrogen and unknown organics.
LOWER EXPLOSION LIMIT (%)	Not applicable
UPPER EXPLOSION LIMIT (%)	Not applicable

6. ACCIDENTAL RELEASE MEASURES

SPILL AND LEAK PROCEDURES	May cause allergic skin reaction. Use suitable protective clothing. Absorb spillages onto sand, earth or any suitable absorbent material. Scrape up and place in suitably labeled container for silver recovery. If recovery is not practical, disposal should be in accordance with approved site procedures. Disposal should be in accordance with local, state or national legislation.
---------------------------	--

For safety and environmental precautions, please review entire Material Safety Data Sheet for necessary information.

7. HANDLING AND STORAGE

STORAGE TEMPERATURE	-40 °C
HANDLING/STORAGE	Keep away from heat, sources of ignition and direct sunlight. Keep in original containers until point of use. Keep containers properly sealed when not in use.
SENSITIVITY TO STATIC ELECTRICITY	No
SPECIAL SENSITIVITY	Heat.
SENSITIVITY TO MECHANICAL IMPACT	No

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

COMPONENT	EXPOSURE LIMITS		
	ACGIH	OSHA	Mfg Working Standard
Silver	0.1 mg/m3 TWA (dust and fume).	0.01 mg/m3 TWA	

CALIFORNIA OSHA

Henkel Electronic Materials

PRODUCT NUMBER: 2030SC

ISSUE DATE: 26-June-2010

COMPONENT	EXPOSURE LIMITS
Silver	0.01 mg/m3 PEL
VENTILATION REQUIREMENTS	Vent curing oven to outdoors.
EYE PROTECTION REQUIREMENTS	Wear safety glasses with side shields.
GLOVE REQUIREMENTS	Employee must wear appropriate protective gloves to prevent contact with this substance. The use of chemically resistant gloves is recommended.
CLOTHING REQUIREMENTS	Employee must wear appropriate protective clothing and equipment to prevent any possibility of skin contact with this substance.
CHANGE/REMOVAL OF CLOTHING	Remove contaminated clothing and launder before reuse. Discard shoes, belts, wallets, and any other contaminated leather items.
WASH REQUIREMENTS	Wash before eating, drinking, or using toilet facilities.
RESPIRATOR REQUIREMENTS	NIOSH approved respirator if required. Self-contained breathing apparatus in emergency and non-routine situations.

9. PHYSICAL AND CHEMICAL PROPERTIES

PURE SUBSTANCE OR MIXTURE	Mixture
PHYSICAL FORM	Paste
COLOR	Silver
ODOR THRESHOLD	Not available
PH AS IS	Not available
OXIDIZING PROPERTIES	Not applicable
SOLUBILITY IN WATER	Insoluble
PARTITION COEFFICIENT (n-octanol/water)	Not applicable
SPECIFIC GRAVITY (WATER=1)	4.68
EVAPORATION RATE	Not available
VAPOR PRESSURE (mmHg)	Not applicable
VAPOR DENSITY (air = 1)	Not applicable
VOLATILES	Not available
VOLATILE ORGANIC COMPOUNDS	Not available
AUTOIGNITION	Not available
FLASH POINT	> 200 °F

10. STABILITY AND REACTIVITY

STABILITY	Stable
STABILITY DETAIL	Material is stable under recommended storage temperatures and pressures.
MATERIALS TO AVOID	Amines
CONDITIONS TO AVOID	Elevated temperatures
HAZARDOUS DECOMPOSITION PRODUCTS	Carbon dioxide, carbon monoxide, oxides of nitrogen and unknown organics. Thermal decomposition products are hazardous and/or toxic.
HAZARDOUS POLYMERIZATION CONDITIONS	Hazardous polymerization may occur.

11. TOXICOLOGICAL INFORMATION

ROUTE OF ENTRY	Skin Contact; Skin Absorption; Inhalation; Eye Contact		
CARCINOGEN	<u>IARC</u>	<u>NTP</u>	<u>OSHA Substance</u>
	<u>(group)</u>		<u>Specific Regulation</u>
COMPONENT			
There is no evidence that			

Henkel Electronic Materials

PRODUCT NUMBER: 2030SC

ISSUE DATE: 26-June-2010

this product poses a carcinogenic risk under normal conditions of handling and use.

CHRONIC (LONG TERM) EFFECTS OF EXPOSURE

EFFECTS OF CHRONIC EXPOSURE

Chronic absorption of silver or silver salts may result in Argyria, a pigmentation of the eyes, respiratory tract, skin and nails.

TARGET ORGANS
SKIN SENSITIZATION

Skin; Eyes; Respiratory system
Sensitizer. May cause allergic reaction.

PRODUCT TOXICOLOGY PRODUCT INFORMATION

This data sheet is based on a consideration of the properties of the constituents.

COMPONENT
Silver

ORAL TOXICITY

NOTES ON ORAL TOXICITY

Ingestion may cause irritation of the gastrointestinal tract. May cause argyria.

Bismaleimide monomer
(Trade Secret - 10049)
Acrylate monomer (Trade
Secret - 10089)

Oral LD50: Rat > 2000 mg/kg

Low oral toxicity.

Acrylate monomer (Trade
Secret - 10050)

Oral LD50: Rat > 2.3 g/kg

Ingestion may cause irritation of the gastrointestinal tract. May cause nausea, vomiting and diarrhea.

Low oral toxicity. No hazard in normal industrial use. Ingestion may cause irritation of the gastrointestinal tract. May cause nausea, vomiting and diarrhea.

COMPONENT
Silver

DERMAL TOXICITY

NOTES ON DERMAL TOXICITY

May cause slight irritation. May cause argyria. May be absorbed through the skin.

Bismaleimide monomer
(Trade Secret - 10049)

Non-irritant. Repeated and/or prolonged contact may cause skin sensitization.

Acrylate monomer (Trade
Secret - 10089)

Dermal LD50: Rabbit > 5 g/kg

Slight/mild irritant. Repeated or prolonged skin contact may result in moderate irritation. Repeated or prolonged contact may cause defatting of the skin resulting in dryness, cracking and dermatitis. Repeated and/or prolonged contact may cause skin sensitization. May be absorbed through the skin.

Acrylate monomer (Trade
Secret - 10050)

Irritating to the skin. Repeated or prolonged contact may cause defatting of the skin resulting in dryness, cracking and dermatitis. Repeated and/or prolonged contact may cause skin sensitization.

COMPONENT
Silver

INHALATION TOXICITY

NOTES ON INHALATION TOXICITY

Dust may cause irritation. Acute inhalation exposure may result in metal fume fever, a temporary

Henkel Electronic Materials

PRODUCT NUMBER: 2030SC

ISSUE DATE: 26-June-2010

	influenza-like illness. May cause argyria.
Bismaleimide monomer (Trade Secret - 10049)	Vapors and/or aerosols which may be formed at elevated temperatures may be irritating to eyes and respiratory tract. Avoid breathing vapors or mists.
Acrylate monomer (Trade Secret - 10089)	Unlikely to be hazardous by inhalation because of the low vapor pressure of the material at ambient temperature. Vapor or aerosol, if generated, can cause irritation of the eyes, nose and respiratory tract. Avoid breathing vapors or mists.
Acrylate monomer (Trade Secret - 10050)	Unlikely to be hazardous by inhalation because of the low vapor pressure of the material at ambient temperature. Vapor or aerosol, if generated, can cause irritation of the eyes, nose and respiratory tract. Avoid breathing vapors or mists.
COMPONENT Silver	NOTES ON EYE IRRITATION Particulates may scratch eye surfaces and cause mechanical irritation. May cause argyria.
Bismaleimide monomer (Trade Secret - 10049)	Slight/mild irritant. Contact with eyes causes redness and discomfort which is transient.
Acrylate monomer (Trade Secret - 10089)	May cause eye irritation. Contact with eyes causes redness and discomfort which is transient.
Acrylate monomer (Trade Secret - 10050)	Irritating, but does not injure eye tissue. The vapor and the liquid may cause burning, intense irritation and excessive watering of the eye.

12. ECOLOGICAL INFORMATION

POTENTIAL EFFECT ON ENVIRONMENT	Do not allow to enter drains, sewers or watercourses.
MOBILITY	Insoluble
POTENTIAL TO BIOACCUMULATE	Unknown.
AQUATIC TOXICITY	None Established

13. DISPOSAL CONSIDERATIONS

WASTE DISPOSAL METHODS	Disposal should be in accordance with local, state or national legislation.
EMPTY CONTAINER WARNINGS	Empty containers may contain product residue; follow MSDS and label warnings even after they have been emptied.

14. TRANSPORTATION INFORMATION

This section provided for general information only. The shipping description below may not represent requirements for all modes of transportation, packaging, shipping methods or locations outside of the United States.

FOR MORE COMPLETE TRANSPORTATION REGULATORY INFORMATION PLEASE REFER TO THE SHIPPING DOCUMENTS ACCOMPANYING THE SHIPMENT OF THIS PRODUCT.

Henkel Electronic Materials

PRODUCT NUMBER: 2030SC

ISSUE DATE: 26-June-2010

DOT CLASSIFICATION	Not Regulated
ICAO/IATA CLASSIFICATION	Not classified as dangerous.

The information provided herein may not include the impact of additional regulatory requirements (eg, for materials meeting the definition of a hazardous waste under RCRA, hazardous substances under CERCLA, and/of marine pollutants under CWA or other similar federal, state or local laws) or any associated exceptions or exemptions under regulations applicable to the transport of this material.

15. REGULATORY INFORMATION

TSCA	This product is manufactured in compliance with all provisions of the Toxic Substances Control Act, 15 U.S.C. 2601 et. seq. This product contains a chemical substance that is manufactured under a Low Volume Exemption (LVE) in compliance with Section 5 (h)(4) of the Toxic Substances Control Act, 15 U.S.C.
------	---

SARA - Section 313 (Superfund Amendments and Reauthorization Act of 1986 - 40CFR 372)	CAS NUMBER
Silver	7440-22-4

CALIFORNIA PROPOSITION 65

WARNING: This product contains the following chemicals that are known to the State of California to cause cancer, birth defects or other reproductive harm.

Unless a concentration is specified in Section 2 of the MSDS, the below chemical/s are present in trace amounts.

COMPONENT	CAS NUMBER
Toluene	108-88-3
Dichloromethane	75-09-2
Benzene	71-43-2

16. OTHER INFORMATION

HMIS® Hazard Ratings

HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings are not required on MSDSs by OSHA's 29 CFR 1910.1200, we choose to provide them as a service to our customers using HMIS®. These ratings are to be used only with a fully implemented HMIS® program. To deal adequately with the safe handling of this material, all the information contained in this MSDS must be considered.

NPCA recommends that employers must determine appropriate PPE for the actual conditions under which this product is used in their workplace. For information on PPE codes, consult the HMIS® Implementation Manual.

When two ratings are provided for Health, the first represents the material 'as supplied', and the second represents the material 'in use'.

* = chronic health hazard

HMIS® is a registered trademark of the National Paint and Coatings Association (NPCA).

<u>Health</u>	<u>Flammability</u>	<u>Physical Hazard</u>
*2	1	1

Henkel Electronic Materials

PRODUCT NUMBER: 2030SC

ISSUE DATE: 26-June-2010

PREPARED BY:

Regulatory Affairs
Henkel Electronic Materials

The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.