

RENESAS SEMICONDUCTOR RELIABILITY REPORT

GROUP : RX63N
DEVICE : R5F563NXXX
APPLICATION : Consumer / Industry

Quality Assurance Div.
Renesas Electronics Corporation

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
 5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
 "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
 Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
 7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
 8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document .
 13. This document shall not be reproduced or duplicated in any form or disclosed to any third party, in whole or in part, without prior written consent of Renesas Electronics.
 14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-2 October 2020)

Table. Reliability test results (QFP)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JEITA ED-4701/302	+/-1000V,1time	0/3	Class: Equivalent to C2b
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

Table. Reliability test results (BGA)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-55 °C to 125 °C , 500 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JEITA ED-4701/302	+/-1000V,1time	0/3	Class: Equivalent to C2b
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

Table. Reliability test results (LGA)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-55 °C to 125 °C , 500 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JEITA ED-4701/302	+/-1000V,1time	0/3	Class: Equivalent to C2b
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

The failure rate of the device in an actual use condition can be estimated by the below procedure.

•Equation for the failure rate estimation (λ)

$$\lambda = \lambda_b \times \pi T \text{ (FIT)}$$

① Unique failure rate (λ_b)

$$\lambda_b = 0.03 \text{ FIT}$$

Unique failure rate at $T_a = 55^\circ\text{C}$ using 60 % confidence level.

② Temperature term (πT)

$$\pi T = \exp\{11600 \times E_a \times (1/(273+55) - 1/(273+T_a))\}$$

E_a : Activation energy (eV)

T_a : Ambient temperature ($^\circ\text{C}$)

πT simplified chart as $E_a = 0.7 \text{ eV}$												
T_a ($^\circ\text{C}$)	40	50	55	60	65	70	75	80	85	90	100	110
πT	0.31	0.68	1	1.45	2.08	2.95	4.15	5.77	7.96	10.88	19.82	34.99

•MTTF (Mean Time To Failure)

$$MTTF = 1/\lambda$$

Reference about Renesas package code

Package type	Package code *1	
Lead type plastic package	QFP	PxQP
Non-lead type plastic package	QFN	PxQN
Grid array type plastic package	BGA	PxBG
	LGA	PxLG

*1. First four digit

Table. Product list

No	Group	Product part number	Package code	No	Group	Product part number	Package code
1	RX63N	R5F563NACDBG	PLBG0176G*	51	RX63N	R5F563NKDDFC	PLQP0176K*
2	RX63N	R5F563NADDBG	PLBG0176G*	52	RX63N	R5F563NKDGFC	PLQP0176K*
3	RX63N	R5F563NBCDBG	PLBG0176G*	53	RX63N	R5F563NWDDFC	PLQP0176K*
4	RX63N	R5F563NBDDBG	PLBG0176G*	54	RX63N	R5F563NWDGFC	PLQP0176K*
5	RX63N	R5F563NDCDBG	PLBG0176G*	55	RX63N	R5F563NWHDFC	PLQP0176K*
6	RX63N	R5F563NDDDBG	PLBG0176G*	56	RX63N	R5F563NWHGFC	PLQP0176K*
7	RX63N	R5F563NECDBG	PLBG0176G*	57	RX63N	R5F563NYDDFC	PLQP0176K*
8	RX63N	R5F563NEDDBG	PLBG0176G*	58	RX63N	R5F563NYDGFC	PLQP0176K*
9	RX63N	R5F563NACDFB	PLQP0144K*	59	RX63N	R5F563NYHDFC	PLQP0176K*
10	RX63N	R5F563NADDFB	PLQP0144K*	60	RX63N	R5F563NYHGFC	PLQP0176K*
11	RX63N	R5F563NADGFB	PLQP0144K*	61	RX63N	R5F563NACDFP	PLQP0100K*
12	RX63N	R5F563NBCDFB	PLQP0144K*	62	RX63N	R5F563NADDFP	PLQP0100K*
13	RX63N	R5F563NBDDFB	PLQP0144K*	63	RX63N	R5F563NADGFP	PLQP0100K*
14	RX63N	R5F563NBDGFB	PLQP0144K*	64	RX63N	R5F563NBCDFP	PLQP0100K*
15	RX63N	R5F563NDCDFB	PLQP0144K*	65	RX63N	R5F563NBDDFP	PLQP0100K*
16	RX63N	R5F563NDDDFB	PLQP0144K*	66	RX63N	R5F563NBDGFP	PLQP0100K*
17	RX63N	R5F563NDDGFB	PLQP0144K*	67	RX63N	R5F563NDCDFP	PLQP0100K*
18	RX63N	R5F563NECDFB	PLQP0144K*	68	RX63N	R5F563NDDDFP	PLQP0100K*
19	RX63N	R5F563NEDDFB	PLQP0144K*	69	RX63N	R5F563NDDGFP	PLQP0100K*
20	RX63N	R5F563NEDGFB	PLQP0144K*	70	RX63N	R5F563NECDFP	PLQP0100K*
21	RX63N	R5F563NFDDFB	PLQP0144K*	71	RX63N	R5F563NEDDFP	PLQP0100K*
22	RX63N	R5F563NFDGFB	PLQP0144K*	72	RX63N	R5F563NEDGFP	PLQP0100K*
23	RX63N	R5F563NFHDFB	PLQP0144K*	73	RX63N	R5F563NFDDFP	PLQP0100K*
24	RX63N	R5F563NFHGFB	PLQP0144K*	74	RX63N	R5F563NFDGFP	PLQP0100K*
25	RX63N	R5F563NKDDFB	PLQP0144K*	75	RX63N	R5F563NFHDFP	PLQP0100K*
26	RX63N	R5F563NKDGFB	PLQP0144K*	76	RX63N	R5F563NFHGFP	PLQP0100K*
27	RX63N	R5F563NWDDFB	PLQP0144K*	77	RX63N	R5F563NKDDFP	PLQP0100K*
28	RX63N	R5F563NWDGFB	PLQP0144K*	78	RX63N	R5F563NKDGFP	PLQP0100K*
29	RX63N	R5F563NWHDFB	PLQP0144K*	79	RX63N	R5F563NWDDFP	PLQP0100K*
30	RX63N	R5F563NWHGFB	PLQP0144K*	80	RX63N	R5F563NWDGFP	PLQP0100K*
31	RX63N	R5F563NYDDFB	PLQP0144K*	81	RX63N	R5F563NWHDFP	PLQP0100K*
32	RX63N	R5F563NYDGFB	PLQP0144K*	82	RX63N	R5F563NWHGFP	PLQP0100K*
33	RX63N	R5F563NYHDFB	PLQP0144K*	83	RX63N	R5F563NYDDFP	PLQP0100K*
34	RX63N	R5F563NYHGFB	PLQP0144K*	84	RX63N	R5F563NYDGFP	PLQP0100K*
35	RX63N	R5F563NACDFC	PLQP0176K*	85	RX63N	R5F563NYHDFP	PLQP0100K*
36	RX63N	R5F563NADDFC	PLQP0176K*	86	RX63N	R5F563NYHGFP	PLQP0100K*
37	RX63N	R5F563NADGFC	PLQP0176K*	87	RX63N	R5F563NACDFR	PLQP0176L*
38	RX63N	R5F563NBCDFC	PLQP0176K*	88	RX63N	R5F563NADDFR	PLQP0176L*
39	RX63N	R5F563NBDDFC	PLQP0176K*	89	RX63N	R5F563NADGFR	PLQP0176L*
40	RX63N	R5F563NBDGFC	PLQP0176K*	90	RX63N	R5F563NBCDFR	PLQP0176L*
41	RX63N	R5F563NDCDFC	PLQP0176K*	91	RX63N	R5F563NBDDFR	PLQP0176L*
42	RX63N	R5F563NDDDFC	PLQP0176K*	92	RX63N	R5F563NBDGFR	PLQP0176L*
43	RX63N	R5F563NDDGFC	PLQP0176K*	93	RX63N	R5F563NDCDFR	PLQP0176L*
44	RX63N	R5F563NECDFC	PLQP0176K*	94	RX63N	R5F563NDDDFR	PLQP0176L*
45	RX63N	R5F563NEDDFC	PLQP0176K*	95	RX63N	R5F563NDDGFR	PLQP0176L*
46	RX63N	R5F563NEDGFC	PLQP0176K*	96	RX63N	R5F563NECDFR	PLQP0176L*
47	RX63N	R5F563NFDDFC	PLQP0176K*	97	RX63N	R5F563NEDDFR	PLQP0176L*
48	RX63N	R5F563NFDGFC	PLQP0176K*	98	RX63N	R5F563NEDGFR	PLQP0176L*
49	RX63N	R5F563NFHDFC	PLQP0176K*	99	RX63N	R5F563NACDLC	PTLG0177K*
50	RX63N	R5F563NFHGFC	PLQP0176K*	100	RX63N	R5F563NADDLC	PTLG0177K*

Table. Product list

MCR-22-0313

No	Group	Product part number	Package code	No	Group	Product part number	Package code
101	RX63N	R5F563NBCDLC	PTLG0177K*	161			
102	RX63N	R5F563NBDDLK	PTLG0177K*	162			
103	RX63N	R5F563NDCDLC	PTLG0177K*	163			
104	RX63N	R5F563NDDDLK	PTLG0177K*	164			
105	RX63N	R5F563NECDLC	PTLG0177K*	165			
106	RX63N	R5F563NEDDLK	PTLG0177K*	166			
107	RX63N	R5F563NACDLE	PTLG0145J*	167			
108	RX63N	R5F563NADDLE	PTLG0145J*	168			
109	RX63N	R5F563NBCDLE	PTLG0145J*	169			
110	RX63N	R5F563NBDDLE	PTLG0145J*	170			
111	RX63N	R5F563NDCDLE	PTLG0145J*	171			
112	RX63N	R5F563NDDDLK	PTLG0145J*	172			
113	RX63N	R5F563NECDLE	PTLG0145J*	173			
114	RX63N	R5F563NEDDLK	PTLG0145J*	174			
115	RX63N	R5F563NACDLJ	PTLG0100J*	175			
116	RX63N	R5F563NADDLJ	PTLG0100J*	176			
117	RX63N	R5F563NBCDLJ	PTLG0100J*	177			
118	RX63N	R5F563NBDDLJ	PTLG0100J*	178			
119	RX63N	R5F563NDCDLJ	PTLG0100J*	179			
120	RX63N	R5F563NDDDLJ	PTLG0100J*	180			
121	RX63N	R5F563NECDLJ	PTLG0100J*	181			
122	RX63N	R5F563NEDDLJ	PTLG0100J*	182			
123	RX63N	R5F563NACDLK	PTLG0145K*	183			
124	RX63N	R5F563NADDLK	PTLG0145K*	184			
125	RX63N	R5F563NBCDLK	PTLG0145K*	185			
126	RX63N	R5F563NBDDLK	PTLG0145K*	186			
127	RX63N	R5F563NDCDLK	PTLG0145K*	187			
128	RX63N	R5F563NDDDLK	PTLG0145K*	188			
129	RX63N	R5F563NECDLK	PTLG0145K*	189			
130	RX63N	R5F563NEDDLK	PTLG0145K*	190			
131				191			
132				192			
133				193			
134				194			
135				195			
136				196			
137				197			
138				198			
139				199			
140				200			
141				201			
142				202			
143				203			
144				204			
145				205			
146				206			
147				207			
148				208			
149				209			
150				210			
151				211			
152				212			
153				213			
154				214			
155				215			
156				216			
157				217			
158				218			
159				219			
160				220			