

# RENESAS SEMICONDUCTOR RELIABILITY REPORT

GROUP : RL78/G13  
DEVICE : R5F100XXX  
APPLICATION : Consumer / Industry

Quality Assurance Div.  
Renesas Electronics Corporation

## Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
  2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
  3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
  4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
  5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
  6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.  
 "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.  
 "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.  
 Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
  7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
  8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
  9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
  10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
  11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
  12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document .
  13. This document shall not be reproduced or duplicated in any form or disclosed to any third party, in whole or in part, without prior written consent of Renesas Electronics.
  14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-2 October 2020)

**Table. Reliability test results (QFP)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

**Table. Reliability test results (QFN)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

**Table. Reliability test results (SOP)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

**Table. Reliability test results (BGA)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-55 °C to 125 °C , 500 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

**Table. Reliability test results (LGA)**

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-55 °C to 125 °C , 500 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

\*1) With preconditioning per JESD22-A113, MSL 3

·It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

The failure rate of the device in an actual use condition can be estimated by the below procedure.

**•Equation for the failure rate estimation ( $\lambda$ )**

$$\lambda = \lambda_b \times \pi T \text{ (FIT)}$$

① Unique failure rate ( $\lambda_b$ )

$$\lambda_b = 3.8 \text{ FIT}$$

Unique failure rate at  $T_a = 55 \text{ }^\circ\text{C}$  using 60 % confidence level.

② Temperature term ( $\pi T$ )

$$\pi T = \exp\{11600 \times E_a \times (1/(273+55) - 1/(273+T_a))\}$$

$E_a$  : Activation energy (eV)

$T_a$  : Ambient temperature ( $^\circ\text{C}$ )

$\pi T$ simplified chart as $E_a = 0.7 \text{ eV}$												
$T_a$ ( $^\circ\text{C}$ )	40	50	55	60	65	70	75	80	85	90	100	110
$\pi T$	0.31	0.68	1	1.45	2.08	2.95	4.15	5.77	7.96	10.88	19.82	34.99

**•MTTF ( Mean Time To Failure )**

$$MTTF = 1/\lambda$$



## Reference about Renesas package code

Package type	Package code *1	
Lead type plastic package	QFP	PxQP
	SOP	PxSP
Non-lead type plastic package	QFN	PxQN
Grid array type plastic package	BGA	PxBG
	LGA	PxLG

\*1. First four digit

Table. Product list

No	Group	Product part number	Package code	No	Group	Product part number	Package code
1	RL78/G13	R5F100AASM	PTSP0020J*	51	RL78/G13	R5F100ADASP	PLSP0030J*
2	RL78/G13	R5F100AASP	PLSP0020J*	52	RL78/G13	R5F100ADDSP	PLSP0030J*
3	RL78/G13	R5F100ADSP	PLSP0020J*	53	RL78/G13	R5F100ADGSP	PLSP0030J*
4	RL78/G13	R5F100AGSM	PTSP0020J*	54	RL78/G13	R5F100AEASP	PLSP0030J*
5	RL78/G13	R5F100AGSP	PLSP0020J*	55	RL78/G13	R5F100AEDSP	PLSP0030J*
6	RL78/G13	R5F100CASM	PTSP0020J*	56	RL78/G13	R5F100AEGSP	PLSP0030J*
7	RL78/G13	R5F100CASP	PLSP0020J*	57	RL78/G13	R5F100AFASP	PLSP0030J*
8	RL78/G13	R5F100CDSP	PLSP0020J*	58	RL78/G13	R5F100AFDSP	PLSP0030J*
9	RL78/G13	R5F100CGSM	PTSP0020J*	59	RL78/G13	R5F100AFGSP	PLSP0030J*
10	RL78/G13	R5F100CGSP	PLSP0020J*	60	RL78/G13	R5F100AGASP	PLSP0030J*
11	RL78/G13	R5F100DASM	PTSP0020J*	61	RL78/G13	R5F100AGDSP	PLSP0030J*
12	RL78/G13	R5F100DASP	PLSP0020J*	62	RL78/G13	R5F100AGGSP	PLSP0030J*
13	RL78/G13	R5F100DDSP	PLSP0020J*	63	RL78/G13	R5F100BAANA	PWQN0032K*
14	RL78/G13	R5F100DGSM	PTSP0020J*	64	RL78/G13	R5F100BADNA	PWQN0032K*
15	RL78/G13	R5F100DGSP	PLSP0020J*	65	RL78/G13	R5F100BAGNA	PWQN0032K*
16	RL78/G13	R5F100EASM	PTSP0020J*	66	RL78/G13	R5F100BCAFP	PLQP0032G*
17	RL78/G13	R5F100EASP	PLSP0020J*	67	RL78/G13	R5F100BCANA	PWQN0032K*
18	RL78/G13	R5F100EDSP	PLSP0020J*	68	RL78/G13	R5F100BCDNA	PWQN0032K*
19	RL78/G13	R5F100EGSM	PTSP0020J*	69	RL78/G13	R5F100BCGFP	PLQP0032G*
20	RL78/G13	R5F100EGSP	PLSP0020J*	70	RL78/G13	R5F100BCGNA	PWQN0032K*
21	RL78/G13	R5F1007AANA	PWQN0024K*	71	RL78/G13	R5F100BDANA	PWQN0032K*
22	RL78/G13	R5F1007ADNA	PWQN0024K*	72	RL78/G13	R5F100BDDNA	PWQN0032K*
23	RL78/G13	R5F1007AGNA	PWQN0024K*	73	RL78/G13	R5F100BDGFP	PLQP0032G*
24	RL78/G13	R5F1007CANA	PWQN0024K*	74	RL78/G13	R5F100BDGNA	PWQN0032K*
25	RL78/G13	R5F1007CDNA	PWQN0024K*	75	RL78/G13	R5F100BEANA	PWQN0032K*
26	RL78/G13	R5F1007CGNA	PWQN0024K*	76	RL78/G13	R5F100BEDNA	PWQN0032K*
27	RL78/G13	R5F1007DANA	PWQN0024K*	77	RL78/G13	R5F100BEGFP	PLQP0032G*
28	RL78/G13	R5F1007DDNA	PWQN0024K*	78	RL78/G13	R5F100BEGNA	PWQN0032K*
29	RL78/G13	R5F1007DGNA	PWQN0024K*	79	RL78/G13	R5F100BFANA	PWQN0032K*
30	RL78/G13	R5F1007EANA	PWQN0024K*	80	RL78/G13	R5F100BFDNA	PWQN0032K*
31	RL78/G13	R5F1007EDNA	PWQN0024K*	81	RL78/G13	R5F100BFGNA	PWQN0032K*
32	RL78/G13	R5F1007EGNA	PWQN0024K*	82	RL78/G13	R5F100BGANA	PWQN0032K*
33	RL78/G13	R5F1008AALA	PWLG0025K*	83	RL78/G13	R5F100BGDNA	PWQN0032K*
34	RL78/G13	R5F1008ADLA	PWLG0025K*	84	RL78/G13	R5F100BGGNA	PWQN0032K*
35	RL78/G13	R5F1008AGLA	PWLG0025K*	85	RL78/G13	R5F100CAALA	PWLG0036K*
36	RL78/G13	R5F1008CALA	PWLG0025K*	86	RL78/G13	R5F100CADLA	PWLG0036K*
37	RL78/G13	R5F1008CDLA	PWLG0025K*	87	RL78/G13	R5F100CAGLA	PWLG0036K*
38	RL78/G13	R5F1008CGLA	PWLG0025K*	88	RL78/G13	R5F100CCALA	PWLG0036K*
39	RL78/G13	R5F1008DALA	PWLG0025K*	89	RL78/G13	R5F100CCDLA	PWLG0036K*
40	RL78/G13	R5F1008DDLA	PWLG0025K*	90	RL78/G13	R5F100CCGLA	PWLG0036K*
41	RL78/G13	R5F1008DGLA	PWLG0025K*	91	RL78/G13	R5F100CDALA	PWLG0036K*
42	RL78/G13	R5F1008EALA	PWLG0025K*	92	RL78/G13	R5F100CDDLA	PWLG0036K*
43	RL78/G13	R5F1008EDLA	PWLG0025K*	93	RL78/G13	R5F100CDGLA	PWLG0036K*
44	RL78/G13	R5F1008EGLA	PWLG0025K*	94	RL78/G13	R5F100CEALA	PWLG0036K*
45	RL78/G13	R5F100AAASP	PLSP0030J*	95	RL78/G13	R5F100CEDLA	PWLG0036K*
46	RL78/G13	R5F100AADSP	PLSP0030J*	96	RL78/G13	R5F100CEGLA	PWLG0036K*
47	RL78/G13	R5F100AAGSP	PLSP0030J*	97	RL78/G13	R5F100CFALA	PWLG0036K*
48	RL78/G13	R5F100ACASP	PLSP0030J*	98	RL78/G13	R5F100CFDLA	PWLG0036K*
49	RL78/G13	R5F100ACDSP	PLSP0030J*	99	RL78/G13	R5F100CFGLA	PWLG0036K*
50	RL78/G13	R5F100ACGSP	PLSP0030J*	100	RL78/G13	R5F100CGALA	PWLG0036K*

Table. Product list

MCR-22-0498

No	Group	Product part number	Package code	No	Group	Product part number	Package code
101	RL78/G13	R5F100CGDLA	PWLG0036K*	161	RL78/G13	R5F100GCDNA	PWQN0048K*
102	RL78/G13	R5F100CGGLA	PWLG0036K*	162	RL78/G13	R5F100GCGFB	PLQP0048K*
103	RL78/G13	R5F100EAANA	PWQN0040K*	163	RL78/G13	R5F100GCGNA	PWQN0048K*
104	RL78/G13	R5F100EADNA	PWQN0040K*	164	RL78/G13	R5F100GDAFB	PLQP0048K*
105	RL78/G13	R5F100EAGNA	PWQN0040K*	165	RL78/G13	R5F100GDANA	PWQN0048K*
106	RL78/G13	R5F100ECANA	PWQN0040K*	166	RL78/G13	R5F100GDDFB	PLQP0048K*
107	RL78/G13	R5F100ECDNA	PWQN0040K*	167	RL78/G13	R5F100GDDNA	PWQN0048K*
108	RL78/G13	R5F100ECGNA	PWQN0040K*	168	RL78/G13	R5F100GDGFB	PLQP0048K*
109	RL78/G13	R5F100EDANA	PWQN0040K*	169	RL78/G13	R5F100GDGNA	PWQN0048K*
110	RL78/G13	R5F100EDDNA	PWQN0040K*	170	RL78/G13	R5F100GEAFB	PLQP0048K*
111	RL78/G13	R5F100EDGNA	PWQN0040K*	171	RL78/G13	R5F100GEANA	PWQN0048K*
112	RL78/G13	R5F100EEANA	PWQN0040K*	172	RL78/G13	R5F100GEDFB	PLQP0048K*
113	RL78/G13	R5F100EEDNA	PWQN0040K*	173	RL78/G13	R5F100GEDNA	PWQN0048K*
114	RL78/G13	R5F100EEGNA	PWQN0040K*	174	RL78/G13	R5F100GEGFB	PLQP0048K*
115	RL78/G13	R5F100EFANA	PWQN0040K*	175	RL78/G13	R5F100GEGNA	PWQN0048K*
116	RL78/G13	R5F100EFDNA	PWQN0040K*	176	RL78/G13	R5F100GFAFB	PLQP0048K*
117	RL78/G13	R5F100EFGNA	PWQN0040K*	177	RL78/G13	R5F100GFANA	PWQN0048K*
118	RL78/G13	R5F100EGANA	PWQN0040K*	178	RL78/G13	R5F100GFDFB	PLQP0048K*
119	RL78/G13	R5F100EGDNA	PWQN0040K*	179	RL78/G13	R5F100GFDNA	PWQN0048K*
120	RL78/G13	R5F100EGGNA	PWQN0040K*	180	RL78/G13	R5F100GFGFB	PLQP0048K*
121	RL78/G13	R5F100EHANA	PWQN0040K*	181	RL78/G13	R5F100GFGNA	PWQN0048K*
122	RL78/G13	R5F100EHDNA	PWQN0040K*	182	RL78/G13	R5F100GGAFB	PLQP0048K*
123	RL78/G13	R5F100EHGNA	PWQN0040K*	183	RL78/G13	R5F100GGANA	PWQN0048K*
124	RL78/G13	R5F100FAAFP	PLQP0044G*	184	RL78/G13	R5F100GGDFB	PLQP0048K*
125	RL78/G13	R5F100FADFP	PLQP0044G*	185	RL78/G13	R5F100GGDNA	PWQN0048K*
126	RL78/G13	R5F100FAGFP	PLQP0044G*	186	RL78/G13	R5F100GGGFB	PLQP0048K*
127	RL78/G13	R5F100FCAFP	PLQP0044G*	187	RL78/G13	R5F100GGGNA	PWQN0048K*
128	RL78/G13	R5F100FCDFP	PLQP0044G*	188	RL78/G13	R5F100GHAFB	PLQP0048K*
129	RL78/G13	R5F100FCGFP	PLQP0044G*	189	RL78/G13	R5F100GHANA	PWQN0048K*
130	RL78/G13	R5F100FDAFP	PLQP0044G*	190	RL78/G13	R5F100GHDFB	PLQP0048K*
131	RL78/G13	R5F100FDDFP	PLQP0044G*	191	RL78/G13	R5F100GHDNA	PWQN0048K*
132	RL78/G13	R5F100FDGFP	PLQP0044G*	192	RL78/G13	R5F100GHGFB	PLQP0048K*
133	RL78/G13	R5F100FEAFP	PLQP0044G*	193	RL78/G13	R5F100GHGNA	PWQN0048K*
134	RL78/G13	R5F100FEDFP	PLQP0044G*	194	RL78/G13	R5F100GJAFB	PLQP0048K*
135	RL78/G13	R5F100FEGFP	PLQP0044G*	195	RL78/G13	R5F100GJANA	PWQN0048K*
136	RL78/G13	R5F100FFAFP	PLQP0044G*	196	RL78/G13	R5F100GJDFB	PLQP0048K*
137	RL78/G13	R5F100FFDFP	PLQP0044G*	197	RL78/G13	R5F100GJDNA	PWQN0048K*
138	RL78/G13	R5F100FFGFP	PLQP0044G*	198	RL78/G13	R5F100GJGFB	PLQP0048K*
139	RL78/G13	R5F100FGAFP	PLQP0044G*	199	RL78/G13	R5F100GJGNA	PWQN0048K*
140	RL78/G13	R5F100FGDFP	PLQP0044G*	200	RL78/G13	R5F100GKAFB	PLQP0048K*
141	RL78/G13	R5F100FGGFP	PLQP0044G*	201	RL78/G13	R5F100GKANA	PWQN0048K*
142	RL78/G13	R5F100FHAFP	PLQP0044G*	202	RL78/G13	R5F100GKDFB	PLQP0048K*
143	RL78/G13	R5F100FHDFP	PLQP0044G*	203	RL78/G13	R5F100GKDNA	PWQN0048K*
144	RL78/G13	R5F100FHGFP	PLQP0044G*	204	RL78/G13	R5F100GLAFB	PLQP0048K*
145	RL78/G13	R5F100FJAFP	PLQP0044G*	205	RL78/G13	R5F100GLANA	PWQN0048K*
146	RL78/G13	R5F100FJDFP	PLQP0044G*	206	RL78/G13	R5F100GLDFB	PLQP0048K*
147	RL78/G13	R5F100FJGFP	PLQP0044G*	207	RL78/G13	R5F100GLDNA	PWQN0048K*
148	RL78/G13	R5F100FKAFP	PLQP0044G*	208	RL78/G13	R5F100JCAFA	PLQP0052J*
149	RL78/G13	R5F100FKDFP	PLQP0044G*	209	RL78/G13	R5F100JCDFB	PLQP0052J*
150	RL78/G13	R5F100FLAFP	PLQP0044G*	210	RL78/G13	R5F100JCGFA	PLQP0052J*
151	RL78/G13	R5F100FLDFP	PLQP0044G*	211	RL78/G13	R5F100JDAFA	PLQP0052J*
152	RL78/G13	R5F100GAAFB	PLQP0048K*	212	RL78/G13	R5F100JDDFA	PLQP0052J*
153	RL78/G13	R5F100GAANA	PWQN0048K*	213	RL78/G13	R5F100JDGFA	PLQP0052J*
154	RL78/G13	R5F100GADFB	PLQP0048K*	214	RL78/G13	R5F100JEAFB	PLQP0052J*
155	RL78/G13	R5F100GADNA	PWQN0048K*	215	RL78/G13	R5F100JEDFA	PLQP0052J*
156	RL78/G13	R5F100GAGFB	PLQP0048K*	216	RL78/G13	R5F100JEGFA	PLQP0052J*
157	RL78/G13	R5F100GAGNA	PWQN0048K*	217	RL78/G13	R5F100JFAFA	PLQP0052J*
158	RL78/G13	R5F100GCAFB	PLQP0048K*	218	RL78/G13	R5F100JFDFA	PLQP0052J*
159	RL78/G13	R5F100GCANA	PWQN0048K*	219	RL78/G13	R5F100JFGFA	PLQP0052J*
160	RL78/G13	R5F100GCDFB	PLQP0048K*	220	RL78/G13	R5F100JGAFA	PLQP0052J*

Table. Product list

MCR-22-0498

No	Group	Product part number	Package code	No	Group	Product part number	Package code
221	RL78/G13	R5F100JGDFA	PLQP0052J*	281	RL78/G13	R5F100LHDBG	PVBG0064L*
222	RL78/G13	R5F100JGGFA	PLQP0052J*	282	RL78/G13	R5F100LHDFA	PLQP0064J*
223	RL78/G13	R5F100JHAFDA	PLQP0052J*	283	RL78/G13	R5F100LHDFB	PLQP0064K*
224	RL78/G13	R5F100JHDFA	PLQP0052J*	284	RL78/G13	R5F100LHGBG	PVBG0064L*
225	RL78/G13	R5F100JHGFA	PLQP0052J*	285	RL78/G13	R5F100LHGFA	PLQP0064J*
226	RL78/G13	R5F100JJAFDA	PLQP0052J*	286	RL78/G13	R5F100LHGFB	PLQP0064K*
227	RL78/G13	R5F100JJDFA	PLQP0052J*	287	RL78/G13	R5F100LJABG	PVBG0064L*
228	RL78/G13	R5F100JJGFA	PLQP0052J*	288	RL78/G13	R5F100LJAFDA	PLQP0064J*
229	RL78/G13	R5F100JKAFDA	PLQP0052J*	289	RL78/G13	R5F100LJAFB	PLQP0064K*
230	RL78/G13	R5F100JKDFA	PLQP0052J*	290	RL78/G13	R5F100LJDBG	PVBG0064L*
231	RL78/G13	R5F100JLAFDA	PLQP0052J*	291	RL78/G13	R5F100LJDFA	PLQP0064J*
232	RL78/G13	R5F100JLDFA	PLQP0052J*	292	RL78/G13	R5F100LJDFB	PLQP0064K*
233	RL78/G13	R5F100LCABG	PVBG0064L*	293	RL78/G13	R5F100LJGBG	PVBG0064L*
234	RL78/G13	R5F100LCAFA	PLQP0064J*	294	RL78/G13	R5F100LJGFA	PLQP0064J*
235	RL78/G13	R5F100LCAFB	PLQP0064K*	295	RL78/G13	R5F100LJGFB	PLQP0064K*
236	RL78/G13	R5F100LCDBG	PVBG0064L*	296	RL78/G13	R5F100LKAFDA	PLQP0064J*
237	RL78/G13	R5F100LCDFA	PLQP0064J*	297	RL78/G13	R5F100LKAFB	PLQP0064K*
238	RL78/G13	R5F100LCDFB	PLQP0064K*	298	RL78/G13	R5F100LKDFA	PLQP0064J*
239	RL78/G13	R5F100LCGBG	PVBG0064L*	299	RL78/G13	R5F100LKDFB	PLQP0064K*
240	RL78/G13	R5F100LCGFA	PLQP0064J*	300	RL78/G13	R5F100LKGFB	PLQP0064K*
241	RL78/G13	R5F100LCGFB	PLQP0064K*	301	RL78/G13	R5F100LLAFDA	PLQP0064J*
242	RL78/G13	R5F100LDABG	PVBG0064L*	302	RL78/G13	R5F100LLAFB	PLQP0064K*
243	RL78/G13	R5F100LDAFA	PLQP0064J*	303	RL78/G13	R5F100LLDFA	PLQP0064J*
244	RL78/G13	R5F100LDAFB	PLQP0064K*	304	RL78/G13	R5F100LLDFB	PLQP0064K*
245	RL78/G13	R5F100LDDDBG	PVBG0064L*	305	RL78/G13	R5F100LLGFB	PLQP0064K*
246	RL78/G13	R5F100LDDFA	PLQP0064J*	306	RL78/G13	R5F100MFADFA	PLQP0080J*
247	RL78/G13	R5F100LDDFB	PLQP0064K*	307	RL78/G13	R5F100MFAFB	PLQP0080K*
248	RL78/G13	R5F100LDGBG	PVBG0064L*	308	RL78/G13	R5F100MFDFA	PLQP0080J*
249	RL78/G13	R5F100LDGFA	PLQP0064J*	309	RL78/G13	R5F100MDFB	PLQP0080K*
250	RL78/G13	R5F100LDGFB	PLQP0064K*	310	RL78/G13	R5F100MFGFA	PLQP0080J*
251	RL78/G13	R5F100LEABG	PVBG0064L*	311	RL78/G13	R5F100MFGFB	PLQP0080K*
252	RL78/G13	R5F100LEAFDA	PLQP0064J*	312	RL78/G13	R5F100MGADFA	PLQP0080J*
253	RL78/G13	R5F100LEAFB	PLQP0064K*	313	RL78/G13	R5F100MGAFB	PLQP0080K*
254	RL78/G13	R5F100LEDBG	PVBG0064L*	314	RL78/G13	R5F100MGDFA	PLQP0080J*
255	RL78/G13	R5F100LEDFA	PLQP0064J*	315	RL78/G13	R5F100MGDFB	PLQP0080K*
256	RL78/G13	R5F100LEDFB	PLQP0064K*	316	RL78/G13	R5F100MGGFA	PLQP0080J*
257	RL78/G13	R5F100LEGBG	PVBG0064L*	317	RL78/G13	R5F100MGGFB	PLQP0080K*
258	RL78/G13	R5F100LEGFA	PLQP0064J*	318	RL78/G13	R5F100MHAFDA	PLQP0080J*
259	RL78/G13	R5F100LEGFB	PLQP0064K*	319	RL78/G13	R5F100MHAFB	PLQP0080K*
260	RL78/G13	R5F100LFABG	PVBG0064L*	320	RL78/G13	R5F100MHDFA	PLQP0080J*
261	RL78/G13	R5F100LFAFDA	PLQP0064J*	321	RL78/G13	R5F100MHDFB	PLQP0080K*
262	RL78/G13	R5F100LFAFB	PLQP0064K*	322	RL78/G13	R5F100MHGFA	PLQP0080J*
263	RL78/G13	R5F100LFDBG	PVBG0064L*	323	RL78/G13	R5F100MHGFB	PLQP0080K*
264	RL78/G13	R5F100LFDFA	PLQP0064J*	324	RL78/G13	R5F100MJADFA	PLQP0080J*
265	RL78/G13	R5F100LFDFB	PLQP0064K*	325	RL78/G13	R5F100MJAFB	PLQP0080K*
266	RL78/G13	R5F100LFGGBG	PVBG0064L*	326	RL78/G13	R5F100MJDFDA	PLQP0080J*
267	RL78/G13	R5F100LFGFA	PLQP0064J*	327	RL78/G13	R5F100MJDFB	PLQP0080K*
268	RL78/G13	R5F100LFGFB	PLQP0064K*	328	RL78/G13	R5F100MJGFA	PLQP0080J*
269	RL78/G13	R5F100LGABG	PVBG0064L*	329	RL78/G13	R5F100MJGFB	PLQP0080K*
270	RL78/G13	R5F100LGADFA	PLQP0064J*	330	RL78/G13	R5F100MKADFA	PLQP0080J*
271	RL78/G13	R5F100LGAFB	PLQP0064K*	331	RL78/G13	R5F100MKAFB	PLQP0080K*
272	RL78/G13	R5F100LGDBG	PVBG0064L*	332	RL78/G13	R5F100MKDFA	PLQP0080J*
273	RL78/G13	R5F100LGDFA	PLQP0064J*	333	RL78/G13	R5F100MKDFB	PLQP0080K*
274	RL78/G13	R5F100LGDFB	PLQP0064K*	334	RL78/G13	R5F100MKGFB	PLQP0080K*
275	RL78/G13	R5F100LGGGBG	PVBG0064L*	335	RL78/G13	R5F100MLADFA	PLQP0080J*
276	RL78/G13	R5F100LGGFA	PLQP0064J*	336	RL78/G13	R5F100MLAFB	PLQP0080K*
277	RL78/G13	R5F100LGGFB	PLQP0064K*	337	RL78/G13	R5F100MLDFA	PLQP0080J*
278	RL78/G13	R5F100LHABG	PVBG0064L*	338	RL78/G13	R5F100MLDFB	PLQP0080K*
279	RL78/G13	R5F100LHAFDA	PLQP0064J*	339	RL78/G13	R5F100MLGFB	PLQP0080K*
280	RL78/G13	R5F100LHAFB	PLQP0064K*	340	RL78/G13	R5F100PFADFA	PLQP0100J*

Table. Product list

MCR-22-0498

No	Group	Product part number	Package code	No	Group	Product part number	Package code
341	RL78/G13	R5F100PFAFB	PLQP0100K*	401			
342	RL78/G13	R5F100PFDFA	PLQP0100J*	402			
343	RL78/G13	R5F100PFDFA	PLQP0100K*	403			
344	RL78/G13	R5F100PFGFA	PLQP0100J*	404			
345	RL78/G13	R5F100PFGFB	PLQP0100K*	405			
346	RL78/G13	R5F100PGAFA	PLQP0100J*	406			
347	RL78/G13	R5F100PGAFA	PLQP0100K*	407			
348	RL78/G13	R5F100PGDFA	PLQP0100J*	408			
349	RL78/G13	R5F100PGDFB	PLQP0100K*	409			
350	RL78/G13	R5F100PGGFA	PLQP0100J*	410			
351	RL78/G13	R5F100PGGFB	PLQP0100K*	411			
352	RL78/G13	R5F100PHAFB	PLQP0100J*	412			
353	RL78/G13	R5F100PHAFB	PLQP0100K*	413			
354	RL78/G13	R5F100PHDFA	PLQP0100J*	414			
355	RL78/G13	R5F100PHDFB	PLQP0100K*	415			
356	RL78/G13	R5F100PHGFA	PLQP0100J*	416			
357	RL78/G13	R5F100PHGFB	PLQP0100K*	417			
358	RL78/G13	R5F100PJAFB	PLQP0100J*	418			
359	RL78/G13	R5F100PJAFB	PLQP0100K*	419			
360	RL78/G13	R5F100PJDFA	PLQP0100J*	420			
361	RL78/G13	R5F100PJDFB	PLQP0100K*	421			
362	RL78/G13	R5F100PJGFA	PLQP0100J*	422			
363	RL78/G13	R5F100PJGFB	PLQP0100K*	423			
364	RL78/G13	R5F100PKAFA	PLQP0100J*	424			
365	RL78/G13	R5F100PKAFB	PLQP0100K*	425			
366	RL78/G13	R5F100PKDFA	PLQP0100J*	426			
367	RL78/G13	R5F100PKDFB	PLQP0100K*	427			
368	RL78/G13	R5F100PKGFB	PLQP0100K*	428			
369	RL78/G13	R5F100PLAFA	PLQP0100J*	429			
370	RL78/G13	R5F100PLAFB	PLQP0100K*	430			
371	RL78/G13	R5F100PLDFA	PLQP0100J*	431			
372	RL78/G13	R5F100PLDFB	PLQP0100K*	432			
373	RL78/G13	R5F100PLGFB	PLQP0100K*	433			
374	RL78/G13	R5F100SHAFB	PLQP0128K*	434			
375	RL78/G13	R5F100SHDFB	PLQP0128K*	435			
376	RL78/G13	R5F100SJAFB	PLQP0128K*	436			
377	RL78/G13	R5F100SJDFB	PLQP0128K*	437			
378	RL78/G13	R5F100SKAFB	PLQP0128K*	438			
379	RL78/G13	R5F100SKDFB	PLQP0128K*	439			
380	RL78/G13	R5F100SLAFB	PLQP0128K*	440			
381	RL78/G13	R5F100SLDFB	PLQP0128K*	441			
382				442			
383				443			
384				444			
385				445			
386				446			
387				447			
388				448			
389				449			
390				450			
391				451			
392				452			
393				453			
394				454			
395				455			
396				456			
397				457			
398				458			
399				459			
400				460			