

RENESAS SEMICONDUCTOR RELIABILITY REPORT

GROUP : RL78/G23

DEVICE : R7F100GXXX

APPLICATION : Consumer / Industry

Quality Assurance Div.
Renesas Electronics Corporation

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
 5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
 7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
 8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document .
 13. This document shall not be reproduced or duplicated in any form or disclosed to any third party, in whole or in part, without prior written consent of Renesas Electronics.
 14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-2 October 2020)

Table. Reliability test results (QFP)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

Table. Reliability test results (QFN)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

Table. Reliability test results (SOP)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-65 °C to 150 °C , 300 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Solderability (SD)	J-STD-002	245 °C, 5 s, Solder coverage ≥95 %	0/5	
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

Table. Reliability test results (LGA)

Test Items	Reference	Test Conditions	Results Failure/Size	Comment
High Temperature Operating Life (HTOL)	JESD22-A108	Ta=125 °C, Vccmax, 1000 hrs	0/22	
High Temperature Storage Life (HTSL)	JESD22-A103	Ta=150 °C, 1000 hrs	0/22	
Temperature Humidity bias (THB) (*1)	JESD22-A101	Ta=85 °C, RH=85 %, Vccmax, 1000 hrs	0/22	
Temperature Cycling (TC) (*1)	JESD22-A104	Ta=-55 °C to 125 °C , 500 cycles	0/22	
Latch-Up (LU)	JESD78	Pulse Current Injection, I=+/-150 mA	0/3	
Electrostatic discharge (ESD-HBM)	JS-001	1.5 kΩ, 100 pF, +/-2000 V, 1 time	0/3	Class: 2
Electrostatic discharge (ESD-CDM)	JESD22-C101	+/-500V,1time	0/3	Class: C2
Resistance to Soldering Heat (PC)	JESD22-A113, J-STD-020	MSL3(Moisture Sensitivity Level 3)	0/22	

*1) With preconditioning per JESD22-A113, MSL 3

•It is tested to confirm that all the samples are satisfied with an individual product specification.

Note :

Basically qualification tests were performed using a representative product with the same wafer process and the same package structure .

The failure rate of the device in an actual use condition can be estimated by the below procedure.

•Equation for the failure rate estimation (λ)

$$\lambda = \lambda_b \times \pi T \text{ (FIT)}$$

①Unique failure rate (λ_b)

$$\lambda_b = 4.1 \text{ FIT}$$

Unique failure rate at $T_a=55^\circ\text{C}$ using 60 % confidence level.

②Temperature term (πT)

$$\pi T = \exp\{11600 \times E_a \times (1/(273+55) - 1/(273+T_a))\}$$

E_a : Activation energy (eV)

T_a : Ambient temperature ($^\circ\text{C}$)

πT simplified chart as $E_a=0.7 \text{ eV}$												
T_a ($^\circ\text{C}$)	40	50	55	60	65	70	75	80	85	90	100	110
πT	0.31	0.68	1	1.45	2.08	2.95	4.15	5.77	7.96	10.88	19.82	34.99

•MTTF (Mean Time To Failure)

$$MTTF = 1/\lambda$$

Reference about Renesas package code

Package type		Package code *1
Lead type plastic package	QFP	PxQP
	SOP	PxSP
Non-lead type plastic package	QFN	PxQN
Grid array type plastic package	BGA	PxBG
	LGA	PxLG

*1. First four digit

Table. Product list

No	Group	Product part number	Package code	No	Group	Product part number	Package code
1	RL78/G23	R7F100GBF2DFP	PLQP0032G*	51	RL78/G23	R7F100GMG2DFA	PLQP0080J*
2	RL78/G23	R7F100GBF3CFP	PLQP0032G*	52	RL78/G23	R7F100GMG3CFA	PLQP0080J*
3	RL78/G23	R7F100GBG2DFP	PLQP0032G*	53	RL78/G23	R7F100GMH2DFA	PLQP0080J*
4	RL78/G23	R7F100GBG3CFP	PLQP0032G*	54	RL78/G23	R7F100GMH3CFA	PLQP0080J*
5	RL78/G23	R7F100GGF2DFB	PLQP0048K*	55	RL78/G23	R7F100GMJ2DFA	PLQP0080J*
6	RL78/G23	R7F100GGF3CFB	PLQP0048K*	56	RL78/G23	R7F100GMJ3CFA	PLQP0080J*
7	RL78/G23	R7F100GGG2DFB	PLQP0048K*	57	RL78/G23	R7F100GBH2DFP	PLQP0032G*
8	RL78/G23	R7F100GGG3CFB	PLQP0048K*	58	RL78/G23	R7F100GBH3CFP	PLQP0032G*
9	RL78/G23	R7F100GLF2DFB	PLQP0064K*	59	RL78/G23	R7F100GBJ2DFP	PLQP0032G*
10	RL78/G23	R7F100GLF3CFB	PLQP0064K*	60	RL78/G23	R7F100GBJ3CFP	PLQP0032G*
11	RL78/G23	R7F100GLG2DFB	PLQP0064K*	61	RL78/G23	R7F100GJH2DFA	PLQP0052J*
12	RL78/G23	R7F100GLG3CFB	PLQP0064K*	62	RL78/G23	R7F100GJH3CFA	PLQP0052J*
13	RL78/G23	R7F100GGK2DFB	PLQP0048K*	63	RL78/G23	R7F100GJJ2DFA	PLQP0052J*
14	RL78/G23	R7F100GGK3CFB	PLQP0048K*	64	RL78/G23	R7F100GJJ3CFA	PLQP0052J*
15	RL78/G23	R7F100GGL2DFB	PLQP0048K*	65	RL78/G23	R7F100GMK2DFA	PLQP0080J*
16	RL78/G23	R7F100GGL3CFB	PLQP0048K*	66	RL78/G23	R7F100GMK2DFB	PLQP0080K*
17	RL78/G23	R7F100GGN2DFB	PLQP0048K*	67	RL78/G23	R7F100GMK3CFA	PLQP0080J*
18	RL78/G23	R7F100GGN3CFB	PLQP0048K*	68	RL78/G23	R7F100GMK3CFB	PLQP0080K*
19	RL78/G23	R7F100GLK2DFB	PLQP0064K*	69	RL78/G23	R7F100GML2DFA	PLQP0080J*
20	RL78/G23	R7F100GLK3CFB	PLQP0064K*	70	RL78/G23	R7F100GML2DFB	PLQP0080K*
21	RL78/G23	R7F100GLL2DFB	PLQP0064K*	71	RL78/G23	R7F100GML3CFA	PLQP0080J*
22	RL78/G23	R7F100GLL3CFB	PLQP0064K*	72	RL78/G23	R7F100GML3CFB	PLQP0080K*
23	RL78/G23	R7F100GLN2DFB	PLQP0064K*	73	RL78/G23	R7F100GMN2DFA	PLQP0080J*
24	RL78/G23	R7F100GLN3CFB	PLQP0064K*	74	RL78/G23	R7F100GMN2DFB	PLQP0080K*
25	RL78/G23	R7F100GPG2DFB	PLQP0100K*	75	RL78/G23	R7F100GMN3CFA	PLQP0080J*
26	RL78/G23	R7F100GPG3CFB	PLQP0100K*	76	RL78/G23	R7F100GMN3CFB	PLQP0080K*
27	RL78/G23	R7F100GPH2DFB	PLQP0100K*	77	RL78/G23	R7F100GJK2DFA	PLQP0052J*
28	RL78/G23	R7F100GPH3CFB	PLQP0100K*	78	RL78/G23	R7F100GJK3CFA	PLQP0052J*
29	RL78/G23	R7F100GPJ2DFB	PLQP0100K*	79	RL78/G23	R7F100GJL2DFA	PLQP0052J*
30	RL78/G23	R7F100GPJ3CFB	PLQP0100K*	80	RL78/G23	R7F100GJL3CFA	PLQP0052J*
31	RL78/G23	R7F100GPK2DFB	PLQP0100K*	81	RL78/G23	R7F100GJN2DFA	PLQP0052J*
32	RL78/G23	R7F100GPK3CFB	PLQP0100K*	82	RL78/G23	R7F100GJN3CFA	PLQP0052J*
33	RL78/G23	R7F100GPL2DFB	PLQP0100K*	83	RL78/G23	R7F100GFK2DFP	PLQP0044G*
34	RL78/G23	R7F100GPL3CFB	PLQP0100K*	84	RL78/G23	R7F100GFK3CFP	PLQP0044G*
35	RL78/G23	R7F100GPN2DFB	PLQP0100K*	85	RL78/G23	R7F100GFL2DFP	PLQP0044G*
36	RL78/G23	R7F100GPN3CFB	PLQP0100K*	86	RL78/G23	R7F100GFL3CFP	PLQP0044G*
37	RL78/G23	R7F100GGH2DFB	PLQP0048K*	87	RL78/G23	R7F100GFN2DFP	PLQP0044G*
38	RL78/G23	R7F100GGH3CFB	PLQP0048K*	88	RL78/G23	R7F100GFN3CFP	PLQP0044G*
39	RL78/G23	R7F100GGJ2DFB	PLQP0048K*	89	RL78/G23	R7F100GLK2DFA	PLQP0064J*
40	RL78/G23	R7F100GGJ3CFB	PLQP0048K*	90	RL78/G23	R7F100GLK3CFA	PLQP0064J*
41	RL78/G23	R7F100GLH2DFB	PLQP0064K*	91	RL78/G23	R7F100GLL2DFA	PLQP0064J*
42	RL78/G23	R7F100GLH3CFB	PLQP0064K*	92	RL78/G23	R7F100GLL3CFA	PLQP0064J*
43	RL78/G23	R7F100GLJ2DFB	PLQP0064K*	93	RL78/G23	R7F100GLN2DFA	PLQP0064J*
44	RL78/G23	R7F100GLJ3CFB	PLQP0064K*	94	RL78/G23	R7F100GLN3CFA	PLQP0064J*
45	RL78/G23	R7F100GMG2DFB	PLQP0080K*	95	RL78/G23	R7F100GPG2DFA	PLQP0100J*
46	RL78/G23	R7F100GMG3CFB	PLQP0080K*	96	RL78/G23	R7F100GPG3CFA	PLQP0100J*
47	RL78/G23	R7F100GMH2DFB	PLQP0080K*	97	RL78/G23	R7F100GPH2DFA	PLQP0100J*
48	RL78/G23	R7F100GMH3CFB	PLQP0080K*	98	RL78/G23	R7F100GPH3CFA	PLQP0100J*
49	RL78/G23	R7F100GMJ2DFB	PLQP0080K*	99	RL78/G23	R7F100GPJ2DFA	PLQP0100J*
50	RL78/G23	R7F100GMJ3CFB	PLQP0080K*	100	RL78/G23	R7F100GPJ3CFA	PLQP0100J*

Table. Product list

MCR-22-0480-C

No	Group	Product part number	Package code	No	Group	Product part number	Package code
101	RL78/G23	R7F100GPK2DFA	PLQP0100J*	161	RL78/G23	R7F100GLH2DFA	PLQP0064J*
102	RL78/G23	R7F100GPK3CFA	PLQP0100J*	162	RL78/G23	R7F100GLH3CFA	PLQP0064J*
103	RL78/G23	R7F100GPL2DFA	PLQP0100J*	163	RL78/G23	R7F100GLJ2DFA	PLQP0064J*
104	RL78/G23	R7F100GPL3CFA	PLQP0100J*	164	RL78/G23	R7F100GLJ3CFA	PLQP0064J*
105	RL78/G23	R7F100GPN2DFA	PLQP0100J*	165	RL78/G23	R7F100GSJ2DFB	PLQP0128K*
106	RL78/G23	R7F100GPN3CFA	PLQP0100J*	166	RL78/G23	R7F100GSJ3CFB	PLQP0128K*
107	RL78/G23	R7F100GBF2DNP	PWQN0032K*	167	RL78/G23	R7F100GSK2DFB	PLQP0128K*
108	RL78/G23	R7F100GBF3CNP	PWQN0032K*	168	RL78/G23	R7F100GSK3CFB	PLQP0128K*
109	RL78/G23	R7F100GBG2DNP	PWQN0032K*	169	RL78/G23	R7F100GSL2DFB	PLQP0128K*
110	RL78/G23	R7F100GBG3CNP	PWQN0032K*	170	RL78/G23	R7F100GSL3CFB	PLQP0128K*
111	RL78/G23	R7F100GEF2DNP	PWQN0040K*	171	RL78/G23	R7F100GSN2DFB	PLQP0128K*
112	RL78/G23	R7F100GEF3CNP	PWQN0040K*	172	RL78/G23	R7F100GSN3CFB	PLQP0128K*
113	RL78/G23	R7F100GEG2DNP	PWQN0040K*	173	RL78/G23	R7F100GCF2DLA	PWL0036K*
114	RL78/G23	R7F100GEG3CNP	PWQN0040K*	174	RL78/G23	R7F100GCF3CLA	PWL0036K*
115	RL78/G23	R7F100GGF2DNP	PWQN0048K*	175	RL78/G23	R7F100GCG2DLA	PWL0036K*
116	RL78/G23	R7F100GGF3CNP	PWQN0048K*	176	RL78/G23	R7F100GCG3CLA	PWL0036K*
117	RL78/G23	R7F100GGG2DNP	PWQN0048K*	177	RL78/G23	R7F100GLF2DLA	PWL0064K*
118	RL78/G23	R7F100GGG3CNP	PWQN0048K*	178	RL78/G23	R7F100GLF3CLA	PWL0064K*
119	RL78/G23	R7F100GBH2DNP	PWQN0032K*	179	RL78/G23	R7F100GLG2DLA	PWL0064K*
120	RL78/G23	R7F100GBH3CNP	PWQN0032K*	180	RL78/G23	R7F100GLG3CLA	PWL0064K*
121	RL78/G23	R7F100GBJ2DNP	PWQN0032K*	181	RL78/G23	R7F100GCH2DLA	PWL0036K*
122	RL78/G23	R7F100GBJ3CNP	PWQN0032K*	182	RL78/G23	R7F100GCH3CLA	PWL0036K*
123	RL78/G23	R7F100GEH2DNP	PWQN0040K*	183	RL78/G23	R7F100GCJ2DLA	PWL0036K*
124	RL78/G23	R7F100GEH3CNP	PWQN0040K*	184	RL78/G23	R7F100GCJ3CLA	PWL0036K*
125	RL78/G23	R7F100GEJ2DNP	PWQN0040K*	185	RL78/G23	R7F100GLH2DLA	PWL0064K*
126	RL78/G23	R7F100GEJ3CNP	PWQN0040K*	186	RL78/G23	R7F100GLH3CLA	PWL0064K*
127	RL78/G23	R7F100GGH2DNP	PWQN0048K*	187	RL78/G23	R7F100GLJ2DLA	PWL0064K*
128	RL78/G23	R7F100GGH3CNP	PWQN0048K*	188	RL78/G23	R7F100GLJ3CLA	PWL0064K*
129	RL78/G23	R7F100GGJ2DNP	PWQN0048K*	189	RL78/G23	R7F100GLK2DLA	PWL0064K*
130	RL78/G23	R7F100GGJ3CNP	PWQN0048K*	190	RL78/G23	R7F100GLK3CLA	PWL0064K*
131	RL78/G23	R7F100GGK2DNP	PWQN0048K*	191	RL78/G23	R7F100GLL2DLA	PWL0064K*
132	RL78/G23	R7F100GGK3CNP	PWQN0048K*	192	RL78/G23	R7F100GLL3CLA	PWL0064K*
133	RL78/G23	R7F100GGL2DNP	PWQN0048K*	193	RL78/G23	R7F100GLN2DLA	PWL0064K*
134	RL78/G23	R7F100GGL3CNP	PWQN0048K*	194	RL78/G23	R7F100GLN3CLA	PWL0064K*
135	RL78/G23	R7F100GGN2DNP	PWQN0048K*	195			
136	RL78/G23	R7F100GGN3CNP	PWQN0048K*	196			
137	RL78/G23	R7F100GJF2DFA	PLQP0052J*	197			
138	RL78/G23	R7F100GJF3CFA	PLQP0052J*	198			
139	RL78/G23	R7F100GJG2DFA	PLQP0052J*	199			
140	RL78/G23	R7F100GJG3CFA	PLQP0052J*	200			
141	RL78/G23	R7F100GFF2DFP	PLQP0044G*	201			
142	RL78/G23	R7F100GFF3CFP	PLQP0044G*	202			
143	RL78/G23	R7F100GFG2DFP	PLQP0044G*	203			
144	RL78/G23	R7F100GFG3CFP	PLQP0044G*	204			
145	RL78/G23	R7F100GLF2DFA	PLQP0064J*	205			
146	RL78/G23	R7F100GLF3CFA	PLQP0064J*	206			
147	RL78/G23	R7F100GLG2DFA	PLQP0064J*	207			
148	RL78/G23	R7F100GLG3CFA	PLQP0064J*	208			
149	RL78/G23	R7F100GAF2DSP	PLSP0030J*	209			
150	RL78/G23	R7F100GAF3CSP	PLSP0030J*	210			
151	RL78/G23	R7F100GAG2DSP	PLSP0030J*	211			
152	RL78/G23	R7F100GAG3CSP	PLSP0030J*	212			
153	RL78/G23	R7F100GAH2DSP	PLSP0030J*	213			
154	RL78/G23	R7F100GAH3CSP	PLSP0030J*	214			
155	RL78/G23	R7F100GAJ2DSP	PLSP0030J*	215			
156	RL78/G23	R7F100GAJ3CSP	PLSP0030J*	216			
157	RL78/G23	R7F100GFH2DFP	PLQP0044G*	217			
158	RL78/G23	R7F100GFH3CFP	PLQP0044G*	218			
159	RL78/G23	R7F100GFJ2DFP	PLQP0044G*	219			
160	RL78/G23	R7F100GFJ3CFP	PLQP0044G*	220			