

Voice Anti-Spoofing (VAS) for Voice User Interface Applications

Quick Start Guide

Renesas RA Family
RA6 Series

All information contained in these materials, including products and product specifications, represents information on the product at the time of publication and is subject to change by Renesas Electronics Corp. without notice. Please review the latest information published by Renesas Electronics Corp. through various means, including the Renesas Electronics Corp. website (<http://www.renesas.com>).

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.

7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 October 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/.

Renesas VOICE KIT RA6E1 Disclaimer

By using this VOICE KIT RA6E1, the User accepts the following terms, which are in addition to, and control in the event of disagreement, with Renesas' General Terms and Conditions available at <https://www.renesas.com/en-us/legal/disclaimer.html>.

The VOICE KIT RA6E1 is not guaranteed to be error free, and the entire risk as to the results and performance of the VOICE KIT RA6E1 is assumed by the User. The VOICE KIT RA6E1 is provided by Renesas on an "as is" basis without warranty of any kind whether express or implied, including but not limited to the implied warranties of good workmanship, fitness for a particular purpose, title, merchantability, and non-infringement of intellectual property rights. Renesas expressly disclaims any implied warranty.

Renesas does not consider the VOICE KIT RA6E1 to be a finished product and therefore the VOICE KIT RA6E1 may not comply with some requirements applicable to finished products, including, but not limited to recycling, restricted substances and electromagnetic compatibility regulations. Refer to Certifications section, for information about certifications and compliance information for the VOICE KIT RA6E1. It is the kit User's responsibility to make sure the kit meets any local requirements applicable to their region.

Renesas or its affiliates shall in no event be liable for any loss of profit, loss of data, loss of contract, loss of business, damage to reputation or goodwill, any economic loss, any reprogramming or recall costs (whether the foregoing losses are direct or indirect) nor shall Renesas or its affiliates be liable for any other direct or indirect special, incidental or consequential damages arising out of or in relation to the use of this VOICE KIT RA6E1, even if Renesas or its affiliates have been advised of the possibility of such damages.

Renesas has used reasonable care in preparing the information included in this document, but Renesas does not warrant that such information is error free nor does Renesas guarantee an exact match for every application or parameter to part numbers designated by other vendors listed herein. The information provided in this document is intended solely to enable the use of Renesas products. No express or implied license to any intellectual property right is granted by this document or in connection with the sale of Renesas products. Renesas reserves the right to make changes to specifications and product descriptions at any time without notice. Renesas assumes no liability for any damages incurred by you resulting from errors in or omissions from the information included herein. Renesas cannot verify, and assumes no liability for, the accuracy of information available on another company's website.

Precautions

This Evaluation Kit is only intended for use in a laboratory environment under ambient temperature and humidity conditions. A safe separation distance should be used between this and any sensitive equipment. Its use outside the laboratory, classroom, study area, or similar such area invalidates conformity with the protection requirements of the Electromagnetic Compatibility Directive and could lead to prosecution.

The product generates, uses, and can radiate radio frequency energy and may cause harmful interference to radio communications. There is no guarantee that interference will not occur in a particular installation. If this equipment causes harmful interference to radio or television reception, which can be determined by turning the equipment off or on, you are encouraged to try to correct the interference by one or more of the following measures:

- Ensure attached cables do not lie across the equipment.
- Reorient the receiving antenna.
- Increase the distance between the equipment and the receiver.
- Connect the equipment into an outlet on a circuit different from that which the receiver is connected.
- Power down the equipment when not in use.
- Consult the dealer or an experienced radio/TV technician for help.

Note: It is recommended that wherever possible shielded interface cables are used.

The product is potentially susceptible to certain EMC phenomena. To mitigate against them it is recommended that the following measures be undertaken:

- The user is advised that mobile phones should not be used within 10 m of the product when in use.
- The user is advised to take ESD precautions when handling the equipment.

The Evaluation Kit does not represent an ideal reference design for an end product and does not fulfill the regulatory standards for an end product.

General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Precaution against Electrostatic Discharge (ESD)

A strong electrical field, when exposed to a CMOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop the generation of static electricity as much as possible, and quickly dissipate it when it occurs. Environmental control must be adequate. When it is dry, a humidifier should be used. This is recommended to avoid using insulators that can easily build up static electricity.

Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors must be grounded. The operator must also be grounded using a wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions must be taken for printed circuit boards with mounted semiconductor devices.

2. Processing at power-on

The state of the product is undefined at the time when power is supplied. The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the time when power is supplied. In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the time when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the time when power is supplied until the power reaches the level at which resetting is specified.

3. Input of signal during power-off state

Do not input signals or an I/O pull-up power supply while the device is powered off. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Follow the guideline for input signal during power-off state as described in your product documentation.

4. Handling of unused pins

Handle unused pins in accordance with the directions given under handling of unused pins in the manual. The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of the LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible.

5. Clock signals

After applying a reset, only release the reset line after the operating clock signal becomes stable. When switching the clock signal during program execution, wait until the target clock signal is stabilized. When the clock signal is generated with an external resonator or from an external oscillator during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Additionally, when switching to a clock signal produced with an external resonator or by an external oscillator while program execution is in progress, wait until the target clock signal is stable.

6. Voltage application waveform at input pin

Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between V_{IL} (Max.) and V_{IH} (Min.) due to noise, for example, the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between V_{IL} (Max.) and V_{IH} (Min.).

7. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited. The reserved addresses are provided for possible future expansion of functions. Do not access these addresses as the correct operation of the LSI is not guaranteed.

8. Differences between products

Before changing from one product to another, for example to a product with a different part number, confirm that the change will not lead to problems. The characteristics of a microprocessing unit or microcontroller unit products in the same group but having a different part number might differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

VOICE KIT RA6E1

VOICE KIT RA6E1 – Quick Start Guide

Contents

Corporate Headquarters	2
Contact information.....	2
Trademarks.....	2
1. Introduction.....	6
1.1 Assumptions and Advisory Notes.....	6
2. Overview of the “Voice Anti-Spoofing (VAS) for Voice User Interface Applications” application example.....	6
2.1 Quick Start Guide Project Flow	7
3. Running the “Voice Anti-Spoofing (VAS) for Voice User Interface Applications” application example.....	8
3.1 Connecting and Powering Up the Voice Kit RA6E1 Board	8
3.2 Programming the application example	8
3.3 UART Terminal Output.....	9
3.4 Guidelines for Demo Operation.....	9
3.5 Running the Quick Start Guide Project	10
Revision History	12

Figures

Figure 1. Overview of VAS	6
Figure 2. Quick Start Guide Project Flow	7
Figure 3. Voice Kit RA6E1 Board & USB Debug cable	8
Figure 4. Serial Port Setup	9
Figure 5. Command group not active as detection dropped	10
Figure 6. Initial information on the model and commands.....	10
Figure 7. Detected Class: Accepted	11
Figure 8. Detected Class: Dropped	11

1. Introduction

This Quick Start Guide (QSG) provides:

- Instructions for running the “Voice Anti-Spoofing (VAS) for Voice User Interface Applications” application example.

1.1 Assumptions and Advisory Notes

1. Prior to running the Quick Start example project or programming the Voice Kit RA6E1 board, default jumper settings must be used. Refer to the Voice Kit RA6E1 user's manual for the default jumper settings.
2. The screen shots provided throughout this document are for reference. The actual screen content may differ depending on the version of software and development tools used.

2. Overview of the “Voice Anti-Spoofing (VAS) for Voice User Interface Applications” application example

The Renesas Reality AI Voice Anti-Spoofing application example is used as an extension of the VUI - Voice Command Recognition from Cyberon, to detect Human real voice vs Machine generated or recorded voice.

Hereby the key wake word “Hi-Renesas” is used and only if real human voice is identified by the Voice Anti-Spoofing feature, the Voice Command Recognition will accept next coming commands accordingly.

For demonstration purposes, limited amount of data and recording devices has been used to train the model on e2studio and Reality AI TOOLS®.

It is strongly recommended that the provided recordings will be used to examine recorded wake word detection.




Figure 1. Overview of VAS

2.1 Quick Start Guide Project Flow




Figure 2. Quick Start Guide Project Flow

3. Running the “Voice Anti-Spoofing (VAS) for Voice User Interface Applications” application example

This section lists the requirements and instructions to power up the Voice Kit RA6E1 board and run application example.

Hardware Requirements

- Voice Kit RA6E1 board
- Micro USB device cable
- A PC with at least 1 USB port

Software Requirements

- Windows® 10 operating system
- Serial terminal (ex. Tera Term, Putty)
- J-Link tools

3.1 Connecting and Powering Up the Voice Kit RA6E1 Board

1. Connect the micro-USB end of the micro-USB device cable to micro-AB USB port (J6) of the Voice Kit RA6E1 board.
2. Connect the other end of this cable to the USB port of the host PC. Power LED (LED5) on the Voice Kit RA6E1 board lights up blue, indicating that the board is powered on.



VOICE-RA6E1 VUI Solution Kit



USB micro-B cable (included with the kit)

Figure 3. Voice Kit RA6E1 Board & USB Debug cable

3.2 Programming the application example

Flash the device with the binary that has been provided with this document.

In the folder Flasher you will find the following files:

- Flash Device.bat
- Flash Device.jlink
- JLink.exe
- JLink_x64.dll

- vk_ra6e1_vas_vcr_22_3_2024.srec

Verify that the Voice Kit RA6E1 board is connected to the PC and run the Flash Device.bat file, the project will be automatically downloaded to the DUT.

3.3 UART Terminal Output

If the user connects the DUT and the PC then UART output can be enabled.

For that the user needs to setup the serial terminal as follows:

- Speed / Baud Rate 460800
- Data 8 bit
- Parity none
- Stop bits 1 bit
- Flow Control none




Figure 4. Serial Port Setup

3.4 Guidelines for Demo Operation

The ML model must reliably distinguish between real and spoof in the following context:

- User either says or plays back a recording of the English phrase “Hi Renesas”.

User may speak with any common spoken English accent and any natural vocal tonal quality (male or female).

- The playback device is a phone speaker (iPhone or Android) *
- Environmental noise is within such a range that the Cyberon voice stack can recognize the wake-word.
- Both real and spoofed utterances are identifiable at a variety of loudness levels.

The following items are explicitly out-of-scope and non-deliverable:

- Specific information about the methodology used to collect data or train the model. That is, a single model is provided as-is, and there is no expectation that the model can be replicated by the end-user.
- Model generalizability to situations other than those described above. Model is not expected to generalize to arbitrary playback devices*, arbitrary utterances, or other languages.

It is strongly recommended that the provided recordings will be used to examine Machine generated or recorded voice detection.

3.5 Running the Quick Start Guide Project

To run application example, use the following instructions:


1. On power up or RESET.

Note: The debug LED (LED OB) will blink or light up green; this can be ignored for now.

2. Give the wake-word “Hi Renesas”.
3. If the detected voice is real the UART in terminal will print “Detected Class: Accepted.”
4. If the VAS detects recorded voice, the result is Dropped, and User can NOT continue to command. The UART in terminal will print “Detected Class: Dropped, as depicted in figure 5 below.
5. If the result is Accepted, then User can continue to command the Terminal will show “Command group active.
6. Give the Command Light On or Light Off or Sequence.
7. Command recognition indicators:
 1. Light On the 3 user LED will flash
 2. Light Off the LEDs will stop flashing
 3. Sequence the 3 LED will blink in sequence

```
Get command<0> : Hi Renesas, Score=58, SG_Diff=97, Energy=718, MapID=0
Detected Class: Dropped
Command group not active.
Light On, Map ID = 1
Light Off, Map ID = 2
Sequence, Map ID = 3
```

Figure 5. Command group not active as detection dropped



```
COM15 - Tera Term VT
File Edit Setup Control Window Help
Successfully initialize DC/DS
Little Endian
MCU board: VOICE-RA6E1
FSP version: 5.1
Dspotter version: DspotterSDK v2.2.12.3 (compiled at Nov 1 2021)
Copyright (C) 2018-2020 Cyberon Corp.
Sample code build: 210312
Unique ID: 0x4106801a-35373536-63614453-4E4B2A98
This Dspotter model declares memory buffer size = 50000
The Dspotter model, group 0 needs working memory size = 40488
Command list for group index 0:
Hi Renesas, Map ID = 0

The Dspotter model, group 1 needs working memory size = 40744
Command list for group index 1:
Light On, Map ID = 1
Light Off, Map ID = 2
Sequence, Map ID = 3

Wake-up group active.
Hi Renesas, Map ID = 0
```

Figure 6. Initial information on the model and commands

If the “Hi Renesas” wake word is accepted as “real” the UART terminal will print the “Detected Class: Accepted” message, as seen bellow, or “Detected Class: Dropped” if the result is recognized as recorded.

Then if the result of the Wake word is Accepted the user can continue and give the command.

```

Successfully initialize DC/DS
Little Endian
MCU board: VOICE-RA6E1
FSP version: 5.1
Dspotter version: DspotterSDK v2.2.12.3 (compiled at Nov  1 2021)
Copyright (C) 2018-2020 Cyberon Corp.
Sample code build: 210312
Unique ID: 0x41068A1A-35373536-63614453-4E4B2A98
This Dspotter model declares memory buffer size = 50000
The Dspotter model, group 0 needs working memory size = 40488
Command list for group index 0:
  Hi Renesas, Map ID = 0

The Dspotter model, group 1 needs working memory size = 40744
Command list for group index 1:
  Light On, Map ID = 1
  Light Off, Map ID = 2
  Sequence, Map ID = 3

Wake-up group active.
  Hi Renesas, Map ID = 0
Get command(0) : Hi Renesas, Score=1, SG_Diff=55, Energy=5217, MapID=0
Detected Class: Accepted
Command group active.
  Light On, Map ID = 1
  Light Off, Map ID = 2
  Sequence, Map ID = 3
Get command(1) : Light On, Score=39, SG_Diff=86, Energy=4722, MapID=1
wake-up group active.
  Hi Renesas, Map ID = 0

```

Figure 7. Detected Class: Accepted

The command will be executed only if the Detected Class of the wake word is Accepted.

```

Successfully initialize DC/DS
Little Endian
MCU board: VOICE-RA6E1
FSP version: 5.1
Dspotter version: DspotterSDK v2.2.12.3 (compiled at Nov  1 2021)
Copyright (C) 2018-2020 Cyberon Corp.
Sample code build: 210312
Unique ID: 0x41068A1A-35373536-63614453-4E4B2A98
This Dspotter model declares memory buffer size = 50000
The Dspotter model, group 0 needs working memory size = 40488
Command list for group index 0:
  Hi Renesas, Map ID = 0

The Dspotter model, group 1 needs working memory size = 40744
Command list for group index 1:
  Light On, Map ID = 1
  Light Off, Map ID = 2
  Sequence, Map ID = 3

Wake-up group active.
  Hi Renesas, Map ID = 0
Get command(0) : Hi Renesas, Score=60, SG_Diff=110, Energy=658, MapID=0
Detected Class: Dropped
Command group not active.
  Light On, Map ID = 1
  Light Off, Map ID = 2
  Sequence, Map ID = 3

```

Figure 8. Detected Class: Dropped

Revision History

Rev.	Date	Description	
		Page	Summary
1.00	Mar.26.24	—	Initial release

Voice Anti-Spoofing (VAS) for Voice User Interface Applications