

IS-1715ARH

Neutron Testing

TR042

Rev 0.00

November 30, 2016

Introduction

This report summarizes results of 1MeV equivalent neutron testing of the [IS-1715ARH](#) complementary power MOSFET driver. The test was conducted in order to determine the sensitivity of the part to displacement damage (DD) caused by neutron or proton environments. Neutron fluences ranged from $1 \times 10^{12} \text{ n/cm}^2$ to $1 \times 10^{14} \text{ n/cm}^2$. This project was carried out in collaboration with Harris Corporation (Melbourne, FL), and their support is gratefully acknowledged.

Part Description

The IS-1715ARH is a complementary power MOSFET driver designed for use in synchronous rectification circuits. Soft switching transitions for the two output waveforms may be managed by setting independently programmable delays. The delay pins T1 and T2 can alternatively be configured for zero-voltage sensing to allow for precise switching control. The IS-1715ARH has a single TTL-compatible input and can operate at frequencies up to 1MHz. The AUX output switches immediately at the rising edge of the INPUT, but waits for the T2 delay before responding to the falling edge. A logic low on the enable pin (ENABLE) places both outputs into an active-low mode, and an Undervoltage Lockout (UVLO) function is set at 9.0V maximum. Constructed using the Intersil dielectrically isolated Radiation Hardened Silicon Gate (RSG) process, the IS-1715ARH is immune to Single-Event Latch-Up (SEL) and is designed to provide highly reliable performance in harsh radiation environments.

Specifications for radiation hardened QML devices are controlled by the Defense Logistics Agency Land and Maritime in Columbus, OH. Detailed electrical specifications for the IS-1715ARH are contained in SMD [5962-00521](#).

Related Literature

- For a full list of related documents, visit our website
 - [IS-1715ARH](#) product page

Test Description

Irradiation Facilities

Neutron irradiation was performed at the Fast Burst Reactor facility at White Sands Missile Range (White Sands, NM), which provides a controlled 1MeV equivalent neutron flux. Parts were tested in an unbiased configuration with all leads shorted together in accordance with TM 1017 of MIL-STD-883. As neutron irradiation activates many of the heavier elements found in a packaged integrated circuit, the parts exposed at the higher neutron levels required (as expected) significant "cool-down" time before being shipped back to Intersil (Palm Bay, FL) for electrical testing.

Characterization Equipment and Procedures

Electrical testing was performed before and after irradiation using Intersil production Automated Test Equipment (ATE). All electrical testing was performed at room temperature.

Experimental Matrix

Testing proceeded in general accordance with the guidelines of MIL-STD-883 Test Method 1017. The experimental matrix consisted of five samples irradiated at $1 \times 10^{12} \text{ n/cm}^2$, five samples irradiated at $1 \times 10^{13} \text{ n/cm}^2$, five samples irradiated at $3 \times 10^{13} \text{ n/cm}^2$, and five samples irradiated at $1 \times 10^{14} \text{ n/cm}^2$. Two control units were used to insure repeatability. The IS-1715ARH samples were taken from current production inventory.

Results

Test Results

Neutron testing of the IS-1715ARH is complete and the results are reported in the balance of this report. It should be realized when reviewing the data that each neutron irradiation was performed on a different five-unit sample; this is not total dose testing, in which the damage is cumulative.

Variables Data

The plots in [Figures 1](#) through [19](#) show data plots for key parameters before and after irradiation to each level. The plots show the median, minimum, and maximum of each parameter as a function of neutron irradiation. We chose to plot the median because of the small sample sizes (five per cell) involved. We also show the applicable electrical limits taken from the SMD; it should be carefully noted that these limits are provided for guidance only as the IS-1715ARH is not specified for the neutron environment.

Variables Data Plots




FIGURE 1. IS-1715ARH nominal supply current as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 1mA to 6mA.




FIGURE 2. IS-1715ARH Sleep mode supply current as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 300µA to 900µA.

Variables Data Plots (Continued)




FIGURE 3. IS-1715ARH Undervoltage Lockout (UVLO) rising threshold as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 8.5V to 9.5V.




FIGURE 4. IS-1715ARH Undervoltage Lockout (UVLO) falling threshold as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 7.7V to 8.8V.

Variables Data Plots (Continued)




FIGURE 5. IS-1715ARH Undervoltage Lockout (UVLO) delta as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 0V to 2V.




FIGURE 6. IS-1715ARH pre-turn-on PWR and AUX stage LOW output voltage as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limit is 2V maximum for both parameters.

Variables Data Plots (Continued)




FIGURE 7. IS-1715ARH PWR stage saturated LOW output voltage, 40mA and 100mA load current cases, as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 1V maximum (40mA load current case) and 1.5V maximum (100mA load current case).




FIGURE 8. IS-1715ARH PWR stage saturated HIGH output voltage, 40mA and 100mA load current cases, as a function of neutron irradiation, showing the median, minimum and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 1V maximum (40mA load current case) and 1.5V maximum (100mA load current case).

Variables Data Plots (Continued)




FIGURE 9. IS-1715ARH AUX stage saturated LOW output voltage, 40mA and 100mA load current cases, as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 1V maximum (40mA load current case) and 1.5V maximum (100mA load current case).




FIGURE 10. IS-1715ARH AUX stage saturated HIGH output voltage, 40mA and 100mA load current cases, as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 1V maximum (40mA load current case) and 1.5V maximum (100mA load current case).

Variables Data Plots (Continued)




FIGURE 11. IS-1715ARH Enable and Input LOW input current as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are $-15 \mu\text{A}$ to $15 \mu\text{A}$ (Enable) and $-20 \mu\text{A}$ to $20 \mu\text{A}$ (Input).




FIGURE 12. IS-1715ARH PWR and AUX output rise time as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 15ns to 50ns for both parameters.

Variables Data Plots (Continued)




FIGURE 13. IS-1715ARH PWR and AUX output fall time as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 15ns to 50ns for both parameters.




FIGURE 14. IS-1715ARH PWR and AUX stage propagation delay as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 50ns to 300ns (PWR) and 50ns to 185ns (AUX).

Variables Data Plots (Continued)




FIGURE 15. IS-1715ARH T1 input time delay, AUX to PWR, RT1 = 10kΩ and RT1 = 100kΩ, as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were 1x10¹²n/cm² (five samples), 1x10¹³n/cm² (five samples), 3x10¹³n/cm² (five samples), and 1x10¹⁴n/cm² (five samples). For reference, the post total dose SMD limits are 45ns to 200ns (RT1 = 10kΩ) and 250ns to 1300ns (RT1 = 100kΩ).




FIGURE 16. IS-1715ARH T2 input time delay, PWR to AUX, RT1 = 10kΩ and RT1 = 100kΩ, as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were 1x10¹²n/cm² (five samples), 1x10¹³n/cm² (five samples), 3x10¹³n/cm² (five samples), and 1x10¹⁴n/cm² (five samples). For reference, the post total dose SMD limits are 50ns to 130ns (RT1 = 10kΩ) and 200ns to 700ns (RT1 = 100kΩ).

Variables Data Plots (Continued)




FIGURE 17. IS-1715ARH T1 and T2 input current limit as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are -5.5mA to -1.6mA (T1) and -5.5mA to -2.1mA (T2). The post $1 \times 10^{14} \text{ n/cm}^2$ samples were nonfunctional and that data is not plotted.




FIGURE 18. IS-1715ARH T1 and T2 pin nominal voltage as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 2.7V to 3.3V for both parameters.

Variables Data Plots (Continued)




FIGURE 19. IS-1715ARH minimum T1 and T2 input pin delay as a function of neutron irradiation, showing the median, minimum, and maximum of the populations following irradiation to each level. Neutron fluences and sample sizes (in parentheses) were $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). For reference, the post total dose SMD limits are 25ns to 120ns (T1) and 20ns to 80ns (T2).

Discussion and Conclusion

This document reports the results of neutron testing of the IS-1715ARH complementary power MOSFET driver. Samples were irradiated to levels of $1 \times 10^{12} \text{ n/cm}^2$ (five samples), $1 \times 10^{13} \text{ n/cm}^2$ (five samples), $3 \times 10^{13} \text{ n/cm}^2$ (five samples), and $1 \times 10^{14} \text{ n/cm}^2$ (five samples). It should again be carefully realized when interpreting the data that each neutron irradiation was performed on a different set of samples; this is not total dose testing, where a single set of samples is used and the damage is cumulative. ATE characterization testing was performed before and after the irradiations, and two control units were used to ensure repeatable data. Variables data for key monitored parameters is presented in [Figures 1](#) through [19](#).

The IS-1715ARH is not formally designed, screened, or acceptance tested for neutron hardness. The part is built in a dielectrically-isolated BiCMOS process; the bipolar transistors are minority carrier devices with fairly wide active base regions and may be sensitive to displacement damage (DD) at higher neutron fluences.

The PWR and AUX section LOW and HIGH output voltage at $I_{OUT} = 40.0 \text{ mA}$ and $I_{OUT} = 40.0 \text{ mA}$ ([Figures 7](#) through [10](#)) showed good stability through the $3 \times 10^{13} \text{ n/cm}^2$ level, but was out of specification or nearly so after $1 \times 10^{14} \text{ n/cm}^2$.

The ENABLE and INPUT pin input LOW currents ([Figure 11 on page 7](#)) showed gradual degradation through the $3 \times 10^{13} \text{ n/cm}^2$ level and were out of specification after $1 \times 10^{14} \text{ n/cm}^2$.

The PWR and AUX section output fall times ([Figure 13 on page 8](#)) showed gradual degradation through the $3 \times 10^{13} \text{ n/cm}^2$ level and were out of specification after $1 \times 10^{14} \text{ n/cm}^2$.

The T1 and T2 pin input current limit ([Figure 17 on page 10](#)) was stable through $1 \times 10^{13} \text{ n/cm}^2$, but increased to nearly the SMD limit at $3 \times 10^{13} \text{ n/cm}^2$ and was nonfunctional at $1 \times 10^{14} \text{ n/cm}^2$. The post $1 \times 10^{14} \text{ n/cm}^2$ data is not plotted.

We conclude that the IS-1715ARH is capable of post $3 \times 10^{13} \text{ n/cm}^2$ operation (likely with some relaxation of parametric specifications) within the post total dose SMD parameters. The part is not capable of post $1 \times 10^{14} \text{ n/cm}^2$ operation as it was nonfunctional following irradiation to that level, failing several parameters.

Appendix

Reported Parameters

TABLE 1. REPORTED PARAMETERS

FIGURE	PARAMETER	LOW	HIGH	UNITS	NOTES
1	Nominal Power Supply Current	1	6	mA	
2	Sleep Mode Power Supply Current	300	900	μA	
3	Undervoltage Lockout Threshold, Rising	8.5	9.5	V	
4	Undervoltage Lockout Threshold, Falling	7.7	8.8	V	
5	Undervoltage Lockout Delta	0	2	V	
6	PWR and AUX Output Voltage	-	2	V	Pre-turn-on
7	PWR Stage LOW Output Voltage	-	1/1.5	V	I _{OUT} = 40mA and 100mA
8	PWR Stage HIGH Output Voltage	-	1/1.5	V	I _{OUT} = 40mA and 100mA
9	AUX Stage LOW Output Voltage	-	1/1.5	V	I _{OUT} = 40mA and 100mA
10	AUX Stage HIGH Output Voltage	-	1/1.5	V	I _{OUT} = 40mA and 100mA
11	Enable LOW Current	-15	15	μA	
	Input LOW Current	-20	20	μA	
12	PWR and AUX Rise Time	15	50	ns	
13	PWR and AUX Fall Time	15	50	ns	
14	PWR Propagation Delay	50	300	ns	
	AUX Propagation Delay	50	185	ns	
15	T1 Input Time Delay	45	200	ns	RT1 = 10kΩ
	T1 Input Time Delay	250	1300	ns	RT1 = 100kΩ
16	T2 Input Time Delay	50	130	ns	RT1 = 10kΩ
	T2 Input Time Delay	200	700	ns	RT1 = 100kΩ
17	T1 Input Current Limit	-5.5	-1.6	mA	
	T2 Input Current Limit	-5.5	-2.1	mA	
18	T1 Nominal Pin Voltage	2.7	3.3	V	
	T2 Nominal Pin Voltage	2.7	3.3	V	
19	T1 Input Pin Delay	25	120	ns	
	T2 Input Pin Delay	20	80	ns	

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338