


Evaluation of Subsystem Clock Oscillation Circuit

[R5F21276SN-32P] QFP(7x7) 0.80mm pitch

Measurement conditions : 3.3V





Model	:SP-T2A
Frequency	:Fo=32.768kHz
Frequency tolerance	:dF/Fo= +/-20x10 ⁶
Load capacitance	:CL=6.0pF
Equivalent series resistance	:R1=50k ohm max
Max. drive level	:DL=1x10 ⁶ W max
Level of drive	:DL=0.1x10 ⁶ W typ

FEATURES

1. Plastic mold package incorporated tubular type quartz crystal.
2. Suitable for automatic and high density surface mounting.
3. Excellent shock and heat resistance
4. Real time clocks, Timers, Portable applications, Clock source for Micro-Computers

RECOMMENDED SOLDERING PATTERN



Remark) Ix : current through crystal

Drivability of oscillation can be changed to "High" or "Low" by user program.

MODEL:SP-T2A 6.0pF with R5F21276SN at 3.3V,25°C

Key specifications	Low	High	Remarks
Negative feedback resistance : Rf (M ohm)	Built-in	Built-in	The build-in 10M ohm Rf can be opened by user program.
Capacitance at gate : Cg (pF)	4	6	Optimal capacity in response to CL
Capacitance at drain : Cd (pF)	3	7	(CL = Cd // Cg + stray capacitance)

Circuit characteristics (at 25°C)	Low	High	Remarks
Matching Accuracy : df / f (x10 ⁻⁶)	-0.1	1.2	Frequency offset volume at specified Vdd
Voltage Fluctuation : +/-df / V (x10 ⁻⁶)	0.4	0.6	Vdd +/-10% (Standard operating voltage range)
Drive Level : DL (x10 ⁻⁶ W)	0.03	0.02	DL=Ix ² Re < 1x10 ⁻⁶ W, Re=R1(1 + Co / CL) ²
Negative resistance : - RL (kohm)	864	3344	5 times larger than R _{1MAX}
Oscillation allowance : M (times)	17.3	66.9	Judgemental standard of oscillation stability
Voltage of oscillation start : Vstart (V)	1.42	1.10	
Voltage of oscillation stop : Vstop (V)	1.29	0.90	
Oscillation start up time : Ts (sec)	0.27	0.18	Time to reach 90% of output level

Temperature characteristics of circuit		Low	High	Remarks
at -40°C	Variation : df / T (x10 ⁻⁶)	-140	-139	Typ.Tp=25°C (K = -3.5x10 ⁻⁸ / °C ²)
at +85°C	Variation : df / T (x10 ⁻⁶)	-134	-135	Typ.Tp=25°C (K = -3.5x10 ⁻⁸ / °C ²)

The above mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics. Please review and check above parameters at customer's end.

Seiko Instruments USA Inc.

2990, West Lomita Blvd., Torrance, CA 90505, U.S.A
 Telephone : +1 310-517-7771 Facsimile : +1 310-517-7792
 Email : crystals@siu-la.com

Seiko Instruments GmbH

Siemensstrasse 9, D-63263 Neu-Isenburg, Germany
 Telephone : +49-6102-297-0 Facsimile : +49-6102-297-320
 Email : info@seiko-instruments.de

Seiko Instruments Inc.

1-8, Nakase, Mihama-ku, Chiba-shi, Chiba 261-8507, Japan
 Facsimile : +81-43-211-8030
 E-mail : component@sii.co.jp



We value the "takumi" spirit.







Seiko Instruments Inc.
 Phone: +81-43-211-1207(Direct)

Evaluation of Subsystem Clock Oscillation Circuit

[R5F21276SN-32P] QFP(7x7) 0.80mm pitch

Measurement conditions : 3.3V

Test Data : Temperature characteristics at Vcc=3.3V



Evaluation of Subsystem Clock Oscillation Circuit

[R5F21276SN-32P] QFP(7x7) 0.80mm pitch

Measurement conditions : 3.3V



Referential components layout(see Figure 1)




Figure 1 Referential components layout

Notes for Board Design

When using a crystal resonator, place the resonator and its load capacitors as close as possible to SUB_in and SUB_out pins.

Other signal lines should be routed away from the resonator circuit to prevent induction from interfering with correct oscillation (see figure 2).




Figure 2 Example of Incorrect Board Design

Remark When using the subsystem clock, insert resistors R_d in series on the SUB_out side.

Evaluation of Subsystem Clock Oscillation Circuit

[R5F21276SN-32P] QFP(7x7) 0.80mm pitch

Measurement conditions : 3.3V



[Evaluation Sample : SP-T2A 6.0pF at 25°C]


SAMPLE	No.	CL (pF)	Fo (Hz)	fr (Hz)	R1 (kohm)	Co (pF)	C1 (fF)	Q (k)
SP-T2A 6.0pF	1	6	32768.34	32763.01	31.6	1.00	2.278	67.5
	2	6	32768.29	32762.96	33.0	1.00	2.278	64.6
	3	6	32768.32	32762.73	31.0	1.01	2.393	65.5

[IC Test Data : IC samples Rd=Built_in,Cg=4 to 6pF,Cd=3 to 7pF at Vcc=3.3V,25°C]

Mode	IC samples	Fosc (Hz)	df / f (x10 ⁻⁶)	DL(x10 ⁻⁶ W)	-RL (kohm)	Vstart(V)	Ts(sec)
High	TYP	32768.300	1.22	0.02	3344	1.10	0.18
	HL	32768.550	8.85	0.01	3344	1.42	0.19
	LH	32768.085	-5.34	0.02	3344	1.62	0.18
	LL	32768.220	-1.22	0.01	3344	1.45	0.18
	HH	32768.340	2.44	0.01	3344	1.55	0.20
Low	TYP	32768.257	-0.09	0.03	864	1.42	0.27
	HL	32768.230	-0.92	0.02	864	1.54	0.26
	LH	32768.230	-0.92	0.03	374	1.74	0.32
	LL	32768.310	1.53	0.02	1044	1.72	0.30
	HH	32768.190	-2.14	0.02	474	1.60	0.31

Remark (see figure 3)

$$F_o = f_r \times \left\{ \frac{C_1}{2 \times (C_o + C_L)} + 1 \right\} \text{ (Hz)}$$



F_o : Load resonance frequency
 f_r : Resonance frequency
 R_1 : Motional resistance
 C_1 : Motional capacitance
 C_o : Shunt capacitance
 C_L : Load Capacitance


Figure 3 Equivalent circuit of crystal unit, and CL

Remark (see figure 4)

Approximate formula of the load capacitance of the circuit CL.

$$C_L = \frac{C_g \times C_d}{C_g + C_d} + C_s \text{ (pF)}$$

Where C_s (=2 to 4pF) Stands for stray capacitance of the circuit.



C_{os} : X1_X2 Stray capacitance
 C_{gs} : X1_Vss Stray capacitance
 C_{ds} : X2_Vss Stray capacitance

Figure 4 Stray capacitance Cos,Cgs,Cds of the circuit

Resonator circuit constants will differ depending on the resonator element, stray capacitance in its interconnecting circuit, and other factors. Suitable constants should be determined in consultation with the resonator element manufacturer.