

## Contents

Chapter 1. Introduction .....	2
Chapter 2. Target Devices .....	3
Chapter 3. Operating Environment.....	7
Chapter 4. Changes .....	8
4.1 Details of Changes .....	8
4.1.1 Additional function generation file mode .....	8
4.1.2 Changes of hdwinit() function.....	9
4.1.3 Changes the setting external interrupts .....	10
Chapter 5. Cautions.....	11
5.1 Cautions List.....	11
5.2 Cautions Details .....	12
5.2.1 Cautions of the LIN-bus function of UART0, UART2, UART3 or UART6.....	12
5.2.2 Cautions of extension code, multimaster,wakeup function of serial interface IICA or IIC0 ..	12
5.2.3 Cautions of CAN controllers.....	12
5.2.4 Restrictions of internal low-speed or internal high-speed oscillator trimming .....	12
5.2.5 Cautions of file merge .....	12

## Chapter 1. Introduction

Applilet3 for 78K is a software tool to generate device driver code for on-chip peripherals. It generates device driver codes using user settings through GUI. Initialize code and API functions are provided.

## Chapter 2. Target Devices

Below is a list of devices supported by the Applilet3 for 78K0R/Fx3 V3.01.00.01	
Nickname	Device name
78K0R/FB3	μPD78F1804, μPD78F1805, μPD78F1806, μPD78F1807
78K0R/FC3	μPD78F1808, μPD78F1809, μPD78F1810, μPD78F1811 μPD78F1812, μPD78F1813, μPD78F1814, μPD78F1815, μPD78F1816, μPD78F1817 μPD78F1826, μPD78F1827, μPD78F1828, μPD78F1829, μPD78F1830
78K0R/FE3	μPD78F1818, μPD78F1819, μPD78F1820, μPD78F1821, μPD78F1822 μPD78F1831, μPD78F1832, μPD78F1833, μPD78F1834, μPD78F1835
78K0R/FF3	μPD78F1823, μPD78F1824, μPD78F1825 μPD78F1836, μPD78F1837, μPD78F1838, μPD78F1839, μPD78F1840
78K0R/FG3	μPD78F1841, μPD78F1842, μPD78F1843, μPD78F1844, μPD78F1845
The Applilet3 is based on the following documents.	
Manual Name	Document Number
78K0R/Fx3 User's Manual	U19145JJ1V0UD00
	U19145EJ1V0UD00

Below is a list of devices supported by the Applilet3 for 78K0R/lx3 V3.01.00.01	
Nickname	Device name
78K0R/IB3	μPD78F1201, μPD78F1203
78K0R/IC3	μPD78F1211(38pin), μPD78F1213(38pin), μPD78F1211(44pin), μPD78F1213(44pin)
78K0R/ID3	μPD78F1213(48pin), μPD78F1214(48pin), μPD78F1215(48pin) μPD78F1223, μPD78F1224, μPD78F1225
78K0R/IE3	μPD78F1233, μPD78F1234, μPD78F1235
The Applilet3 is based on the following documents.	
Manual Name	Document Number
78K0R/lx3 User's Manual	U19678JJ1V1UD00
	U19678EJ1V1UD00

Below is a list of devices supported by the Applilet3 for 78K0R/Kx3 V3.01.00.01	
Nickname	Device name
78K0R/KE3	μPD78F1142/A, μPD78F1143/A, μPD78F1144/A, μPD78F1145/A, μPD78F1146/A
78K0R/KF3	μPD78F1152/A, μPD78F1153/A, μPD78F1154/A, μPD78F1155/A, μPD78F1156/A
78K0R/KG3	μPD78F1162/A, μPD78F1163/A, μPD78F1164/A, μPD78F1165/A, μPD78F1166/A, μPD78F1167/A, μPD78F1168/A
78K0R/KH3	μPD78F1174/A, μPD78F1175/A, μPD78F1176/A, μPD78F1177/A, μPD78F1178/A
78K0R/KJ3	μPD78F1184A, μPD78F1185A, μPD78F1186A, μPD78F1187A, μPD78F1188A
The Applilet3 is based on the following documents	
Manual Name	Document Number
78K0R/KE3 User's Manual	U17854JJ8V0UD00
	U17854EJ8V0UD00
78K0R/KF3 User's Manual	U17893JJ7V0UD00
	U17893EJ7V0UD00
78K0R/KG3 User's Manual	U17894JJ8V0UD00
	U17894EJ8V0UD00
78K0R/KH3 User's Manual	U18432JJ4V0UD00
	U18432EJ4V0UD00
78K0R/KJ3 User's Manual	U18417JJ3V0UD00
	U18417EJ3V0UD00

Below is a list of devices supported by the Applilet3 for 78K0R/Kx3-A V3.01.00.01	
Nickname	Device name
78K0R/KE3-A	μPD78F1016, μPD78F1017, μPD78F1018
The Applilet3 is based on the following documents	
Manual Name	Document Number
78K0R/Kx3-A User's Manual	U19653JJ1V0UD
	U19653EJ1V0UD

Below is a list of devices supported by the Applilet3 for 78K0R/Kx3-L V3.01.00.01	
Nickname	Device name
78K0R/KC3-L	μPD78F1000(44pin), μPD78F1001(44pin), μPD78F1002(44pin),μPD78F1003(44pin), μPD78F1001(48pin), μPD78F1002(48pin), μPD78F1003(48pin)
78K0R/KD3-L	μPD78F1004, μPD78F1005, μPD78F1006
78K0R/KE3-L	μPD78F1007, μPD78F1008, μPD78F1009
78K0R/KF3-L	μPD78F1010, μPD78F1011, μPD78F1012
78K0R/KG3-L	μPD78F1013, μPD78F1014
The Applilet3 is based on the following documents	
Manual Name	Document Number
78K0R/Kx3-L User's Manual	U19291JJ3V0UD00
	U19291EJ2V0UD00
78K0R/KF3-L User's Manual	U19459JJ1V0UD00
	U19459EJ1V0UD00
78K0R/KG3-L User's Manual	U19460JJ1V0UD00
	U19460EJ1V0UD00

Below is a list of devices supported by the Applilet3 for 78K0R/Lx3 V3.01.00.01	
Nickname	Device name
78K0R/LF3	μPD78F1500, μPD78F1501, μPD78F1502
78K0R/LG3	μPD78F1503, μPD78F1504, μPD78F1505
78K0R/LH3	μPD78F1506, μPD78F1507, μPD78F1508
The Applilet3 is based on the following documents	
Manual Name	Document Number
78K0R/Lx3 User's Manual	U19155JJ3V0UD
	U19155EJ3V0UD

Below is a list of devices supported by the Applilet3 for 78K0/Ix2 V3.01.00.01	
Nickname	Device name
78K0/IY2	μPD78F0740, μPD78F0741, μPD78F0742, μPD78F0750, μPD78F0751, μPD78F0752
78K0/IA2	μPD78F0743, μPD78F0744, μPD78F0753, μPD78F0754
78K0/IB2	μPD78F0745, μPD78F0746, μPD78F0755, μPD78F0756 32pin are not supporting.
The Applilet3 is based on the following documents.	
Manual Name	Document Number
78K0/Ix2 User's Manual	U19353JJ3V0UD00
	U19353EJ3V0UD00

Below is a list of devices supported by the Applilet3 for 78K0/Kx2-L V3.01.00.02	
Nickname	Device name
78K0/KY2-L	μPD78F0550, μPD78F0551, μPD78F0552, μPD78F0555, μPD78F0556, μPD78F0557
78K0/KA2-L	μPD78F0560, μPD78F0561, μPD78F0562, μPD78F0565, μPD78F0566, μPD78F0567
78K0/KB2-L	μPD78F0571, μPD78F0572, μPD78F0573, μPD78F0576, μPD78F0577, μPD78F0578
78K0/KC2-L	μPD78F0581(44pin), μPD78F0582(44pin), μPD78F0583(44pin), μPD78F0581(48pin), μPD78F0582(48pin), μPD78F0583(48pin), μPD78F0586(44pin), μPD78F0587(44pin), μPD78F0588(44pin), μPD78F0586(48pin), μPD78F0587(48pin), μPD78F0588(48pin)
The Applilet3 is based on the following documents.	
Manual Name	Document Number
78K0/Kx2-L User's Manual	U19111JJ2V1UD
	U19111EJ2V1UD

## Chapter 3. Operating Environment

### ▪ Host machine

- IBM PC/AT compatibles (Windows® 8, Windows® 7, Windows Vista®)
- Processor: 1 GHz or higher (must support hyper-threading, multi-core CPUs)
- Memory capacity: 2 GB or more recommended. Minimum requirement is 1 GB or more (64-bit Windows requires 2 G or more)
- Hard disk capacity: 200 MB or more spare capacity
- Display: 1024 x 768 or higher resolution, 65,536 or more colors
- All other necessary software environments in addition to WindowsOS
- .NET Framework version4.5
- Microsoft Visual C++ 2010 SP1 runtime library

### ▪ Development Environments

Product Name	Version
IAR Embedded Workbench for Renesas RL78	V4.80 or later

## Chapter 4. Changes

This chapter describes change of Applilet3 for 78K V1.02.00

No	Description	Corresponds of Applilet3							
		78K0R/Fx3 V3.01.00.01	78K0R/lx3 V3.01.00.01	78K0R/Kx3 V3.01.00.01	78K0R/Kx3-A V3.01.00.01	78K0R/Kx3-L V3.01.00.01	78K0R/Lx3 V3.01.00.01	78K0/lx2 V3.01.00.01	78K0/Kx2-L V3.01.00.02
1	Additional function generation file mode	-	-	-	-	-	-	-	-
2	Changes of hdwinit() function	-	-	-	-	-	-	-	-
3	Changes the setting external interrupts	/	/	/	/	-	/	/	/

○ : Correspondence, -: Not correspondence(finish of correction), /: Outside of function

### 4.1 Details of Changes

#### 4.1.1 Additional function generation file mode

"Output control of API function" has been added to the Code Generator Property for 78K0R and 78K0.

"Output all API functions according to the setting": Outputs necessary API functions according to the GUI settings (conventional output method).

"Output only initialization API function": Outputs only initialization functions (Create functions) regardless of the GUI settings. Users can configure the settings such as interrupt functions according to their needs.

This issue has been corrected in Applilet3 for 78K V1.02.00

Code Generator Property

**Product Information**

Version: V1.03.03.04

Release date: 8/30/2012

**Generate File Mode**

Output control of API function: **Output only initialization API function**

Generate file: Output all API functions according to the setting

Output folder: Output only initialization API function

Report type: HTML file

Register files: Output files to project

**Pin Configurator Reflect Mode**

Mode: Reflected



#### 4.1.2 Changes of hdwinit() function

We have changed the initial code for the hdwinit() and main() functions.

```
void hdwinit(void)
{
    DI();
    R_Systeminit();
    EI();
}
```

The above code has been changed to the code given below. Accordingly, interrupts are not enabled within the hdwinit function.

```
void hdwinit(void)
{
    DI();
    R_Systeminit();
}
```

Interrupts are now enabled within the main() function.

```

/*****
* Function Name: main
* Description : This function implements main function.
*****/
void main(void)
{
    R_MAIN_UserInit();
    /* Start user code. Do not edit comment generated here */
    while (1U)
    {
        ;
    }
    /* End user code. Do not edit comment generated here */
}
/*****
* Function Name: R_MAIN_UserInit
* Description : This function adds user code before implementing main function.
*****/
void R_MAIN_UserInit(void)
{
    /* Start user code. Do not edit comment generated here */
    EI();
    /* End user code. Do not edit comment generated here */
}
```

When an old project is used in code generation, the definitions of variables within the main function may lead to errors.

```
[Old project]
void main(void)
{
  /* Start user code. Do not edit comment generated here */
  char c;
  while (1U)
  {
    ...
  }
}
```

[When an old project is loaded into CubeSuite+V1.03.00 and used for code generation]

```
void main(void)
{
  R_MAIN_UserInit();
  /* Start user code. Do not edit comment generated here */
  char c;      <- error!!
  while (1U)
  {
    ...
  }
}
```

In that case, use { }.

```
void main(void)
{
  R_MAIN_UserInit();
  /* Start user code. Do not edit comment generated here */
  {      <- add "{"
    char c;      <- not error!
    while (1U)
    {
      ...
    }
  }      <- add "}"
}
```

This issue has been corrected in Applilet3 for 78K V1.01.00.

#### 4.1.3 Changes the setting external interrupts

In the 78K0R/Kx3-L (with 44 or 48 pins), when the external interrupt INTP3 or INTP7 is selected, the code for initialization which changes PIM8 into a digital signal is not present.

This issue has been corrected in Applilet3 for 78K V1.01.00.

## Chapter 5. Cautions

This section describes cautions for using Applilet3 for 78K

### 5.1 Cautions List

No.	Description	Corresponds of code generation							
		78K0R/Fx3 V3.01.00.01	78K0R/Ix3 V3.01.00.01	78K0R/Kx3 V3.01.00.01	78K0R/Kx3-A V3.01.00.01	78K0R/Kx3-L V3.01.00.01	78K0R/Lx3 V3.01.00.01	78K0/Ix2 V3.01.00.01	78K0/Kx2-L V3.01.00.02
1	Cautions of the LIN-bus function of UART0, UART2, UART3 or UART6.	○	○	○	○	○	○	○	○
2	Cautions of extension code, wakeup function and multimaster of serial interface IICA or IIC0	/	○	○	○	○	○	○	○
3	Cautions of CAN controllers	○	/	/	/	/	/	/	/
4	Restrictions of internal low-speed or internal high-speed oscillator trimming	○	/	○	/	/	/	/	/
5	Cautions of file merge	○	○	○	○	○	○	○	○

○ : Correspondence, -: Not correspondence, /:Outside of function.

## 5.2 Cautions Details

### 5.2.1 Cautions of the LIN-bus function of UART0, UART2, UART3 or UART6

The Applilet3 for 78K is not supporting the LIN-bus functions of serial interface UART0 , UART2, UART3 or UART6.

[Workaround] There is no workaround.

### 5.2.2 Cautions of extension code, multimaster, wakeup function of serial interface IICA or IIC0

The Applilet3 for 78K is not supporting the extension code, multimaster, wakeup function of serial interface IIC.

[Workaround] There is no workaround.

### 5.2.3 Cautions of CAN controllers

The Applilet3 for 78K is not supporting the CAN Controllers.

[Workaround] There is no workaround.

### 5.2.4 Restrictions of internal low-speed or internal high-speed oscillator trimming

Applilet3 for 78K is not equivalent to a setup of internal low-speed or internal high-speed oscillator trimming register

### 5.2.5 Cautions of file merge

If you select Merge File in Generate File Mode in the property of Applilet3 and the source codes are written between each comment below, the file will be merged.

/\* Start user code. Do not edit comment generated here \*/

/\* End user code. Do not edit comment generated here \*/

However, if the number of braces ("{" and "}") in the edited source codes (including the comments) are not the same, the edited source codes may disappear when you run the Applilet3.

[Workaround] There is no workaround.

## Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
  2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
  3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
  4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
  5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.  
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.  
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.  
Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.
  6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
  7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
  8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
  9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
  10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
  11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
  12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



### SALES OFFICES

### Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

#### **Renesas Electronics America Inc.**

2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A.  
Tel: +1-408-588-6000, Fax: +1-408-588-6130

#### **Renesas Electronics Canada Limited**

1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada  
Tel: +1-905-898-5441, Fax: +1-905-898-3220

#### **Renesas Electronics Europe Limited**

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.  
Tel: +44-1628-585-100, Fax: +44-1628-585-900

#### **Renesas Electronics Europe GmbH**

Arcadiastrasse 10, 40472 Düsseldorf, Germany  
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

#### **Renesas Electronics (China) Co., Ltd.**

Room 1709, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China  
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

#### **Renesas Electronics (Shanghai) Co., Ltd.**

Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333  
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

#### **Renesas Electronics Hong Kong Limited**

Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong  
Tel: +852-2265-6688, Fax: +852 2886-9022/9044

#### **Renesas Electronics Taiwan Co., Ltd.**

13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan  
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

#### **Renesas Electronics Singapore Pte. Ltd.**

80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949  
Tel: +65-6213-0200, Fax: +65-6213-0300

#### **Renesas Electronics Malaysia Sdn.Bhd.**

Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia  
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

#### **Renesas Electronics Korea Co., Ltd.**

12F., 234 Teheran-ro, Gangnam-Ku, Seoul, 135-920, Korea  
Tel: +82-2-558-3737, Fax: +82-2-558-5141