

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

Be sure to read this Note

M3T-MR30/4 V.4.00 Release 01 Release Note

RENESAS SOLUTIONS CORPORATION

June, 16, 2008

Abstract

Welcome to M3T-MR30/4 V.4.00 Release 01 . This document contains supplementary descriptions to Manual. When you read certain items in the Manual, please read this document as well.

Also, this document contains a License Agreement in the last. Please read it before using. By using the software, you are accepting and agreeing to such term.

Contents

1. Components of the Product	2
2. Versions of Crosstool compatible with M3T-MR30/4 V.4.00 Release 01.....	2
3. What are updated from M3T-MR30/4 V.4.00 Release 01.....	2
4. Installing.....	3
5. Entering user registration.....	3
6. Using electronic manuals	4
7. Technical Support	4
8. How to make M3T-MR30/4 Library	5
9. Use of GUI Configurator	5
10. Cautions	6
10.1. About extern declaration or prototype declaration of service call	6
10.2. About the pointer on using M3T-MR30/4	6
10.3. About build of the sample program	6
10.4. Procedures for Supporting the R8C/Tiny Series	6
10.5. Note on using M16C/64, M16C/65 group MCU.....	8

1. Components of the Product

M3T-MR30/4 is comprises the following. If any of the above is missing, contact either Renesas Technology Corporation's office or its distributor from which you purchased the product.

1. Software (CD-R)

The CD-R contains the software product and electronic manual necessary for program development.

2. M3T-MR30/4 V.4.00 Release 01 Release note

This is the latest version of the M3T-MR30/4.

3. License Agreement(M3T-MR30K/4 only)

Please read it before using. By using the software, you are accepting and agreeing to such term.

4. License ID Certificate

A license ID is required when you install this product in your computer. The License ID Certificate certifies that you are an official user of the product. Please keep this certificate in a safe place because it will be needed when the product is upgraded in the future.

2. Versions of Crosstool compatible with M3T-MR30/4 V.4.00 Release 01

You can use M3T-MR30/4 V.4.00 Release 01 in combination either with M3T-NC30WA V.5.40 Release 00 or later version.

3. What are updated from M3T-MR30/4 V.4.00 Release 01

- The following problems are fixed.
 1. With using mailboxes of property TA_MPRI
(See 2008/06/16 Renesas Tool News)
 2. On calculation of stack size
(See 2008/06/16 Renesas Tool News)
 3. With using a set_flg or iset_flg service call in combination with ichg_pri
(See 2007/08/01 Renesas Tool News)
 4. With using objects of property TA_TPRI
(See 2007/08/01 Renesas Tool News)
 5. With clearing an event flag for which two or more tasks waiting
(See 2007/08/01 Renesas Tool News)
 6. With using the ter_tsk service call
(See 2007/07/01 Renesas Tool News)
 7. On using objects that have a property of TA_TPRI
(See 2006/10/16 Renesas Tool News)
 8. On defining the interrupt handler
(See 2006/08/16 Renesas Tool News)
 9. On modifying the values concerning a fixed-size memory pool
(See 2006/08/16 Renesas Tool News)

4. Installing

Before installing M3T-MR30/4 in your computer, please read the "License Agreement" and "Release Note" included with the product. You need to select the same directory in installing as installing NC30WA .

1. Starting up the installer

- Start up the installer and follow the messages displayed on the screen as you install M3T-MR30/4.
- You need to input a license ID in the middle of installation. Before you start installing M3T-MR30/4, check your license ID.
- The data you input in the middle of installation is necessary to create a file for user registration.
- The installer programs included with the product are listed below.

Supported Host	Supported OS	Product Name	Installer Name
PC	Windows 2000	M3T-MR30K/4	\MR30K\WIN\setup.exe
	Windows XP	M3T-MR30S/4	\MR30_C1\WIN\setup.exe
	Windows Vista	(w/o SOURCE) M3T-MR30S/4	\MR30_B1\WIN\setup.exe

2. Setting environment after installation

After you finished installing M3T-MR30/4, set environment variables next.

The environment variables marked by "Auto" in the tables below do not need to be set because the Windows installer automatically rewrites AUTOEXEC.BAT.

The following examples are the cases where it is installed in c:\Program Files\Renesas\Hew\Tools\Renasas\nc30 wa\v544r00.

Environment Variable	Example of setting
BIN30	Auto(SET BIN30= c:\Program Files\Renesas\Hew\Tools\Renasas\nc30 wa\v544r00\bin)
INC30	Auto(SET INC30= c:\Program Files\Renesas\Hew\Tools\Renasas\nc30 wa\v544r00\inc30)
LIB30	Auto(SET LIB30= c:\Program Files\Renesas\Hew\Tools\Renasas\nc30 wa\v544r00\lib30)
Command path	Auto(c:\Program Files\Renesas\Hew\Tools\Renasas\nc30 wa\v544r00\bin is added)

5. Entering user registration

To be eligible for upgrade information, technical support, and other services, you must be registered as a user with Renesas. Unless you are a registered user, the said services cannot be received.

Please register your name with Renesas within 30 days after purchase.

- Registering your name for the PC version

1. When you've installed MR30/4, the following file is created.

[In case of M3T-MR30K/4]

c:\Program Files\Renesas\Hew\Tools\Renasas\nc30 wa\v544r00\support\mr30k\regist.txt

[In case of M3T-MR30S/4]

c:\Program Files\Renesas\Hew\Tools\Renasas\nc30 wa\v544r00\support\mr30s\regist.txt

c:\Program Files\Renesas\Hew\Tools\Renasas\nc30 wa\v544r00\ is the directory created by default when you installed M3T-MR30/4.

2. Cut all contents of the regist.txt file and paste them into a file, then send it to the electronic mail address given below.

regist_tool@renesas.com

If you are not using an electronic mail, output the contents of the regist.txt file to a printer and send the printout to Renesas by facsimile.

* For information on our policy concerning the protection of personal information, please refer to the Renesas Technology Homepage.

URL: <http://www.renesas.com/fmwk.jsp?cnt=privacy.htm&fp=/privacy/&site=i>

The information we receive via the User Registration Form aids us greatly in our customer support activities. We provide Renesas Technology and related companies, distributors, etc., with essential user information (electronically or on paper) that will further help them provide customer support.

If you do not wish to have your user information provided to other related companies, please contact us to let us know. Note, however, this will limit our ability to provide complete product support.

6. Using electronic manuals

The electronic manuals of this product are offered in PDF(Portable Document Format) files. To see these electronic manuals, use a PDF file display program such as the Adobe Reader.

- Opening electronic manual file

Electronic manuals are installed in the following directory by the installer.

Directory	PDF file	Content
manual	rej10j1249_mr30_4ue.pdf	M3T-MR30/4 User's Manual in English

When you double-click on the PDF file of the electronic manual you want to see, Adobe Reader reads in the data of that manual and bring it up the display. Or after starting up Adobe Reader you can use the menus [File-Open...] to specify the electronic manual.

7. Technical Support

If what occurred in your environment doesn't replicate in our environment, we may ask a favor of you to solve the problem (there can be an instance in which we borrow your equipment). We appreciate your in-advance approval.

8. How to make M3T-MR30/4 Library

The kernel library sources and the C language I/F library sources are included in the product as follows.

Products	C Language Interface Library Source	Kernel Library Source
M3T-MR30K/4	Included(src30\c30mr)	Not included
M3T-MR30S/4 (W/O Source)	Included(src30\c30mr)	Not included
M3T-MR30S/4	Included(src30\c30mr)	Included(src30\mr30)

These libraries can be created by executing the command shown below in the directory with these source files.

make -f makefile.dos

9. Use of GUI Configurator

1. Execution of GUI Configurator

From the Start menu, select [MR30 GUI Configurator] from the [Renesas] -> [M3T-MR30K (or S) V.4.00 Release 01] to start up the configurator.

Also, when “Guiconfig_mr30.exe” in the “bin” directory under the M3T-MR30/4 install directory is executed, the GUI configurator starts up.

2. GUI Configurator Manual

For the GUI configurator, the user’s manual is prepared in the Help format. From the GUI screen of GUI configurator or by selecting [MR30 GUI Configurator HELP] from [Renesas] -> [M3T-MR30K (or S) V.4.00 Release 01], the Help can be referenced.

10. Cautions

10.1. About extern declaration or prototype declaration of service call

Don't describe extern declaration nor prototype declaration if service call is issued from your program.

10.2. About the pointer on using M3T-MR30/4

M3T-MR30/4 treats all pointers as a near pointer in order to make lessen RAM size which the kernel uses.

Be careful of the argument of a service call, and the return value.

10.3. About build of the sample program

When the sample program which is included in the product is built, it is necessary to modify a startup program to call the initialization routine of a standard-input/output function. ((a) should be modified.)

```
-----  
; Copy edata_E(O) section from edata_EI(OI) section  
-----  
BCOPY    data_FEI_top,data_FE_top,data_FE  
BCOPY    data_FOI_top,data_FO_top,data_FO  
  
ldc      #(__Sys_Sp&0FFFFH),    sp  
ldc      #(__Sys_Sp&0FFFFH),    fb  
  
=====  
; Initialize standard I/O  
-----  
      .glb    __init          ;(a)  
      jsr.a  __init          ;(a)  
  
-----  
; Set System IPL  
; and  
; Set Interrupt Vector  
-----  
      mov.b  #0,R0L  
      mov.b  #__SYS_IPL,R0H  
      ldc   R0,FLG                ; set system IPL  
      ldc   #((__INT_VECTOR>>16)&0FFFFH),INTBH  
      ldc   #((__INT_VECTOR&0FFFFH),INTBL__init
```

10.4. Procedures for Supporting the R8C/Tiny Series

10.4.1. Settings of the GUI Configurator and the Configuration Files

(1) In the definition of the system clock, set "timer" to "OTHER".

Example:

```
clock{  
    .....  
    timer = OTHER;  
    .....  
};
```


- (2) In the definitions of the interrupt handlers, define the timer interrupts as those handled by the system-clock interrupt handler, where the name of the system-clock interrupt handler must be "`__SYS_STMR_INH`".

Example:

This is an example of defining the timer RA interrupt in the R8C/Tiny series as the one handled by the system-clock interrupt handler.

```
interrupt_vector[22]{
    entry_address=__SYS_STMR_INH;
    os_int=YES;
};
```

10.4.2. Modifications Made to the Startup Files (crt0mr.a30, start.a30) Modify a portion of initializing the system clock in the startup files so that the user can use the timers in the R8C/Tiny series.

Example:

This is an example of calling the initializing function of the RA timer written in C.

```
; +-----+
; |      System timer interrupt setting          |
; +-----+
;      mov.b    #stmr_mod_val,stmr_mod_reg    ;set timer mode
;      mov.b    #stmr_int_IPL,stmr_int_reg    ;set timer IPL
;      mov.w    #stmr_cnt,stmr_ctr_reg       ;set interval count
;      or.b     #stmr_bit+1,stmr_start       ;system timer start
.glb _timer_ra_init
JSR.W _timer_ra_init
```

For details of the initializing function of the RA timer, see Application Note of the R8C/Tiny series.

10.4.3. Modifications Made to the Section Definition Files (c_sec.inc, asm_sec.inc)

Modify the address locations of the fixed vector table to meet the R8C/Tiny series.

Example :

This is an example of locating sections in the c_sec.inc file. In this example, modifications are made to address locations of the variable vector table according to the modifications made to those of the fixed vector table.

```
;-----
; VECTOR TABLE
;-----
.glb    __INT_VECTOR
.section INTERRUPT_VECTOR    ;Interrupt vector table
.org    0fd00H
__INT_VECTOR:
.section FIX_INTERRUPT_VECTOR ;Fixed Interrupt vector table
.org    0ffdcH
```

10.4.4. Notices

(1) On Disabling the Watchdog Timer

If you don't use the watchdog timer, disable it using the assembly directive command ".ofsreg".

Example:

```
Place the following two lines at the end of the example shown in 10.4.3:  
;WDT disable  
.ofsreg OFFH
```

(2) On the Cycle of the System Clock

The cycle of the system clock set in the configuration file (the value to which "tic_num" has been set in the system definitions) must be the same as the cycle of interrupts generated by the initialization of the system clock by the user.

(3) On Combination with High-performance Embedded Workshop 4

- Creating Projects

In the "New Project-2/6-Select RTOS" dialog box, you must select "All Target" as "Target Type" when creating projects.

- Selecting the "-R8C" Option in the Toolchain

"-R8C" option is not selected automatically at creating projects. You need to specify it as a command option explicitly.

10.5. Note on using M16C/64, M16C/65 group MCU.

10.5.1. About automatic initialization of a timer

Since IO address of a timer differs with the conventional M16C microcomputer between M16C/64 and M16C/65 group microcomputer, automatic initialization of a timer cannot be performed at start-up. Please correct the timer initialization part of a start-up file.

Examples :

```
.IF USE_TIMER  
; +-----+  
; | System timer interrupt setting |  
; +-----+  
mov.b #stmr_mod_val,stmr_mod_reg ;set timer mode  
-> Change into the address of the timer xx mode register which uses  
stmr_mod_reg.  
; mov.b #1H,0AH  
; bset 6,07H  
mov.b #stmr_int_IPL,stmr_int_reg ;set timer IPL  
-> Change into the address of the timer xx interruption control register which  
uses stmr_int_reg.  
; bclr 6,07H  
; mov.b #0,0AH  
mov.w #stmr_cnt,stmr_ctr_reg ;set interval count  
-> Change into the address of the timer xx register which uses stmr_ctr_reg.  
or.b #stmr_bit+1,stmr_start ;system timer start  
-> Change into the address of the count start flag of the timer xx which uses  
stmr_start.
```

10.5.2. About an automatic start of a watch dog timer

M3T-MR30/4 does not participate in operation of a watch dog timer. Therefore, stop processing and start processing of a watch dog timer need to correspond by the user program.