

QE for Segment LCD[RL78, RA] V1.2.0

Release Note

Thank you very much for using the QE for Segment LCD[RL78, RA] V1.2.0, a QE (Quick and Effective Tool Solution) product of Renesas Solution Toolkit - Development Support Tool for Various Applications.

This release note covers product installation, restrictions, and so on. Please read this document before using the product.

Contents

1.	About QE for Segment LCD[RL78, RA]	3
1.1	Summary	3
1.2	Functions	3
1.3	New Features	3
1.3.1	Support RA4L1 Device	3
1.3.2	Add Custom Component feature	3
1.3.3	Add 7 new components	4
1.3.4	Add Component Alignment feature	4
1.3.5	Add Change Segment Name feature	4
1.4	Supported Environment	5
1.5	Supported Emulators	5
1.6	Supported Microcontrollers	5
1.7	Supported Evaluation Board	5
2.	Installation and Uninstallation	6
2.1	Installing This Product	6
2.1.1	Install from the "Renesas software installer" menu of e ² studio	6
2.1.2	Install using QE (zip file) downloaded from the Renesas website	6
2.2	Updating This Product	6
2.3	Uninstalling This Product	6
3.	Notes / Restrictions	7
3.1	Usage Considerations	7
3.1.1	Notes on opening [Segment LCD Workflow (QE)] view	7
3.1.2	Notes on sample code build error	7
3.1.3	Notes on qe_breakpoint_trap calling	8
3.1.4	Notes on Display Scaling Settings	8
3.2	Functional Restrictions	8
4.	Related Videos	9
5.	BSD 3-Clause License	10

6. About the Software Bill of Materials (SBOM)..... 11

Revision History 12

1. About QE for Segment LCD[RL78, RA]

1.1 Summary

QE for Segment LCD[RL78, RA] is an assistance tool for segment LCD solution development which provides full-flow support to configure LCD pin setting, verify pin setting and wiring, design display patterns, generate a sample application program, and do software debug. Using this tool makes the development of the segment LCD solution simple, quick, and efficient.

1.2 Functions

The main functions are listed below:

1. Create LCD components and configure COM and SEG pins for each segment.
2. Verify LCD wiring by blinking the target segment.
3. Prepare design patterns and pattern API to light on/off the patterns.
4. Generate a sample program that displays design patterns in each component one by one.
5. Do software debug by designing stop condition and setting checkpoints.

1.3 New Features

1.3.1 Support RA4L1 Device

This product adds support for the RA4L1 MCU.

With this update, you can select RA4L1 as the target device and perform configuration and adjustment using the supported QE functionalities.

1.3.2 Add Custom Component feature

The "Custom Component" dialog provides a graphical user interface for importing an image and generating a user-defined Segment LCD component.

You can refine image extraction while checking the component preview, assign segments and add the generated component into the "Custom Components" tab.

After a custom component is added, it can be used in the same way as built-in components.




Figure 1-1 Custom Component Dialog

1.3.3 Add 7 new components

Add 7 new components shown below to component list in LCD Setting view.




Figure 1-2 7 new components

1.3.4 Add Component Alignment feature

Add a new Component Alignment feature in the LCD Setting view. You can align components with real-time alignment guides while dragging components.




Figure 1-3 Component Alignment

1.3.5 Add Change Segment Name feature

Add a new Segment Name Editing feature in the LCD Setting view. You can open this view by double-clicking the component on LCD setting view and assign any name to each segments.




Figure 1-4 Change Segment Name Dialog

1.4 Supported Environment

- Windows 11 (64-bit version)
- Renesas e² studio 2026-07
- RA Flexible Software Package (FSP) V6.5.0

1.5 Supported Emulators

- RL78 Family
 - E2 emulator
 - E2 emulator Lite
- RA Family
 - E2 emulator
 - E2 emulator Lite
 - J-Link

1.6 Supported Microcontrollers

- RL78 Family
 - RL78/L23
- RA Family
 - RA4L1

1.7 Supported Evaluation Board

- RL78/L23 fast prototyping board.
- EK-RA4L1.
- Custom board.

2. Installation and Uninstallation

2.1 Installing This Product

Use either of the following procedures to install this product.

2.1.1 Install from the "Renesas software installer" menu of e² studio

1. Start e² studio.
2. Select the "Renesas Views" - "Renesas Software Installer" menu of e² studio to open the "Renesas Software Installer" dialog box.
3. Select the "Renesas QE" and click the "Next >" button
4. Select the "QE for Segment LCD (V1.2.0)" check box and click the "Finish" button.
5. Check that the "Renesas QE for Segment LCD[RL78, RA]" check box is selected in the "Install" dialog box and click the "Next >" button.
6. Check that the "Renesas QE for Segment LCD[RL78, RA]" check box is selected as the target of installation and click the "Next>" button.
7. After confirming the license agreements, if you agree to the license, select the "I accept the terms of the license agreements" radio button, and click the "Finish" button.
8. When the dialog box for selecting a trusted certificate appears, check the displayed certificate, and then click on the "Trust Selected" button to continue installation.
9. Restart the e² studio by following the instructions on the screen.
10. Start this product from the "Renesas Views" - "Renesas QE" menu of e² studio. For details about how to use this product, see the "Help" menu of e² studio.

2.1.2 Install using QE (zip file) downloaded from the Renesas website

1. Extract the downloaded zip file.
2. Start the e² studio.
3. Click on "Help", and then click on the "Install New Software..." menu item to open the "Install" dialog box.
4. Click on the "Add..." button to open the "Add Repository" dialog box.
5. Click on the "Archive..." button, select the installation file (zip file under the QE-SegmentLCD folder) in the opened file selection dialog box, and then click on the "Open" button.
6. Click on the "Add" button in the "Add Repository" dialog box.
7. Expand the "Renesas QE" item shown in the "Install" dialog box, select the "Renesas QE for Segment LCD[RL78, RA]" check box, and then click on the "Next>" button.
*If you check off the "Contact all update sites during install to find required software" checkbox, you can shorten the installation time.
8. Confirm that the installation target is "Renesas QE for Segment LCD[RL78, RA]", and then click on the "Next>" button.
9. After checking the license, select the "I accept the terms of the license agreements" radio button if you agree it, and then click on the "Finish" button.
10. When the dialog box for selecting a trusted certificate appears, check the displayed certificate, and then click on the "Trust Selected" button to continue the installation.
11. Restart the e² studio by following the instructions on the screen.
12. Start this product from the "Renesas Views" - "Renesas QE" menu of the e² studio. For details about how to use this product, see the "Help" menu of e² studio.

2.2 Updating This Product

If you have already used this product, you can update it in the same way as the procedure for installation.

2.3 Uninstalling This Product

Follow the procedure below to uninstall this product.

1. Start the e² studio.
2. Select "Help -> About e² studio" to open the "About e² studio" dialog box.
3. Click the "Installation Details" button to open the "e² studio Installation Details" dialog box.
4. Select "Renesas QE for Segment LCD[RL78, RA]" displayed on the "Installed Software" tabbed page and click on the "Uninstall..." button to open the "Uninstall" dialog box.
5. Check the displayed information and click on the "Finish" button.
6. Restart the e² studio by following the instructions on the screen.

3. Notes / Restrictions

3.1 Usage Considerations

Please pay attention to the following items.

3.1.1 Notes on opening [Segment LCD Workflow (QE)] view

1. The workflow cannot be opened if WebView2 Runtime is not installed on your PC.

[Workaround]

Download and install WebView2 (x64 version) from the Microsoft web page. (FAQ: [3000670](#))

2. An incorrect workflow display may occur when clicking on the workflow view again during the view is refreshing.




Figure 3-1 Incorrect Display in Workflow View

[Workaround]

Reselect the project in the "Select a project" step.

3.1.2 Notes on sample code build error

When using an RL78 device, the sample code will have build error "undeclared function R_BSP_SoftwareDelay" if R_BSP_SoftwareDelay is disabled on BSP.

[Workaround]

Enable the setting "API functions disable(R_BSP_SoftwareDelay)" of BSP on the Components tab of Smart Configurator (Figure 3-2) and build the code again.




Figure 3-2 Enable R_BSP_SoftwareDelay function

3.1.3 Notes on qe_breakpoint_trap calling

Please don't remove the calling of `qe_breakpoint_trap` in `R_SLDCDC_Set_Pattern`, otherwise, [Set checkpoint to the API function generated by QE for Segment LCD] in `Configure Stop Condition Dialog` cannot work normally.




Figure 3-3 Calling of qe_breakpoint_trap

3.1.4 Notes on Display Scaling Settings

Depending on the display scaling setting, the GUI of this product may not be displayed correctly. In such cases, please set Windows display scaling to "100%".

3.2 Functional Restrictions

There is no restriction in QE for Segment LCD[RL78, RA] V1.2.0.

4. Related Videos

The videos about this product are published on the Renesas website.

- Getting Started with QE for Segment LCD
 - <https://www.renesas.com/en/video/getting-started-qe-segment-lcd>

5. BSD 3-Clause License

The license for source code output by this product has been changed from the Renesas Default Disclaimer to the BSD-3-Clause license.

BSD 3-Clause License

Copyright 2025, Renesas Electronics Corporation and/or its affiliates

Redistribution and use in source and binary forms, with or without modification, are permitted provided that the following conditions are met:

Redistributions of source code must retain the above copyright notice, this list of conditions and the following disclaimer.

Redistributions in binary form must reproduce the above copyright notice, this list of conditions and the following disclaimer in the documentation and/or other materials provided with the distribution.

Neither the name of the copyright holder nor the names of its contributors may be used to endorse or promote products derived from this software without specific prior written permission.

THIS SOFTWARE IS PROVIDED BY THE COPYRIGHT HOLDERS AND CONTRIBUTORS "AS IS" AND ANY EXPRESS OR IMPLIED WARRANTIES, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE DISCLAIMED. IN NO EVENT SHALL THE COPYRIGHT HOLDER OR CONTRIBUTORS BE LIABLE FOR ANY DIRECT, INDIRECT, INCIDENTAL, SPECIAL, EXEMPLARY, OR CONSEQUENTIAL DAMAGES (INCLUDING, BUT NOT LIMITED TO, PROCUREMENT OF SUBSTITUTE GOODS OR SERVICES; LOSS OF USE, DATA, OR PROFITS; OR BUSINESS INTERRUPTION) HOWEVER CAUSED AND ON ANY THEORY OF LIABILITY, WHETHER IN CONTRACT, STRICT LIABILITY, OR TORT (INCLUDING NEGLIGENCE OR OTHERWISE) ARISING IN ANY WAY OUT OF THE USE OF THIS SOFTWARE, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

6. About the Software Bill of Materials (SBOM)

For this release, a Software Bill of Materials (SBOM) is provided to describe the software components and OSS license information included in this product.

The SBOM is created in SPDX Lite format and is included in the zip archive distributed together with this release note.

Revision History

Rev.	Date	Description	
		Page	Summary
1.00	Jul.31.2026	-	First edition issued.

General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Precaution against Electrostatic Discharge (ESD)

A strong electrical field, when exposed to a CMOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop the generation of static electricity as much as possible, and quickly dissipate it when it occurs. Environmental control must be adequate. When it is dry, a humidifier should be used. This is recommended to avoid using insulators that can easily build up static electricity.

Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors must be grounded. The operator must also be grounded using a wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions must be taken for printed circuit boards with mounted semiconductor devices.

2. Processing at power-on

The state of the product is undefined at the time when power is supplied. The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the time when power is supplied. In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the time when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the time when power is supplied until the power reaches the level at which resetting is specified.

3. Input of signal during power-off state

Do not input signals or an I/O pull-up power supply while the device is powered off. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Follow the guideline for input signal during power-off state as described in your product documentation.

4. Handling of unused pins

Handle unused pins in accordance with the directions given under handling of unused pins in the manual. The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of the LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible.

5. Clock signals

After applying a reset, only release the reset line after the operating clock signal becomes stable. When switching the clock signal during program execution, wait until the target clock signal is stabilized. When the clock signal is generated with an external resonator or from an external oscillator during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Additionally, when switching to a clock signal produced with an external resonator or by an external oscillator while program execution is in progress, wait until the target clock signal is stable.

6. Voltage application waveform at input pin

Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between V_{IL} (Max.) and V_{IH} (Min.) due to noise, for example, the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between V_{IL} (Max.) and V_{IH} (Min.).

7. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited. The reserved addresses are provided for possible future expansion of functions. Do not access these addresses as the correct operation of the LSI is not guaranteed.

8. Differences between products

Before changing from one product to another, for example to a product with a different part number, confirm that the change will not lead to problems. The characteristics of a microprocessing unit or microcontroller unit products in the same group but having a different part number might differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 October 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/.