

RENESAS TECHNICAL UPDATE

1753, Shimonumabe, Nakahara-ku, Kawasaki-shi, Kanagawa 211-8668 Japan
 Renesas Electronics Corporation

Product Category	MPU/MCU		Document No.	TN-RX*-A062A/E	Rev.	1.00
Title	Changes to RX63T Group Specifications of VCC rising gradient		Information Category	Technical Notification		
Applicable Product	RX63T Group	Lot No.	Reference Document	RX63T Group User's Manual: Hardware Rev.2.00 (R01UH0238EJ0200)		
		All lots				

This document describes changes to specifications of VCC rising gradient in RX63T Group User's Manual: Hardware Rev.2.00.

Pages 1709 of 1799

Specifications Table 41.4 DC Characteristics (3) are changed as follows:

Before change

Item	Symbol	min	typ	max	Unit	Test Conditions
VCC rising gradient ⁷	SV _{CC}	—	—	20	ms/V	

Note 7. This is conditional on the low level being on the RES# pin when power is supplied.

After change

Item	Symbol	min	typ	max	Unit	Test Conditions
VCC rising gradient	SV _{CC}	—	—	20	ms/V	