

## ISL71090SEH25

### Neutron Test Report

TR037  
Rev.0.00  
Aug 31, 2017

## Introduction

This report summarizes results of 1MeV equivalent neutron testing of the [ISL71090SEH25](#) precision voltage reference. The test was conducted in order to characterize the sensitivity of the part to Displacement Damage (DD) caused by neutron or proton environments. Neutron irradiation fluences ranged from  $2 \times 10^{12} \text{ n/cm}^2$  to  $1 \times 10^{14} \text{ n/cm}^2$ . This project was carried out in collaboration with Boeing Satellite Systems (El Segundo, CA), whose support is gratefully acknowledged.

## Related Literature

- For a full list of related documents please visit our website - [ISL71090SEH25](#), [ISL71090SEH Family](#) product pages

## Part Description

The ISL71090SEH25 is a low noise 2.5V precision voltage reference with a wide supply voltage range from 4.0V to 30V, with four output voltage options selected through on-chip trimming. The ISL71090SEH25 is built on the Intersil PR40 bonded-wafer process, which uses dielectric isolation for important electrical and SEE performance improvements. The part achieves sub 2 $\mu\text{V}$  peak-to-peak 0.1Hz noise and a 10ppm/ $^{\circ}\text{C}$  temperature coefficient with an initial voltage accuracy of 0.05%. The base ISL71090SEH offers four output voltage options including 1.25V, 2.5V, 5.0V, and 7.5V. It also features a 10ppm/ $^{\circ}\text{C}$  temperature coefficient and excellent line and load regulation. The device is offered in an 8 Ld hermetic flatpack, with the pin assignment shown in [Table 1](#) for reference. Applications include instrumentation, data acquisition systems, and strain and pressure sensing for space applications. Detailed features and specifications for all four variants may be found in the applicable Intersil datasheets.

TABLE 1. ISL71090SEH25 PIN ASSIGNMENTS

TERMINAL #	TERMINAL SYMBOL
1	DNC, <a href="#">Note 1</a>
2	VIN
3	COMP
4	GND
5	TRIM
6	VOUT
7	DNC, <a href="#">Note 1</a>
8	DNC, <a href="#">Note 1</a>

NOTE:

- DNC indicates a device pin that is not available for any external connections.

The ISL71090SEH25 is specified for a total dose (TID) tolerance of 100krad(Si) at high (50-300rad(Si)/s) dose rate and at 50krad(Si) at low (<0.01rad(Si)/s) dose rate, as specified in MIL-STD-883 test method 1019. The part is acceptance tested on a wafer-by-wafer basis at low dose rate to 50krad(Si) and at high dose rate to 100krad(Si). The ISL71090SEH25 is also SEE tolerant to a Linear Energy Transfer (LET) value of 86.4MeV  $\cdot$  cm<sup>2</sup>/mg and features latchup-free performance.

## Test Description

### Irradiation Facilities

Neutron irradiation was performed at the White Sands Missile Range fast burst reactor. Parts were tested in an unbiased configuration with all leads shorted together in accordance with TM 1017 of MIL-STD-883. As neutron irradiation activates many of the heavier elements found in a packaged integrated circuit, the parts exposed at the higher neutron levels required 'cooldown' time before being shipped back to Intersil (Palm Bay, FL) for electrical testing.

### Test Fixturing

No formal irradiation test fixturing was involved, as these DD tests (informally referred to as 'bag tests') irradiate the parts in an electrically inactive state with all leads shorted together.

### Characterization Equipment and Procedures

Electrical testing was performed before and after irradiation using Intersil production Automated Test Equipment (ATE). All electrical testing was performed at room temperature.

### Experimental Matrix

Testing proceeded in accordance with the guidelines of MIL-STD-883 TM 1017. The experimental matrix consisted of five samples irradiated at  $2 \times 10^{12} \text{ n/cm}^2$ , five irradiated at  $1 \times 10^{13} \text{ n/cm}^2$ , five irradiated at  $3 \times 10^{13} \text{ n/cm}^2$ , and five irradiated at  $1 \times 10^{14} \text{ n/cm}^2$ . Five control units were used. The ISL71090SEHF25/PROTO samples were drawn from fabrication lot X3C6PAB. Samples were packaged in the standard hermetic 8 Ld ceramic flatpack production package, code K8.A. Samples were screened to the SMD limits over temperature before the start of neutron testing. The neutron data discussed in this report applies to all four of the ISL71090SEH variants.

## Results

Neutron testing of the ISL71090SEH25 is complete and the results are reported in the balance of this report. It should be carefully realized when interpreting the data that each neutron irradiation was performed on a different five-unit sample; this is *not* total dose testing, where the damage is cumulative over a number of downpoints.

## Attributes Data

TABLE 2. ISL71090SEH25 ATTRIBUTES DATA.

PART #	SERIAL	SAMPLE SIZE	FLUENCE, (n/cm <sup>2</sup> )	PASS (Note 2)	FAIL	NOTES
ISL71090SEH25	1-5	5	2x10 <sup>12</sup>	5	0	All passed
ISL71090SEH25	6-10	5	1x10 <sup>13</sup>	0	5	All failed, parametric
ISL71090SEH25	11-15	5	3x10 <sup>13</sup>	0	5	All failed, parametric
ISL71090SEH25	16-20	5	1x10 <sup>14</sup>	0	5	All failed, nonfunctional

NOTE:

- 'Pass' is defined as a sample that passes all SMD limits.

## Variables Data

The plots in [Figures 1](#) through [5](#) show data plots for key parameters before and after irradiation to each level. The reported parameters and their datasheet limits are shown in ["Appendices" on page 5](#). The plots show the population median of each parameter as a function of neutron irradiation, as well as the population minimum and maximum. We chose to plot the median because of the small sample sizes (five per cell) involved. We also show the applicable electrical limits taken from the SMD; it should be carefully noted that these limits are provided for *guidance only* as the ISL71090SEH25 is not specified or guaranteed for the neutron environment. Intersil does not design, qualify or guarantee its parts for the DD environment, but has performed some limited neutron testing for customer guidance.

## Variables Data Plots




FIGURE 1. ISL71090SEH25 output voltage as a function of 1MeV equivalent neutron irradiation at 2x10<sup>12</sup>n/cm<sup>2</sup>, 1x10<sup>13</sup>n/cm<sup>2</sup>, 3x10<sup>13</sup>n/cm<sup>2</sup>, and 1x10<sup>14</sup>n/cm<sup>2</sup>. The plot shows the median, minimum, and maximum at each level. Sample size for each cell was five. The SMD post-irradiation specification limits are 2.495625V to 2.504375V.

Variables Data Plots (Continued)




FIGURE 2. ISL71090SEH25 load regulation, sourcing, 0mA to 20mA, as a function of 1MeV equivalent neutron irradiation at  $2 \times 10^{12} \text{ n/cm}^2$ ,  $1 \times 10^{13} \text{ n/cm}^2$ ,  $3 \times 10^{13} \text{ n/cm}^2$ , and  $1 \times 10^{14} \text{ n/cm}^2$ . The plot shows the median, minimum, and maximum at each level. Sample size for each cell was five. The SMD post-irradiation specification limit is 35ppm/mA maximum.






FIGURE 3. ISL71090SEH25 line regulation as a function of 1MeV equivalent neutron irradiation at  $2 \times 10^{12} \text{ n/cm}^2$ ,  $1 \times 10^{13} \text{ n/cm}^2$ ,  $3 \times 10^{13} \text{ n/cm}^2$ , and  $1 \times 10^{14} \text{ n/cm}^2$ . The plot shows the median, minimum, and maximum at each level. Sample size for each cell was five. The SMD post-irradiation specification limit is 18ppm/V maximum.

**Variables Data Plots (Continued)**



**FIGURE 4.** ISL71090SEH25 supply current as a function of 1MeV equivalent neutron irradiation at  $2 \times 10^{12} \text{ n/cm}^2$ ,  $1 \times 10^{13} \text{ n/cm}^2$ ,  $3 \times 10^{13} \text{ n/cm}^2$ , and  $1 \times 10^{14} \text{ n/cm}^2$ . The plot shows the median, minimum, and maximum at each level. Sample size for each cell was five. The SMD post-irradiation specification limit is 1.28mA maximum.



**FIGURE 5.** ISL71090SEH25 dropout voltage as a function of 1MeV equivalent neutron irradiation at  $2 \times 10^{12} \text{ n/cm}^2$ ,  $1 \times 10^{13} \text{ n/cm}^2$ ,  $3 \times 10^{13} \text{ n/cm}^2$ , and  $1 \times 10^{14} \text{ n/cm}^2$ . The plot shows the median, minimum, and maximum at each level. Sample size for each cell was five. The SMD post-irradiation specification limit is 1700mV maximum.

## Conclusion

This report summarizes results of 1MeV equivalent neutron testing of the ISL71090SEH25 2.5V voltage reference. The test was conducted in order to determine the sensitivity of the part to Displacement Damage (DD) caused by neutron or proton environments in space. Neutron fluences ranged from  $2 \times 10^{12} \text{ n/cm}^2$  to  $1 \times 10^{14} \text{ n/cm}^2$ . This project was carried out in collaboration with Boeing Satellite Systems (El Segundo, CA), and their support is gratefully acknowledged.

The samples met all specifications (Bin 1) after  $2 \times 10^{12} \text{ n/cm}^2$ , but failed parametrically at the  $1 \times 10^{13} \text{ n/cm}^2$  and  $3 \times 10^{13} \text{ n/cm}^2$  levels. The samples were nonfunctional after  $1 \times 10^{14} \text{ n/cm}^2$ .

## Appendices

### Reported Parameters

These limits are post-total dose parametric limits from the SMD and are provided for guidance only as the part is not designed or guaranteed for the neutron environment.

TABLE 3. REPORTED PARAMETERS

FIG.	PARAMETER	LIMIT LOW	LIMIT HIGH	UNIT
<a href="#">1</a>	Output voltage	2.495625	2.504375	V
<a href="#">2</a>	Load regulation, sourcing	-	35.0	ppm/mA
<a href="#">3</a>	Line regulation	-	18.0	ppm/V
<a href="#">4</a>	Power supply current	-	1.28	mA
<a href="#">5</a>	Dropout voltage	-	1700	mV

## Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.  
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.  
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.  
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.  
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.  
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



### SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

**Renesas Electronics America Inc.**  
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.  
Tel: +1-408-432-8888, Fax: +1-408-434-5351

**Renesas Electronics Canada Limited**  
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3  
Tel: +1-905-237-2004

**Renesas Electronics Europe Limited**  
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.  
Tel: +44-1628-651-700, Fax: +44-1628-651-804

**Renesas Electronics Europe GmbH**  
Arcadiastrasse 10, 40472 Düsseldorf, Germany  
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

**Renesas Electronics (China) Co., Ltd.**  
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China  
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

**Renesas Electronics (Shanghai) Co., Ltd.**  
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China  
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

**Renesas Electronics Hong Kong Limited**  
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong  
Tel: +852-2265-6688, Fax: +852-2886-9022

**Renesas Electronics Taiwan Co., Ltd.**  
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan  
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

**Renesas Electronics Singapore Pte. Ltd.**  
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949  
Tel: +65-6213-0200, Fax: +65-6213-0300

**Renesas Electronics Malaysia Sdn.Bhd.**  
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia  
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

**Renesas Electronics India Pvt. Ltd.**  
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India  
Tel: +91-80-67208700, Fax: +91-80-67208777

**Renesas Electronics Korea Co., Ltd.**  
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea  
Tel: +82-2-558-3737, Fax: +82-2-558-5338