

Getting started with the RX72N Envision Kit

This tutorial provides instructions for getting started with the Renesas Envision Kit for RX72N. If you do not have the Renesas REK for RX72N, visit the AWS Partner Device Catalog, and purchase one from our partners.

Before you begin, you must configure AWS IoT and your FreeRTOS download to connect your device to the AWS Cloud. See <u>First steps</u> for instructions.

Note

RX72N Envision Kit currently does not support "Quick Connect" workflow. Please return to this "Getting started guide" after completing the instructions in "Step 1: Setting up your AWS account and permissions" and "Step 2: Registering your MCU board with AWS IoT".

In this tutorial, the path to the FreeRTOS download directory is referred to as *freertos*.

Overview

This tutorial contains instructions for the following getting started steps:

- 1. Connecting your board to a host machine.
- 2. Confirm REK for RX72N performance by confirming factory image behavior.
- 3. Installing software on the host machine for developing and debugging embedded applications for your microcontroller board.
- 4. Cross compiling a FreeRTOS demo application to a binary image.
- 5. Loading the application binary image to your board, and then running the application.

Set up the Renesas hardware

To confirm functionality of the REK for RX72N

1. Connect ECN1 (USB Micro-B) on the REK for RX72N to power source USB port (PC,etc).



2. Confirm SPORT GAMES starting on display.



3. User can select 4 types of Games with sliding on title display, and user can start by pushing [PLAY] button.

To set up the REK for RX72N and (onboard) E2 Lite Debugger

- 1. REK for RX72N is equipped with an onboard E2 Lite emulator, emulator usage is controlled by switch SW1.
- 2. SW1-2 is turned ON by default, user needs to turn SW1-2 OFF to enable emulator use.
- 3. Connect ECN1 (USB Micro-B) on the REK for RX72N to power source USB port (PC,etc), LED1 illuminates when power is supplied to the board.
- 4. Connect your computer to the USB-to-serial port (CN8) on the REK for RX72N, the green 'ACT' LED flashes when E2 Lite debugger is connected.
- 5. After the debugger on REK for RX72N is connected to your host machine, E2 Lite debugger drivers begin installing.

Note that Windows 7, 8, and 10 administrator privileges are required to install the drivers.

6. Connect a router or internet-connected Ethernet port to the Ethernet port (CN10) on the REK for RX72N.



Set up your development environment

To set up FreeRTOS configurations for the REK for RX72N, use the Renesas e^2 studio IDE and CC-RX compiler.

Note

The Renesas e²studio IDE and CC-RX compiler are only supported on Windows 7, 8, and 10 operating systems.

To download and install e²studio

- 1. Go to the <u>Renesas e²studio installer</u> download page, and download the offline installer.
- 2. You are directed to a Renesas Login page.

If you have an account with Renesas, enter your username and password and then choose **Login**.

If you do not have an account, choose **Register now**, and follow the first registration steps. You should receive an email with a link to activate your Renesas account. Follow this link to complete your registration with Renesas, and then login to Renesas.

- 3. After you log in, download the e²studio installer to your computer.
- 4. Open the installer and follow the steps to completion.

For more information, see the <u>e²studio</u> on the Renesas website.

To download and install the RX Family C/C++ Compiler Package

- 1. Go to the <u>RX Family C/C++ Compiler Package</u> download page, and download the v3.02.00 package.
- 2. Open the executable and install the compiler.

For more information, see the <u>C/C++ Compiler Package for RX Family</u> on the Renesas website.

Note

The compiler is available free for evaluation version only and valid for 60 days. On the 61st day, you need to get a License Key. For more information, see <u>Evaluation Software Tools</u>.

Build and run FreeRTOS samples

Now that you have configured the demo project, you are ready to build and run the project on your board.

Build the FreeRTOS Demo in e²studio

To download and build the demo in e²studio

- 1. Launch e²studio from the Start menu.
- 2. On the **Select a directory as a workspace** window, browse to the folder that you want to work in, and choose **Launch**.
- 3. The first time you open e2studio, the **Toolchain Registry** window opens. Choose **Renesas Toolchains**, and confirm that CC-RX v3.02.00 is selected. Choose **Register**, and then choose **OK**.
- 4. If you are opening e²studio for the first time, the **Code Generator Registration** window appears. Choose **OK**.
- 5. The Code Generator COM component register window appears. Under Please restart e²studio to use Code Generator, choose OK.
- 6. The **Restart e²studio** window appears. Choose **OK**.
- 7. e²studio restarts. On the **Select a directory as a workspace** window, choose **Launch**.
- 8. On the e²studio welcome screen, choose the Go to the e²studio workbench arrow icon.
- 9. Right-click the Project Explorer window, and choose Import.
- 10. In the import wizard, choose General, Renesas GitHub FreeRTOS (with IoT libraries) Project, and the choose Next.
- 11. Choose Browse to specify a folder to copy downloaded RTOS content in order to import project.
- 12. In RTOS version setting, choose **Check for more version...** to see a list of all supported RTOS version. On the **FreeRTOS (with IoT libraries) Module Download** window, select the FreeRTOS version (recommended: 202002.00-rx-1.0.2) you want to work on by clicking the checkbox, then choose **Download**.

2				_		×
	RTOS (with IoT libraries) Module ect RTOS modules for download	e Download				ก
	Title FreeRTOS (with IoT libraries) FreeRTOS (with IoT libraries) FreeRTOS (with IoT libraries) FreeRTOS (with IoT libraries) FreeRTOS (with IoT libraries)	Rev. 202002.00-rx-1.0.2 202002.00-r178-1.0.1 v202002.00-rx-1.0.1 202002.00-r178-1.0.0 v202002.00-rx-1.0.0	Issue date 2020-10-14 2020-09-30 2020-08-06 2020-08-05 2020-07-29		Select	
Mo	dule Folder Path: D:\RTOS_loT		Download		Browse Cancel	

- 13. Once download is completed, choose **Next** in the **Renesas GitHub FreeRTOS (with IoT libraries) Project** window.
- 14. If you are *not* using an empty folder, the **Copy Resources** warning message appears. Choose **Yes**.
- 15. Choose the project aws_demos (\${FOLDER_DIR}/projects/renesas/rx72n-envision-kit/e2studio/aws_demos), then choose **Finish**.
- 16. From **Project** menu, choose **Build All**.

To import and build the demo in e²studio

- 17. Launch e²studio from the Start menu.
- 18. On the **Select a directory as a workspace** window, browse to the folder that you want to work in, and choose **Launch**.
- 19. The first time you open e2studio, the **Toolchain Registry** window opens. Choose **Renesas Toolchains**, and confirm that CC-RX v3.02.00 is selected. Choose **Register**, and then choose **OK**.
- 20. If you are opening e²studio for the first time, the **Code Generator Registration** window appears. Choose **OK**.
- 21. The Code Generator COM component register window appears. Under Please restart e²studio to use Code Generator, choose OK.
- 22. The Restart e²studio window appears. Choose OK.
- 23. e²studio restarts. On the **Select a directory as a workspace** window, choose **Launch**.
- 24. On the e²studio welcome screen, choose the **Go to the e²studio workbench** arrow icon.
- 25. Right-click the **Project Explorer** window, and choose Import.
- 26. In the import wizard, choose General, Existing Projects into Workspace, and the choose Next.
- 27. Choose **Browse**, locate the directory projects/renesas/rx72n-envision-kit/e2studio/aws_demos, and the choose **Finish**.
- 28. From Project menu, choose Build All.

The build console issues a warning message that the License Manager is not installed. You can ignore this message unless you have a license key for the CC-RX compiler. To install the License Manger, see the License Manager download page.

Run the FreeRTOS project

To run the project in e²studio

- 1. Confirm that you have connected your computer to the USB-to-serial port (CN8) on your REK for RX72N.
- 2. From the top menu, choose Run, Debug Configurations....
- 3. Expand Renesas GDB Hardware Debugging, and choose aws_demos HardwareDebug.
- 4. Choose the **Debugger** tab, and then choose the **Connection Settings** tab. Confirm that your connection settings are correct.
- 5. Choose **Debug** to download the code to your board and begin debugging.

You might be prompted by a firewall warning for **e2-server-gdb.exe**. Check **Private networks, such as my home or work network**, and then choose **Allow access**.

6. e²studio might ask to change to **Renesas Debug Perspective**. Choose **Yes**.

The flashing green 'ACT' LED on the REK for RX72N illuminates.

7. After the code is downloaded to the board, choose **Resume** to run the code up to the first line of the main function. Choose **Resume** again to run the rest of the code.

Monitoring MQTT messages on the cloud

You can use the MQTT client in the AWS IoT console to monitor the messages that your device sends to the AWS Cloud.

To subscribe to the MQTT topic with the AWS IoT MQTT client

- 1. Sign in to the <u>AWS IoT console</u>...
- 2. In the navigation pane, choose **Test** to open the MQTT client.
- 3. In Subscription topic, enter iotdemo/#, and then choose Subscribe to topic.
- 4. Successful demo run looks like following the picture

Subscriptions	iotdemo/#	Export Clear Pause
Subscriptions Subscribe to a topic Publish to a topic iotdemo/# X	Intermed/# Publish Specify a topic and a message to publish with a QoS of 0. Intermed/# 1	Export Clear Pause Publish to topic Export Hide
	iotdemo/acknowledgements October 14, 2020, 20:03:12 (UTC+0900) C11ent has received PUBLISH 19 from server. iotdemo/acknowledgements October 14, 2020, 20:03:12 (UTC+0900) C11ent has received PUBLISH 16 from server. iotdemo/topic/4 October 14, 2020, 20:03:12 (UTC+0900) Hello world 19!	Export Hide Export Hide Export Hide

For the latest projects released by Renesas, see the renesas fork of the amazon-freertos repository on <u>GitHub</u>.

We are supporting FreeRTOS project creation feature on e2 studio, please download the latest version to create RX72N Envision Kit project with FreeRTOS by one-click.

Troubleshooting

Checking serial port output

Serial connection is established upon driver installation which is executed automatically when you connect your computer to the USB-to-serial port (CN8) on your REK for RX72N.

After driver installation is completed, a new COM port will appear in the Windows Device Manager window:



For debugging purposes, you can start a session to the port with any terminal utility tool (e.g: TeraTerm).

Note

If new COM port is not displayed after connecting computer to the USB-to-serial port, please reestablish the connection (disconnect and reconnect microUSB cable).

Debugging FreeRTOS projects in e²studio

To use the debugging feature in e²studio

- 1. Confirm that you have connected your computer to the USB-to-serial port (CN8) on your REK for RX72N.
- 2. Launch e²studio.
- 3. Follow the steps to build and run the FreeRTOS demo project in <u>Build and run the FreeRTOS</u> <u>demo project</u>.
- 4. When e²studio ask to change to **Renesas Debug Perspective**. Choose **Yes**.
- 5. After the code is downloaded to the board, choose **Resume** to run the code up to the first line of the main function.
- 6. In the **Renesas Debug Perspective**, you can set breakpoints in the source code of your project. It should look something as follows:



To configure debug settings in e²studio

If you encounter problems while debugging a FreeRTOS project, please check that your debug settings are set correctly in e²studio.

- 1. Launch e²studio.
- 2. Follow the steps to build the FreeRTOS demo project in <u>Build and run the FreeRTOS demo</u> project.
- 3. From the top menu, choose Run, Debug Configurations....
- 4. Expand Renesas GDB Hardware Debugging, and choose aws_demos HardwareDebug.
- 5. Choose the **Debugger** tab, and then choose the **Connection Settings** tab. Confirm that your connection settings are correct:
 - Debug hardware: E2 Lite (RX)
 - Target Device: R5F572NN
 - Main Clock Source: EXTAL
 - Extal Frequency:16.0000
 - Power Target From The Emulator (MAX 200mA): No

	os HardwareDebug	-		
	bugger 🕞 Startup 🦃 Source 🔲 re: E2 Lite (RX) 🛛 Target Devi	ce: R5F572NN		
GDB Settings	Connection Settings Debug Tool Sett	ings		
✓ Clock				^
Main Cl	ock Source	EXTAL		~
Extal Fre	quency[MHz]	16.0000		
Operatir	ng Frequency [MHz]	240.000		
Permit (Clock Source Change On Writing Interna	Yes		~
✓ Connection	n with Target Board			
Emulato	or	(Auto)		
Connec	tion Type	Fine		~
JTag Clo	ock Frequency[MHz]	6.00		\sim
Fine Bau	ud RatelMbps1	1.50		\checkmark
			Revert	Apply
			Debug	Close

6. After confirming, choose **Debug** to download the code to your board and begin debugging.

Troubleshooting FreeRTOS projects in e²studio

If you do not see the expected messages in AWS IoT console, please refer to e²studio build console log. It will provide further information regarding the cause of the problem.

To enable build console in e²studio

- 1. The e²studio console should be enabled by default.
- 2. If it is not displayed after you launch e²studio, you may need to enable it manually.
- 3. From the top menu, choose **Window >> Show view >> Console**.
- 4. To show the relevant build console for troubleshooting, choose CDT Build Console. You can do this by clicking the and choose C/C++ Build Console. It should look something as follows:

🖹 Problems 📮 Console 🛚 🍬 Smart Browser 🔋 Memory Usage 🔗 Search 🌲 Call Hierarchy 🖆 Include Browser 🔋 Memory 🎄 Debug	🕂 🕆 🛐 🗊 🖬 = 🚉 📑 🛡 🕶 🗖 🕶 🗖
CDT Build Console Jaws demos) TREND September 2015 Section 2015 Secti	^
make -j8 all 'Build complete.'	
18:34:06 Build Finished. 0 errors, 0 warnings. (took 768ms)	
	>

The following suggestions might help fix some common build errors you might encounter:

- 1. Make sure your aws_demos pathname does not exceed ~260 characters, this can cause build errors.
- 2. Make sure full pathname is used for pre-include file (-preinclude) implicitlyinclude.h, incomplete/partial pathname can cause build errors with CC-RX v3.02.00
- 3. If the build message is below

```
Console Tasks Problems Smart Browser Debugger Console Renesas Debug Virtual Console

CDT Build Console [aws_demos]

Extracting support files...

[ERROR] No toolchain set or toolchain not integrated.

11:14:32 **** Incremental Build of configuration HardwareDebug for project aws_demos ****

make -j4 all

'Build complete.'
```

11:14:33 Build Finished. 0 errors, 0 warnings. (took 826ms)

Make sure that the latest version of toolchain (CC-RX v3.02.00) is already installed on local PC. Then right click on aws_demos \rightarrow Properties \rightarrow C/C++ build \rightarrow Settings \rightarrow Toolchain tab and set parameters as following picture

type filter text	Settings	<> ▼ ⇒ ▼ 8
 > Resource Builders > C/C++ Build Build Variables Environment 	Configuration: HardwareDebug [Active] ~	Manage Configurations
Logging Settings Stack Analysis Tool Chain Editor C/C++ General MCU Project Natures Project References Renesas QE Run/Debug Settings Task Tags Validation	Toolchain Device Pailed Steps Build Artifact Binary Parsers Err Image: Enable toolchain integration Image: Enable toolchain <	ror Parsers

If the steps did not solve your problem, please refer to e²studio build console log. It will provide further information regarding the cause of the problem.

For general troubleshooting information about Getting Started with FreeRTOS, see <u>Troubleshooting</u> <u>getting started</u>.